



PROPRIETARY DATA
This document may not be reproduced,
disclosed, or otherwise used, in whole or
in part, without the written permission of
SIRENZA MICRODEVICES


REVISION HISTORY					
ZN	REV	DESCRIPTION	ECD	APPR	DATE
	A	INITIAL RELEASE	4125	Barcome	8/20/04
	B	Corrected Dim Tol Notation	5081	Barcome	5/13/05



TOP VIEW



BOTTOM VIEW



SIDE VIEW

- Notes:
1. LF Base Metal - Qlin 194
 2. Exterior Plating
Basic PN - Sn/Pb 85/15
Z Option - 100% Matte Sn
94V0
 3. Flammability Rating
 4. Marking
Laser or White Phenolic
Ink.

THIRD ANGLE PROJECTION

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN mm
PER ANSI Y14.5M-1982
TOLERANCES ARE:
DECIMAL
.XX ±.25
ANGLE
±1/2
MATERIAL(S)
XXX±0.13

DO NOT SCALE DRAWING

SIGNATURE

DATE

DWG PATH/FILENAME:
B

DWG TITLE:
Outline, 2X2 mm 8 ld .5 mm pitch QFN

SIZE
B

DWG NO.
MPD-103772

REV
B

SHEET 1 OF 1