















Symbol	Hit Count	Tool Size	Plated	Hole Type
o	364	12mil (0.305mm)	PTH	Round
v	4	25mil (0.635mm)	PTH	Round
d	48	36mil (0.914mm)	PTH	Round
x	5	47.244mil (1.2mm)	PTH	Round
s	10	55.118mil (1.4mm)	PTH	Round
o	12	63mil (1.6mm)	PTH	Round
x	5	125mil (3.175mm)	PTH	Round
148 Total				

