















Symbol	Hit Count	Finished Hole Size	Plated	Hole Type	Physical Length	Rout Path Length
E	4	25.00mil (0.635mm)	PTH	Round	-	-
⊕	4	28.00mil (0.711mm)	PTH	Round	-	-
⊗	5	47.24mil (1.200mm)	PTH	Round	-	-
C	5	125.00mil (3.175mm)	PTH	Round	-	-
□	9	35.43mil (0.900mm)	PTH	Round	-	-
✕	10	55.12mil (1.400mm)	PTH	Round	-	-
☆	17	63.00mil (1.600mm)	PTH	Round	-	-
A	20	25.59mil (0.650mm)	PTH	Round	-	-
B	56	36.00mil (0.914mm)	PTH	Round	-	-
D	319	12.00mil (0.305mm)	PTH	Round	-	-
	449 Total					

