















Symbol	Hit Count	Finished Hole Size	Plated	Hole Type	Physical Length	Rout Path Length
E	4	25.00mil (0.635mm)	PTH	Round	—	—
⊕	4	28.00mil (0.711mm)	PTH	Round	—	—
□	4	35.43mil (0.900mm)	PTH	Round	—	—
⊗	5	47.24mil (1.200mm)	PTH	Round	—	—
C	5	125.00mil (3.175mm)	PTH	Round	—	—
✕	10	55.12mil (1.400mm)	PTH	Round	—	—
☆	17	63.00mil (1.600mm)	PTH	Round	—	—
A	20	25.59mil (0.650mm)	PTH	Round	—	—
B	56	36.00mil (0.914mm)	PTH	Round	—	—
D	383	12.00mil (0.305mm)	PTH	Round	—	—
	508 Total					

