




BOTTOM LAYER


-4000.00


TOP OVERLAY











Symbol	Hit Count	Finished Hole Size	Plated	Hole Type	Physical Length	Rout Path Length
M	1148	12.00mil (0.305mm)	PTH	Round	-	-
O	13	16.00mil (0.406mm)	PTH	Round	-	-
I	17	25.00mil (0.635mm)	PTH	Round	-	-
E	2	27.56mil (0.700mm)	PTH	Round	-	-
☆	19	35.43mil (0.900mm)	PTH	Round	-	-
F	30	36.00mil (0.914mm)	PTH	Round	-	-
K	4	39.37mil (1.000mm)	PTH	Round	-	-
H	5	47.24mil (1.200mm)	PTH	Round	-	-
B	4	63.00mil (1.600mm)	PTH	Round	-	-
▽	20	72.84mil (1.850mm)	PTH	Round	-	-
J	2	86.61mil (2.200mm)	PTH	Round	-	-
L	4	125.00mil (3.175mm)	PTH	Round	-	-
	1268 Total					

