



ART FILM - assy_top




ART FILM - assy_top

ART FILM - assy_bottom




ART FILM - assy_bottom

ART FILM - copper_top




ART FILM - copper_top

ART FILM - copper_layer2




ART FILM - copper_layer2

ART FILM - copper_layer3



ART FILM - copper_layer3

ART FILM - copper_bottom



ART FILM - copper_bottom

ART FILM - silkscreen_top


QPG6200M 20dBm

SAP#308511

RF1


LC5
LC4
LC3

FOR EVALUATION ONLY
NOT FCC APPROVED FOR
RESALE




ART FILM - silkscreen_top

ART FILM - silkscreen_bottom




ART FILM - silkscreen_bottom

ART FILM - soldermask_top




ART FILM - soldermask_top

ART FILM - soldermask_bottom




ART FILM - soldermask_bottom

ART FILM - solderpaste_top




ART FILM - solderpaste_top

ART FILM - solderpaste_bottom




ART FILM - solderpaste_bottom

ART FILM - dimensions_drill



DRILL CHART: TOP & BOTTOM				
FIGURE	SIZE MM	SIZE MILS	PLATED	QTY
*	0.25	10.00	PLATED	334
•	0.51	20.00	PLATED	14
⊖	0.99	39.00	PLATED	4
⊗	0.65	25.59	NON-PLATED	2
⊕	1.42	56.00	NON-PLATED	4
⊙	2.50	98.43	NON-PLATED	1
⊖	1.40x0.60	55.12x23.62	PLATED	2
⊖	1.70x0.60	66.93x23.62	PLATED	2



ART FILM - dimensions_drill