

Item Num	Lvl	Rev	WJ Part Number	Description	MFR Part Number	CAGE Code	Qty	Per	Ref Desg	Mfr Name
1	1	--6	452526-001	ASSY. APP-BRD. LOW COST GAIN BLOCK, SOT363			1.0000			
2	1	--2	AG302-63G	AMP. INGAP LOW COST GAIN BLOCKS. DC-3GHZ. SOT-363. GRE			1.0000		U1	
			** SUB ** AG302-63	AMP. INGAP LOW COST GAIN BLOCKS. DC-3GHZ. SOT363						
3	1	-	444731-031	RES. 22.1. 1PCT. 1/16W. CHIP. SMD. 0603	CRCW060322R1FRT2 ERJ3EKF22R1H LR-HPWAF221JT50 P22.1HTR-ND RK73H1JTE22R1F RM06F22R1CT	56845 0J4G8	1.0000		R4	DALE PANASONIC LAUBE DIGI-KEY CORPORATION KOA CAL-CHIP
4	1	-	453115-000	REF. AG302-63 APP BOARD. TEST REQUIREMENTS			.0000			

Report successfully completed

Item Num	Lvl	Rev	WJ Part Number	Description	MFR Part Number	CAGE Code	Qty Per	Ref Desg	Mfr Name
0	1	--3	452526-000	REF. APP-BRD. LOW COST GAIN BLOCK, SOT363			.0000		
0	1	--2	452526AW	REF. APP-BRD. LOW COST GAIN BLOCK, SOT363			.0000		
0	1	--2	452526SD	REF. APP-BRD. LOW COST GAIN BLOCK, SOT363			.0000		
1	1	--2	452526PC	PCB. APP-BRD. LOW COST GAIN BLOCK, SOT363. 10 BOARDS/P			.1000		
2	1	-	861000-105	IND. 39NH. 5PCT. WIRE-BOUND. SMD	0603CS-39NKJBC		1.0000	L1	COILCRAFT
3	1	-A	412720-022	CAP. 56PF. 5PCT. 50V. NPO/COG. SMD. 0603	06035A560JAT2A		2.0000	C1	AVX
					500R14N560JV4E			C2	JOHANSON DIELECTRICS
					ECUY1H560JCV				PANASONIC
					GMC10CG560J50NT				CAL-CHIP
					GRM39COG560J050AL				MURATA
					LC-CC410603CG560J5NT				LAUBE
4	1	-A	412720-052	CAP. 0.018UF. 5PCT. 50V. X7R. SMD. 0603	06035C183JAT1A	04222	1.0000	C3	AVX
					500R14W183JV4E	29454			JOHANSON DIELECTRICS
					ECUY1H183JBV				PANASONIC
					GMC10X7R183J50NT				CAL-CHIP
					GRM39X7R183J050AL				MURATA
7	1	-	862000-055	TERMINAL. SOLDER TURRET. .062 PCB	2533-0-00-44-00-00-07-0		2.0000	J3 J4	MILL-MAX
8	1	-	862000-349	CONN. RF. SMA. F. STRT. SMD. 1. END LAUNCH JACK RECEPT 142-0701-801			2.0000	J1 J2	JOHNSON COMPONENTS

Report successfully completed