


### Product Overview

The CMD309P4 is a broadband MMIC low noise amplifier housed in a leadless 4x4 mm plastic surface mount package. The CMD309P4 is ideally suited for microwave radios and C and X-band applications where high gain, low noise figure and low power consumption are needed. The broadband device delivers 27 dB of gain with a corresponding output 1 dB compression point of +13 dBm and a noise figure of 1.5 dB. The CMD309P4 is a 50 ohm matched design eliminating the need for external DC blocks and RF port matching.

### Functional Block Diagram



### Key Features

- Low Noise Figure
- High Gain Broadband Performance
- Low Current Consumption
- Single Positive Bias
- Pb-Free RoHs Compliant 4x4 QFN Package

### Ordering Information

Part No.	Description
CMD309P4	Tape and Reel, 7", Qty 500 Piece
CMD309P4-EVB	1 Piece Bag

### Electrical Performance ( $V_{dd} = 4.0 \text{ V}$ , $T_A = 25^\circ \text{C}$ , $F = 8 \text{ GHz}$ )

Parameter	Min	Typ	Max	Units
Frequency Range		5 - 11		GHz
Gain		27		dB
Noise Figure		1.5		dB
Input Return Loss		15		dB
Output Return Loss		10		dB
Output P1dB		13		dBm
Supply Current		45		mA

## Absolute Maximum Ratings

Parameter	Rating
Drain Voltage, $V_{dd}$	5.5 V
RF Input Power	+20 dBm
Channel Temperature, $T_{ch}$	150° C
Power Dissipation, $P_{diss}$	380 mW
Thermal Resistance, $Q_{JC}$	170° C/W
Operating Temperature	-40 to 85° C
Storage Temperature	-55 to 150° C

Exceeding any one or combination of the maximum ratings may cause permanent damage to the device.

## Recommended Operating Conditions

Parameter	Min	Typ	Max	Units
$V_{dd}$	3.0	4.0	5.0	V
$I_{dd}$		45		mA


Electrical performance is measured at specific test conditions.  
 Electrical specifications are not guaranteed over all recommended operating conditions.

## Electrical Specifications ( $V_{dd} = 4.0$ V, $T_A = 25^\circ$ C)


Parameter	Min	Typ	Max	Min	Typ	Max	Units
Frequency Range		6 - 9			5 - 11		GHz
Gain	24	27.5		23	27		dB
Noise Figure		1.4	2		1.4	2.3	dB
Input Return Loss		13			13		dB
Output Return Loss		10			10		dB
Output P1dB		13			13		dBm
Output IP3		23			23		dBm
Supply Current	30	45	60	30	45	60	mA
Gain Temperature Coefficient		0.017			0.017		dB/°C
Noise Figure Temperature Coefficient		0.009			0.009		dB/°C

## Typical Performance

Broadband Performance,  $V_{dd} = 4.0 \text{ V}$ ,  $T_A = 25^\circ \text{C}$




Narrow-band Performance,  $V_{dd} = 4.0 \text{ V}$ ,  $T_A = 25^\circ \text{C}$




## Typical Performance

Gain vs. Temperature,  $V_{dd} = 4.0\text{ V}$




Gain vs.  $V_{dd}$ ,  $T_A = 25^\circ\text{C}$




## Typical Performance

Noise Figure vs. Temperature,  $V_{dd} = 4.0 \text{ V}$




Noise Figure vs.  $V_{dd}$ ,  $T_A = 25^\circ \text{C}$




## Typical Performance

P1dB vs. Temperature,  $V_{dd} = 4.0\text{ V}$




P1dB vs.  $V_{dd}$ ,  $T_A = 25^\circ\text{C}$




## Typical Performance

Psat vs. Temperature,  $V_{dd} = 4.0\text{ V}$




Psat vs.  $V_{dd}$ ,  $T_A = 25^\circ\text{C}$




## Typical Performance

Output IP3 vs. Temperature,  $V_{dd} = 4.0\text{ V}$




Output IP3 vs.  $V_{dd}$ ,  $T_A = 25^\circ\text{C}$





## Mechanical Information

### Package Information and Dimensions



### Recommended PCB Land Pattern


Qorvo recommends that the user develop the land pattern that will provide the best design for proper solder reflow and device attach for their specific application. Please review Qorvo Application Note AN 105 for a recommended land pattern approach.

### Recommended Solder Reflow Profile

Qorvo recommends screen printing with belt furnace reflow to ensure proper solder reflow and device attach. Please review Qorvo Application Note AN 102 for a recommended solder reflow profile.

Pin Description

Pin Diagram




Functional Description

Pad	Function	Description	Schematic
1, 5 - 14, 18, 19, 21 - 24	N/C	No connection required These pins may be connected to RF / DC ground	
2, 4, 15, 17 and die paddle	Ground	Connect to RF / DC ground	
3	RF in	DC blocked and 50 ohm matched	
16	RF out	DC blocked and 50 ohm matched	
20	V <sub>dd</sub>	Power supply voltage Decoupling and bypass caps required	

## Applications Information

### Application Circuit



### Biasing and Operation

The CMD309P4 is biased with a single positive drain supply.

Turn ON procedure:

1. Apply drain voltage  $V_{dd}$  and set to +4 V

Turn OFF procedure:


1. Turn off drain voltage  $V_{dd}$

RF power can be applied at any time.

**GaAs MMIC devices are susceptible to damage from Electrostatic Discharge. Proper precautions should be observed during handling, assembly and test.**

Applications Information

Evaluation Board



Bill of Material

Designator	Value	Description
J1, J2		SMA End Launch Connector
P1		10 Pin DC Header
C1	0.33 $\mu$ F	Capacitor, Tantalum
C2	1000 pF	Capacitor, 0603
C3	100 pF	Capacitor, 0402
U1		CMD309P4 Low Noise Amplifier
PCB		100727 Evaluation PCB

## Handling Precautions

Parameter	Rating	Standard
ESD – Human Body Model (HBM)	Class TBD	ESDA / JEDEC JS-001-2012
MSL – Moisture Sensitivity Level	Level 1	JEDEC standard IPC/JEDEC J-STD-020



Caution!  
ESD-Sensitive Device

## RoHS Compliance

This part is compliant with 2011/65/EU RoHS directive (Restrictions on the Use of Certain Hazardous Substances in Electrical and Electronic Equipment) as amended by Directive 2015/863/EU.

This product also has the following attributes:

- Lead Free
- Antimony Free
- TBBP-A (C<sub>15</sub>H<sub>12</sub>Br<sub>4</sub>O<sub>2</sub>) Free
- SVHC Free
- Halogen Free
- PFOS Free

## Contact Information

For the latest specifications, additional product information, worldwide sales and distribution locations:

Web: [www.qorvo.com](http://www.qorvo.com)

Tel: 1-844-890-8163

Email: [customer.support@qorvo.com](mailto:customer.support@qorvo.com)

## Important Notice

The information contained in this Data Sheet and any associated documents (“Data Sheet Information”) is believed to be reliable; however, Qorvo makes no warranties regarding the Data Sheet Information and assumes no responsibility or liability whatsoever for the use of said information. All Data Sheet Information is subject to change without notice. Customers should obtain and verify the latest relevant Data Sheet Information before placing orders for Qorvo® products. Data Sheet Information or the use thereof does not grant, explicitly, implicitly or otherwise any rights or licenses to any third party with respect to patents or any other intellectual property whether with regard to such Data Sheet Information itself or anything described by such information.

DATA SHEET INFORMATION DOES NOT CONSTITUTE A WARRANTY WITH RESPECT TO THE PRODUCTS DESCRIBED HEREIN, AND QORVO HEREBY DISCLAIMS ANY AND ALL WARRANTIES WITH RESPECT TO SUCH PRODUCTS WHETHER EXPRESS OR IMPLIED BY LAW, COURSE OF DEALING, COURSE OF PERFORMANCE, USAGE OF TRADE OR OTHERWISE, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. Without limiting the generality of the foregoing, Qorvo® products are not warranted or authorized for use as critical components in medical, life-saving, or life-sustaining applications, or other applications where a failure would reasonably be expected to cause severe personal injury or death. Applications described in the Data Sheet Information are for illustrative purposes only. Customers are responsible for validating that a particular product described in the Data Sheet Information is suitable for use in a particular application.

© 2023 Qorvo US, Inc. All rights reserved. This document is subject to copyright laws in various jurisdictions worldwide and may not be reproduced or distributed, in whole or in part, without the express written consent of Qorvo US, Inc. | QORVO® is a registered trademark of Qorvo US, Inc.