



# United Silicon Carbide, Inc.

## Product Qualification Report

Discrete TO-247 1200V Generation 4 Stacked Cascode Devices

Included Products:

TO247-4L

UF4SC120023K4S

UF4SC120030K4S



This report summarizes the JEDEC qualification results for the 1200V Discrete SiC Cascodes in TO-247 plastic packages.

The environmental stress tests listed below are performed with pre-stress and post-stress electrical tests. Reviewing the electrical results for new failures and any significant shift in performance satisfies the qualification requirements.

### Reliability Stress Test Summary

Test Name	Test Standard	# Samples x # Lots	Failures
High Temperature Reverse Bias (HTRB)	MIL-STD-750-1 M1038 Method A (1000 Hours) $T_J=175^{\circ}\text{C}$ , $V=80\% V_{\text{max}}$	77x3 lots	0/231
High Temperature Gate Bias (HTGB)	JESD22 A-108 (1000 Hours) $T_J=175^{\circ}\text{C}$ , $V=100\% V_{\text{max}}$ (+20V), bias in one direction	77x3 lots	0/231
High Humidity, High Temperature Reverse Bias (H3TRB)	JESD22-A101C (1000 Hours) $T_A=85^{\circ}\text{C}$ , 85% RH, $V_{\text{GS}}=0\text{V}$ , $V_{\text{DS}}=100\text{V}$	77x3 lots	0/231
Temperature Cycle (TC)	JESD22 A-104 -55°C to +150°C 2cycles/Hr (1000 Cycles)	77x2 lots	0/154
Autoclave (PCT)	JESD22 A-102 121°C/ RH = 100%, 96 hours, 15psig	77x3 lots	0/231
Intermittent Operating Life (IOL)	MIL-STD-750 Method 1037 DTJ $\geq 125^{\circ}\text{C}$ , 3000 cycles (5 minutes on/ 5 minutes off)	77x3 lots	0/231
Parametric Verification	Per Datasheet	100% FT x 3 lots	
Physical Dimensions	Per AEC-Q101 Rev D	30x1 packages	0/30
Bondline Thickness	Per Assembly Spec	10x3 lots	0/30

Die Shear	Per Assembly Spec	10x3 lots	0/30
Die Attach Voids	Per Assembly Spec	10x3 lots	0/30
Wire Pull	Per Assembly Spec	10x3 lots	0/30
Wedge Shear	Per Assembly Spec	10x3 lots	0/30
CSAM	Per Assembly Spec	60x3 lots	0/180
Lead Integrity Test	Per AEC-Q101 Rev E	30x1 lots	0/30
Solderability Test	Per AEC-Q101 Rev E	10x1 lots	0/10

### Reliability Evaluation:

The FIT rate data presented below is determined according to JEDEC Standard JESD 85 and is determined from the HTRB and HTGB Burn-In sample size.

**FIT = 2.608 failures per billion device hours**

**MTTF = 43771.03 years**

From the equations:

$$\lambda_{hours} = \frac{X^2(\alpha, \nu)}{2 \times D \times H \times A_f}$$

$$FIT = \lambda_{hours} \times 10^9$$

$$MTTF_{hours} = 1/\lambda_{hours}$$

And

$$A_f = e^{\frac{E_a}{k} \left( \frac{1}{T_{use}} - \frac{1}{T_{test}} \right)}$$

Where:

$X^2$  = Chi-Squared probability function for a given Confidence Level ( $\alpha$ ) and Degree of Freedom ( $\nu = 2r+2$ , where  $r$  = the number of failures in the Test Population),

$D$  = Number of Devices in the Test Population,

$H$  = Test Hours per Device,



$A_f$  = Acceleration Factor from the Arrhenius equation,

$E_a$  = Activation Energy (eV),

$T_{use}$  = standardized Use Temperature,

$T_{test}$  = Temperature of Stress Test,

and

$k$  = Boltzmann's Constant.

In our calculations, we used our HTGB and HTRB Burn-In data:

$D = 231$  for HTRB, and  $231$  for HTGB

$H = 1000$  hours of HTRB, and  $1000$  hours of HTGB

$1 - \alpha = 0.6$  (60% Confidence Level)

$r = 0$  Failures

$E_a = 0.7$  eV

$T_{use} = 55$  °C or  $328$  K

$T_{test} = 175$  °C or  $448$  K