



| REVISIONS |                                  |          |
|-----------|----------------------------------|----------|
| LTR       | DESCRIPTION                      | DATE     |
| -         | ORIGINAL ISSUE PER EWR NO. V5776 | 12/04/01 |
| A         | CHANGE PER ECO NO. 3612          | 3/23/04  |



|                              |           | PLL350 PACKAGE |                | SIZE  |         |
|------------------------------|-----------|----------------|----------------|-------|---------|
|                              |           | ITEMS          | SYMBOL         | MM    | INCHES  |
| POCKET                       | LENGTH    |                | A <sub>O</sub> | 15.39 | (0.606) |
|                              | WIDTH     |                | B <sub>O</sub> | 20.90 | (0.823) |
|                              | DEPTH     |                | K <sub>O</sub> | 4.50  | (0.177) |
|                              | PITCH     |                | P              | 24.00 | (0.945) |
| PERFORATION                  | DIAMETER  |                | D              | 1.50  | (0.059) |
|                              | PITCH     |                | P <sub>O</sub> | 4.00  | (0.157) |
|                              | POSITION  |                | E              | 1.75  | (0.069) |
| DISTANCE BETWEEN CENTERLINES | WIDTH 1   |                | F              | 14.20 | (0.559) |
|                              | WIDTH 2   |                | S              | 28.40 | (1.118) |
| CARRIER TAPE                 | WIDTH     |                | C <sub>W</sub> | 32.0  | (1.260) |
|                              | THICKNESS |                | c              | 0.350 | (0.014) |

NOTES:

1. A<sub>O</sub> AND B<sub>O</sub> ARE MEASURED AT 0.03mm ABOVE THE BASE OF THE POCKET.
2. 10 PITCHES CUMULATIVE TOLERANCE ± 0.2mm.
3. ALL CAVITY WALLS HAVE A 7° DRAFT UNLESS OTHERWISE SPECIFIED.
4. DO NOT SCALE PRINT
5. ALL DIMENSIONS ARE IN MILLIMETERS (INCHES) UNLESS OTHERWISE SPECIFIED.
6. MUST CONFORM TO E.I.A. STANDARD 481 LATEST REVISION.

|   |           |            |             |   |                   |                  |           |
|---|-----------|------------|-------------|---|-------------------|------------------|-----------|
| TOLERANCES UNLESS OTHERWISE SPECIFIED<br>.X = ± 0.3mm<br>.XX = ± 0.13mm<br>.XXX = ± 0.03mm<br>ANGLE = ± 0.5°<br>MATERIAL: CONDUCTIVE POLYSTYRENE<br>PER DWG. 60615<br>LATEST REVISION<br>FINISH   | APPROVALS |            | DATE        | <br>SIRENZA MICRODEVICES, INC.<br>BROOMFIELD, COLORADO |                   |                  |           |
|   | DRAWN BY  | A.R.AUSTAD | 12/04/01    |   |                   |                  |           |
|   | CHKD BY   |            |             |   |                   |                  |           |
|   | PROC ENG  |            |             |   |                   |                  |           |
|   | DESN ENG  |            |             |   |                   |                  |           |
|   | QUALITY   |            |             | TITLE<br><br>PLL350 PACKAGE<br>TAPE SCD   |                   |                  |           |
|   | APPROVAL  |            |             |   |                   |                  |           |
| PROPRIETARY STATEMENT<br>THIS DOCUMENT DISCLOSES INFORMATION AND DATA IN WHICH SIRENZA MICRODEVICES, INC. HAS PROPRIETARY RIGHTS. NEITHER RECEIPT NOR POSSESSION THEREOF CONFERS OR TRANSFERS ANY RIGHT TO REPRODUCE, USE, OR DISCLOSE IN WHOLE OR IN PART EXCEPT BY WRITTEN PERMISSION FROM SIRENZA MICRODEVICES, INC. |           |            | SIZE<br>A   |   | FSCM NO.<br>05375 | DWG NO.<br>61129 | REV.<br>A |
|   |           |            | SCALE: NONE | DO NOT SCALE DWG  |                   | SHEET 1 OF 1     |           |