

PAC5210

Power Application Controller™

Multi-Mode Power Manager™

Configurable Analog Front End™

Application Specific Power Drivers™

ARM® Cortex™-M0 Controller Core



TABLE OF CONTENTS

| | |
|---|----|
| 1. Styles and Formatting Conventions..... | 31 |
| 1.1. Overview..... | 31 |
| 1.2. Number Representation..... | 31 |
| 1.3. Formatting Styles..... | 31 |
| 2. Memory and Register Map..... | 32 |
| 2.1. Memory Map..... | 32 |
| 2.2. Register Map..... | 33 |
| 3. System Clock Control..... | 45 |
| 3.1. Register..... | 45 |
| 3.1.1. Register Map..... | 45 |
| 3.1.2. SCCTL..... | 45 |
| 3.1.3. PLLCTL..... | 46 |
| 3.1.4. ROSCCTL..... | 46 |
| 3.1.5. XTALCTL..... | 46 |
| 3.2. Details of Operation..... | 47 |
| 3.2.1. Block Diagram..... | 47 |
| 3.2.2. Configuration..... | 47 |
| 3.2.3. ROSC..... | 48 |
| 3.2.4. CLKREF..... | 48 |
| 3.2.5. XTAL..... | 48 |
| 3.2.6. EXTCLK..... | 48 |
| 3.2.7. PLL..... | 48 |
| 3.2.8. FRCLK..... | 49 |
| 3.2.9. FCLK..... | 49 |
| 3.2.10. HCLK..... | 49 |
| 3.2.11. ACLK..... | 49 |
| 3.2.12. Clock Gating..... | 49 |
| 4. Watchdog Timer..... | 50 |
| 4.1. Register..... | 50 |
| 4.1.1. Register Map..... | 50 |
| 4.1.2. WDTCTL..... | 50 |
| 4.1.3. WDTCDV..... | 51 |
| 4.1.4. WDTCTR..... | 51 |
| 4.2. Details of Operation..... | 52 |
| 4.2.1. Block Diagram..... | 52 |
| 4.2.2. Configuration..... | 52 |
| 4.2.3. Watchdog Timer..... | 52 |
| 4.2.4. Access WDT Registers..... | 52 |
| 4.2.5. WDT Clock Setting..... | 52 |
| 4.2.6. General Purpose Timer Mode..... | 52 |
| 4.2.7. Watchdog Timer Mode..... | 53 |
| 5. General Purpose Timer..... | 54 |
| 5.1. Register..... | 54 |
| 5.1.1. Register Map..... | 54 |
| 5.1.2. GPTCTL..... | 54 |
| 5.1.3. GPTCDV..... | 55 |
| 5.1.4. GPTCTR..... | 55 |
| 5.2. Details of Operation..... | 56 |
| 5.2.1. Block Diagram..... | 56 |
| 5.2.2. Configuration..... | 56 |
| 5.2.3. General Purpose Timer..... | 56 |

| | |
|--|----|
| 5.2.4. Access GPT Registers..... | 56 |
| 5.2.5. GPT Clock Setting..... | 56 |
| 5.2.6. General Purpose Timer Mode..... | 56 |
| 6. GPIO Port A..... | 57 |
| 6.1. Register..... | 57 |
| 6.1.1. Register Map..... | 57 |
| 6.1.2. GPIOAO..... | 57 |
| 6.1.3. GPIOAOE..... | 58 |
| 6.1.4. GPIOADS..... | 58 |
| 6.1.5. GPIOARUP..... | 59 |
| 6.1.6. GPIOARDN..... | 60 |
| 6.1.7. GPIOAI..... | 60 |
| 6.1.8. GPIOAPSEL..... | 61 |
| 6.1.9. GPIOAINTP..... | 62 |
| 6.1.10. GPIOAINTEN..... | 62 |
| 6.1.11. GPIOAINT..... | 63 |
| 6.1.12. GPIOAINTM..... | 64 |
| 6.2. Details of Operation..... | 65 |
| 6.2.1. Block Diagram..... | 65 |
| 6.2.2. Configuration..... | 65 |
| 6.2.3. GPIO A Block..... | 65 |
| 6.2.4. Input..... | 65 |
| 6.2.5. Output and Output Enable..... | 65 |
| 6.2.6. Output Drive Strength..... | 66 |
| 6.2.7. Weak Pull Up and Pull Down..... | 66 |
| 6.2.8. Peripheral Select..... | 66 |
| 6.2.9. Interrupt..... | 66 |
| 7. GPIO Port B..... | 67 |
| 7.1. Register..... | 67 |
| 7.1.1. Register Map..... | 67 |
| 7.1.2. GPIOBO..... | 67 |
| 7.1.3. GPIOBOE..... | 67 |
| 7.1.4. GPIOBDS..... | 68 |
| 7.1.5. GPIOBRUP..... | 68 |
| 7.1.6. GPIOBRDN..... | 69 |
| 7.1.7. GPIOBI..... | 69 |
| 7.1.8. GPIOBSEL..... | 69 |
| 7.1.9. GPIOBINTP..... | 70 |
| 7.1.10. GPIOBINTEN..... | 71 |
| 7.1.11. GPIOBINT..... | 71 |
| 7.1.12. GPIOBINTM..... | 72 |
| 7.2. Details of Operation..... | 73 |
| 7.2.1. Block Diagram..... | 73 |
| 7.2.2. Configuration..... | 73 |
| 7.2.3. GPIO B Block..... | 73 |
| 7.2.4. Input..... | 73 |
| 7.2.5. Output and Output Enable..... | 73 |
| 7.2.6. Output Drive Strength..... | 73 |
| 7.2.7. Weak Pull Up and Pull Down..... | 74 |
| 7.2.8. Peripheral Select..... | 74 |
| 7.2.9. Interrupt..... | 74 |
| 8. GPIO Port C..... | 75 |
| 8.1. Register..... | 75 |
| 8.1.1. Register Map..... | 75 |

| | |
|--|-----|
| 8.1.2. GPIOCO..... | 75 |
| 8.1.3. GPIOCOE..... | 76 |
| 8.1.4. GPIOCI..... | 76 |
| 8.1.5. GPIOCIE..... | 77 |
| 8.1.6. GPIOCINTP..... | 78 |
| 8.1.7. GPIOCINTEN..... | 78 |
| 8.1.8. GPIOCINT..... | 79 |
| 8.1.9. GPIOCINTM..... | 79 |
| 8.2. Details of Operation..... | 81 |
| 8.2.1. Block Diagram..... | 81 |
| 8.2.2. Configuration..... | 81 |
| 8.2.3. GPIO C Block..... | 81 |
| 8.2.4. Analog Input..... | 81 |
| 8.2.5. Output and Output Enable..... | 81 |
| 8.2.6. Interrupt..... | 81 |
| 9. GPIO Port D..... | 83 |
| 9.1. Register..... | 83 |
| 9.1.1. Register Map..... | 83 |
| 9.1.2. GPIODO..... | 83 |
| 9.1.3. GPIODOE..... | 84 |
| 9.1.4. GPIODDS..... | 84 |
| 9.1.5. GPIODRUP..... | 85 |
| 9.1.6. GPIODRDN..... | 86 |
| 9.1.7. GPIODI..... | 86 |
| 9.1.8. GPIODPSEL..... | 87 |
| 9.1.9. GPIODINTP..... | 88 |
| 9.1.10. GPIODINTEN..... | 88 |
| 9.1.11. GPIODINT..... | 89 |
| 9.1.12. GPIODINTM..... | 89 |
| 9.2. Details of Operation..... | 91 |
| 9.2.1. Block Diagram..... | 91 |
| 9.2.2. Configuration..... | 91 |
| 9.2.3. GPIO D Block..... | 91 |
| 9.2.4. Input..... | 91 |
| 9.2.5. Output and Output Enable..... | 91 |
| 9.2.6. Output Drive Strength..... | 92 |
| 9.2.7. Weak Pull Up and Pull Down..... | 92 |
| 9.2.8. Peripheral Select..... | 92 |
| 9.2.9. Interrupt..... | 92 |
| 10. GPIO Port E..... | 93 |
| 10.1. Register..... | 93 |
| 10.1.1. Register Map..... | 93 |
| 10.1.2. GPIOEO..... | 93 |
| 10.1.3. GPIOEOE..... | 94 |
| 10.1.4. GPIOEDS..... | 94 |
| 10.1.5. GPIOERUP..... | 95 |
| 10.1.6. GPIOERDN..... | 96 |
| 10.1.7. GPIOEI..... | 96 |
| 10.1.8. GPIOEPSEL..... | 97 |
| 10.1.9. GPIOEINTP..... | 98 |
| 10.1.10. GPIOEINTEN..... | 98 |
| 10.1.11. GPIOEINT..... | 99 |
| 10.1.12. GPIOEINTM..... | 99 |
| 10.2. Details of Operation..... | 101 |

| | |
|---|-----|
| 10.2.1. Block Diagram..... | 101 |
| 10.2.2. Configuration..... | 101 |
| 10.2.3. GPIO E Block..... | 101 |
| 10.2.4. Input..... | 101 |
| 10.2.5. Output and Output Enable..... | 101 |
| 10.2.6. Output Drive Strength..... | 101 |
| 10.2.7. Weak Pull Up and Pull Down..... | 102 |
| 10.2.8. Peripheral Select..... | 102 |
| 10.2.9. Interrupt..... | 102 |
| 11. Timer A..... | 103 |
| 11.1. Register..... | 103 |
| 11.1.1. Register Map..... | 103 |
| 11.1.2. TACTL..... | 104 |
| 11.1.3. TAPRD..... | 105 |
| 11.1.4. TACTR..... | 105 |
| 11.1.5. TACC0CTL..... | 105 |
| 11.1.6. TACC0CTR..... | 105 |
| 11.1.7. TACC1CTL..... | 106 |
| 11.1.8. TACC1CTR..... | 106 |
| 11.1.9. TACC2CTL..... | 106 |
| 11.1.10. TACC2CTR..... | 107 |
| 11.1.11. TACC3CTL..... | 107 |
| 11.1.12. TACC3CTR..... | 107 |
| 11.1.13. TACC4CTL..... | 107 |
| 11.1.14. TACC4CTR..... | 108 |
| 11.1.15. TACC5CTL..... | 108 |
| 11.1.16. TACC5CTR..... | 108 |
| 11.1.17. TACC6CTL..... | 109 |
| 11.1.18. TACC6CTR..... | 109 |
| 11.1.19. TACC7CTL..... | 109 |
| 11.1.20. TACC7CTR..... | 110 |
| 11.1.21. DTGA0CTL..... | 110 |
| 11.1.22. DTGA0LED..... | 110 |
| 11.1.23. DTGA0TED..... | 110 |
| 11.1.24. DTGA1CTL..... | 111 |
| 11.1.25. DTGA1LED..... | 111 |
| 11.1.26. DTGA1TED..... | 111 |
| 11.1.27. DTGA2CTL..... | 111 |
| 11.1.28. DTGA2LED..... | 112 |
| 11.1.29. DTGA2TED..... | 112 |
| 11.1.30. DTGA3CTL..... | 112 |
| 11.1.31. DTGA3LED..... | 113 |
| 11.1.32. DTGA3TED..... | 113 |
| 11.2. Details of Operation..... | 114 |
| 11.2.1. Block Diagram..... | 114 |
| 11.2.2. Configuration..... | 114 |
| 11.2.3. Timer A Block..... | 114 |
| 11.2.4. Timer..... | 114 |
| 11.2.5. Register update..... | 115 |
| 11.2.6. Timer Modes..... | 115 |
| 11.2.7. Single Shot Mode..... | 115 |
| 11.2.8. Input Clock And Pre-Scaler..... | 115 |
| 11.2.9. Timer Synchronization..... | 115 |
| 11.2.10. PWM/Compare Units..... | 116 |

| | |
|---|-----|
| 11.2.10.1. PWM Mode..... | 116 |
| 11.2.10.2. Capture Mode..... | 117 |
| 11.2.11. Timer and PWM/Capture Interrupt..... | 117 |
| 11.2.12. Dead-Time Generator..... | 118 |
| 11.2.12.1. Dead Time Input Clock Selection..... | 118 |
| 11.2.12.2. Dead Time Range..... | 118 |
| 11.2.12.3. Bypass Mode..... | 118 |
| 11.2.12.4. Inverting PWM Signal..... | 118 |
| 11.2.12.5. Dead Time Insertion..... | 119 |
| 11.2.12.6. Dead Time Insertion with On Time Preservation..... | 119 |
| 11.2.13. PWM Output and Capture Input Pin Selection..... | 120 |
| 12. Timer B..... | 121 |
| 12.1. Register..... | 121 |
| 12.1.1. Register Map..... | 121 |
| 12.1.2. TBCTL..... | 121 |
| 12.1.3. TBPRD..... | 122 |
| 12.1.4. TBCTR..... | 122 |
| 12.1.5. TBCC0CTL..... | 122 |
| 12.1.6. TBCC0CTR..... | 123 |
| 12.1.7. TBCC1CTL..... | 123 |
| 12.1.8. TBCC1CTR..... | 123 |
| 12.1.9. TBCC2CTL..... | 124 |
| 12.1.10. TBCC2CTR..... | 124 |
| 12.1.11. TBCC3CTL..... | 124 |
| 12.1.12. TBCC3CTR..... | 125 |
| 12.1.13. DTGB0CTL..... | 125 |
| 12.1.14. DTGB0LED..... | 125 |
| 12.1.15. DTGB0TED..... | 126 |
| 12.2. Details of Operation..... | 127 |
| 12.2.1. Block Diagram..... | 127 |
| 12.2.2. Configuration..... | 127 |
| 12.2.3. Timer B Block..... | 127 |
| 12.2.4. Timer..... | 127 |
| 12.2.5. Register update..... | 128 |
| 12.2.6. Timer Modes..... | 128 |
| 12.2.7. Single Shot Mode..... | 128 |
| 12.2.8. Input Clock And Pre-Scaler..... | 128 |
| 12.2.9. Timer Synchronization..... | 128 |
| 12.2.10. PWM/Compare Units..... | 129 |
| 12.2.10.1. PWM Mode..... | 129 |
| 12.2.10.2. Capture Mode..... | 130 |
| 12.2.11. Timer and PWM/Capture Interrupt..... | 130 |
| 12.2.12. Dead-Time Generator..... | 131 |
| 12.2.12.1. Dead Time Input Clock Selection..... | 131 |
| 12.2.12.2. Dead Time Range..... | 131 |
| 12.2.12.3. Bypass Mode..... | 131 |
| 12.2.12.4. Inverting PWM Signal..... | 131 |
| 12.2.12.5. Dead Time Insertion..... | 132 |
| 12.2.12.6. Dead Time Insertion with On Time Preservation..... | 132 |
| 12.2.13. PWM Output and Capture Input Pin Selection..... | 133 |
| 13. Timer C..... | 134 |
| 13.1. Register..... | 134 |
| 13.1.1. Register Map..... | 134 |
| 13.1.2. TCCTL..... | 134 |

| | |
|---|-----|
| 13.1.3. TCPRD..... | 135 |
| 13.1.4. TCCTR..... | 135 |
| 13.1.5. TCCC0CTL..... | 135 |
| 13.1.6. TCCC0CTR..... | 136 |
| 13.1.7. TCCC1CTL..... | 136 |
| 13.1.8. TCCC1CTR..... | 136 |
| 13.1.9. DTGC0CTL..... | 137 |
| 13.1.10. DTGC0LED..... | 137 |
| 13.1.11. DTGC0TED..... | 137 |
| 13.2. Details of Operation..... | 138 |
| 13.2.1. Block Diagram..... | 138 |
| 13.2.2. Configuration..... | 138 |
| 13.2.3. Timer C Block..... | 138 |
| 13.2.4. Timer..... | 138 |
| 13.2.5. Register update..... | 139 |
| 13.2.6. Timer Modes..... | 139 |
| 13.2.7. Single Shot Mode..... | 139 |
| 13.2.8. Input clock and Pre-scaler..... | 139 |
| 13.2.9. Timer synchronization..... | 139 |
| 13.2.10. PWM/Compare Units..... | 140 |
| 13.2.10.1. PWM Mode..... | 140 |
| 13.2.10.2. Capture Mode..... | 141 |
| 13.2.11. Timer and PWM/Capture Interrupt..... | 141 |
| 13.2.12. Dead-Time Generator..... | 142 |
| 13.2.12.1. Dead Time Input Clock Selection..... | 142 |
| 13.2.12.2. Dead Time Range..... | 142 |
| 13.2.12.3. Bypass Mode..... | 142 |
| 13.2.12.4. Inverting PWM Signal..... | 142 |
| 13.2.12.5. Dead Time Insertion..... | 143 |
| 13.2.12.6. Dead Time Insertion With On Time Preservation..... | 143 |
| 13.2.13. PWM Output and Capture Input Pin Selection..... | 144 |
| 14. Timer D..... | 145 |
| 14.1. Register..... | 145 |
| 14.1.1. Register Map..... | 145 |
| 14.1.2. TDCTL..... | 145 |
| 14.1.3. TDPRD..... | 146 |
| 14.1.4. TDCTR..... | 146 |
| 14.1.5. TDCC0CTL..... | 146 |
| 14.1.6. TDCC0CTR..... | 147 |
| 14.1.7. TDCC1CTL..... | 147 |
| 14.1.8. TDCC1CTR..... | 147 |
| 14.1.9. DTGD0CTL..... | 148 |
| 14.1.10. DTGD0LED..... | 148 |
| 14.1.11. DTGD0TED..... | 148 |
| 14.2. Details of Operation..... | 149 |
| 14.2.1. Block Diagram..... | 149 |
| 14.2.2. Configuration..... | 149 |
| 14.2.3. Timer D Block..... | 149 |
| 14.2.4. Timer..... | 149 |
| 14.2.5. Register Update..... | 150 |
| 14.2.6. Timer Modes..... | 150 |
| 14.2.7. Single Shot Mode..... | 150 |
| 14.2.8. Input Clock And Pre-Scaler..... | 150 |
| 14.2.9. Timer Synchronization..... | 150 |

| | |
|---|-----|
| 14.2.10. PWM/Compare Units..... | 151 |
| 14.2.10.1. PWM Mode..... | 151 |
| 14.2.10.2. Capture Mode..... | 152 |
| 14.2.11. Timer and PWM/Capture Interrupt..... | 152 |
| 14.2.12. Dead-Time Generator..... | 152 |
| 14.2.12.1. Dead Time Input Clock Selection..... | 152 |
| 14.2.12.2. Dead Time Range..... | 152 |
| 14.2.12.3. Bypass Mode..... | 153 |
| 14.2.12.4. Inverting PWM Signal..... | 153 |
| 14.2.12.5. Dead Time Insertion..... | 153 |
| 14.2.12.6. Dead Time Insertion with On Time Preservation..... | 154 |
| 14.2.13. PWM Output and Capture Input Pin Selection..... | 154 |
| 15. FLASH Memory Controller..... | 155 |
| 15.1. Register..... | 155 |
| 15.1.1. Register Map..... | 155 |
| 15.1.2. FLASHLOCK..... | 155 |
| 15.1.3. FLASHSTATUS..... | 156 |
| 15.1.4. FLASHPAGE..... | 156 |
| 15.1.5. FLASHPERASE..... | 157 |
| 15.1.6. SWDACCESS..... | 157 |
| 15.1.7. FLASHWSTATE..... | 157 |
| 15.1.8. FLASHBWRITE..... | 157 |
| 15.1.9. FLASHBWDATA..... | 158 |
| 15.2. Details of Operation..... | 159 |
| 15.2.1. Block Diagram..... | 159 |
| 15.2.2. Configuration..... | 159 |
| 15.2.3. FLASH Memory..... | 159 |
| 15.2.4. Writing to FLASH Controller Registers..... | 159 |
| 15.2.5. FLASH Wait State..... | 159 |
| 15.2.6. FLASH Page Erase..... | 160 |
| 15.2.7. Write to FLASH..... | 160 |
| 15.2.8. Buffered Write to FLASH..... | 160 |
| 15.2.9. SWD Debug Access Disable..... | 161 |
| 16. ADC and AUTO SEQUENCER..... | 162 |
| 16.1. Register..... | 162 |
| 16.1.1. Register Map..... | 162 |
| 16.1.2. EMUXCTL..... | 163 |
| 16.1.3. EMUXDATA..... | 164 |
| 16.1.4. ADCCTL..... | 164 |
| 16.1.5. ADCCR..... | 165 |
| 16.1.6. ADCINT..... | 165 |
| 16.1.7. AS0CTL..... | 166 |
| 16.1.8. AS0S0..... | 167 |
| 16.1.9. AS0R0..... | 167 |
| 16.1.10. AS0S1..... | 168 |
| 16.1.11. AS0R1..... | 168 |
| 16.1.12. AS0S2..... | 168 |
| 16.1.13. AS0R2..... | 169 |
| 16.1.14. AS0S3..... | 169 |
| 16.1.15. AS0R3..... | 169 |
| 16.1.16. AS0S4..... | 170 |
| 16.1.17. AS0R4..... | 170 |
| 16.1.18. AS0S5..... | 170 |
| 16.1.19. AS0R5..... | 171 |

| | |
|--|-----|
| 16.1.20. AS0S6..... | 171 |
| 16.1.21. AS0R6..... | 171 |
| 16.1.22. AS0S7..... | 172 |
| 16.1.23. AS0R7..... | 172 |
| 16.1.24. AS1CTL..... | 172 |
| 16.1.25. AS1S0..... | 173 |
| 16.1.26. AS1R0..... | 174 |
| 16.1.27. AS1S1..... | 174 |
| 16.1.28. AS1R1..... | 174 |
| 16.1.29. AS1S2..... | 174 |
| 16.1.30. AS1R2..... | 175 |
| 16.1.31. AS1S3..... | 175 |
| 16.1.32. AS1R3..... | 176 |
| 16.1.33. AS1S4..... | 176 |
| 16.1.34. AS1R4..... | 176 |
| 16.1.35. AS1S5..... | 176 |
| 16.1.36. AS1R5..... | 177 |
| 16.1.37. AS1S6..... | 177 |
| 16.1.38. AS1R6..... | 178 |
| 16.1.39. AS1S7..... | 178 |
| 16.1.40. AS1R7..... | 178 |
| 16.2. Details of Operation..... | 178 |
| 16.2.1. Block Diagram..... | 178 |
| 16.3. Details of Operation..... | 179 |
| 16.3.1. Basic Configuration..... | 179 |
| 16.3.2. ADC, Autosequencer and EMUX..... | 179 |
| 16.3.3. Clock Setting..... | 180 |
| 16.3.4. ADC..... | 180 |
| 16.3.5. EMUX..... | 180 |
| 16.3.6. Auto Sequencer ASC0, ASC1..... | 181 |
| 16.3.6.1. Auto Sequencer Modes..... | 181 |
| 16.3.6.2. Sequencer trigger..... | 182 |
| 16.3.6.3. ASC Samples..... | 182 |
| 16.3.6.4. ASC0, ASC1 Priority and Collision..... | 183 |
| 17. I2C..... | 185 |
| 17.1. Register..... | 185 |
| 17.1.1. Register Map..... | 185 |
| 17.1.2. I2CCFG..... | 185 |
| 17.1.3. I2CINT..... | 185 |
| 17.1.4. I2CINTEN..... | 187 |
| 17.1.5. I2CMACTL..... | 187 |
| 17.1.6. I2CMARXDATA..... | 188 |
| 17.1.7. I2CMATXDATA..... | 188 |
| 17.1.8. I2CBAUD..... | 188 |
| 17.1.9. I2CSLRXDATA..... | 188 |
| 17.1.10. I2CSLTXDATA..... | 189 |
| 17.1.11. I2CSLADDR..... | 189 |
| 17.2. Details of Operation..... | 190 |
| 17.2.1. Block Diagram..... | 190 |
| 17.2.2. Configuration..... | 190 |
| 17.2.3. I2C..... | 190 |
| 17.2.4. I2C Clock setting..... | 190 |
| 17.2.5. I2C Addressing..... | 191 |
| 18. UART..... | 192 |

| | |
|--|-----|
| 18.1. Register..... | 192 |
| 18.1.1. Register Map..... | 192 |
| 18.1.2. UARTRXTX/UARTDL_L..... | 192 |
| 18.1.3. UARTIEN/UARTDL_H..... | 193 |
| 18.1.4. UARTII..... | 193 |
| 18.1.5. UARLTC..... | 194 |
| 18.1.6. UARLTS..... | 194 |
| 18.1.7. UARTFCTL..... | 195 |
| 18.1.8. UARTIEN..... | 195 |
| 18.1.9. UARTDL_L..... | 195 |
| 18.1.10. UARTDL_H..... | 196 |
| 18.1.11. UARTFD_F..... | 196 |
| 18.1.12. UARTFSTAT..... | 196 |
| 18.2. Details of Operation..... | 197 |
| 18.2.1. Block Diagram..... | 197 |
| 18.2.2. Configuration..... | 197 |
| 18.2.3. UART..... | 197 |
| 18.2.4. UART Clock Rate Setting..... | 197 |
| 18.2.5. Data settings..... | 199 |
| 18.2.6. FIFO Settings..... | 199 |
| 18.2.7. Error Checking on Received Data..... | 199 |
| 19. SOC Bus bridge..... | 200 |
| 19.1. Register..... | 200 |
| 19.1.1. Register Map..... | 200 |
| 19.1.2. SOCBCTL..... | 200 |
| 19.1.3. SOCBCFG..... | 200 |
| 19.1.4. SOCBCLKDIV..... | 201 |
| 19.1.5. SOCBSTAT..... | 201 |
| 19.1.6. SOCBBD..... | 202 |
| 19.1.7. SOCBINT_EN..... | 203 |
| 19.2. Details of Operation..... | 204 |
| 19.2.1. Block Diagram..... | 204 |
| 19.2.2. Configuration..... | 204 |
| 19.2.3. SOC Bridge..... | 204 |
| 19.2.4. SOC Bridge Clock Rate Setting..... | 204 |
| 19.2.5. Enable and Setup of SOC Bridge..... | 205 |
| 19.2.6. SOC Interrupt..... | 205 |
| 19.2.7. SOC Bridge Protocol..... | 205 |
| 19.2.8. Reading from SOC Bridge..... | 205 |
| 19.2.9. Writing to SOC Bridge..... | 205 |
| 20. SPI..... | 206 |
| 20.1. Register..... | 206 |
| 20.1.1. Register Map..... | 206 |
| 20.1.2. SPICTL..... | 206 |
| 20.1.3. SPICFG..... | 207 |
| 20.1.4. SPICLKDIV..... | 208 |
| 20.1.5. SPISTAT..... | 208 |
| 20.1.6. SPICSSTR..... | 210 |
| 20.1.7. SPID..... | 210 |
| 20.1.8. SPIINT_EN..... | 211 |
| 20.2. Details of Operation..... | 212 |
| 20.2.1. Block Diagram..... | 212 |
| 20.2.2. Configuration..... | 212 |
| 20.2.3. SPI..... | 212 |

| | |
|---|-----|
| 20.2.4. SPI Clock Rate Setting..... | 212 |
| 20.2.5. Master Slave Mode..... | 213 |
| 20.2.6. Clock Phase, Polarity..... | 213 |
| 20.2.7. SPI Early Data Transmit..... | 213 |
| 20.2.8. Data Format..... | 214 |
| 20.2.9. Chip Select Settings..... | 215 |
| 20.2.10. Auto Retransmit Data Word..... | 215 |
| 20.2.11. Loop Back Mode..... | 215 |
| 20.2.12. SPI Interrupt..... | 216 |
| 20.2.13. SPI Enable..... | 216 |
| 21. Multi-mode Power Manager..... | 217 |
| 21.1. Register..... | 217 |
| 21.1.1. Register Map..... | 217 |
| 21.1.2. SOC.SYSSTAT..... | 217 |
| 21.1.3. SOC.PWRCTL..... | 218 |
| 21.1.4. SOC.PWRSTAT..... | 218 |
| 21.1.5. SOC.PWRSTATCFG..... | 219 |
| 21.1.6. SOC.SCFG..... | 219 |
| 21.1.7. SOC.PWRCFG..... | 220 |
| 22. Configurable Analog FRONT END..... | 221 |
| 22.1. Register..... | 221 |
| 22.1.1. Register Map..... | 221 |
| 22.1.2. SOC.AIO0CFG..... | 221 |
| 22.1.3. SOC.AIO1CFG..... | 222 |
| 22.1.4. SOC.AIO2CFG..... | 223 |
| 22.1.5. SOC.AIO3CFG..... | 224 |
| 22.1.6. SOC.AIO4CFG..... | 225 |
| 22.1.7. SOC.AIO5CFG..... | 226 |
| 22.1.8. SOC.AIO6CFG..... | 227 |
| 22.1.9. SOC.AIO7CFG..... | 229 |
| 22.1.10. SOC.AIO8CFG..... | 230 |
| 22.1.11. SOC.AIO9CFG..... | 232 |
| 22.1.12. SOC.SMCFG..... | 233 |
| 22.1.13. SOC.HPDAC..... | 234 |
| 22.1.14. SOC.LPDAC0..... | 234 |
| 22.1.15. SOC.LPDAC1..... | 234 |
| 22.1.16. SOC.ADCSCANCFG..... | 234 |
| 22.1.17. SOC.ADMUX..... | 235 |
| 22.1.18. SOC.PROINTEN..... | 235 |
| 22.1.19. SOC.PROINT..... | 236 |
| 22.1.20. SOC.AIOOUT0..... | 236 |
| 22.1.21. SOC.AIOOUT1..... | 237 |
| 22.1.22. SOC.AIOIN0..... | 237 |
| 22.1.23. SOC.AIOIN1..... | 238 |
| 22.1.24. SOC.AIOINTEN..... | 238 |
| 22.1.25. SOC.AIOINT..... | 238 |
| 22.1.26. SOC.SMCTL..... | 239 |
| 22.2. Details of Operation..... | 240 |
| 22.2.1. Block Diagram..... | 240 |
| 22.2.2. Configuration..... | 240 |
| 22.2.3. Configurable Analog Front End..... | 240 |
| 22.2.3.1. Configurable Analog Front End Enable..... | 240 |
| 22.3. AIO1, AIO0..... | 241 |
| 22.3.1. Block Diagram..... | 241 |

| | |
|--|-----|
| 22.3.2. AIO1, AIO0..... | 241 |
| 22.3.3. AIO1, AIO0 digital I/O Mode..... | 241 |
| 22.3.3.1. AIO0 IO..... | 242 |
| 22.3.3.2. AIO1 IO..... | 242 |
| 22.3.3.3. AIO0 Polarity..... | 242 |
| 22.3.3.4. AIO1 Polarity..... | 242 |
| 22.3.4. AIO1, AIO0 differential Amplifier Mode..... | 242 |
| 22.3.4.1. AIO1, AIO0 Differential Amplifier Gain..... | 242 |
| 22.3.4.2. AIO1, AIO0 Differential Amplifier Reference..... | 242 |
| 22.3.4.3. AIO1, AIO0 Differential Amplifier Calibration..... | 242 |
| 22.3.5. AIO1, AIO0 Protection..... | 242 |
| 22.3.5.1. HP10 Comparator..... | 243 |
| 22.3.5.2. LP10 Comparator..... | 243 |
| 22.4. AIO3, AIO2..... | 244 |
| 22.4.1. Block Diagram..... | 244 |
| 22.4.2. AIO3, AIO2..... | 244 |
| 22.4.3. AIO3, AIO2 digital I/O Mode..... | 244 |
| 22.4.3.1. AIO2 IO..... | 245 |
| 22.4.3.2. AIO3 IO..... | 245 |
| 22.4.3.3. AIO2 Polarity..... | 245 |
| 22.4.3.4. AIO3 Polarity..... | 245 |
| 22.4.4. AIO3, AIO2 differential Amplifier Mode DAO32..... | 245 |
| 22.4.4.1. DAO32 Differential Amplifier Gain..... | 245 |
| 22.4.4.2. DAO32 Differential Amplifier Reference..... | 245 |
| 22.4.4.3. DAO32 Differential Amplifier Calibration..... | 245 |
| 22.4.5. AIO3, AIO2 Protection..... | 245 |
| 22.4.5.1. HP32 Comparator..... | 246 |
| 22.4.5.2. LP32 Comparator..... | 246 |
| 22.5. AIO5, AIO4..... | 247 |
| 22.5.1. Block Diagram..... | 247 |
| 22.5.2. AIO5, AIO4..... | 247 |
| 22.5.3. AIO5, AIO4 digital I/O Mode..... | 247 |
| 22.5.3.1. AIO4 IO..... | 248 |
| 22.5.3.2. AIO5 IO..... | 248 |
| 22.5.3.3. AIO4 Polarity..... | 248 |
| 22.5.3.4. AIO5 Polarity..... | 248 |
| 22.5.4. AIO5, AIO4 differential Amplifier Mode DAO54..... | 248 |
| 22.5.4.1. DAO54 Differential Amplifier Gain..... | 248 |
| 22.5.4.2. DAO54 Differential Amplifier Reference..... | 248 |
| 22.5.4.3. DAO54 Differential Amplifier Calibration..... | 248 |
| 22.5.5. AIO5, AIO4 Protection..... | 248 |
| 22.5.5.1. HP54 Comparator..... | 249 |
| 22.5.5.2. LP54 Comparator..... | 249 |
| 22.6. AIO6..... | 250 |
| 22.6.1. Block Diagram..... | 250 |
| 22.6.2. AIO6..... | 250 |
| 22.6.3. AIO6 digital I/O Mode..... | 251 |
| 22.6.3.1. AIO6 IO..... | 251 |
| 22.6.3.2. AIO6 IO Interrupt..... | 251 |
| 22.6.3.3. AIO6 Polarity..... | 251 |
| 22.6.4. AIO6 Single Ended Amplifier Mode..... | 251 |
| 22.6.4.1. AIO6 Amplifier Gain..... | 251 |
| 22.6.4.2. AIO6 Analog MUX..... | 251 |
| 22.6.5. AIO6 Comparator Mode..... | 251 |

| | |
|---|-----|
| 22.6.5.1. AIO6 Comparator Hysteresis..... | 252 |
| 22.6.5.2. AIO6 Comparator setting..... | 252 |
| 22.6.5.3. AIO6 Comparator Polarity..... | 252 |
| 22.6.5.4. AIO6 Comparator Output MUX..... | 252 |
| 22.6.6. AIO6 Special Mode..... | 252 |
| 22.6.6.1. AIO6 Special Mode MUX..... | 252 |
| 22.6.6.2. AIO6 Special Mode ADMUX..... | 252 |
| 22.6.6.3. AIO6 Special Mode OFFSET SWAP..... | 252 |
| 22.6.7. AIO6 Push Button Mode..... | 252 |
| 22.6.7.1. AIO6 Push Button Wake Up..... | 253 |
| 22.6.7.2. AIO6 Push Button Power Down..... | 253 |
| 22.6.7.3. AIO6 Push Button Hard Reset..... | 253 |
| 22.7. AIO7..... | 254 |
| 22.7.1. Block Diagram..... | 254 |
| 22.7.2. AIO7..... | 254 |
| 22.7.3. AIO7 digital I/O Mode..... | 254 |
| 22.7.3.1. AIO7 IO..... | 255 |
| 22.7.3.2. AIO7 IO Interrupt..... | 255 |
| 22.7.3.3. AIO7 Polarity..... | 255 |
| 22.7.4. AIO7 Single Ended Amplifier Mode..... | 255 |
| 22.7.4.1. AIO7 Amplifier Gain..... | 255 |
| 22.7.4.2. AIO7 Analog MUX..... | 255 |
| 22.7.5. AIO7 Comparator Mode..... | 255 |
| 22.7.5.1. AIO7 Comparator Hysteresis..... | 255 |
| 22.7.5.2. AIO7 Comparator Reference..... | 256 |
| 22.7.5.3. AIO7 Comparator Polarity..... | 256 |
| 22.7.5.4. AIO7 Comparator Output..... | 256 |
| 22.7.6. AIO7 Special Mode..... | 256 |
| 22.7.6.1. AIO7 Comparator Hysteresis..... | 256 |
| 22.7.6.2. AIO7 Comparator Reference..... | 256 |
| 22.7.6.3. AIO7 Comparator Reference Star Point..... | 256 |
| 22.7.6.4. AIO7 Voltage Reading..... | 256 |
| 22.7.6.5. AIO7 Comparator Output..... | 256 |
| 22.7.6.6. AIO7 POS S/H Bypass..... | 257 |
| 22.7.6.7. AIO7 nIRQ2/POS Selector..... | 257 |
| 22.8. AIO8..... | 258 |
| 22.8.1. Block Diagram..... | 258 |
| 22.8.2. AIO8..... | 258 |
| 22.8.3. AIO8 digital I/O Mode..... | 259 |
| 22.8.3.1. AIO8 IO..... | 259 |
| 22.8.3.2. AIO8 IO Interrupt..... | 259 |
| 22.8.3.3. AIO8 Polarity..... | 259 |
| 22.8.4. AIO8 Single Ended Amplifier Mode..... | 259 |
| 22.8.4.1. AIO8 Amplifier Gain..... | 259 |
| 22.8.4.2. AIO8 Analog MUX..... | 259 |
| 22.8.5. AIO8 Comparator Mode..... | 259 |
| 22.8.5.1. AIO8 Comparator Hysteresis..... | 259 |
| 22.8.5.2. AIO8 Comparator Reference..... | 260 |
| 22.8.5.3. AIO8 Comparator Polarity..... | 260 |
| 22.8.5.4. AIO8 Comparator Output..... | 260 |
| 22.8.6. AIO8 Special Mode..... | 260 |
| 22.8.6.1. AIO8 Comparator Hysteresis..... | 260 |
| 22.8.6.2. AIO8 Comparator Reference..... | 260 |
| 22.8.6.3. AIO8 Comparator Reference Star Point..... | 260 |

| | |
|---|-----|
| 22.8.6.4. AIO8 Voltage Reading..... | 260 |
| 22.8.6.5. AIO8 Comparator Output..... | 261 |
| 22.8.6.6. AIO8 POS S/H Bypass..... | 261 |
| 22.8.6.7. AIO8 nIRQ2/POS Selector..... | 261 |
| 22.9. AIO9..... | 262 |
| 22.9.1. Block Diagram..... | 262 |
| 22.9.2. AIO9..... | 262 |
| 22.9.3. AIO9 digital I/O Mode..... | 263 |
| 22.9.3.1. AIO9 IO..... | 263 |
| 22.9.3.2. AIO9 IO Interrupt..... | 263 |
| 22.9.3.3. AIO9 Polarity..... | 263 |
| 22.9.4. AIO9 Single Ended Amplifier Mode..... | 263 |
| 22.9.4.1. AIO9 Amplifier Gain..... | 263 |
| 22.9.4.2. AIO9 Analog MUX..... | 263 |
| 22.9.5. AIO9 Comparator Mode..... | 263 |
| 22.9.5.1. AIO9 Comparator Hysteresis..... | 263 |
| 22.9.5.2. AIO9 Comparator Reference..... | 264 |
| 22.9.5.3. AIO9 Comparator Polarity..... | 264 |
| 22.9.5.4. AIO9 Comparator Output..... | 264 |
| 22.9.6. AIO9 Special Mode..... | 264 |
| 22.9.6.1. AIO9 Comparator Hysteresis..... | 264 |
| 22.9.6.2. AIO9 Comparator Reference..... | 264 |
| 22.9.6.3. AIO9 Comparator Reference Star Point..... | 264 |
| 22.9.6.4. AIO9 Voltage Reading..... | 264 |
| 22.9.6.5. AIO9 Comparator Output..... | 265 |
| 22.9.6.6. AIO9 POS S/H Bypass..... | 265 |
| 22.9.6.7. AIO9 nIRQ2/POS Selector..... | 265 |
| 22.10. EMUX and ADMUX..... | 266 |
| 22.10.1. Block Diagram..... | 266 |
| 22.10.2. EMUX..... | 266 |
| 22.10.2.1. EMUX Enable..... | 266 |
| 22.10.2.2. EMUXD Packet Structure..... | 266 |
| 22.10.2.3. EMUX Timing..... | 267 |
| 22.10.3. ADMUX..... | 267 |
| 22.10.3.1. ADMUX Control..... | 267 |
| 22.10.3.2. ADMUX Buffer..... | 268 |
| 22.10.3.3. ADMUX..... | 268 |
| 23. Application Specific Power Driver..... | 269 |
| 23.1. Register..... | 269 |
| 23.1.1. Register Map..... | 269 |
| 23.1.2. SOC.PRCTL..... | 269 |
| 23.1.3. SOC.OMOUT..... | 269 |
| 23.1.4. SOC.DRVCTL..... | 270 |
| 23.1.5. SOC.PROTCTL..... | 270 |
| 23.2. Details of Operation..... | 271 |
| 23.2.1. Block Diagram..... | 271 |
| 23.2.2. Configuration..... | 271 |
| 23.2.3. Application Specific Power Driver..... | 271 |
| 23.2.3.1. Application Specific Power Driver Enable..... | 271 |
| 23.3. OM0..... | 272 |
| 23.3.1. Block Diagram..... | 272 |
| 23.3.2. OM0..... | 272 |
| 23.3.2.1. OM0 Open Drain Output..... | 272 |
| 23.4. OM2..... | 273 |

| | |
|---|-----|
| 23.4.1. Block Diagram..... | 273 |
| 23.4.2. OM2..... | 273 |
| 23.4.2.1. OM2 Open Drain Output..... | 273 |
| 23.5. OM4..... | 274 |
| 23.5.1. Block Diagram..... | 274 |
| 23.5.2. OM4..... | 274 |
| 23.5.2.1. OM4 Open Drain Output..... | 274 |
| 23.6. ENHS1 Protection..... | 275 |
| 23.6.1. Block Diagram..... | 275 |
| 23.6.2. ENHS1 Protection..... | 275 |
| 23.6.2.1. Protection Enable..... | 275 |
| 23.6.2.2. Input Signal Selection..... | 275 |
| 23.7. ENHS2 Protection..... | 276 |
| 23.7.1. Block Diagram..... | 276 |
| 23.7.2. ENHS2 Protection..... | 276 |
| 23.7.2.1. Protection Enable..... | 276 |
| 24. Arm Cortex-M0 Reference..... | 277 |
| 24.1. Introduction..... | 277 |
| 24.1.1. Overview..... | 277 |
| 24.1.2. About the Cortex-M0 processor and core peripherals..... | 277 |
| 24.1.2.1. System-level interface..... | 278 |
| 24.1.2.2. Integrated configurable debug..... | 278 |
| 24.1.2.3. Cortex-M0 processor features summary..... | 278 |
| 24.1.2.4. Cortex-M0 core peripherals..... | 278 |
| 24.1.2.4.1. NVIC..... | 278 |
| 24.1.2.4.2. System Control Block..... | 279 |
| 24.1.2.4.3. System timer..... | 279 |
| 24.2. The Cortex-M0 Processor..... | 279 |
| 24.2.1. Programmers Model..... | 279 |
| 24.2.1.1. Processor modes..... | 279 |
| 24.2.1.2. Stacks..... | 279 |
| 24.2.1.3. Core Registers..... | 280 |
| 24.2.1.3.1. General-purpose registers..... | 280 |
| 24.2.1.3.2. Stack Pointer..... | 281 |
| 24.2.1.3.3. Link Register..... | 281 |
| 24.2.1.3.4. Program Counter..... | 281 |
| 24.2.1.3.5. Program Status Register..... | 281 |
| 24.2.1.3.6. Application Program Status Register..... | 282 |
| 24.2.1.3.7. Interrupt Program Status Register..... | 282 |
| 24.2.1.3.8. Execution Program Status Register..... | 283 |
| 24.2.1.3.9. Interruptible-restartable instructions..... | 283 |
| 24.2.1.3.10. Exception mask register..... | 284 |
| 24.2.1.3.11. Priority Mask Register..... | 284 |
| 24.2.1.3.12. Control Register..... | 284 |
| 24.2.1.4. Exceptions and interrupts..... | 285 |
| 24.2.1.5. Data Types..... | 285 |
| 24.2.1.6. The Cortex Microcontroller Software Interface Standard..... | 286 |
| 24.2.2. Memory model..... | 286 |
| 24.2.2.1. Memory regions, types and attributes..... | 287 |
| 24.2.2.1.1. Normal..... | 287 |
| 24.2.2.1.2. Device..... | 288 |
| 24.2.2.1.3. Strongly-ordered..... | 288 |
| 24.2.2.1.4. Execute Never (XN)..... | 288 |
| 24.2.2.2. Memory system ordering of memory accesses..... | 288 |

| | |
|---|-----|
| 24.2.2.3. Behavior of memory accesses..... | 289 |
| 24.2.2.4. Software ordering of memory accesses..... | 289 |
| 24.2.2.4.1. DMB..... | 289 |
| 24.2.2.4.2. DSB..... | 289 |
| 24.2.2.4.3. ISB..... | 290 |
| 24.2.2.4.4. Vector table..... | 290 |
| 24.2.2.4.5. Self-modifying code..... | 290 |
| 24.2.2.4.6. Memory map switching..... | 290 |
| 24.2.2.5. Memory endianness..... | 290 |
| 24.2.2.5.1. Little-endian format..... | 290 |
| 24.2.3. Exception model..... | 291 |
| 24.2.3.1. Exception states..... | 291 |
| 24.2.3.1.1. Inactive..... | 291 |
| 24.2.3.1.2. Pending..... | 291 |
| 24.2.3.1.3. Active..... | 291 |
| 24.2.3.1.4. Active and pending..... | 291 |
| 24.2.3.2. Exception types..... | 291 |
| 24.2.3.2.1. Reset..... | 292 |
| 24.2.3.2.2. NMI..... | 292 |
| 24.2.3.2.3. HardFault..... | 292 |
| 24.2.3.2.4. SVCall..... | 292 |
| 24.2.3.2.5. PendSV..... | 292 |
| 24.2.3.2.6. SysTick..... | 292 |
| 24.2.3.2.7. Interrupt (IRQ)..... | 292 |
| 24.2.3.3. Exception handlers..... | 293 |
| 24.2.3.3.1. Interrupt Service Routines (ISRs)..... | 293 |
| 24.2.3.3.2. Fault handler..... | 293 |
| 24.2.3.3.3. System handlers..... | 293 |
| 24.2.3.4. Vector table..... | 293 |
| 24.2.3.5. Exception priorities..... | 294 |
| 24.2.3.6. Exception entry and return..... | 295 |
| 24.2.3.6.1. Preemption..... | 295 |
| 24.2.3.6.2. Return..... | 295 |
| 24.2.3.6.3. Tail-chaining..... | 295 |
| 24.2.3.6.4. Late-arriving..... | 295 |
| 24.2.3.6.5. Exception entry..... | 296 |
| 24.2.3.6.6. Exception return..... | 296 |
| 24.2.4. Fault handling..... | 297 |
| 24.2.4.1. Lockup..... | 297 |
| 24.2.5. Power management..... | 298 |
| 24.2.5.1. Entering sleep mode..... | 298 |
| 24.2.5.1.1. Wait for interrupt..... | 298 |
| 24.2.5.1.2. Wait for event..... | 298 |
| 24.2.5.1.3. Sleep-on-exit..... | 299 |
| 24.2.5.2. Wakeup from sleep mode..... | 299 |
| 24.2.5.2.1. Wakeup from WFI or sleep-on-exit..... | 299 |
| 24.2.5.2.2. Wakeup from WFE..... | 299 |
| 24.2.5.3. The Wakeup Interrupt Controller..... | 299 |
| 24.2.5.4. The external event input..... | 300 |
| 24.2.5.5. Power management programming hints..... | 300 |
| 24.3. The Cortex-M0 Instruction Set..... | 300 |
| 24.3.1. Instruction set summary..... | 300 |
| 24.3.2. Intrinsic Functions..... | 302 |
| 24.3.3. About the Instruction Descriptions..... | 303 |

| | |
|---|-----|
| 24.3.3.1. Operands..... | 303 |
| 24.3.3.2. Restrictions when using PC or SP..... | 304 |
| 24.3.3.3. Shift Operations..... | 304 |
| 24.3.3.3.1. ASR..... | 304 |
| 24.3.3.3.2. LSR..... | 305 |
| 24.3.3.3.3. LSL..... | 305 |
| 24.3.3.3.4. ROR..... | 306 |
| 24.3.3.4. Address alignment..... | 306 |
| 24.3.3.5. PC-relative expressions..... | 306 |
| 24.3.3.6. Conditional execution..... | 307 |
| 24.3.3.6.1. The condition flags..... | 307 |
| 24.3.3.6.2. Condition code suffixes..... | 308 |
| 24.3.4. Memory access instructions..... | 308 |
| 24.3.4.1. ADR..... | 309 |
| 24.3.4.1.1. Syntax..... | 309 |
| 24.3.4.1.2. Operation..... | 309 |
| 24.3.4.1.3. Restrictions..... | 309 |
| 24.3.4.1.4. Condition flags..... | 309 |
| 24.3.4.1.5. Examples..... | 309 |
| 24.3.4.2. LDR and STR, immediate offset..... | 310 |
| 24.3.4.2.1. Syntax..... | 310 |
| 24.3.4.2.2. Operation..... | 310 |
| 24.3.4.2.3. Restrictions..... | 310 |
| 24.3.4.2.4. Condition flags..... | 311 |
| 24.3.4.2.5. Examples..... | 311 |
| 24.3.4.3. LDR and STR, register offset..... | 311 |
| 24.3.4.3.1. Syntax..... | 311 |
| 24.3.4.3.2. Operation..... | 311 |
| 24.3.4.3.3. Restrictions..... | 311 |
| 24.3.4.3.4. Condition flags..... | 312 |
| 24.3.4.3.5. Examples..... | 312 |
| 24.3.4.4. LDR, PC-relative..... | 312 |
| 24.3.4.4.1. Syntax..... | 312 |
| 24.3.4.4.2. Operation..... | 312 |
| 24.3.4.4.3. Restrictions..... | 312 |
| 24.3.4.4.4. Condition flags..... | 312 |
| 24.3.4.4.5. Examples..... | 313 |
| 24.3.4.5. LDM and STM..... | 313 |
| 24.3.4.5.1. Syntax..... | 313 |
| 24.3.4.5.2. Operation..... | 313 |
| 24.3.4.5.3. Restrictions..... | 314 |
| 24.3.4.5.4. Condition flags..... | 314 |
| 24.3.4.5.5. Examples..... | 314 |
| 24.3.4.5.6. Incorrect examples..... | 314 |
| 24.3.4.6. PUSH and POP..... | 314 |
| 24.3.4.6.1. Syntax..... | 314 |
| 24.3.4.6.2. Operation..... | 314 |
| 24.3.4.6.3. Restrictions..... | 315 |
| 24.3.4.6.4. Condition flags..... | 315 |
| 24.3.4.6.5. Examples..... | 315 |
| 24.3.5. General data processing instructions..... | 315 |
| 24.3.5.1. ADC, ADD, RSB, SBC, and SUB..... | 316 |
| 24.3.5.1.1. Syntax..... | 316 |
| 24.3.5.1.2. Operation..... | 317 |

| | |
|--|-----|
| 24.3.5.1.3. Restrictions..... | 317 |
| 24.3.5.1.4. Examples..... | 318 |
| 24.3.5.2. AND, ORR, EOR, and BIC..... | 318 |
| 24.3.5.2.1. Syntax..... | 319 |
| 24.3.5.2.2. Operation..... | 319 |
| 24.3.5.2.3. Restrictions..... | 319 |
| 24.3.5.2.4. Condition flags..... | 319 |
| 24.3.5.2.5. Examples..... | 319 |
| 24.3.5.3. ASR, LSL, LSR, and ROR..... | 320 |
| 24.3.5.3.1. Syntax..... | 320 |
| 24.3.5.3.2. Operation..... | 320 |
| 24.3.5.3.3. Restrictions..... | 321 |
| 24.3.5.3.4. Condition flags..... | 321 |
| 24.3.5.3.5. Examples..... | 321 |
| 24.3.5.4. CMP and CMN..... | 321 |
| 24.3.5.4.1. Syntax..... | 321 |
| 24.3.5.4.2. Operation..... | 321 |
| 24.3.5.4.3. Restrictions..... | 322 |
| 24.3.5.4.4. Condition flags..... | 322 |
| 24.3.5.4.5. Examples..... | 322 |
| 24.3.5.5. MOV and MVN..... | 322 |
| 24.3.5.5.1. Syntax..... | 322 |
| 24.3.5.5.2. Operation..... | 323 |
| 24.3.5.5.3. Restrictions..... | 323 |
| 24.3.5.5.4. Condition flags..... | 323 |
| 24.3.5.5.5. Example..... | 323 |
| 24.3.5.6. MULS..... | 323 |
| 24.3.5.6.1. Syntax..... | 324 |
| 24.3.5.6.2. Operation..... | 324 |
| 24.3.5.6.3. Restrictions..... | 324 |
| 24.3.5.6.4. Condition flags..... | 324 |
| 24.3.5.6.5. Examples..... | 324 |
| 24.3.5.7. REV, REV16, and REVSH..... | 324 |
| 24.3.5.7.1. Syntax..... | 324 |
| 24.3.5.7.2. Operation..... | 325 |
| 24.3.5.7.3. Restrictions..... | 325 |
| 24.3.5.7.4. Condition flags..... | 325 |
| 24.3.5.7.5. Examples..... | 325 |
| 24.3.5.8. SXT and UXT..... | 325 |
| 24.3.5.8.1. Syntax..... | 325 |
| 24.3.5.8.2. Operation..... | 326 |
| 24.3.5.8.3. Restrictions..... | 326 |
| 24.3.5.8.4. Condition flags..... | 326 |
| 24.3.5.8.5. Examples..... | 326 |
| 24.3.5.9. TST..... | 326 |
| 24.3.5.9.1. Syntax..... | 326 |
| 24.3.5.9.2. Operation..... | 327 |
| 24.3.5.9.3. Restrictions..... | 327 |
| 24.3.5.9.4. Condition flags..... | 327 |
| 24.3.5.9.5. Examples..... | 327 |
| 24.3.6. Branch and control instructions..... | 327 |
| 24.3.6.1. B, BL, BX, and BLX..... | 328 |
| 24.3.6.1.1. Syntax..... | 328 |
| 24.3.6.1.2. Operation..... | 328 |

| | |
|---|-----|
| 24.3.6.1.3. Restrictions..... | 328 |
| 24.3.7. Miscellaneous instructions..... | 329 |
| 24.3.7.1. BKPT..... | 330 |
| 24.3.7.1.1. Syntax..... | 330 |
| 24.3.7.1.2. Operation..... | 330 |
| 24.3.7.1.3. Restrictions..... | 330 |
| 24.3.7.1.4. Condition flags..... | 330 |
| 24.3.7.1.5. Examples..... | 330 |
| 24.3.7.2. CPS..... | 330 |
| 24.3.7.2.1. Syntax..... | 330 |
| 24.3.7.2.2. Operation..... | 331 |
| 24.3.7.2.3. Restrictions..... | 331 |
| 24.3.7.2.4. Condition flags..... | 331 |
| 24.3.7.2.5. Examples..... | 331 |
| 24.3.7.3. DMB..... | 331 |
| 24.3.7.3.1. Syntax..... | 331 |
| 24.3.7.3.2. Operation..... | 331 |
| 24.3.7.3.3. Restrictions..... | 331 |
| 24.3.7.3.4. Condition flags..... | 332 |
| 24.3.7.3.5. Examples..... | 332 |
| 24.3.7.4. DSB..... | 332 |
| 24.3.7.4.1. Syntax..... | 332 |
| 24.3.7.4.2. Operation..... | 332 |
| 24.3.7.4.3. Restrictions..... | 332 |
| 24.3.7.4.4. Condition flags..... | 332 |
| 24.3.7.4.5. Examples..... | 332 |
| 24.3.7.5. ISB..... | 332 |
| 24.3.7.5.1. Syntax..... | 333 |
| 24.3.7.5.2. Operation..... | 333 |
| 24.3.7.5.3. Restrictions..... | 333 |
| 24.3.7.5.4. Condition flags..... | 333 |
| 24.3.7.5.5. Examples..... | 333 |
| 24.3.7.6. MRS..... | 333 |
| 24.3.7.6.1. Syntax..... | 333 |
| 24.3.7.6.2. Operation..... | 333 |
| 24.3.7.6.3. Restrictions..... | 334 |
| 24.3.7.6.4. Condition flags..... | 334 |
| 24.3.7.6.5. Examples..... | 334 |
| 24.3.7.7. MSR..... | 334 |
| 24.3.7.7.1. Syntax..... | 334 |
| 24.3.7.7.2. Operation..... | 334 |
| 24.3.7.7.3. Restrictions..... | 334 |
| 24.3.7.7.4. Condition flags..... | 334 |
| 24.3.7.7.5. Examples..... | 335 |
| 24.3.7.8. NOP..... | 335 |
| 24.3.7.8.1. Syntax..... | 335 |
| 24.3.7.8.2. Operation..... | 335 |
| 24.3.7.8.3. Restrictions..... | 335 |
| 24.3.7.8.4. Condition flags..... | 335 |
| 24.3.7.8.5. Examples..... | 335 |
| 24.3.7.9. SEV..... | 335 |
| 24.3.7.9.1. Syntax..... | 335 |
| 24.3.7.9.2. Operation..... | 336 |
| 24.3.7.9.3. Restrictions..... | 336 |

| | |
|---|-----|
| 24.3.7.9.4. Condition flags..... | 336 |
| 24.3.7.9.5. Examples..... | 336 |
| 24.3.7.10. SVC..... | 336 |
| 24.3.7.10.1. Syntax..... | 336 |
| 24.3.7.10.2. Operation..... | 336 |
| 24.3.7.10.3. Restrictions..... | 336 |
| 24.3.7.10.4. Condition flags..... | 337 |
| 24.3.7.10.5. Examples..... | 337 |
| 24.3.7.11. WFE..... | 337 |
| 24.3.7.11.1. Syntax..... | 337 |
| 24.3.7.11.2. Operation..... | 337 |
| 24.3.7.11.3. Restrictions..... | 337 |
| 24.3.7.11.4. Condition flags..... | 338 |
| 24.3.7.11.5. Examples..... | 338 |
| 24.3.7.12. WFI..... | 338 |
| 24.3.7.12.1. Syntax..... | 338 |
| 24.3.7.12.2. Operation..... | 338 |
| 24.3.7.12.3. Restrictions..... | 338 |
| 24.3.7.12.4. Condition flags..... | 338 |
| 24.3.7.12.5. Examples..... | 338 |
| 24.4. Cortex-M0 Peripherals..... | 339 |
| 24.4.1. About the Cortex-M0 peripherals..... | 339 |
| 24.4.2. Nested Vectored Interrupt Controller..... | 339 |
| 24.4.2.1. Accessing the Cortex-M0 NVIC registers using CMSIS..... | 340 |
| 24.4.2.2. Interrupt Set-enable Register..... | 340 |
| 24.4.2.3. Interrupt Clear-enable Register..... | 341 |
| 24.4.2.4. Interrupt Set-pending Register..... | 341 |
| 24.4.2.5. Interrupt Clear-pending Register..... | 342 |
| 24.4.2.6. Interrupt Priority Registers..... | 342 |
| 24.4.2.7. Level-sensitive and pulse interrupts..... | 343 |
| 24.4.2.7.1. Hardware and software control of interrupts..... | 344 |
| 24.4.2.8. NVIC usage hints and tips..... | 344 |
| 24.4.2.8.1. NVIC programming hints..... | 344 |
| 24.4.3. System Control Block..... | 345 |
| 24.4.3.1. The CMSIS mapping of the Cortex-M0 SCB registers..... | 345 |
| 24.4.3.2. CPUID Register..... | 346 |
| 24.4.3.3. Interrupt Control and State Register..... | 346 |
| 24.4.3.4. Application Interrupt and Reset Control Register..... | 348 |
| 24.4.3.5. System Control Register..... | 349 |
| 24.4.3.6. Configuration and Control Register..... | 350 |
| 24.4.3.7. System Handler Priority Registers..... | 350 |
| 24.4.3.7.1. System Handler Priority Register 2..... | 351 |
| 24.4.3.7.2. System Handler Priority Register 3..... | 351 |
| 24.4.3.8. SCB usage hints and tips..... | 352 |
| 24.4.4. System timer, SysTick..... | 352 |
| 24.4.4.1. SysTick Control and Status Register..... | 352 |
| 24.4.4.2. SysTick Reload Value Register..... | 353 |
| 24.4.4.2.1. Calculating the RELOAD value..... | 353 |
| 24.4.4.3. SysTick Current Value Register..... | 354 |
| 24.4.4.4. SysTick Calibration Value Register..... | 354 |
| 24.4.4.5. SysTick usage hints and tips..... | 355 |
| 25. Legal Information..... | 356 |

LIST OF TABLES

| | |
|---|-----|
| Table 2-1. Embedded FLASH Register Map..... | 33 |
| Table 2-2. ROM Register Map..... | 34 |
| Table 2-3. System Clock Control Register Map..... | 34 |
| Table 2-4. FLASH Memory Controller Register Map..... | 34 |
| Table 2-5. Watchdog Timer Register Map..... | 35 |
| Table 2-6. General Purpose Timer Register Map..... | 35 |
| Table 2-7. GPIO Port A Register Map..... | 35 |
| Table 2-8. GPIO Port B Register Map..... | 36 |
| Table 2-9. GPIO Port AB Register Map..... | 37 |
| Table 2-10. GPIO Port C Register Map..... | 37 |
| Table 2-11. GPIO Port D Register Map..... | 37 |
| Table 2-12. GPIO Port CD Register Map..... | 38 |
| Table 2-13. GPIO Port E Register Map..... | 38 |
| Table 2-14. Timer A Register Map..... | 39 |
| Table 2-15. Timer B Register Map..... | 40 |
| Table 2-16. Timer C Register Map..... | 40 |
| Table 2-17. Timer D Register Map..... | 41 |
| Table 2-18. EMUX Register Map..... | 41 |
| Table 2-19. ADC Register Map..... | 41 |
| Table 2-20. ADC Auto-Sampling Sequencer 0 Register Map..... | 41 |
| Table 2-21. ADC Auto-Sampling Sequencer 1 Register Map..... | 42 |
| Table 2-22. I2C Register Map..... | 42 |
| Table 2-23. UART Register Map..... | 43 |
| Table 2-24. SOC Bus Bridge Register Map..... | 43 |
| Table 2-25. SPI Register Map..... | 44 |
| Table 2-26. Multi-Mode Power Manager Register Map..... | 44 |
| Table 3-1. System Clock Control Register Map..... | 45 |
| Table 4-1. Watchdog Timer Register Map..... | 50 |
| Table 5-1. General Purpose Timer Register Map..... | 54 |
| Table 6-1. GPIO Port A Register Map..... | 57 |
| Table 7-1. GPIO Port B Register Map..... | 67 |
| Table 8-1. GPIO Port C Register Map..... | 75 |
| Table 9-1. GPIO Port D Register Map..... | 83 |
| Table 10-1. GPIO Port E Register Map..... | 93 |
| Table 11-1. Timer A Register Map..... | 103 |
| Table 11-2. Timer A Signal to Pin Mapping..... | 120 |
| Table 12-1. Timer B Register Map..... | 121 |
| Table 12-2. Timer B Signal to Pin Mapping..... | 133 |
| Table 13-1. Timer C Register Map..... | 134 |
| Table 13-2. Timer C Signal to Pin Mapping..... | 144 |
| Table 14-1. Timer D Register Map..... | 145 |
| Table 14-2. Timer D Signal to Pin Mapping..... | 154 |
| Table 15-1. FLASH Memory Controller Register Map..... | 155 |
| Table 16-1. Register Map – EMUX..... | 162 |
| Table 16-2. Register Map – ADC..... | 162 |
| Table 16-3. Register Map – ADC Auto Sequencer 0..... | 162 |
| Table 16-4. Register Map – ADC Auto Sequencer 1..... | 163 |
| Table 17-1. I2C Register Map..... | 185 |
| Table 18-1. UART Register Map..... | 192 |
| Table 19-1. SOC Bus Bridge Register Map..... | 200 |
| Table 20-1. SPI Register Map..... | 206 |

| | |
|---|-----|
| Table 21-1. Multi-Mode Power Manager Register Map..... | 217 |
| Table 22-1. Configurable Analog Front End Register Map..... | 221 |
| Table 23-1. Application Specific Power Driver Register Map..... | 269 |
| Table 24-1. Summary of processor mode and stack use options..... | 279 |
| Table 24-2. Core register set summary..... | 280 |
| Table 24-3. Core register set summary..... | 282 |
| Table 24-4. APSR bit assignments..... | 282 |
| Table 24-5. IPSR bit assignments..... | 282 |
| Table 24-6. EPSR bit assignments..... | 283 |
| Table 24-7. PRIMASK register bit assignments..... | 284 |
| Table 24-8. CONTROL register bit assignments..... | 285 |
| Table 24-9. Memory Access Behavior..... | 289 |
| Table 24-10. Properties of the different exception types..... | 292 |
| Table 24-11. Execution return behavior..... | 297 |
| Table 24-12. Cortex-M0 instructions..... | 301 |
| Table 24-13. CMSIS intrinsic functions to generate some Cortex-M0 instructions..... | 302 |
| Table 24-14. CMSIS intrinsic functions to access special registers..... | 303 |
| Table 24-15. Condition code suffixes..... | 308 |
| Table 24-16. Memory access instructions..... | 308 |
| Table 24-17. Data processing instructions..... | 315 |
| Table 24-18. ADC, ADD, RSB, SBC, and SUB operand restrictions..... | 317 |
| Table 24-19. Branch and Control instructions..... | 327 |
| Table 24-20. Branch ranges..... | 328 |
| Table 24-21. Miscellaneous instructions..... | 329 |
| Table 24-22. Core peripheral register regions..... | 339 |
| Table 24-23. NVIC register summary..... | 339 |
| Table 24-24. CMSIS access NVIC functions..... | 340 |
| Table 24-25. ISER bit assignments..... | 340 |
| Table 24-26. ICER bit assignments..... | 341 |
| Table 24-27. ISPR bit assignments..... | 342 |
| Table 24-28. ICPR bit assignments..... | 342 |
| Table 24-29. IPR bit assignments..... | 343 |
| Table 24-30. CMSIS access NVIC functions..... | 345 |
| Table 24-31. Summary of the SCB register..... | 345 |
| Table 24-32. CPUID register bit assignments..... | 346 |
| Table 24-33. ICSR register bit assignments..... | 347 |
| Table 24-34. AIRCR register bit assignments..... | 348 |
| Table 24-35. SCR register bit assignments..... | 349 |
| Table 24-36. CCR register bit assignments..... | 350 |
| Table 24-37. System fault handler priority fields..... | 351 |
| Table 24-38. SHPR2 register bit assignments..... | 351 |
| Table 24-39. SHPR3 register bit assignments..... | 351 |
| Table 24-40. System timer register summary..... | 352 |
| Table 24-41. SYST_CSR register bit assignments..... | 353 |
| Table 24-42. SYST_RVR register bit assignments..... | 353 |
| Table 24-43. SYST_CVR register bit assignments..... | 354 |
| Table 24-44. SYST_CALIB register bit assignments..... | 354 |

LIST OF REGISTERS

| | |
|--|----|
| Register 3-1. SCCTL (System Clock Control, 0x4000 0000)..... | 45 |
| Register 3-2. PLLCTL (PLL Control, 0x4000 0004)..... | 46 |
| Register 3-3. ROSCCTL (Ring Oscillator Control, 0x4000 0008)..... | 46 |
| Register 3-4. XTALCTL (Crystal Driver Control, 0x4000 000C)..... | 46 |
| Table 3-5. PLL output frequency settings using 4MHz ROSC as input..... | 49 |
| Register 4-1. WDTCTL (Watchdog Timer Control, 0x4003 0000)..... | 50 |
| Register 4-2. WDTCDV (Watchdog Timer Count-Down Value, 0x4003 0004)..... | 51 |
| Register 4-3. WDTCTR (Watchdog Timer Counter, 0x4003 0008)..... | 51 |
| Register 5-1. GPTCTL (Real Time Clock Control, 0x4004 0000)..... | 54 |
| Register 5-2. GPTCDV (Real Time Clock Count-Down Value, 0x4004 0004)..... | 55 |
| Register 5-3. GPTCTR (Real Time Clock Counter, 0x4004 0008)..... | 55 |
| Register 6-1. GPIOAO (GPIO Port A Output, 0x4007 0000)..... | 57 |
| Register 6-2. GPIOAOE (GPIO Port A Output Enable, 0x4007 0004)..... | 58 |
| Register 6-3. GPIOADS (GPIO Port A Output Drive Strength, 0x4007 0008)..... | 58 |
| Register 6-4. GPIOARUP (GPIO Port A Weak Pull Up, 0x4007 000C)..... | 59 |
| Register 6-5. GPIOARDN (GPIO Port A Weak Pull Down, 0x4007 0010)..... | 60 |
| Register 6-6. GPIOAI (GPIO Port A Input, 0x4007 0014)..... | 60 |
| Register 6-7. GPIOAPSEL (GPIO Port A Peripheral Select, 0x4007 001C)..... | 61 |
| Register 6-8. GPIOAINTP (GPIO Port A Interrupt Polarity, 0x4007 0020)..... | 62 |
| Register 6-9. GPIOAINTEN (GPIO Port A Interrupt Enable, 0x4007 0024)..... | 62 |
| Register 6-10. GPIOAINT (GPIO Port A Interrupt, 0x4007 0028)..... | 63 |
| Register 6-11. GPIOAINTM (GPIO Port A Interrupt Mask, 0x4007 002C)..... | 64 |
| Register 7-1. GPIOBO (GPIO Port B Output, 0x4007 0040)..... | 67 |
| Register 7-2. GIOBOE (GPIO Port B Output Enable, 0x4007 0044)..... | 67 |
| Register 7-3. GPIOBDS (GPIO Port B Output Drive Strength, 0x4007 0048)..... | 68 |
| Register 7-4. GPIOBRUP (GPIO Port B Weak Pull Up, 0x4007 004C)..... | 68 |
| Register 7-5. GPIOBRDN (GPIO Port B Weak Pull Down, 0x4007 0050)..... | 69 |
| Register 7-6. GPIOBI (GPIO Port B Input, 0x4007 0054)..... | 69 |
| Register 7-7. GPIOBPSEL (GPIO Port B Peripheral Select, 0x4007 005C)..... | 69 |
| Register 7-8. GPGPIOBINTP (GPIO Port B Interrupt Polarity, 0x4007 0060)..... | 70 |
| Register 7-9. GPIOBINTEN (GPIO Port B Interrupt Enable, 0x4007 0064)..... | 71 |
| Register 7-10. GPIOBINT (GPIO Port B Interrupt, 0x4007 0068)..... | 71 |
| Register 7-11. GPIOBINTM (GPIO Port B Interrupt Mask, 0x4007 006C)..... | 72 |
| Register 8-1. GPIOCO (GPIO Port C Output, 0x4008 0000)..... | 75 |
| Register 8-2. GPIOCOE (GPIO Port C Output Enable, 0x4008 0004)..... | 76 |
| Register 8-3. GPIOCI (GPIO Port C Input, 0x4008 0018)..... | 76 |
| Register 8-4. GPIOCIE (GPIO Port C Input Enable, 0x4008 0014)..... | 77 |
| Register 8-5. GPIOCINTP (GPIO Port C Interrupt Polarity, 0x4008 0020)..... | 78 |
| Register 8-6. GPIOCINTEN (GPIO Port C Interrupt Enable, 0x4008 0024)..... | 78 |
| Register 8-7. GPIOCINT (GPIO Port C Interrupt, 0x4008 0028)..... | 79 |
| Register 8-8. GPIOCINTM (GPIO Port C Interrupt Mask, 0x4008 002C)..... | 79 |
| Register 9-1. GPIODO (GPIO Port D Output, 0x4008 0040)..... | 83 |
| Register 9-2. GPIODOE (GPIO Port D Output Enable, 0x4008 0044)..... | 84 |
| Register 9-3. GPIODDS (GPIO Port D Output Drive Strength, 0x4008 0048)..... | 84 |
| Register 9-4. GPIODRUP (GPIO Port D Weak Pull Up, 0x4008 004C)..... | 85 |
| Register 9-5. GPIODRDN (GPIO Port D Weak Pull Down, 0x4008 0050)..... | 86 |
| Register 9-6. GPIODI (GPIO Port D Input, 0x4008 0054)..... | 86 |
| Register 9-7. GPIODPSEL (GPIO Port D Peripheral Select, 0x4008 005C)..... | 87 |
| Register 9-8. GPIODINTP (GPIO Port D Interrupt Polarity, 0x4008 0060)..... | 88 |
| Register 9-9. GPIODINTEN (GPIO Port D Interrupt Enable, 0x4008 0064)..... | 88 |
| Register 9-10. GPIODINT (GPIO Port D Interrupt, 0x4008 0068)..... | 89 |

| | |
|--|-----|
| Register 9-11. GPIODINTM (GPIO Port D Interrupt Mask, 0x4008 006C)..... | 89 |
| Register 10-1. GPIOEO (GPIO Port E Output, 0x4009 0000)..... | 93 |
| Register 10-2. GPIOEOE (GPIO Port E Output Enable, 0x4009 0004)..... | 94 |
| Register 10-3. GPIOEDS (GPIO Port E Output Drive Strength, 0x4009 0008)..... | 94 |
| Register 10-4. GPIOERUP (GPIO Port E Weak Pull Up, 0x4009 000C)..... | 95 |
| Register 10-5. GPIOERDN (GPIO Port E Weak Pull Down, 0x4009 0010)..... | 96 |
| Register 10-6. GPIOEI (GPIO Port E Input, 0x4009 0014)..... | 96 |
| Register 10-7. GPIOEPSEL (GPIO Port E Peripheral Select, 0x4009 001C)..... | 97 |
| Register 10-8. GPIOEINTP (GPIO Port E Interrupt Polarity, 0x4009 0020)..... | 98 |
| Register 10-9. GPIOEINTEN (GPIO Port E Interrupt Enable, 0x4009 0024)..... | 98 |
| Register 10-10. GPIOEINT (GPIO Port E Interrupt, 0x4009 0028)..... | 99 |
| Register 10-11. GPIOEINTM (GPIO Port E Interrupt Mask, 0x4009 002C)..... | 99 |
| Register 11-1. TACTL (Timer A Control, 0x400D 0000)..... | 104 |
| Register 11-2. TAPRD (Timer A Period, 0x400D 0004)..... | 105 |
| Register 11-3. TACTR (Timer A Counter, 0x400D 0008)..... | 105 |
| Register 11-4. TACC0CTL (Timer A PWMA0 Capture and Compare Control, 0x400D 0040)..... | 105 |
| Register 11-5. TACC0CTR (Timer A PWMA0 Capture and Compare Counter, 0x400D 0044)..... | 105 |
| Register 11-6. TACC1CTL (Timer A PWMA1 Capture and Compare Control, 0x400D 0048)..... | 106 |
| Register 11-7. TACC1CTR (Timer A PWMA1 Capture and Compare Counter, 0x400D 004C)..... | 106 |
| Register 11-8. TACC2CTL (Timer A PWMA2 Capture and Compare Control, 0x400D 0050)..... | 106 |
| Register 11-9. TACC2CTR (Timer A PWMA2 Capture and Compare Counter, 0x400D 0054)..... | 107 |
| Register 11-10. TACC3CTL (Timer A PWMA3 Capture and Compare Control, 0x400D 0058)..... | 107 |
| Register 11-11. TACC3CTR (Timer A PWMA3 Capture and Compare Counter, 0x400D 005C)..... | 107 |
| Register 11-12. TACC4CTL (Timer A PWMA4 Capture and Compare Control, 0x400D 0060)..... | 107 |
| Register 11-13. TACC4CTR (Timer A PWMA4 Capture and Compare Counter, 0x400D 0064)..... | 108 |
| Register 11-14. TACC5CTL (Timer A PWMA5 Capture and Compare Control, 0x400D 0068)..... | 108 |
| Register 11-15. TACC5CTR (Timer A PWMA5 Capture and Compare Counter, 0x400D 006C)..... | 108 |
| Register 11-16. TACC6CTL (Timer A PWMA6 Capture and Compare Control, 0x400D 0070)..... | 109 |
| Register 11-17. TACC6CTR (Timer A PWMA6 Capture and Compare Counter, 0x400D 0074)..... | 109 |
| Register 11-18. TACC7CTL (Timer A PWMA7 Capture and Compare Control, 0x400D 0078)..... | 109 |
| Register 11-19. TACC7CTR (Timer A PWMA7 Capture and Compare Counter, 0x400D 007C)..... | 110 |
| Register 11-20. DTGA0CTL (Timer A Dead Time Generator 0 Control, 0x400D 00A0)..... | 110 |
| Register 11-21. DTGA0LED (Timer A Dead Time Generator 0 Leading Edge Delay, 0x400D 00A4)..... | 110 |
| Register 11-22. DTGA0TED (Timer A Dead Time Generator 0 Trailing Edge Delay, 0x400D 00A8)..... | 110 |
| Register 11-23. DTGA1CTL (Timer A Dead Time Generator 1 Control, 0x400D 00B0)..... | 111 |
| Register 11-24. DTGA1LED (Timer A Dead Time Generator 1 Leading Edge Delay, 0x400D 00B4)..... | 111 |
| Register 11-25. DTGA1TED (Timer A Dead Time Generator 1 Trailing Edge Delay, 0x400D 00B8)..... | 111 |
| Register 11-26. DTGA2CTL (Timer A Dead Time Generator 2 Control, 0x400D 00C0)..... | 111 |
| Register 11-27. DTGA2LED (Timer A Dead Time Generator 2 Leading Edge Delay, 0x400D 00C4)..... | 112 |
| Register 11-28. DTGA2TED (Timer A Dead Time Generator 2 Trailing Edge Delay, 0x400D 00C8)..... | 112 |
| Register 11-29. DTGA3CTL (Timer A Dead Time Generator 3 Control, 0x400D 00D0)..... | 112 |
| Register 11-30. DTGA3LED (Timer A Dead Time Generator 3 Leading Edge Delay, 0x400D 00D4)..... | 113 |
| Register 11-31. DTGA3TED (Timer A Dead Time Generator 3 Trailing Edge Delay, 0x400D 00D8)..... | 113 |
| Register 12-1. TBCTL (Timer B Control, 0x400E 0000)..... | 121 |
| Register 12-2. TBPRD (Timer B Period, 0x400E 0004)..... | 122 |
| Register 12-3. TBCTR (Timer B Counter, 0x400E 0008)..... | 122 |
| Register 12-4. TBCC0CTL (Timer B PWMB0 Capture and Compare Control, 0x400E 0040)..... | 122 |
| Register 12-5. TBCC0CTR (Timer B PWMB0 Capture and Compare Counter, 0x400E 0044)..... | 123 |
| Register 12-6. TBCC1CTL (Timer B PWMB1 Capture and Compare Control, 0x400E 0048)..... | 123 |
| Register 12-7. TBCC1CTR (Timer B PWMB1 Capture and Compare Counter, 0x400E 004C)..... | 123 |
| Register 12-8. TBCC2CTL (Timer B PWMB2 Capture and Compare Control, 0x400E 0050)..... | 124 |
| Register 12-9. TBCC2CTR (Timer B PWMB2 Capture and Compare Counter, 0x400E 0054)..... | 124 |
| Register 12-10. TBCC3CTL (Timer B PWMB3 Capture and Compare Control, 0x400E 0058)..... | 124 |
| Register 12-11. TBCC3CTR (Timer B PWMB3 Capture and Compare Counter, 0x400E 005C)..... | 125 |

| | |
|--|-----|
| Register 12-12. DTGB0CTL (Timer B Dead Time Generator 0 Control, 0x400E 00A0)..... | 125 |
| Register 12-13. DTGB0LED (Timer B Dead Time Generator 0 Leading Edge Delay, 0x400E 00A4)..... | 125 |
| Register 12-14. DTGB0TED (Timer B Dead Time Generator 0 Trailing Edge Delay, 0x400E 00A8)..... | 126 |
| Register 13-1. TCCTL (Timer C Control, 0x400F 0000)..... | 134 |
| Register 13-2. TCPRD (Timer C Period, 0x400F 0004)..... | 135 |
| Register 13-3. TCCTR (Timer C Counter, 0x400F 0008)..... | 135 |
| Register 13-4. TCCC0CTL (Timer C PWMCO Capture and Compare Control, 0x400F 0040)..... | 135 |
| Register 13-5. TCCC0CTR (Timer C PWMCO Capture and Compare Counter, 0x400F 0044)..... | 136 |
| Register 13-6. TCCC1CTL (Timer C PWMC1 Capture and Compare Control, 0x400F 0048)..... | 136 |
| Register 13-7. TCCC1CTR (Timer C PWMC1 Capture and Compare Counter, 0x400F 004C)..... | 136 |
| Register 13-8. DTGC0CTL (Timer C Dead Time Generator 0 Control, 0x400F 00A0)..... | 137 |
| Register 13-9. DTGC0LED (Timer C Dead Time Generator 0 Leading Edge Delay, 0x400F 00A4)..... | 137 |
| Register 13-10. DTGC0TED (Timer C Dead Time Generator 0 Trailing Edge Delay, 0x400F 00A8)..... | 137 |
| Register 14-1. TDCTL (Timer D Control, 0x4010 0000)..... | 145 |
| Register 14-2. TDPRD (Timer D Period, 0x4010 0004)..... | 146 |
| Register 14-3. TDCTR (Timer D Counter, 0x4010 0008)..... | 146 |
| Register 14-4. TDCC0CTL (Timer D PWMD0 Capture and Compare Control, 0x4010 0040)..... | 146 |
| Register 14-5. TDCC0CTR (Timer D PWMD0 Capture and Compare Counter, 0x4010 0044)..... | 147 |
| Register 14-6. TDCC1CTL (Timer D PWMD1 Capture and Compare Control, 0x4010 0048)..... | 147 |
| Register 14-7. TDCC1CTR (Timer D PWMD1 Capture and Compare Counter, 0x4010 004C)..... | 147 |
| Register 14-8. DTGD0CTL (Timer D Dead Time Generator 0 Control, 0x4010 00A0)..... | 148 |
| Register 14-9. DTGD0LED (Timer D Dead Time Generator 0 Leading Edge Delay, 0x4010 00A4)..... | 148 |
| Register 14-10. DTGD0TED (Timer D Dead Time Generator 0 Trailing Edge Delay, 0x4010 00A8)..... | 148 |
| Register 15-1. FLASHLOCK (FLASH Lock, 0x4002 0000)..... | 155 |
| Register 15-2. FLASHSTATUS (FLASH Status, 0x4002 0004)..... | 156 |
| Register 15-3. FLASHPAGE (FLASH Page Selector, 0x4002 0008)..... | 156 |
| Register 15-4. FLASHPERASE (FLASH Page Erase, 0x4002 0014)..... | 157 |
| Register 15-5. SWDACCESS (SDW Access Status, 0x4002 0024)..... | 157 |
| Register 15-6. FLASHWSTATE (FLASH Access Wait State, 0x4002 0028)..... | 157 |
| Register 15-7. FLASHBWRITER (Buffered FLASH Write, 0x4002 002C)..... | 157 |
| Register 15-8. FLASHBWDATA (Buffered FLASH Write Data, 0x4002 0030)..... | 158 |
| Register 16-1. EMUXCTL (ADC external MUX control register 0x4015 0000)..... | 163 |
| Register 16-2. EMUXDATA (EMUX data register 0x4015 0004)..... | 164 |
| Register 16-3. ADCCTL (ADC control register 0x4015 0008)..... | 164 |
| Register 16-4. ADCCR (ADC conversion result register 0x4015 000C)..... | 165 |
| Register 16-5. ADCINT (ADC Interrupt register 0x4015 0010)..... | 165 |
| Register 16-6. AS0CTL (Auto Sequencer 0 control register 0x4015 0040)..... | 166 |
| Register 16-7. AS0S0 (Auto sequencer 0-sample 0 control 0x4015 0044)..... | 167 |
| Register 16-8. AS0R0 (Auto sequencer 0-sample 0 result register 0x4015 0048)..... | 167 |
| Register 16-9. AS0S1 (Auto sequencer 0-sample 1 control 0x4015 004C)..... | 168 |
| Register 16-10. AS0R1 (Auto sequencer 0-sample 1 result register 0x4015 0050)..... | 168 |
| Register 16-11. AS0S2 (Auto sequencer 0-sample 2 control 0x4015 0054)..... | 168 |
| Register 16-12. AS0R2 (Auto sequencer 0-sample 2 result register 0x4015 0058)..... | 169 |
| Register 16-13. AS0S3 (Auto sequencer 0-sample 3 control 0x4015 005C)..... | 169 |
| Register 16-14. AS0R3 (Auto sequencer 0-sample 3 result register 0x4015 0060)..... | 169 |
| Register 16-15. AS0S4 (Auto sequencer 0-sample 4 control 0x4015 0064)..... | 170 |
| Register 16-16. AS0R4 (Auto sequencer 0-sample 4 result register 0x4015 0068)..... | 170 |
| Register 16-17. AS0S5 (Auto sequencer 0-sample 5 control 0x4015 006C)..... | 170 |
| Register 16-18. AS0R5 (Auto sequencer 0-sample 5 result register 0x4015 0070)..... | 171 |
| Register 16-19. AS0S6 (Auto sequencer 0-sample 6 control 0x4015 0074)..... | 171 |
| Register 16-20. AS0R6 (Auto sequencer 0-sample 6 result register 0x4015 0078)..... | 171 |
| Register 16-21. AS0S7 (Auto sequencer 0-sample 7 control 0x4015 007C)..... | 172 |
| Register 16-22. AS0R7 (Auto sequencer 0-sample 7 result register 0x4015 0080)..... | 172 |
| Register 16-23. AS1CTL (Auto Sequencer 1 control register 0x4015 0100)..... | 172 |

| | |
|---|-----|
| Register 16-24. AS1S0 (Auto sequencer 1-sample 0 control 0x4015 0104)..... | 173 |
| Register 16-25. AS1R0 (Auto sequencer 1-sample 0 result register 0x4015 0108)..... | 174 |
| Register 16-26. AS1S1 (Auto sequencer 1-sample 1 control 0x4015 010C)..... | 174 |
| Register 16-27. AS1R1 (Auto sequencer 1-sample 1 result register 0x4015 0110)..... | 174 |
| Register 16-28. AS1S2 (Auto sequencer 1-sample 2 control 0x4015 0114)..... | 174 |
| Register 16-29. AS1R2 (Auto sequencer 1-sample 2 result register 0x4015 0118)..... | 175 |
| Register 16-30. AS1S3 (Auto sequencer 1-sample 3 control 0x4015 011C)..... | 175 |
| Register 16-31. AS1R3 (Auto sequencer 1-sample 3 result register 0x4015 0120)..... | 176 |
| Register 16-32. AS1S4 (Auto sequencer 1-sample 4 control 0x4015 0124)..... | 176 |
| Register 16-33. AS1R4 (Auto sequencer 1-sample 4 result register 0x4015 0128)..... | 176 |
| Register 16-34. AS1S5 (Auto sequencer 1-sample 5 control 0x4015 012C)..... | 176 |
| Register 16-35. AS1R5 (Auto sequencer 1-sample 5 result register 0x4015 0130)..... | 177 |
| Register 16-36. AS1S6 (Auto sequencer 1-sample 6 control 0x4015 0134)..... | 177 |
| Register 16-37. AS1R6 (Auto sequencer 1-sample 6 result register 0x4015 0138)..... | 178 |
| Register 16-38. AS1S7 (Auto sequencer 1-sample 7 control 0x4015 013C)..... | 178 |
| Register 16-39. AS1R7 (Auto sequencer 1-sample 7 result register 0x4015 0140)..... | 178 |
| Register 17-1. I2CCFG (I2C Configuration, 0x401B 0000)..... | 185 |
| Register 17-2. I2CINT (I2C Interrupt, 0x401B 0004)..... | 185 |
| Register 17-3. I2CINTEN (I2C Interrupt Enable, 0x401B 0008)..... | 187 |
| Register 17-4. I2CMACTL (I2C Master Access Control, 0x401B 0030)..... | 187 |
| Register 17-5. I2CMARXDATA (I2C Master Receive Data, 0x401B 0034)..... | 188 |
| Register 17-6. I2CMATXDATA (I2C Master Transmit Data, 0x401B 0038)..... | 188 |
| Register 17-7. I2CBAUD (I2C Baud Rate, 0x401B 0040)..... | 188 |
| Register 17-8. I2CSLRXDATA (I2C Slave Receive Data, 0x401B 0070)..... | 188 |
| Register 17-9. I2CSLTXDATA (I2C Slave Transmit Data, 0x401B 0074)..... | 189 |
| Register 17-10. I2CSLADDR (I2C Slave Address, 0x401B 0074)..... | 189 |
| Table 17-11. I2CBAUD settings for different HCLK..... | 190 |
| Register 18-1. UARTRXTX (UART Receive/Transmit FIFO, 0x401D 0000)..... | 192 |
| Register 18-2. UARTIEN (UART Interrupt Enable, 0x401D 0004)..... | 193 |
| Register 18-3. UARTII (UART Interrupt Identification, 0x401D 0008)..... | 193 |
| Register 18-4. UARTELC (UART Line Control, 0x401D 000C)..... | 194 |
| Register 18-5. UARTLS (UART Line Status, 0x401D 0014)..... | 194 |
| Register 18-6. UARTFCTL (FIFO Control, 0x401D 0020)..... | 195 |
| Register 18-7. UARTIEN (UART Interrupt Enable, 0x401D 0024)..... | 195 |
| Register 18-8. UARTDL_L (UART Divisor Latch Low Byte, 0x401D 0028)..... | 195 |
| Register 18-9. UARTDL_H (UART Divisor Latch High Byte, 0x401D 002C)..... | 196 |
| Register 18-10. UARTFD_F (UART Fractional Divisor Value, 0x401D 0038)..... | 196 |
| Register 18-11. UARTFSTAT (UART FIFO Status, 0x401D 0040)..... | 196 |
| Register 18-12. UART Divisor Settings for 50 MHz HCLK..... | 198 |
| Register 19-1. SOCBCTL (SOC Bus Bridge Control, 0x4020 0000)..... | 200 |
| Register 19-2. SOCBCFG (SOC Bus Bridge Configuration, 0x4020 0004)..... | 200 |
| Register 19-3. SOCBCLK (SOC Bus Bridge Clock Divider, 0x4020 0008)..... | 201 |
| Register 19-4. SOCBSTAT (SOC Bus Bridge Status, 0x4020 0014)..... | 201 |
| Register 19-5. SOCBBD (SOC Bus Bridge Data, 0x4020 001C)..... | 202 |
| Register 19-6. SOCBINT_EN (SOC Bus Bridge Interrupt Enable, 0x4020 0020)..... | 203 |
| Register 20-1. SPICTL (SPI Control, 0x4021 0000)..... | 206 |
| Register 20-2. SPICFG (SPI Configuration, 0x4021 0004)..... | 207 |
| Register 20-3. SPICLKDIV (SPI Clock Divider, 0x4021 0008)..... | 208 |
| Register 20-4. SPISTAT (SPI Status, 0x4021 0014)..... | 208 |
| Register 20-5. SPICSSTR (SPI Chip Select Steering, 0x4021 0018)..... | 210 |
| Register 20-6. SPID (SPI Data, 0x4021 001C)..... | 210 |
| Register 20-7. SPIINT_EN (SPI Interrupt Enable, 0x4021 0020)..... | 211 |
| Register 21-1. SOC.SYSSTAT (Analog System Status, SOC 0x00)..... | 217 |
| Register 21-2. SOC.PWRCTL (Power Control, SOC 0x10)..... | 218 |

| | |
|--|-----|
| Register 21-3. SOC.PWRSTAT (Power Manager Status, Persistent In Hibernate mode, SOC 0x11)..... | 218 |
| Register 21-4. SOC.PWRSTATCFG (Power Status Configuration, SOC 0x12)..... | 219 |
| Register 21-5. SOC.SCFG (Power Switcher Configuration, SOC 0x14)..... | 219 |
| Register 21-6. SOC.PWRCFG (Power Status Configuration, SOC 0x15)..... | 220 |
| Register 22-1. SOC.AIO0CFG (AIO0 Configuration, SOC 0x20)..... | 221 |
| Register 22-2. SOC.AIO1CFG (AIO1 Configuration, SOC 0x21)..... | 222 |
| Register 22-3. SOC.AIO2CFG (AIO2 Configuration, SOC 0x22)..... | 223 |
| Register 22-4. SOC.AIO3CFG (AIO3 Configuration, SOC 0x23)..... | 224 |
| Register 22-5. SOC.AIO4CFG (AIO4 Configuration, SOC 0x24)..... | 225 |
| Register 22-6. SOC.AIO5CFG (AIO5 Configuration, SOC 0x25)..... | 226 |
| Register 22-7. SOC.AIO6CFG (AIO6 Configuration, SOC 0x26)..... | 227 |
| Register 22-8. SOC.AIO7CFG (AIO7 Configuration, SOC 0x27)..... | 229 |
| Register 22-9. SOC.AIO8CFG (AIO8 Configuration, SOC 0x28)..... | 230 |
| Register 22-10. SOC.AIO9CFG (AIO9 Configuration, SOC 0x29)..... | 232 |
| Register 22-11. SOC.SMCFG (Signal Manager Configuration, SOC 0x2A)..... | 233 |
| Register 22-12. SOC.HPDAC (HPDAC Setting, SOC 0x2B)..... | 234 |
| Register 22-13. SOC.LPDAC0 (LPDAC Setting [9:2], SOC 0x2C)..... | 234 |
| Register 22-14. SOC.LPDAC1 (LPDAC Setting [1:0], SOC 0x2C)..... | 234 |
| Register 22-15. SOC.ADCSCANCFG (ADCSCAN Configuration, SOC 0x2E)..... | 234 |
| Register 22-16. SOC.ADMUX (AD Mux Selector, SOC 0x2F)..... | 235 |
| Register 22-17. SOC.PROTINTEN (Protection Interrupt Enable, SOC 0x30)..... | 235 |
| Register 22-18. SOC.PROTINT (Protection Interrupt, SOC 0x31)..... | 236 |
| Register 22-19. SOC.AIOOUT0 (AIO Digital Output, SOC 0x32)..... | 236 |
| Register 22-20. SOC.AIOOUT0 (AIO Digital Output, SOC 0x33)..... | 237 |
| Register 22-21. SOC.AIOIN0 (AIO Digital Input, SOC 0x34)..... | 237 |
| Register 22-22. SOC.AIOIN1 (AIO Digital Input 1, SOC 0x35)..... | 238 |
| Register 22-23. SOC.AIOINTEN (AIO6,7,8,9 Interrupt Enable, SOC 0x36)..... | 238 |
| Register 22-24. SOC.AIOINT (AIO6,7,8,9 Interrupt, SOC 0x37)..... | 238 |
| Register 22-25. SOC.SMCTL (Signal Manager Control SOC 0x38)..... | 239 |
| Register 22-26. SOC.AIOIN0 (AIO Digital Input, SOC 0x34)..... | 266 |
| Register 23-1. SOC.PRCTL (PR1, PR2 Control, SOC 0x61)..... | 269 |
| Register 23-2. SOC.OMOUT (OM0/2/4 Output, SOC 0x64)..... | 269 |
| Register 23-3. SOC.DRVCTL (Application Specific Power Driver Control, SOC 0x66)..... | 270 |
| Register 23-4. SOC.PROTCTL (PROT Control, SOC 0x67)..... | 270 |

LIST OF FIGURES

| | |
|--|-----|
| Figure 2-1. Memory Map..... | 32 |
| Figure 3-1. System Clock Control..... | 47 |
| Figure 4-1. WDT..... | 52 |
| Figure 5-1. GPT..... | 56 |
| Figure 6-1. GPIO Port A..... | 65 |
| Figure 7-1. GPIO Port B..... | 73 |
| Figure 8-1. GPIO Port C..... | 81 |
| Figure 9-1. GPIO Port D..... | 91 |
| Figure 10-1. GPIO Port E..... | 101 |
| Figure 11-1. Timer A..... | 114 |
| Figure 11-2. PWMA[x] and PWMA[x+4] Example Using Timer A Up Mode and Up/Down Mode..... | 117 |
| Figure 11-3. CA[x] and CA[x+4] Capture Example..... | 117 |
| Figure 11-4. DTGAX Bypass Example..... | 118 |
| Figure 11-5. DTGAX Bypass and Inverting LS Example..... | 119 |
| Figure 11-6. DTGAX LED and TED Example..... | 119 |
| Figure 11-7. DTGAX LED and TED with On Time Preservation Example..... | 120 |
| Figure 12-1. Timer B..... | 127 |
| Figure 12-2. PWMB0 and PWMB1 Example Using Timer B Up Mode and Up/Down Mode..... | 130 |
| Figure 12-3. CB0 and CB1 Capture Example..... | 130 |
| Figure 12-4. DTGB0 Bypass Example..... | 131 |
| Figure 12-5. DTGB0 Bypass and Inverting LS Example..... | 132 |
| Figure 12-6. DTGB0 LED and TED Example..... | 132 |
| Figure 12-7. DTGB0 LED and TED with On Time Preservation Example..... | 133 |
| Figure 13-1. Timer C..... | 138 |
| Figure 13-2. PWMC0 and PWMC1 Example Using Timer C Up Mode and Up/Down Mode..... | 141 |
| Figure 13-3. CC0 and CC1 Capture Example..... | 141 |
| Figure 13-4. DTGC0 Bypass Example..... | 142 |
| Figure 13-5. DTGC0 Bypass and Inverting LS Example..... | 143 |
| Figure 13-6. DTGC0 LED and TED Example..... | 143 |
| Figure 13-7. DTGC0 LED and TED with On Time Preservation Example..... | 144 |
| Figure 14-1. Timer D..... | 149 |
| Figure 14-2. PWMD0 and PWMD1 Example Using Timer D Up Mode and Up/Down Mode..... | 151 |
| Figure 14-3. CD0 and CD1 Capture Example..... | 152 |
| Figure 14-4. DTGD0 Bypass Example..... | 153 |
| Figure 14-5. DTGD0 Bypass and Inverting LS Example..... | 153 |
| Figure 14-6. DTGD0 LED and TED Example..... | 154 |
| Figure 14-7. DTGD0 LED and TED with On Time Preservation Example..... | 154 |
| Figure 15-1. FLASH Memory Controller..... | 159 |
| Figure 16-1. ADC, EMUX, ASC0, ASC1..... | 179 |
| Figure 16-2. ADC Conversion (Single Shot)..... | 180 |
| Figure 16-3. ADC Conversion (Repeat Mode)..... | 180 |
| Figure 16-4. ASCx, ADCCTL.ADCMODE = 001b, 010b, 100b, 101b..... | 181 |
| Figure 16-5. ASCx, ADCCTL.ADCMODE = 011b, 110b..... | 181 |
| Figure 16-6. ASCx, ADCCTL.ADCMODE = 111b..... | 182 |
| Figure 16-7. ASxSy Sample with ASxSy.EMUXS = 00b and ASxSy.DELAY = 11b..... | 182 |
| Figure 16-8. ASxSy Sample with ASxSy.EMUXS = 01b and ASxSy.DELAY = 11b..... | 183 |
| Figure 16-9. ASxSy Sample with ASxSy.EMUXS = 10b and ASxSy.DELAY = 11b..... | 183 |
| Figure 16-10. ASCx, 8 samples, No Collision..... | 183 |
| Figure 16-11. ASCx 8 samples, Collision..... | 184 |
| Figure 16-12. ASC0 8 samples, ASC1 4 samples, Collision..... | 184 |
| Figure 17-1. I2C..... | 190 |

| | |
|---|-----|
| Figure 18-1. UART..... | 197 |
| Figure 19-1. SOC Bridge..... | 204 |
| Figure 19-2. Single Read from SOC Bridge..... | 205 |
| Figure 19-3. Single Write to SOC Bridge..... | 205 |
| Figure 20-1. SPI..... | 212 |
| Figure 20-2. SPI clock polarity and phase..... | 213 |
| Figure 20-3. SPIMOSI early transmit in master mode..... | 214 |
| Figure 20-4. SPIMISO early transmit in slave mode..... | 214 |
| Figure 20-5. SPICSx..... | 215 |
| Figure 22-1. Configurable Analog Front End..... | 240 |
| Figure 22-2. AIO1, AIO0..... | 241 |
| Figure 22-3. AIO3, AIO2..... | 244 |
| Figure 22-4. AIO5, AIO4..... | 247 |
| Figure 22-5. AIO6..... | 250 |
| Figure 22-6. AIO7..... | 254 |
| Figure 22-7. AIO8..... | 258 |
| Figure 22-8. AIO9..... | 262 |
| Figure 22-9. EMUX..... | 266 |
| Figure 22-10. EMUX Timing..... | 267 |
| Figure 23-1. Application Specific Power Driver..... | 271 |
| Figure 23-2. OM0..... | 272 |
| Figure 23-3. OM2..... | 273 |
| Figure 23-4. OM4..... | 274 |
| Figure 23-5. ENHS1 Protection..... | 275 |
| Figure 23-6. ENHS2 Protection..... | 276 |
| Figure 24-1. Cortex-M0 implementation..... | 277 |
| Figure 24-2. Core Registers..... | 280 |
| Figure 24-3. PSR..... | 281 |
| Figure 24-4. PRIMASK..... | 284 |
| Figure 1-6. CONTROL..... | 284 |
| Figure 24-5. CONTROL..... | 284 |
| Figure 24-6. Memory Map..... | 287 |
| Figure 24-7. Memory Ordering Restrictions..... | 288 |
| Figure 24-8. Little Endian Format..... | 291 |
| Figure 24-9. Vector Table..... | 294 |
| Figure 24-10. Exception Entry Stack Contents..... | 296 |
| Figure 24-11. ASR #3..... | 304 |
| Figure 24-12. LSR #3..... | 305 |
| Figure 24-13. LSL #3..... | 306 |
| Figure 24-14. ROR #3..... | 306 |
| Figure 24-15. ISER..... | 340 |
| Figure 24-16. ICER..... | 341 |
| Figure 24-17. ISPR..... | 341 |
| Figure 24-18. ICPR..... | 342 |
| Figure 24-19. IPR..... | 343 |
| Figure 24-20. CPUID..... | 346 |
| Figure 24-21. ICSR..... | 347 |
| Figure 24-22. AIRCR..... | 348 |
| Figure 24-23. SCR..... | 349 |
| Figure 24-24. CCR..... | 350 |
| Figure 24-25. SHPR2..... | 351 |
| Figure 24-26. SHPR3..... | 351 |
| Figure 24-27. SYST_CSR..... | 353 |
| Figure 24-28. SYST_RVR..... | 353 |

| | |
|-------------------------------|-----|
| Figure 24-29. SYST_CVR..... | 354 |
| Figure 24-30. SYST_CALIB..... | 354 |

1. STYLES AND FORMATTING CONVENTIONS

1.1. Overview

This chapter describes formatting and styles used through the document.

1.2. Number Representation

Numbers in a base other than decimal have a prefix or postfix as indicator. All numbers use little endian formatting, most significant bit/digit is to the left. Digits for binary and hexadecimal representation are grouped with a single space every four digits to improve readability. Binary numbers use “b” as postfix, hexadecimal numbers use “0x” as prefix.

For example 1011b binary = 0xB hexadecimal = 11 decimal.


1.3. Formatting Styles

| TYPE | EXAMPLE | DESCRIPTION |
|--------------------------------------|---------------------------------------|--|
| Register Name | RTCCTL | Register names use capital letter and bold formatting. |
| Register Bit(s) | RTCCTL.RTCCLKDIV | Register bits are always represented with the register name separated with a period |
| Function selected by Register bit(s) | [RTCCTL.RTCCLKDIV] | Within text blocks, functions selected with a register bit setting are set in brackets. For example [RTCCTL.RTCCLKDIV] means divider settings /2 to /65536. |
| Pin Function | XIN | Pin functions use capital letters |
| Formulas | CLK = FCLK / DIV | Formulas use Teletype font. |
| Links | Number Representation | Clickable Links are underlined and blue |
| CPU Mnemonic | MRS | CPU Mnemonic use Teletype font. |
| Operands | {Rd, } Rn, Rm | Operands use Italic |
| Code examples | B loopA | Code examples use Teletype font. |

2. MEMORY AND REGISTER MAP

2.1. Memory Map

Figure 2-1. Memory Map



2.2. Register Map

Table 2-1. Embedded FLASH Register Map

| ADDRESS | NAME | DESCRIPTION |
|---------------------------|------------------|----------------|
| Embedded FLASH | | |
| 0x0000 0000 – 0x0000 03FF | EFLASHP0 | EFLASH page 0 |
| 0x0000 0400 – 0x0000 07FF | EFLASHP1 | EFLASH page 1 |
| 0x0000 0800 – 0x0000 0BFF | EFLASHP2 | EFLASH page 2 |
| 0x0000 0C00 – 0x0000 0FFF | EFLASHP3 | EFLASH page 3 |
| 0x0000 1000 – 0x0000 13FF | EFLASHP4 | EFLASH page 4 |
| 0x0000 1400 – 0x0000 17FF | EFLASHP5 | EFLASH page 5 |
| 0x0000 1800 – 0x0000 1BFF | EFLASHP6 | EFLASH page 6 |
| 0x0000 1C00 – 0x0000 1FFF | EFLASHP7 | EFLASH page 7 |
| 0x0000 2000 – 0x0000 23FF | EFLASHP8 | EFLASH page 8 |
| 0x0000 2400 – 0x0000 27FF | EFLASHP9 | EFLASH page 9 |
| 0x0000 2800 – 0x0000 2BFF | EFLASHP10 | EFLASH page 10 |
| 0x0000 2C00 – 0x0000 2FFF | EFLASHP11 | EFLASH page 11 |
| 0x0000 3000 – 0x0000 33FF | EFLASHP12 | EFLASH page 12 |
| 0x0000 3400 – 0x0000 37FF | EFLASHP13 | EFLASH page 13 |
| 0x0000 3800 – 0x0000 3BFF | EFLASHP14 | EFLASH page 14 |
| 0x0000 3C00 – 0x0000 3FFF | EFLASHP15 | EFLASH page 15 |
| 0x0000 4000 – 0x0000 43FF | EFLASHP16 | EFLASH page 16 |
| 0x0000 4400 – 0x0000 47FF | EFLASHP17 | EFLASH page 17 |
| 0x0000 4800 – 0x0000 4BFF | EFLASHP18 | EFLASH page 18 |
| 0x0000 4C00 – 0x0000 4FFF | EFLASHP19 | EFLASH page 19 |
| 0x0000 5000 – 0x0000 53FF | EFLASHP20 | EFLASH page 20 |
| 0x0000 5400 – 0x0000 57FF | EFLASHP21 | EFLASH page 21 |
| 0x0000 5800 – 0x0000 5BFF | EFLASHP22 | EFLASH page 22 |
| 0x0000 5C00 – 0x0000 5FFF | EFLASHP23 | EFLASH page 23 |
| 0x0000 6000 – 0x0000 63FF | EFLASHP24 | EFLASH page 24 |
| 0x0000 6400 – 0x0000 67FF | EFLASHP25 | EFLASH page 25 |
| 0x0000 6800 – 0x0000 6BFF | EFLASHP26 | EFLASH page 26 |
| 0x0000 6C00 – 0x0000 6FFF | EFLASHP27 | EFLASH page 27 |
| 0x0000 7000 – 0x0000 73FF | EFLASHP28 | EFLASH page 28 |
| 0x0000 7400 – 0x0000 77FF | EFLASHP29 | EFLASH page 29 |
| 0x0000 7800 – 0x0000 7BFF | EFLASHP30 | EFLASH page 30 |
| 0x0000 7C00 – 0x0000 7FFF | EFLASHP31 | EFLASH page 31 |

Table 2-2. ROM Register Map

| ADDRESS | NAME | DESCRIPTION |
|---------------------------|-----------------|--|
| INFO ROM | | |
| 0x0010 0000 – 0x0010 000F | Reserved | Reserved |
| 0x0010 0010 | ROSC11 | ROSC frequency in Hz at 11b setting |
| 0x0010 0014 | ROSC10 | ROSC frequency in Hz at 10b setting |
| 0x0010 0018 | ROSC01 | ROSC frequency in Hz at 01b setting |
| 0x0010 001C | ROSC00 | ROSC frequency in Hz at 00b setting |
| 0x0010 0020 | VREF | 2.5V Voltage reference in mV |
| 0x0010 0022 | ADCGAIN | ADC gain in mV |
| 0x0010 0024 | ADCOFF | AD offset in mV |
| 0x0010 0026 | Reserved | Reserved |
| 0x0010 0028 | FTTEMP | Test temperature for internal temp sensor in °C |
| 0x0010 002A | TEMPS | Internal temp sensor reading at FTTEMP temperature in AD count |
| 0x0010 002C | CLKREF | 4MHz CLKREF frequency in Hz |
| 0x0010 0030 – 0x0010 003B | Reserved | Reserved |
| 0x0010 003C | PKGDC | Package topside date code |
| 0x0010 0040 | DIEREV | Die revision |
| 0x0010 0044 | PACIDR | PAC part number and rev |
| 0x0010 0048 – 0x0010 004E | Reserved | Reserved |
| 0x0010 004F | CHKSUM | 8-bit CRC checksum of address 0x0010 0000 to 0x0010 004E |
| 0x0010 0050 – 0x0010 00FF | Reserved | Reserved |
| DATA ROM | | |
| 0x0020 0400 – 0x0020 7FFF | ROM | ROM Area |

Table 2-3. System Clock Control Register Map

| ADDRESS | NAME | DESCRIPTION |
|-----------------------------|----------------|-------------------------|
| System Clock Control | | |
| 0x4000 0000 | SCCTL | System clock control |
| 0x4000 0004 | PLLCTL | PLL control |
| 0x4000 0008 | ROSCCTL | Ring oscillator control |
| 0x4000 000C | XTALCTL | Crystal driver control |

Table 2-4. FLASH Memory Controller Register Map

| ADDRESS | NAME | DESCRIPTION |
|--------------------------------|--------------------|---------------------------------------|
| FLASH Memory Controller | | |
| 0x4002 0000 | FLASHLOCK | FLASH lock |
| 0x4002 0004 | FLASHSTATUS | FLASH status |
| 0x4002 0008 | FLASHPAGE | FLASH page selection |
| 0x4002 000C | Reserved | Reserved |
| 0x4002 0010 | Reserved | Reserved |
| 0x4002 0014 | FLASHPERASE | FLASH page erase |
| 0x4002 0018 | Reserved | Reserved |
| 0x4002 001C | Reserved | Reserved |
| 0x4002 0020 | Reserved | Reserved |
| 0x4002 0024 | SWDACCESS | SWD access control |
| 0x4002 0028 | FLASHWSTATE | FLASH wait state control |
| 0x4002 002C | FLASHBWRITE | FLASH buffered write enable |
| 0x4002 0030 | FLASHBWDATA | FLASH buffered write data and address |

Table 2-5. Watchdog Timer Register Map

| ADDRESS | NAME | DESCRIPTION |
|-----------------------|---------------|---------------------------------|
| Watchdog Timer | | |
| 0x4003 0000 | WDTCTL | Watchdog timer control |
| 0x4003 0004 | WDTCDV | Watchdog timer count-down value |
| 0x4003 0008 | WDTCTR | Watchdog timer counter |

Table 2-6. General Purpose Timer Register Map

| ADDRESS | NAME | DESCRIPTION |
|------------------------|---------------|--|
| Real Time Clock | | |
| 0x4004 0000 | GPTCTL | General purpose timer control |
| 0x4004 0004 | GPTCDV | General purpose timer count-down value |
| 0x4004 0008 | GPTCTR | General purpose timer counter |

Table 2-7. GPIO Port A Register Map

| ADDRESS | NAME | DESCRIPTION |
|--------------------|-------------------|---------------------------------------|
| GPIO Port A | | |
| 0x4007 0000 | GPIOAO | GPIO Port A output |
| 0x4007 0004 | GPIOAOE | GPIO Port A output enable |
| 0x4007 0008 | GPIOADS | GPIO Port A output drive strength |
| 0x4007 000C | GPIOAORUP | GPIO Port A output weak pull up |
| 0x4007 0010 | GPIOAORDN | GPIO Port A output weak pull down |
| 0x4007 0014 | GPIOAI | GPIO Port A input |
| 0x4007 0018 | Reserved | Reserved |
| 0x4007 001C | GPIOAPSEL | GPIO Port A peripheral select |
| 0x4007 0020 | GPIOAINTP | GPIO Port A interrupt polarity select |
| 0x4007 0024 | GPIOAINTEN | GPIO Port A interrupt enable select |
| 0x4007 0028 | GPIOAINT | GPIO Port A interrupt flag |
| 0x4007 002C | GPIOAINTM | GPIO Port A interrupt mask |

Table 2-8. GPIO Port B Register Map

| ADDRESS | NAME | DESCRIPTION |
|--------------------|-------------------|---------------------------------------|
| GPIO Port B | | |
| 0x4007 0040 | GPIOBO | GPIO Port B output |
| 0x4007 0044 | GPIOBOE | GPIO Port B output enable |
| 0x4007 0048 | GPIOBODS | GPIO Port B output drive strength |
| 0x4007 004C | GPIOBORUP | GPIO Port B output weak pull up |
| 0x4007 0050 | GPIOBORDN | GPIO Port B output weak pull down |
| 0x4007 0054 | GPIOBI | GPIO Port B input |
| 0x4007 0058 | Reserved | Reserved |
| 0x4007 005C | GPIOBPSEL | GPIO Port B peripheral select |
| 0x4007 0060 | GPIOBINTP | GPIO Port B interrupt polarity select |
| 0x4007 0064 | GPIOBINTEN | GPIO Port B interrupt enable select |
| 0x4007 0068 | GPIOBINT | GPIO Port B interrupt flag |
| 0x4007 006C | GPIOBINTM | GPIO Port B interrupt mask |

Table 2-9. GPIO Port AB Register Map

| ADDRESS | NAME | DESCRIPTION |
|---------------------|--------------------|--|
| GPIO Port AB | | |
| 0x4007 0080 | GPIOABO | GPIO Port AB output |
| 0x4007 0084 | GPIOABOE | GPIO Port AB output enable |
| 0x4007 0088 | GPIOABODS | GPIO Port AB output drive strength |
| 0x4007 008C | GPIOABORUP | GPIO Port AB output weak pull up |
| 0x4007 0090 | GPIOABORDN | GPIO Port AB output weak pull down |
| 0x4007 0094 | GPIOABI | GPIO Port AB input |
| 0x4007 0098 | Reserved | Reserved |
| 0x4007 009C | GPIOABPSEL | GPIO Port AB peripheral select |
| 0x4007 00A0 | GPIOABINTP | GPIO Port AB interrupt polarity select |
| 0x4007 00A4 | GPIOABINTEN | GPIO Port AB interrupt enable select |
| 0x4007 00A8 | GPIOABINT | GPIO Port AB interrupt flag |
| 0x4007 00AC | GPIOABINTM | GPIO Port AB interrupt mask |

Table 2-10. GPIO Port C Register Map

| ADDRESS | NAME | DESCRIPTION |
|--------------------|-------------------|---------------------------------------|
| GPIO Port C | | |
| 0x4008 0000 | GPIOCO | GPIO Port C output |
| 0x4008 0004 | GPIOCOE | GPIO Port C output enable |
| 0x4008 0008 | Reserved | Reserved |
| 0x4008 000C | Reserved | Reserved |
| 0x4008 0010 | Reserved | Reserved |
| 0x4008 0014 | GPIOCI | GPIO Port C input |
| 0x4008 0018 | GPIOCIE | GPIO Port C input enable |
| 0x4008 001C | Reserved | Reserved |
| 0x4008 0020 | GPIOCINTP | GPIO Port C interrupt polarity select |
| 0x4008 0024 | GPIOCINTEN | GPIO Port C interrupt enable select |
| 0x4008 0028 | GPIOCINT | GPIO Port C interrupt flag |
| 0x4008 002C | GPIOCINTM | GPIO Port C interrupt mask |

Table 2-11. GPIO Port D Register Map

| ADDRESS | NAME | DESCRIPTION |
|--------------------|------------------|-----------------------------------|
| GPIO Port D | | |
| 0x4008 0040 | GPIODO | GPIO Port D output |
| 0x4008 0044 | GPIODOE | GPIO Port D output enable |
| 0x4008 0048 | GPIODODS | GPIO Port D output drive strength |
| 0x4008 004C | GPIOGORUP | GPIO Port D output weak pull up |

| ADDRESS | NAME | DESCRIPTION |
|-------------|-------------------|---------------------------------------|
| 0x4008 0050 | GPIODORDN | GPIO Port D output weak pull down |
| 0x4008 0054 | GPIODI | GPIO Port D input |
| 0x4008 0058 | Reserved | Reserved |
| 0x4008 005C | GPIODPSEL | GPIO Port D peripheral select |
| 0x4008 0060 | GPIODINTP | GPIO Port D interrupt polarity select |
| 0x4008 0064 | GPIODINTEN | GPIO Port D interrupt enable select |
| 0x4008 0068 | GPIODINT | GPIO Port D interrupt flag |
| 0x4008 006C | GPIODINTM | GPIO Port D interrupt mask |

Table 2-12. GPIO Port CD Register Map

| ADDRESS | NAME | DESCRIPTION |
|---------------------|--------------------|--|
| GPIO Port CD | | |
| 0x4008 0080 | GPIOCDO | GPIO Port CD output |
| 0x4008 0084 | GPIOCDOE | GPIO Port CD output enable |
| 0x4008 0088 | Reserved | Reserved |
| 0x4008 008C | Reserved | Reserved |
| 0x4008 0090 | Reserved | Reserved |
| 0x4008 0094 | GPIOCDI | GPIO Port CD input |
| 0x4008 0098 | Reserved | Reserved |
| 0x4008 009C | GPIOCDPSEL | GPIO Port CD peripheral select |
| 0x4008 00A0 | GPIOCDINTP | GPIO Port CD interrupt polarity select |
| 0x4008 00A4 | GPIOCDINTEN | GPIO Port CD interrupt enable select |
| 0x4008 00A8 | GPIOCDINT | GPIO Port CD interrupt flag |
| 0x4008 00AC | GPIOCDINTM | GPIO Port CD interrupt mask |

Table 2-13. GPIO Port E Register Map

| ADDRESS | NAME | DESCRIPTION |
|--------------------|-------------------|---------------------------------------|
| GPIO Port E | | |
| 0x4009 0000 | GPIOEO | GPIO Port E output |
| 0x4009 0004 | GPIOEOE | GPIO Port E output enable |
| 0x4009 0008 | GPIOEODS | GPIO Port E output drive strength |
| 0x4009 000C | GPIOEORUP | GPIO Port E output weak pull up |
| 0x4009 0010 | GPIOEORDN | GPIO Port E output weak pull down |
| 0x4009 0014 | GPIOEI | GPIO Port E input |
| 0x4009 0018 | Reserved | Reserved |
| 0x4009 001C | GPIOEPSEL | GPIO Port E peripheral select |
| 0x4009 0020 | GPIOEINTP | GPIO Port E interrupt polarity select |
| 0x4009 0024 | GPIOEINTEN | GPIO Port E interrupt enable select |
| 0x4009 0028 | GPIOEINT | GPIO Port E interrupt flag |

| ADDRESS | NAME | DESCRIPTION |
|-------------|------------------|----------------------------|
| 0x4009 002C | GPIOEINTM | GPIO Port E interrupt mask |

Table 2-14. Timer A Register Map

| ADDRESS | NAME | DESCRIPTION |
|---|-----------------|---|
| Timer A | | |
| 0x400D 0000 | TACTL | Timer A control |
| 0x400D 0004 | TAPRD | Timer A period |
| 0x400D 0008 | TACTR | Timer A counter |
| Timer A PWMA Capture and Compare | | |
| 0x400D 0040 | TACCTL0 | Timer A capture and compare 0 control |
| 0x400D 0044 | TACTR0 | Timer A counter 0 |
| 0x400D 0048 | TACCTL1 | Timer A capture and compare 1 control |
| 0x400D 004C | TACTR1 | Timer A counter 1 |
| 0x400D 0050 | TACCTL2 | Timer A capture and compare 2 control |
| 0x400D 0054 | TACTR2 | Timer A counter 2 |
| 0x400D 0058 | TACCTL3 | Timer A capture and compare 3 control |
| 0x400D 005C | TACTR3 | Timer A counter 3 |
| 0x400D 0060 | TACCTL4 | Timer A capture and compare 4 control |
| 0x400D 0064 | TACTR4 | Timer A counter 4 |
| 0x400D 0068 | TACCTL5 | Timer A capture and compare 5 control |
| 0x400D 006C | TACTR5 | Timer A counter 5 |
| 0x400D 0070 | TACCTL6 | Timer A capture and compare 6 control |
| 0x400D 0074 | TACTR6 | Timer A counter 6 |
| 0x400D 0078 | TACCTL7 | Timer A capture and compare 7 control |
| 0x400D 007C | TACTR7 | Timer A counter 7 |
| Timer A Dead Time Generator | | |
| 0x400D 00A0 | DTGA0CTL | Timer A dead time generator 0 control |
| 0x400D 00A4 | DTGA0LED | Timer A dead time generator 0 leading edge delay |
| 0x400D 00A8 | DTGA0TED | Timer A dead time generator 0 trailing edge delay |
| 0x400D 00B0 | DTGA1CTL | Timer A dead time generator 1 control |
| 0x400D 00B4 | DTGA1LED | Timer A dead time generator 1 leading edge delay |
| 0x400D 00B8 | DTGA1TED | Timer A dead time generator 1 trailing edge delay |
| 0x400D 00C0 | DTGA2CTL | Timer A dead time generator 2 control |
| 0x400D 00C4 | DTGA2LED | Timer A dead time generator 2 leading edge delay |
| 0x400D 00C8 | DTGA2TED | Timer A dead time generator 2 trailing edge delay |
| 0x400D 00D0 | DTGA3CTL | Timer A dead time generator 3 control |
| 0x400D 00D4 | DTGA3LED | Timer A dead time generator 3 leading edge delay |
| 0x400D 00D8 | DTGA3TED | Timer A dead time generator 3 trailing edge delay |

Table 2-15. Timer B Register Map

| ADDRESS | NAME | DESCRIPTION |
|---|-----------------|---|
| Timer B | | |
| 0x400E 0000 | TBCTL | Timer B control |
| 0x400E 0004 | TBPRD | Timer B period |
| 0x400E 0008 | TBCTR | Timer B counter |
| Timer B PWMB Capture and Compare | | |
| 0x400E 0040 | TBCCTL0 | Timer B capture and compare 0 control |
| 0x400E 0044 | TBCTR0 | Timer B counter 0 |
| 0x400E 0048 | TBCCTL1 | Timer B capture and compare 1 control |
| 0x400E 004C | TBCTR1 | Timer B counter 1 |
| 0x400E 0050 | TBCCTL2 | Timer B capture and compare 2 control |
| 0x400E 0054 | TBCTR2 | Timer B counter 2 |
| 0x400E 0058 | TBCCTL3 | Timer B capture and compare 3 control |
| 0x400E 005C | TBCTR3 | Timer B counter 3 |
| Timer B Dead Time Generator | | |
| 0x400E 00A0 | DTGB0CTL | Timer B dead time generator 0 control |
| 0x400E 00A4 | DTGB0LED | Timer B dead time generator 0 leading edge delay |
| 0x400E 00A8 | DTGB0TED | Timer B dead time generator 0 trailing edge delay |

Table 2-16. Timer C Register Map

| ADDRESS | NAME | DESCRIPTION |
|---|-----------------|---|
| Timer C | | |
| 0x400F 0000 | TCCTL | Timer C control |
| 0x400F 0004 | TCPRD | Timer C period |
| 0x400F 0008 | TCCTR | Timer C counter |
| Timer C PWMC Capture and Compare | | |
| 0x400F 0040 | TCCCTL0 | Timer C capture and compare 0 control |
| 0x400F 0044 | TCCTR0 | Timer C counter 0 |
| 0x400F 0048 | TCCCTL1 | Timer C capture and compare 1 control |
| 0x400F 004C | TCCTR1 | Timer C counter 1 |
| Timer C Dead Time Generator | | |
| 0x400F 00A0 | DTGC0CTL | Timer C dead time generator 0 control |
| 0x400F 00A4 | DTGC0LED | Timer C dead time generator 0 leading edge delay |
| 0x400F 00A8 | DTGC0TED | Timer C dead time generator 0 trailing edge delay |

Table 2-17. Timer D Register Map

| ADDRESS | NAME | DESCRIPTION |
|---|-----------------|---|
| Timer D | | |
| 0x4010 0000 | TDCTL | Timer D control |
| 0x4010 0004 | TDPRD | Timer D period |
| 0x4010 0008 | TDCTR | Timer D counter |
| Timer D PWMD Capture and Compare | | |
| 0x4010 0040 | TDCCTL0 | Timer D capture and compare 0 control |
| 0x4010 0044 | TDCTR0 | Timer D counter 0 |
| 0x4010 0048 | TDCCTL1 | Timer D capture and compare 1 control |
| 0x4010 004C | TDCTR1 | Timer D counter 1 |
| Timer D Dead Time Generator | | |
| 0x4010 00A0 | DTGD0CTL | Timer D dead time generator 0 control |
| 0x4010 00A4 | DTGD0LED | Timer D dead time generator 0 leading edge delay |
| 0x4010 00A8 | DTGD0TED | Timer D dead time generator 0 trailing edge delay |

Table 2-18. EMUX Register Map

| ADDRESS | NAME | DESCRIPTION |
|-------------|-----------------|--------------------------|
| EMUX | | |
| 0x4015 0000 | EMUXCTL | ADC external MUX control |
| 0x4015 0004 | EMUXDATA | ADC external MUX data |

Table 2-19. ADC Register Map

| ADDRESS | NAME | DESCRIPTION |
|-------------|---------------|-----------------------|
| ADC | | |
| 0x4015 0008 | ADCCTL | ADC control |
| 0x4015 000C | ADCR | ADC conversion result |
| 0x4015 0010 | ADCINT | ADC interrupt |

Table 2-20. ADC Auto-Sampling Sequencer 0 Register Map

| ADDRESS | NAME | DESCRIPTION |
|--------------------------------------|---------------|--|
| ADC Auto-Sampling Sequencer 0 | | |
| 0x4015 0040 | ASCTL0 | Auto-sampling sequencer 0 control |
| 0x4015 0044 | AS0S0 | Auto-sampling sequencer 0 sample 0 control |
| 0x4015 0048 | AS0R0 | Auto-sampling sequencer 0 sample 0 result |
| 0x4015 004C | AS0S1 | Auto-sampling sequencer 0 sample 1 control |
| 0x4015 0050 | AS0R1 | Auto-sampling sequencer 0 sample 1 result |
| 0x4015 0054 | AS0S2 | Auto-sampling sequencer 0 sample 2 control |
| 0x4015 0058 | AS0R2 | Auto-sampling sequencer 0 sample 2 result |

| ADDRESS | NAME | DESCRIPTION |
|-------------|--------------|--|
| 0x4015 005C | AS0S3 | Auto-sampling sequencer 0 sample 3 control |
| 0x4015 0060 | AS0R3 | Auto-sampling sequencer 0 sample 3 result |
| 0x4015 0064 | AS0S4 | Auto-sampling sequencer 0 sample 4 control |
| 0x4015 0068 | AS0R4 | Auto-sampling sequencer 0 sample 4 result |
| 0x4015 006C | AS0S5 | Auto-sampling sequencer 0 sample 5 control |
| 0x4015 0070 | AS0R5 | Auto-sampling sequencer 0 sample 5 result |
| 0x4015 0074 | AS0S6 | Auto-sampling sequencer 0 sample 6 control |
| 0x4015 0078 | AS0R6 | Auto-sampling sequencer 0 sample 6 result |
| 0x4015 007C | AS0S7 | Auto-sampling sequencer 0 sample 7 control |
| 0x4015 0080 | AS0R7 | Auto-sampling sequencer 0 sample 7 result |

Table 2-21. ADC Auto-Sampling Sequencer 1 Register Map

| ADDRESS | NAME | DESCRIPTION |
|--------------------------------------|---------------|--|
| ADC Auto-Sampling Sequencer 1 | | |
| 0x4015 0100 | ASCTL1 | Auto-sampling sequencer 1 control |
| 0x4015 0104 | AS1S0 | Auto-sampling sequencer 1 sample 0 control |
| 0x4015 0108 | AS1R0 | Auto-sampling sequencer 1 sample 0 result |
| 0x4015 010C | AS1S1 | Auto-sampling sequencer 1 sample 1 control |
| 0x4015 0110 | AS1R1 | Auto-sampling sequencer 1 sample 1 result |
| 0x4015 0114 | AS1S2 | Auto-sampling sequencer 1 sample 2 control |
| 0x4015 0118 | AS1R2 | Auto-sampling sequencer 1 sample 2 result |
| 0x4015 011C | AS1S3 | Auto-sampling sequencer 1 sample 3 control |
| 0x4015 0120 | AS1R3 | Auto-sampling sequencer 1 sample 3 result |
| 0x4015 0124 | AS1S4 | Auto-sampling sequencer 1 sample 4 control |
| 0x4015 0128 | AS1R4 | Auto-sampling sequencer 1 sample 4 result |
| 0x4015 012C | AS1S5 | Auto-sampling sequencer 1 sample 5 control |
| 0x4015 0130 | AS1R5 | Auto-sampling sequencer 1 sample 5 result |
| 0x4015 0134 | AS1S6 | Auto-sampling sequencer 1 sample 6 control |
| 0x4015 0138 | AS1R6 | Auto-sampling sequencer 1 sample 6 result |
| 0x4015 013C | AS1S7 | Auto-sampling sequencer 1 sample 7 control |
| 0x4015 0140 | AS1R7 | Auto-sampling sequencer 1 sample 7 result |

Table 2-22. I²C Register Map

| ADDRESS | NAME | DESCRIPTION |
|-----------------------|-------------------|--|
| I²C | | |
| 0x40B0 0000 | I2CCFG | I ² C configuration |
| 0x40B0 0004 | I2CINTSTAT | I ² C interrupt and status |
| 0x40B0 0008 | I2CINTEN | I ² C interrupt enable |
| 0x40B0 0030 | I2CMCTL | I ² C master access control |

| ADDRESS | NAME | DESCRIPTION |
|-------------|------------|---------------------------------------|
| 0x40B0 0034 | I2CMRXDATA | I ² C master receive data |
| 0x40B0 0038 | I2CMTXDATA | I ² C master transmit data |
| 0x40B0 0040 | I2CBAUD | I ² C master baud rate |
| 0x40B0 0070 | I2CSRXDATA | I ² C slave receive data |
| 0x40B0 0074 | I2CSTXDATA | I ² C slave transmit data |
| 0x40B0 0078 | I2CSADDR | I ² C slave address |

Table 2-23. UART Register Map

| ADDRESS | NAME | DESCRIPTION |
|-------------|------------|---------------------------------|
| UART | | |
| 0x401D 0000 | UARTRXTX | UART receive/transmit FIFO |
| 0x401D 0004 | UARTIEN | UART interrupt enable |
| 0x401D 0008 | UARTII | UART interrupt identification |
| 0x401D 000C | UARTLC | UART line control |
| 0x401D 0010 | Reserved | Reserved |
| 0x401D 0014 | UARTLS | UART line status |
| 0x401D 0018 | Reserved | Reserved |
| 0x401D 001C | Reserved | Reserved |
| 0x401D 0020 | UARTFCTL | UART FIFO control |
| 0x401D 0024 | UARTIEN | UART interrupt enable |
| 0x401D 0028 | UARTDL_L | UART divisor latch low byte |
| 0x401D 002C | UARTDL_H | UART divisor latch high byte |
| 0x401D 0038 | UARTFD_F | UART fractional divisor value |
| 0x401D 003C | UARTFD_CTL | UART fractional divisor control |
| 0x401D 0040 | UARTFSTAT | UART FIFO status |

Table 2-24. SOC Bus Bridge Register Map

| ADDRESS | NAME | DESCRIPTION |
|-----------------------|------------|---------------------------------|
| SOC Bus Bridge | | |
| 0x4020 0000 | SOCBCTL | SOC Bus Bridge control |
| 0x4020 0004 | SOCBCFG | SOC Bus Bridge configuration |
| 0x4020 0008 | SOCBCLKDIV | SOC Bus Bridge clock divider |
| 0x4000 000C | Reserved | Reserved |
| 0x4000 0010 | Reserved | Reserved |
| 0x4020 0014 | SOCBSTAT | SOC Bus Bridge status |
| 0x4020 0018 | Reserved | Reserved |
| 0x4020 001C | SOCBD | SOC Bus Bridge data |
| 0x4020 0020 | SOCBINT_EN | SOC Bus Bridge interrupt enable |

Table 2-25. SPI Register Map

| ADDRESS | NAME | DESCRIPTION |
|-------------|------------------|--------------------------|
| SPI | | |
| 0x4021 0000 | SPICTL | SPI control |
| 0x4021 0004 | SPICFG | SPI configuration |
| 0x4021 0008 | SPICLKDIV | SPI clock divider |
| 0x4021 000C | Reserved | Reserved |
| 0x4021 0010 | Reserved | Reserved |
| 0x4021 0014 | SPISTAT | SPI status |
| 0x4021 0018 | SPICSSTR | SPI chip select steering |
| 0x4021 001C | SPID | SPI data |
| 0x4021 0020 | SPIINT_EN | SPI interrupt enable |

Table 2-26. Multi-Mode Power Manager Register Map

| ADDRESS | NAME | DESCRIPTION |
|---------------------------------|-----------------|--------------------------------|
| Multi-Mode Power Manager | | |
| 0x00 | SYSSSTAT | System status |
| 0x08 | DEVID | Device identification |
| 0x09 | VERID | Version identification |
| 0x10 | PWRCTL | Power manager control |
| 0x11 | PWRSTAT | Power manager status |
| 0x12 | PWRSET | Power manager setting |
| 0x13 | IMOD | Current modulation |
| 0x14 | SSCFG | Switching supply configuration |

3. SYSTEM CLOCK CONTROL

3.1. Register

3.1.1. Register Map

Table 3-1. System Clock Control Register Map

| ADDRESS | NAME | DESCRIPTION | RESET VALUE |
|-----------------------------|----------------|-------------------------|-------------|
| System Clock Control | | | |
| 0x4000 0000 | SCCTL | System clock control | 0x0000 0000 |
| 0x4000 0004 | PLLCTL | PLL control | 0x0000 0000 |
| 0x4000 0008 | ROSCCTL | Ring oscillator control | 0x0000 0007 |
| 0x4000 000C | XTALCTL | Crystal driver control | 0x0000 0000 |

3.1.2. SCCTL

Register 3-1. SCCTL (System Clock Control, 0x4000 0000)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | R | 0x0 | Reserved |
| 7 | FCLK | RW | 0x0 | FCLK input clock select 1b: PLLOUT clock 0b: FRCLK |
| 6:5 | HCLKDIV | RW | 0x0 | HCLK divider 11b = FCLK / 8 10b = FCLK / 4 01b = FCLK / 2 00b = FCLK / 1 |
| 4:2 | ACLKDIV | RW | 0x0 | ACLK divider 111b = FCLK / 128 110b = FCLK / 44 101b = FCLK / 32 100b = FCLK / 16 011b = FCLK / 8 010b = FCLK / 4 001b = FCLK / 2 000b = FCLK / 1 |
| 1:0 | CLKIN | R/W | 0x0 | FRCLK input clock select 11b = XTAL driver XIN/XOUT 10b = EXTCLK input 01b = CLKREF input (4MHz trimmed RC oscillator) 00b = internal ring oscillator ROSC |

3.1.3. PLLCTL

Register 3-2. PLLCTL (PLL Control, 0x4000 0004)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|------------------|--------|-------|--|
| 31:24 | Reserved | R | 0x0 | Reserved |
| 23:20 | Reserved | RW | 0x0 | Reserved, must be set to 0x0 |
| 19:16 | PLLOUTDIV | RW | 0x0 | PLL output divider 1111b: / 15 ... 0001b: / 1 0000b: reserved |
| 15:7 | PLLFB DIV | RW | 0x0 | PLL feedback divider 1 1111 1111b: / 513 ... 0 0000 0001b: / 3 0 0000 0000b: / 2 |
| 6:2 | PLLINDIV | RW | 0x0 | PLL input divider 1 1111b: / 33 ... 0 0001b: / 3 0 0000b: / 2 |
| 1 | Reserved | RW | 0x0 | Reserved, must be set to 0x0 |
| 0 | PLLEN | RW | 0x0 | PLL oscillator 1b: enable PLL 0b: disable PLL |

3.1.4. ROSCCTL

Register 3-3. ROSCCTL (Ring Oscillator Control, 0x4000 0008)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|--|
| 31:3 | Reserved | R | 0x0 | Reserved |
| 2:1 | ROSCP | RW | 0x3 | Ring oscillator frequency setting 11b = 8.3MHz 10b = 10.7MHz 01b = 15.3MHz 00b = 28.7MHz |
| 0 | ROSCEN | RW | 0x1 | Enable Ring oscillator 1b: enable ROSC 0b: disable ROSC |

3.1.5. XTALCTL


Register 3-4. XTALCTL (Crystal Driver Control, 0x4000 000C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:1 | Reserved | R | 0x0 | Reserved |
| 0 | XTALEN | RW | 0x0 | Enable XTAL driver 1b: enable crystal driver 0b: disable crystal driver |

3.2. Details of Operation

3.2.1. Block Diagram

Figure 3-1. System Clock Control



3.2.2. Configuration

Following blocks need to be configured for correct use of the system clock control:

- GPIO.D.PD1
- RTC
- WDT
- WIC
- ADC/ASC
- SYSTICK
- SRAM
- FLASH
- ADC EMUX
- SOC BUS
- I2C

- SPI
- UART
- Timer A, B, C, D

3.2.3. ROSC

The internal ring oscillator has four frequency settings controllable with **ROSCCTL.ROSCP** from 8.3MHz to 28.7MHz in four steps. The ROSC can also be disabled using **ROSCCTL.ROSCEN**.

3.2.4. CLKREF

The CLKREF provides a 1% trimmed 4MHz clock.

3.2.5. XTAL

The crystal driver supports a range of crystal frequencies from 2MHz to 10MHz. The crystal driver can also be used to input an external clock using XIN.

The crystal driver can be enabled with **XTALCTL.XTALEN**.

3.2.6. EXTCLK

PD1 can be configured as clock input, EXTCLK.

3.2.7. PLL

The clock input to the PLL is FRCLK.

The PLL can be enabled with **PLLCTL.PLLEN**.

The PLL output clock PLLOUT is following following equation:

$$PLLOUT = \frac{PLLIN * PLLFBDIV}{PLLINDIV * PLLOUTDIV * 2} \quad (1)$$

Where:

PLLOUT: PLL output frequency in MHz

PLLIN: PLL input frequency in MHz (FRCLK)

PLLINDIV: PLL input divider (2 to 33) **PLLCTL.PLLINDIV**

PLLFBDIV: PLL feedback divider (2 to 513) **PLLCTL.PLLFBDIV**

PLLOUTDIV: PLL output divider (1 to 16) **PLLCTL.PLLOUTDIV**

The input clock frequency and input clock divider selection must follow formula below for correct operation of PLL:

$$1\text{MHz} \leq \frac{PLLIN}{PLLINDIV} \leq 25\text{MHz} \quad (2)$$

The output clock frequency and output clock divider selection must following formula below for correct operation of the PLL

$$100\text{MHz} \leq PLLOUT * PLLOUTDIV \leq 250\text{MHz} \quad (3)$$

$$PLLOUTDIV \geq 1$$

The table below shows pre-calculated PLL output frequency settings using the 4MHz ROSC as input.

Table 3-5. PLL output frequency settings using 4MHz ROSC as input

| PLL output | PLLOUTDIV | PLLFB DIV | PLLINDIV |
|------------|---------------|--------------|----------|
| 10MHz | 0x01 (/[1*2]) | 0x008 (*10) | 0x0 (/2) |
| 16.8MHz | 0x05 (/[5*2]) | 0x052 (*84) | 0x0 (/2) |
| 20MHz | 0x01 (/[1*2]) | 0x012 (*20) | 0x0 (/2) |
| 25MHz | 0x01 (/[1*2]) | 0x019 (*25) | 0x0 (/2) |
| 30MHz | 0x01 (/[1*2]) | 0x01C (*30) | 0x0 (/2) |
| 33.333MHz | 0x01 (/[1*2]) | 0x030 (*50) | 0x1 (/3) |
| 40MHz | 0x01 (/[1*2]) | 0x026 (*40) | 0x0 (/2) |
| 50MHz | 0x01 (/[1*2]) | 0x030 (*50) | 0x0 (/2) |
| 60MHz | 0x01 (/[1*2]) | 0x03A (*60) | 0x0 (/2) |
| 70MHz | 0x01 (/[1*2]) | 0x044 (*70) | 0x0 (/2) |
| 80MHz | 0x01 (/[1*2]) | 0x04E (*80) | 0x0 (/2) |
| 90MHz | 0x01 (/[1*2]) | 0x058 (*90) | 0x0 (/2) |
| 100MHz | 0x01 (/[1*2]) | 0x062 (*100) | 0x0 (/2) |

3.2.8. FRCLK

The free running clock FRCLK clock source can be selected with **SCCTL.CLKIN**. From XTAL, EXTCLK, CLKREF, or ROSC.

3.2.9. FCLK

The fast clock FCLK clock source can be selected with **SCCTL.FCLK** to be either PLLOUT or FRCLK.

3.2.10. HCLK

The high speed clock HCLK clock source input is FCLK. The HCLK can be divided down from FCLK using **SCCTL.HCLKDIV** from /1 to /8 in 4 steps.

3.2.11. ACLK

The auxiliary clock ACLK clock source input is FCLK. The ACLK can be divided down from FCLK from ./1 to ./128 in 8 steps.

3.2.12. Clock Gating

When the CPU enters deep sleep mode, the HCLK, ACLK and FCLK to the ADC are clock gated and stopped to save power. Only FRCLK and FCLK continue to run to supply WIC, RTC, and WDT.

4. WATCHDOG TIMER

4.1. Register

4.1.1. Register Map

Table 4-1. Watchdog Timer Register Map

| ADDRESS | NAME | DESCRIPTION | RESET VALUE |
|-----------------------|---------------|---------------------------------|-------------|
| Watchdog Timer | | | |
| 0x4003 0000 | WDTCTL | Watchdog timer control | 0x6300 0000 |
| 0x4003 0004 | WDTCDV | Watchdog timer count-down value | 0x63FF FFFF |
| 0x4003 0008 | WDTCTR | Watchdog timer counter | 0x00FF FFFF |

4.1.2. WDTCTL

Register 4-1. WDTCTL (Watchdog Timer Control, 0x4003 0000)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-------------------|--------|-------|--|
| 31:24 | KEY | RW | 0x63 | Key for writing WDTCTL register 0xA: allow writes to WDTCTL register 0x63: read value of WDTCTL.KEY |
| 23:12 | Reserved | R | 0x0 | Reserved |
| 11 | WRBUSY | RW | 0x0 | WDTCTL write busy 1b = write to WDTCTL still being processed. Any register writes received while this bit is set to a 1b will be dropped and not written to the given register. Any reads will return indeterminate data. 0b = WDT registers not busy |
| 10 | WDTCLKSEL | RW | 0x0 | WDT input clock select 1b: FCLK 0b: FRCLK |
| 9:6 | WDTCLKDIV | RW | 0x0 | WDT clock input divider 111b: /65536 110b: /32768 1101b: /16384 1100b: /8192 1011b: /4096 1010b: /2048 1001b: /1024 1000b: /512 0111b: /256 0110b: /128 0101b: /64 0100b: /32 0011b: /16 0010b: /8 0001b: /4 0000b: /2 |
| 5 | WDTRESETEN | RW | 0x0 | Watchdog device RESET enable 1b = WDT trigger device RESET when WDTCTR register counts to 0x0 0b = WDT trigger device RESET disabled |
| 4 | WDTINT | RW | 0x0 | Watchdog interrupt 1b = WDT interrupt 0b = no WDT interrupt |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|------------------|--------|-------|--|
| 3 | WDTINTEN | RW | 0x0 | Watchdog interrupt enable 1b = enable WDT interrupt 0b = disable WDT interrupt |
| 2:0 | WDTCTRRST | RW | 0x0 | WDTCTR counter reset 101b = write of 101b reset WDTCTR to WDTCDV value |

4.1.3. WDTCDV

Register 4-2. WDTCDV (Watchdog Timer Count-Down Value, 0x4003 0004)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-----------|--|
| 31:24 | KEY | RW | 0x63 | Key for writing WDTCDV register 0x4A: allow writes to WDTCDV register 0x63: read value of WDTCDV.KEY |
| 23:0 | RSTVALUE | RW | 0xFF FFFF | 24-bit WDT count-down value |

4.1.4. WDTCTR


Register 4-3. WDTCTR (Watchdog Timer Counter, 0x4003 0008)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-----------|----------------------|
| 31:24 | Reserved | R | 0x0 | Reserved |
| 23:0 | CTR | RW | 0xFF FFFF | Current value of WDT |

4.2. Details of Operation

4.2.1. Block Diagram

Figure 4-1. WDT



4.2.2. Configuration

Following blocks need to be configured for correct use of the WDT:

- Clock Control System (CCS)
- Nested Vectored Interrupt Controller (NVIC)

4.2.3. Watchdog Timer

The Watchdog timer consist of a 24-bit timer and reset logic. The WDT can be used as general purpose 16bit timer or as watchdog timer that need to be serviced periodically to avoid device reset.

4.2.4. Access WDT Registers

The **WDTCTL** and **WDTCDV** registers can only be written to if **WDTCTL.KEY** or **WDTCDV.KEY** are set to 0x4A.

The read back value of **WDTCTL.KEY** or **WDTCDV.KEY** is always 0x63. The watchdog timer has 2 clock domains, HCLK and WDT clock domain set by **WDTCTL.CLKSEL** and **WDTCTL.WDTCLKDIV**. Writing to any WDT registers may take up to 1 clock cycle on the WDT clock domain to finish. Any ongoing writes to WDT registers are shown with **WDTCTL.WRBUSY**. As long as **WDTCTL.WRBUSY** is 1b, any subsequent writes to WDT registers are ignored and reads only provide undetermined data.

4.2.5. WDT Clock Setting

The WDT can use 2 clocks FCLK or FRCLK, selectable with **WDTCTL.CLKSEL**. For applications where the WDT need to run in CPU sleep mode, FRCLK should be used. The clock input can be further divided down from /2 to /65536 using **WDTCTL.WDTCLKDIV**.

4.2.6. General Purpose Timer Mode

Set **WDTCTL.WDTRESETEN** to 0b to use the WDT as general purpose 24-bit timer. Set the desired count value in WDT clocks in **WDTCDV.RSTVALUE**, set **WDTCTL.WDTCTRRST** to 101b to load **WDTCTR.CTR** with **WDTCDV.RSTVALUE**. To start the GPT timer set **GPTCTL.INTEN**. When **WDTCTR.CTR** reaches 0x0, the timer

automatic reloads **WDTCTR.CTR** with **WDTCDV.RSTVALUE** and continues countdown. The WDT is stopped when **WDTCTL.INTEN** is cleared.

4.2.7. Watchdog Timer Mode

Set **WDTCTL.WDTRESETEN** to 1b to use the WDT as 24-bit watchdog timer with device reset capability. Set **WDTCTL.WDTINTEN** to 1b to enable interrupt when WDT counts to 0x0. Set the desired count value in WDT clocks in **WDTCDV.RSTVALUE**. To start the WDT count down, set **WDTCTL.WDTCTRRST** to 101b. The WDT will copy the **WDTCTL.RSTVALUE** to **WDTCTR.CTR** and start counting down. When **WDTCTR.CTR** reaches 0x0, the WDT will automatic copy **WDTCTL.RSTVALUE** to **WDTCTR.CTR**, restart the counter and set the interrupt flag if enabled is set. During the second count down, set **WDTCTL.WDTCTRRST** to 101b to restart the 1st WDT countdown and avoid device reset. If the **WDTCTR.CTR** reaches 0x0 during the second count down without being reloaded, the WDT will toggle device reset.

5. GENERAL PURPOSE TIMER

5.1. Register

5.1.1. Register Map

Table 5-1. General Purpose Timer Register Map

| ADDRESS | NAME | DESCRIPTION | RESET VALUE |
|------------------------|---------------|--|-------------|
| Real Time Clock | | | |
| 0x4004 0000 | GPTCTL | General purpose timer control | 0x6300 0000 |
| 0x4004 0004 | GPTCDV | General purpose timer count-down value | 0x63FF FFFF |
| 0x4004 0008 | GPTCTR | General purpose timer counter | 0x00FF FFFF |

5.1.2. GPTCTL

Register 5-1. GPTCTL (Real Time Clock Control, 0x4004 0000)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|------------------|--------|-------|---|
| 31:24 | KEY | RW | 0x63 | Key for writing GPTCTL register 0x4A: allow writes to GPTCTL register 0x63: read value of GPTCTL.KEY |
| 23:12 | Reserved | R | 0x0 | Reserved |
| 11 | WRBUSY | RW | 0x0 | GPTCTL write busy 1b = write to GPTCTL still being processed. Any register writes received while this bit is set to a 1b will be dropped and not written to the given register. Any reads will return indeterminate data. 0b = GPT registers not busy |
| 10 | GPTCLKSEL | RW | 0x0 | GPT input clock select 1b: FCLK 0b: FRCLK |
| 9:6 | GPTCLKDIV | RW | 0x0 | GPT clock input divider 1111b: /65536 1110b: /32768 1101b: /16384 1100b: /8192 1011b: /4096 1010b: /2048 1001b: /1024 1000b: /512 0111b: /256 0110b: /128 0101b: /64 0100b: /32 0011b: /16 0010b: /8 0001b: /4 0000b: /2 |
| 5 | Reserved | R | 0x0 | Reserved |
| 4 | GPTINT | RW | 0x0 | Real time clock interrupt 1b = GPT interrupt 0b = no GPT interrupt |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|------------------|--------|-------|--|
| 3 | GPTINTEN | RW | 0x0 | Real time clock interrupt enable 1b = enable GPT interrupt 0b = disable GPT interrupt |
| 2:0 | GPTCTRRST | RW | 0x0 | GPTCTR counter reset 101b = write of 101b reset GPTCTR to GPTCDV value |

5.1.3. GPTCDV

Register 5-2. GPTCDV (Real Time Clock Count-Down Value, 0x4004 0004)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-----------|---|
| 31:24 | KEY | RW | 0x63 | Key for writing GPTCTL register 0x4A: allow writes to GPTCTL register 0x63: read value of GPTCTL.KEY |
| 23:0 | RSTVALUE | RW | 0xFF FFFF | 24bit GPT count-down value |

5.1.4. GPTCTR


Register 5-3. GPTCTR (Real Time Clock Counter, 0x4004 0008)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-----------|----------------------|
| 31:24 | Reserved | R | 0x0 | Reserved |
| 23:0 | CTR | RW | 0xFF FFFF | Current value of GPT |

5.2. Details of Operation

5.2.1. Block Diagram

Figure 5-1. GPT



5.2.2. Configuration

Following blocks need to be configured for correct use of the GPT:

- Clock Control System (CCS)
- Nested Vectored Interrupt Controller (NVIC)

5.2.3. General Purpose Timer

The General purpose timer consist of a 24-bit timer, can can also run in device sleep mode if FRLCK is used.

5.2.4. Access GPT Registers

The **GPTCTL** and **GPTCDV** registers can only be written to if **GPTCTL.KEY** or **GPTCDV.KEY** are set to 0x4A.

The read back value of **GPTCTL.KEY** or **GPTCDV.KEY** is always 0x63. The general purpose timer has 2 clock domains, HCLK and GPT clock domain set by **GPTCTL.CLKSEL** and **GPTCTL.GPTCLKDIV**. Writing to any GPT registers may take up to 1 clock cycle on the GPT clock domain to finish. Any ongoing writes to GPT registers are shown with **GPTCTL.WRBUSY**. As long as **GPTCTL.WRBUSY** is 1b, any subsequent writes to GPT registers are ignored and reads only provide undetermined data.

5.2.5. GPT Clock Setting

The GPT can use 2 clocks HCLK or FRCLK, selectable with **GPTCTL.CLKSEL**. For applications where the GPT need to run in CPU sleep mode, FRCLK should be used. The clock input can be further divided down from /2 to /65536 using **GPTCTL.GPTCLKDIV**.

5.2.6. General Purpose Timer Mode

Set **GPTCTL.GPTRESETEN** to 0b to use the GPT as general purpose 24-bit timer. Set the desired count value in GPT clocks in **GPTCDV.RSTVALUE**, set **GPTCTL.GPTCTRRST** to 101b to load **GPTCTR.CTR** with **GPTCDV.RSTVALUE**. To start the GPT timer set **GPTCTL.INTEN**. When **GPTCTR.CTR** reaches 0x0, the timer automatic reloads **GPTCTR.CTR** with **GPTCDV.RSTVALUE** and continues countdown. The GPT is stopped when **GPTCTL.INTEN** is cleared.

6. GPIO PORT A

6.1. Register

6.1.1. Register Map

Table 6-1. GPIO Port A Register Map

| ADDRESS | NAME | DESCRIPTION | RESET VALUE |
|--------------------|-------------------|---------------------------------------|-------------|
| GPIO Port A | | | |
| 0x4007 0000 | GPIOAO | GPIO Port A output | 0x0000 0000 |
| 0x4007 0004 | GPIOAOE | GPIO Port A output enable | 0x0000 0000 |
| 0x4007 0008 | GPIOADS | GPIO Port A output drive strength | 0x0000 0000 |
| 0x4007 000C | GPIOAORUP | GPIO Port A output weak pull up | 0x0000 0000 |
| 0x4007 0010 | GPIOAORDN | GPIO Port A output weak pull down | 0x0000 0000 |
| 0x4007 0014 | GPIOAI | GPIO Port A input | 0x0000 0000 |
| 0x4007 0018 | Reserved | Reserved | 0x0000 0000 |
| 0x4007 001C | GPIOAPSEL | GPIO Port A peripheral select | 0x0000 0000 |
| 0x4007 0020 | GPIOAINTP | GPIO Port A interrupt polarity select | 0x0000 0000 |
| 0x4007 0024 | GPIOAINTEN | GPIO Port A interrupt enable select | 0x0000 0000 |
| 0x4007 0028 | GPIOAINT | GPIO Port A interrupt flag | 0x0000 0000 |
| 0x4007 002C | GPIOAINTM | GPIO Port A interrupt mask | 0x0000 0000 |

6.1.2. GPIOAO

Register 6-1. GPIOAO (GPIO Port A Output, 0x4007 0000)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|--|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PA7O | RW | 0x0 | Port A output 7 1b: set output high if GPIOAOE.PAOE7 = 1b 0b: set output low if GPIOAOE.PAOE7 = 1b |
| 6 | PA6O | RW | 0x0 | Port A output 6 1b: set output high if GPIOAOE.PAOE6 = 1b 0b: set output low if GPIOAOE.PAOE6 = 1b |
| 5 | PA5O | RW | 0x0 | Port A output 5 1b: set output high if GPIOAOE.PAOE5 = 1b 0b: set output low if GPIOAOE.PAOE5 = 1b |
| 4 | PA4O | RW | 0x0 | Port A output 4 1b: set output high if GPIOAOE.PAOE4 = 1b 0b: set output low if GPIOAOE.PAOE4 = 1b |
| 3 | PA3O | RW | 0x0 | Port A output 3 1b: set output high if GPIOAOE.PAOE3 = 1b 0b: set output low if GPIOAOE.PAOE3 = 1b |
| 2 | PA2O | RW | 0x0 | Port A output 2 1b: set output high if GPIOAOE.PAOE2 = 1b 0b: set output low if GPIOAOE.PAOE2 = 1b |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-------------|--------|-------|--|
| 1 | PA1O | RW | 0x0 | Port A output 1 1b: set output high if GPIOAOE.PAOE1 = 1b 0b: set output low if GPIOAOE.PAOE1 = 1b |
| 0 | PA0O | RW | 0x0 | Port A output 0 1b: set output high if GPIOAOE.PAOE0 = 1b 0b: set output low if GPIOAOE.PAOE0 = 1b |

6.1.3. GPIOAOE

Register 6-2. GPIOAOE (GPIO Port A Output Enable, 0x4007 0004)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PA7OE | RW | 0x0 | Port A output 7 enable 1b: output state set by GPIOAO.PAO7 0b: output disabled, high-impedance state |
| 6 | PA6OE | RW | 0x0 | Port A output 6 enable 1b: output state set by GPIOAO.PAO6 0b: output disabled, high-impedance state |
| 5 | PA5OE | RW | 0x0 | Port A output 5 enable 1b: output state set by GPIOAO.PAO5 0b: output disabled, high-impedance state |
| 4 | PA4OE | RW | 0x0 | Port A output 4 enable 1b: output state set by GPIOAO.PAO4 0b: output disabled, high-impedance state |
| 3 | PA3OE | RW | 0x0 | Port A output 3 enable 1b: output state set by GPIOAO.PAO3 0b: output disabled, high-impedance state |
| 2 | PA2OE | RW | 0x0 | Port A output 2 enable 1b: output state set by GPIOAO.PAO2 0b: output disabled, high-impedance state |
| 1 | PA1OE | RW | 0x0 | Port A output 1 enable 1b: output state set by GPIOAO.PAO1 0b: output disabled, high-impedance state |
| 0 | PA0OE | RW | 0x0 | Port A output 0 enable 1b: output state set by GPIOAO.PAO0 0b: output disabled, high-impedance state |

6.1.4. GPIOADS

Register 6-3. GPIOADS (GPIO Port A Output Drive Strength, 0x4007 0008)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|--|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PA7ODS | RW | 0x0 | Port A output 7 drive strength select 1b: high 0b: low |
| 6 | PA6ODS | RW | 0x0 | Port A output 6 drive strength select 1b: high 0b: low |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|---------------|--------|-------|--|
| 5 | PA5ODS | RW | 0x0 | Port A output 5 drive strength select 1b: high 0b: low |
| 4 | PA4ODS | RW | 0x0 | Port A output 4 drive strength select 1b: high 0b: low |
| 3 | PA3ODS | RW | 0x0 | Port A output 3 drive strength select 1b: high 0b: low |
| 2 | PA2ODS | RW | 0x0 | Port A output 2 drive strength select 1b: high 0b: low |
| 1 | PA1ODS | RW | 0x0 | Port A output 1 drive strength select 1b: high 0b: low |
| 0 | PA0ODS | RW | 0x0 | Port A output 0 drive strength select 1b: high 0b: low |

6.1.5. GPIOARUP

Register 6-4. GPIOARUP (GPIO Port A Weak Pull Up, 0x4007 000C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PA7RUP | RW | 0x0 | Port A 7 weak pull up select 1b: enable weak pull-up to VCCIO 0b: disable weak pull-up to VCCIO |
| 6 | PA6RUP | RW | 0x0 | Port A 6 weak pull up select 1b: enable weak pull-up to VCCIO 0b: disable weak pull-up to VCCIO |
| 5 | PA5RUP | RW | 0x0 | Port A 5 weak pull up select 1b: enable weak pull-up to VCCIO 0b: disable weak pull-up to VCCIO |
| 4 | PA4RUP | RW | 0x0 | Port A 4 weak pull up select 1b: enable weak pull-up to VCCIO 0b: disable weak pull-up to VCCIO |
| 3 | PA3RUP | RW | 0x0 | Port A 3 weak pull up select 1b: enable weak pull-up to VCCIO 0b: disable weak pull-up to VCCIO |
| 2 | PA2RUP | RW | 0x0 | Port A 2 weak pull up select 1b: enable weak pull-up to VCCIO 0b: disable weak pull-up to VCCIO |
| 1 | PA1RUP | RW | 0x0 | Port A 1 weak pull up select 1b: enable weak pull-up to VCCIO 0b: disable weak pull-up to VCCIO |
| 0 | PA0RUP | RW | 0x0 | Port A 0 weak pull up select 1b: enable weak pull-up to VCCIO 0b: disable weak pull-up to VCCIO |

6.1.6. GPIOARDN

Register 6-5. GPIOARDN (GPIO Port A Weak Pull Down, 0x4007 0010)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PA7RDN | RW | 0x0 | Port A 7 weak pull down select 1b: enable weak pull-down to VSS 0b: disable weak pull-down to VSS |
| 6 | PA6RDN | RW | 0x0 | Port A 6 weak pull down select 1b: enable weak pull-down to VSS 0b: disable weak pull-down to VSS |
| 5 | PA5RDN | RW | 0x0 | Port A 5 weak pull down select 1b: enable weak pull-down to VSS 0b: disable weak pull-down to VSS |
| 4 | PA4RDN | RW | 0x0 | Port A 4 weak pull down select 1b: enable weak pull-down to VSS 0b: disable weak pull-down to VSS |
| 3 | PA3RDN | RW | 0x0 | Port A 3 weak pull down select 1b: enable weak pull-down to VSS 0b: disable weak pull-down to VSS |
| 2 | PA2RDN | RW | 0x0 | Port A 2 weak pull down select 1b: enable weak pull-down to VSS 0b: disable weak pull-down to VSS |
| 1 | PA1RDN | RW | 0x0 | Port A 1 weak pull down select 1b: enable weak pull-down to VSS 0b: disable weak pull-down to VSS |
| 0 | PA0RDN | RW | 0x0 | Port A 0 weak pull down select 1b: enable weak pull-down to VSS 0b: disable weak pull-down to VSS |

6.1.7. GPIOAI

Register 6-6. GPIOAI (GPIO Port A Input, 0x4007 0014)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RW | 0x0 | Reserved |
| 7 | PA7I | RW | 0x0 | Port A 7 input state 1b: input high 0b: input low |
| 6 | PA6I | RW | 0x0 | Port A 6 input state 1b: input high 0b: input low |
| 5 | PA5I | RW | 0x0 | Port A 5 input state 1b: input high 0b: input low |
| 4 | PA4I | RW | 0x0 | Port A 4 input state 1b: input high 0b: input low |
| 3 | PA3I | RW | 0x0 | Port A 3 input state 1b: input high 0b: input low |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-------------|--------|-------|---|
| 2 | PA2I | RW | 0x0 | Port A 2 input state 1b: input high 0b: input low |
| 1 | PA1I | RW | 0x0 | Port A 1 input state 1b: input high 0b: input low |
| 0 | PA0I | RW | 0x0 | Port A 0 input state 1b: input high 0b: input low |

6.1.8. GPIOAPSEL

Register 6-7. GPIOAPSEL (GPIO Port A Peripheral Select, 0x4007 001C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|--|
| 31:16 | Reserved | RW | 0x0 | Reserved |
| 15:14 | PA7PSEL | RW | 0x0 | Port A 7 peripheral select 11b: PWMC1 / DTGC0HS output or CC1 capture and compare input 10b: PWMA7 / DTGA3HS output or CA7 capture and compare input 01b: PWMA5 / DTGA1HS output or CA5 capture and compare input 00b: I/O mode PA7 |
| 13:12 | PA6PSEL | RW | 0x0 | Port A 6 peripheral select 11b: reserved 10b: PWMB0 / DTGB0LS output or CB0 capture and compare input 01b: PWMA4 / DTGA0HS output or CA4 capture and compare input 00b: I/O mode PA6 |
| 11:10 | PA5PSEL | RW | 0x0 | Port A 5 peripheral select 11b: reserved 10b: PWMD0 / DTGD0LS output or CD0 capture and compare input / IBCTL5 01b: PWMA6 / DTGA2HS output or CA6 capture and compare input / IBCTL5 00b: I/O mode PA5 |
| 9:8 | PA4PSEL | RW | 0x0 | Port A 4 peripheral select 11b: reserved 10b: PWMC0 / DTGC0LS output or CC0 capture and compare input / IBCTL4 01b: PWMA5 / DTGA1HS output or CA5 capture and compare input IBCTL4 00b: I/O mode PA4 |
| 7:6 | PA3PSEL | RW | 0x0 | Port A 3 peripheral select 11b: PWMB0 / DTGB0LS output or CB0 capture and compare input / IBCTL3 10b: PWMA4 / DTGA0HS output or CA4 capture and compare input / IBCTL3kI 01b: PWMA3 / DTGA3LS output or CA3 capture and compare input / IBCTL3 00b: I/O mode PA3 |
| 5:4 | PA2PSEL | RW | 0x0 | Port A 2 peripheral select 11b: reserved 10b: reserved 01b: PWMA2 / DTGA2LS output or CA2 capture and compare input / IBCTL2 00b: I/O mode PA2 |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|----------------|--------|-------|--|
| 3:2 | PA1PSEL | RW | 0x0 | Port A 1 peripheral select 11b: reserved 10b: reserved 01b: PWMA1 / DTGA1LS output or CA1 capture and compare input / IBCTL1 00b: I/O mode PA1 |
| 1:0 | PA0PSEL | RW | 0x0 | Port A 0 peripheral select 11b: reserved 10b: reserved 01b: PWMA0 / DTGA0LS output or CA0 capture and compare input / IBCTL0 00b: I/O mode PA0 |

6.1.9. GPIOAINTP

Register 6-8. GPIOAINTP (GPIO Port A Interrupt Polarity, 0x4007 0020)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PA7INTP | RW | 0x0 | Port A 7 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |
| 6 | PA6INTP | RW | 0x0 | Port A 6 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |
| 5 | PA5INTP | RW | 0x0 | Port A 5 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |
| 4 | PA4INTP | RW | 0x0 | Port A 4 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |
| 3 | PA3INTP | RW | 0x0 | Port A 3 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |
| 2 | PA2INTP | RW | 0x0 | Port A 2 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |
| 1 | PA1INTP | RW | 0x0 | Port A 1 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |
| 0 | PA0INTP | RW | 0x0 | Port A 0 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |

6.1.10. GPIOAINTEN

Register 6-9. GPIOAINTEN (GPIO Port A Interrupt Enable, 0x4007 0024)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PA7INTEN | RW | 0x0 | Port A 7 interrupt enable 1b: enabled interrupt 0b: disable interrupt |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|---|
| 6 | PA6INTEN | RW | 0x0 | Port A 6 interrupt enable 1b: enabled interrupt 0b: disable interrupt |
| 5 | PA5INTEN | RW | 0x0 | Port A 5 interrupt enable 1b: enabled interrupt 0b: disable interrupt |
| 4 | PA4INTEN | RW | 0x0 | Port A 4 interrupt enable 1b: enabled interrupt 0b: disable interrupt |
| 3 | PA3INTEN | RW | 0x0 | Port A 3 interrupt enable 1b: enabled interrupt 0b: disable interrupt |
| 2 | PA2INTEN | RW | 0x0 | Port A 2 interrupt enable 1b: enabled interrupt 0b: disable interrupt |
| 1 | PA1INTEN | RW | 0x0 | Port A 1 interrupt enable 1b: enabled interrupt 0b: disable interrupt |
| 0 | PA0INTEN | RW | 0x0 | Port A 0 interrupt enable 1b: enabled interrupt 0b: disable interrupt |

6.1.11. GPIOAINT

Register 6-10. GPIOAINT (GPIO Port A Interrupt, 0x4007 0028)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PA7INT | RW | 0x0 | Port A 7 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |
| 6 | PA6INT | RW | 0x0 | Port A 6 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |
| 5 | PA5INT | RW | 0x0 | Port A 5 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |
| 4 | PA4INT | RW | 0x0 | Port A 4 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |
| 3 | PA3INT | RW | 0x0 | Port A 3 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |
| 2 | PA2INT | RW | 0x0 | Port A 2 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |
| 1 | PA1INT | RW | 0x0 | Port A 1 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |
| 0 | PA0INT | RW | 0x0 | Port A 0 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |

6.1.12. GPIOINTM


Register 6-11. GPIOINTM (GPIO Port A Interrupt Mask, 0x4007 002C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|--|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PA7INTM | RW | 0x0 | Port A 7 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |
| 6 | PA6INTM | RW | 0x0 | Port A 6 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |
| 5 | PA5INTM | RW | 0x0 | Port A 5 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |
| 4 | PA4INTM | RW | 0x0 | Port A 4 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |
| 3 | PA3INTM | RW | 0x0 | Port A 3 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |
| 2 | PA2INTM | RW | 0x0 | Port A 2 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |
| 1 | PA1INTM | RW | 0x0 | Port A 1 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |
| 0 | PA0INTM | RW | 0x0 | Port A 0 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |

6.2. Details of Operation

6.2.1. Block Diagram

Figure 6-1. GPIO Port A



6.2.2. Configuration

Following blocks need to be configured for correct use of the GPIO A:

- Nested Vectored Interrupt Controller (NVIC)
- Gate Driver
- Timer A, PWMA, DTGA
- Timer B, PWMB, DTGB
- Timer C, PWMC, DTGC
- Timer D, PWMD, DTGD
- General Purpose Gate Drivers

6.2.3. GPIO A Block

The GPIO A block consists of up to 8 general purpose input output (GPIO). Each GPIO has interrupt capabilities, weak pull-up or pull-down, programmable output drive strength, High-Z output operation. Some of the GPIO can be configured as PWM output, or capture and compare input.

6.2.4. Input

The input state of GPIOA can be monitored with **GPIOAI.PAxI**. The input state can be monitored regardless of the peripheral select setting **GPIOAPSEL**.

6.2.5. Output and Output Enable

When **GPIOAOE.PAxOE** is enabled, the output state is controlled by **GPIOAO.PAxO**.

When **GPIOAOE.PAxOE** is disabled, the output is in High-Z state.

6.2.6. Output Drive Strength

The output drive strength can be adjusted using **GPIOADS** to meet application needs. Set **GPIOADS.PAxODS** to enable high current drive strength, reset to enable low current drive strength.

6.2.7. Weak Pull Up and Pull Down

Independent from the output settings, weak pull up can be enabled with **GPIOAORUP** and weak pull down can be enabled with **GPIOARDN**.

NOTE:

GPIOARUP.PAxRUP or **GPIOARDN.PAxRDN** should never be enabled at the same time for a single GPIO. If switching from weak pull-up to weak pull-down is required, disable weak pull-up first before enable weak pull-down and vice versa.

6.2.8. Peripheral Select

Each GPIO is connected to up to 4 digital peripherals, selectable with **GPIOAPSEL**. When a different function than IO is selected the input state can still be read with **GPIOAI** and the pull-up and pull-down is still controllable.

6.2.9. Interrupt

The interrupt for each GPIO can be enabled with **GPIOAINEN**. The interrupt can be configured to be rising signal edge or falling signal edge using **GPIOAINTP**. The state of the interrupt can be read from **GPIOAINT**. The individual interrupt bits can be cleared by writing to 1.

When the GPIO interrupts are enabled for the first time after device start-up, it may be in an uncertain state and generate an interrupt. To avoid this the **GPIOAINTM** mask bit need to be set before enabled interrupt bits.

To allow interrupt to be recognized by the CPU the GPIO interrupt need also be enabled in the NVIC.

7. GPIO PORT B

7.1. Register

7.1.1. Register Map

Table 7-1. GPIO Port B Register Map

| ADDRESS | NAME | DESCRIPTION | RESET VALUE |
|--------------------|-------------------|---------------------------------------|-------------|
| GPIO Port B | | | |
| 0x4007 0040 | GPIOBO | GPIO Port B output | 0x0000 0000 |
| 0x4007 0044 | GPIOBOE | GPIO Port B output enable | 0x0000 0000 |
| 0x4007 0048 | GPIOBODS | GPIO Port B output drive strength | 0x0000 0000 |
| 0x4007 004C | GPIOBORUP | GPIO Port B output weak pull up | 0x0000 0000 |
| 0x4007 0050 | GPIOBORDN | GPIO Port B output weak pull down | 0x0000 0000 |
| 0x4007 0054 | GPIOBI | GPIO Port B input | 0x0000 0000 |
| 0x4007 0058 | Reserved | Reserved | 0x0000 0000 |
| 0x4007 005C | GPIOBPSEL | GPIO Port B peripheral select | 0x0000 0000 |
| 0x4007 0060 | GPIOBINTP | GPIO Port B interrupt polarity select | 0x0000 0000 |
| 0x4007 0064 | GPIOBINTEN | GPIO Port B interrupt enable select | 0x0000 0000 |
| 0x4007 0068 | GPIOBINT | GPIO Port B interrupt flag | 0x0000 0000 |
| 0x4007 006C | GPIOBINTM | GPIO Port B interrupt mask | 0x0000 0000 |

7.1.2. GPIOBO

Register 7-1. GPIOBO (GPIO Port B Output, 0x4007 0040)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---------------------------------|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 6 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 5 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 4 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 3 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 2 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 1 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 0 | Reserved | RW | 0x0 | Reserved, must be written to 0b |

7.1.3. GPIOBOE

Register 7-2. GIOBOE (GPIO Port B Output Enable, 0x4007 0044)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|-------------|
| 31:8 | Reserved | RO | 0 | Reserved |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|---------------------------------|
| 7 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 6 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 5 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 4 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 3 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 2 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 1 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 0 | Reserved | RW | 0x0 | Reserved, must be written to 0b |

7.1.4. GPIOBDS

Register 7-3. GPIOBDS (GPIO Port B Output Drive Strength, 0x4007 0048)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---------------------------------|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 6 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 5 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 4 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 3 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 2 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 1 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 0 | Reserved | RW | 0x0 | Reserved, must be written to 0b |

7.1.5. GPIOBRUP

Register 7-4. GPIOBRUP (GPIO Port B Weak Pull Up, 0x4007 004C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---------------------------------|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 6 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 5 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 4 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 3 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 2 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 1 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 0 | Reserved | RW | 0x0 | Reserved, must be written to 0b |

7.1.6. GPIOBRDN

Register 7-5. GPIOBRDN (GPIO Port B Weak Pull Down, 0x4007 0050)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---------------------------------|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 6 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 5 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 4 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 3 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 2 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 1 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 0 | Reserved | RW | 0x0 | Reserved, must be written to 0b |

7.1.7. GPIOBI

Register 7-6. GPIOBI (GPIO Port B Input, 0x4007 0054)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RW | 0x0 | Reserved |
| 7 | PB7I | R | 0x0 | Port B 7 input state 1b: input high 0b: input low |
| 6 | Reserved | R | 0x0 | Reserved |
| 5 | Reserved | R | 0x0 | Reserved |
| 4 | Reserved | R | 0x0 | Reserved |
| 3 | Reserved | R | 0x0 | Reserved |
| 2 | Reserved | R | 0x0 | Reserved |
| 1 | Reserved | R | 0x0 | Reserved |
| 0 | PB0I | R | 0x0 | Port B 0 input state 1b: input high 0b: input low |

7.1.8. GPIOBPSEL

Register 7-7. GPIOBPSEL (GPIO Port B Peripheral Select, 0x4007 005C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|---|
| 31:16 | Reserved | RW | 0x0 | Reserved |
| 15:14 | PB7PSEL | RW | 0x0 | Port B 7 peripheral select 11b: reserved 10b: reserved 01b: reserved 00b: nIRQ2 / POS |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|----------------|--------|-------|--|
| 13:12 | PB6PSEL | RW | 0x0 | Port B 6 peripheral select 11b: reserved 10b: reserved 01b: EMUXDATA 00b: reserved |
| 11:10 | PB5PSEL | RW | 0x0 | Port B 5 peripheral select 11b: reserved 10b: reserved 01b: EMUXCLK 00b: reserved |
| 9:8 | PB4PSEL | RW | 0x0 | Port B 4 peripheral select 11b: reserved 10b: reserved 01b: SOC Bus SCLK 00b: reserved |
| 7:6 | PB3PSEL | RW | 0x0 | Port B 3 peripheral select 11b: reserved 10b: reserved 01b: SOC Bus MOSI 00b: reserved |
| 5:4 | PB2PSEL | RW | 0x0 | Port B 2 peripheral select 11b: reserved 10b: reserved 01b: SOC Bus MISO 00b: reserved |
| 3:2 | PB1PSEL | RW | 0x0 | Port B 1 peripheral select 11b: reserved 10b: reserved 01b: SOC Bus CS 00b: reserved |
| 1:0 | PB0PSEL | RW | 0x0 | Port B 0 peripheral select 11b: reserved 10b: reserved 01b: reserved 00b: nIRQ1 |

7.1.9. GPIOBINTP

Register 7-8. GPGPIOBINTP (GPIO Port B Interrupt Polarity, 0x4007 0060)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RW | 0x0 | Reserved |
| 7 | PB7INTP | RW | 0x0 | Port B 7 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |
| 6 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 5 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 4 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 3 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 2 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 1 | Reserved | RW | 0x0 | Reserved, must be written to 0b |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|----------------|--------|-------|---|
| 0 | PB0INTP | RW | 0x0 | Port B 0 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |

7.1.10. GPIOBINTEN

Register 7-9. GPIOBINTEN (GPIO Port B Interrupt Enable, 0x4007 0064)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RW | 0x0 | Reserved |
| 7 | PB7INTEN | RW | 0x0 | Port B 7 interrupt enable 1b: enabled interrupt 0b: disable interrupt |
| 6 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 5 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 4 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 3 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 2 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 1 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 0 | PB0INTEN | RW | 0x0 | Port B 0 interrupt enable 1b: enabled interrupt 0b: disable interrupt |

7.1.11. GPIOBINT

Register 7-10. GPIOBINT (GPIO Port B Interrupt, 0x4007 0068)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RW | 0x0 | Reserved |
| 7 | PB7INT | RW | 0x0 | Port B 7 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |
| 6 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 5 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 4 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 3 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 2 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 1 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 0 | PB0INT | RW | 0x0 | Port B 0 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |

7.1.12. GPIOBINTM


Register 7-11. GPIOBINTM (GPIO Port B Interrupt Mask, 0x4007 006C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|--|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PB7INTM | RW | 0x0 | Port B 7 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |
| 6 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 5 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 4 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 3 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 2 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 1 | Reserved | RW | 0x0 | Reserved, must be written to 0b |
| 0 | PB0INTM | RW | 0x0 | Port B 0 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |

7.2. Details of Operation

7.2.1. Block Diagram

Figure 7-1. GPIO Port B



7.2.2. Configuration

Following blocks need to be configured for correct use of the GPIO B:

- Nested Vectored Interrupt Controller (NVIC)
- SOC Bus

7.2.3. GPIO B Block

The GPIO B block consists of up to 8 general purpose input output (GPIO). Each GPIO has interrupt capabilities, weak pull-up or pull-down, programmable output drive strength, High-Z output operation. Some of the GPIO can be configured as PWM output, or capture and compare input.

7.2.4. Input

The input state of GPIOB can be monitored with **GPIOB1.PBxI**. The input state can be monitored regardless of the peripheral select setting **GPIOBSEL**.

7.2.5. Output and Output Enable

When **GPIOBOE.PBxOE** is enabled, the output state is controlled by **GPIOB0.PBxO**.

When **GPIOBOE.PBxOE** is disabled, the output is in High-Z state.

7.2.6. Output Drive Strength

The output drive strength can be adjusted using **GPIOBDS** to meet application needs. Set **GPIOBDS.PBxODS** to enable high current drive strength, reset to enable low current drive strength.

7.2.7. Weak Pull Up and Pull Down

Independent from the output settings, weak pull up can be enabled with **GPIOBORUP** and weak pull down can be enabled with **GPIOB RDN**.

NOTE:

GPIOB RUP.PAxRUP or **GPIOB RDN.PAxRDN** should never be enabled at the same time for a single GPIO. If switching from weak pull-up to weak pull-down is required, disable weak pull-up first before enable weak pull-down and vice versa.

7.2.8. Peripheral Select

Each GPIO is connected to up to 4 digital peripherals, selectable with **GPIOB PSEL**. When a different function than IO is selected the input state can still be read with **GPIOBI** and the pull-up and pull-down is still controllable.

7.2.9. Interrupt

The interrupt for each GPIO can be enabled with **GPIOB INTEN**. The interrupt can be configured to be rising signal edge or falling signal edge using **GPIOB INTP**. The state of the interrupt can be read from **GPIOB INT**. The individual interrupt bits can be cleared by writing to 1.

When the GPIO interrupts are enabled for the first time after device start-up, it may be in an uncertain state and generate an interrupt. To avoid this the **GPIOB INTM** mask bit need to be set before enabled interrupt bits.

To allow interrupt to be recognized by the CPU the GPIO interrupt need also be enabled in the NVIC.

8. GPIO PORT C

8.1. Register

8.1.1. Register Map

Table 8-1. GPIO Port C Register Map

| ADDRESS | NAME | DESCRIPTION | RESET VALUE |
|--------------------|-------------------|---------------------------------------|-------------|
| GPIO Port C | | | |
| 0x4008 0000 | GPIOCO | GPIO Port C output | 0x0000 0000 |
| 0x4008 0004 | GPIOCOE | GPIO Port C output enable | 0x0000 0000 |
| 0x4008 0008 | Reserved | Reserved | 0x0000 0000 |
| 0x4008 000C | Reserved | Reserved | 0x0000 0000 |
| 0x4008 0010 | Reserved | Reserved | 0x0000 0000 |
| 0x4008 0014 | GPIOCI | GPIO Port C input | 0x0000 0000 |
| 0x4008 0018 | GPIOCIE | GPIO Port C input enable | 0x0000 0000 |
| 0x4008 001C | Reserved | Reserved | 0x0000 0000 |
| 0x4008 0020 | GPIOCINTP | GPIO Port C interrupt polarity select | 0x0000 0000 |
| 0x4008 0024 | GPIOCINTEN | GPIO Port C interrupt enable select | 0x0000 0000 |
| 0x4008 0028 | GPIOCINT | GPIO Port C interrupt flag | 0x0000 0000 |
| 0x4008 002C | GPIOCINTM | GPIO Port C interrupt mask | 0x0000 0000 |

8.1.2. GPIOCO

Register 8-1. GPIOCO (GPIO Port C Output, 0x4008 0000)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|--|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PC7O | RW | 0x0 | Port C output 7 1b: set output high if GPIOCOE.PCOE7 = 1b 0b: set output low if GPIOCOE.PCOE7 = 1b |
| 6 | PC6O | RW | 0x0 | Port C output 6 1b: set output high if GPIOCOE.PCOE6 = 1b 0b: set output low if GPIOCOE.PCOE6 = 1b |
| 5 | PC5O | RW | 0x0 | Port C output 5 1b: set output high if GPIOCOE.PCOE5 = 1b 0b: set output low if GPIOCOE.PCOE5 = 1b |
| 4 | PC4O | RW | 0x0 | Port C output 4 1b: set output high if GPIOCOE.PCOE4 = 1b 0b: set output low if GPIOCOE.PCOE4 = 1b |
| 3 | PC3O | RW | 0x0 | Port C output 3 1b: set output high if GPIOCOE.PCOE3 = 1b 0b: set output low if GPIOCOE.PCOE3 = 1b |
| 2 | PC2O | RW | 0x0 | Port C output 2 1b: set output high if GPIOCOE.PCOE2 = 1b 0b: set output low if GPIOCOE.PCOE2 = 1b |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-------------|--------|-------|--|
| 1 | PC1O | RW | 0x0 | Port C output 1 1b: set output high if GPIOCOE.PCOE1 = 1b 0b: set output low if GPIOCOE.PCOE1 = 1b |
| 0 | PC0O | RW | 0x0 | Port C output 0 1b: set output high if GPIOCOE.PCOE0 = 1b 0b: set output low if GPIOCOE.PCOE0 = 1b |

8.1.3. GPIOCOE

Register 8-2. GPIOCOE (GPIO Port C Output Enable, 0x4008 0004)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RO | 0 | Reserved |
| 7 | PC7OE | RW | 0x0 | Port C output 7 enable 1b: output state set by GPIOCO.PCO7 0b: output disabled, high-impedance state |
| 6 | PC6OE | RW | 0x0 | Port C output 6 enable 1b: output state set by GPIOCO.PCO6 0b: output disabled, high-impedance state |
| 5 | PC5OE | RW | 0x0 | Port C output 5 enable 1b: output state set by GPIOCO.PCO5 0b: output disabled, high-impedance state |
| 4 | PC4OE | RW | 0x0 | Port C output 4 enable 1b: output state set by GPIOCO.PCO4 0b: output disabled, high-impedance state |
| 3 | PC3OE | RW | 0x0 | Port C output 3 enable 1b: output state set by GPIOCO.PCO3 0b: output disabled, high-impedance state |
| 2 | PC2OE | RW | 0x0 | Port C output 2 enable 1b: output state set by GPIOCO.PCO2 0b: output disabled, high-impedance state |
| 1 | PC1OE | RW | 0x0 | Port C output 1 enable 1b: output state set by GPIOCO.PCO1 0b: output disabled, high-impedance state |
| 0 | PC0OE | RW | 0x0 | Port C output 0 enable 1b: output state set by GPIOCO.PCO0 0b: output disabled, high-impedance state |

8.1.4. GPIOCI

Register 8-3. GPIOCI (GPIO Port C Input, 0x4008 0018)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PC7I | RW | 0x0 | Port C 7 input state 1b: input high 0b: input low |
| 6 | PC6I | RW | 0x0 | Port C 6 input state 1b: input high 0b: input low |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-------------|--------|-------|---|
| 5 | PC5I | RW | 0x0 | Port C 5 input state 1b: input high 0b: input low |
| 4 | PC4I | RW | 0x0 | Port C 4 input state 1b: input high 0b: input low |
| 3 | PC3I | RW | 0x0 | Port C 3 input state 1b: input high 0b: input low |
| 2 | PC2I | RW | 0x0 | Port C 2 input state 1b: input high 0b: input low |
| 1 | PC1I | RW | 0x0 | Port C 1 input state 1b: input high 0b: input low |
| 0 | PC0I | RW | 0x0 | Port C 0 input state 1b: input high 0b: input low |

8.1.5. GPIOCIE

Register 8-4. GPIOCIE (GPIO Port C Input Enable, 0x4008 0014)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|--|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PC7IE | RW | 0x0 | Port C 7 input enable 1b: input enabled, for I/O operation 0b: input disabled |
| 6 | PC6IE | RW | 0x0 | Port C 6 input enable 1b: input enabled, for I/O operation 0b: input disabled |
| 5 | PC5IE | RW | 0x0 | Port C 5 input enable 1b: input enabled, for I/O operation 0b: input disabled, for AD5 ADC input operation |
| 4 | PC4IE | RW | 0x0 | Port C 4 input enable 1b: input enabled, for I/O operation 0b: input disabled, for AD4 ADC input operation |
| 3 | PC3IE | RW | 0x0 | Port C 3 input enable 1b: input enabled, for I/O operation 0b: input disabled, for AD3 ADC input operation |
| 2 | PC2IE | RW | 0x0 | Port C 2 input enable 1b: input enabled, for I/O operation 0b: input disabled, for AD2 ADC input operation |
| 1 | PC1IE | RW | 0x0 | Port C 1 input enable 1b: input enabled, for I/O operation 0b: input disabled, for AD1 ADC input operation |
| 0 | PC0IE | RW | 0x0 | Port C 0 input enable 1b: input enabled, for I/O operation 0b: input disabled, for AD0 ADC input operation |

8.1.6. GPIOCINTP

Register 8-5. GPIOCINTP (GPIO Port C Interrupt Polarity, 0x4008 0020)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PC7INTP | RW | 0x0 | Port C 7 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |
| 6 | PC6INTP | RW | 0x0 | Port C 6 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |
| 5 | PC5INTP | RW | 0x0 | Port C 5 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |
| 4 | PC4INTP | RW | 0x0 | Port C 4 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |
| 3 | PC3INTP | RW | 0x0 | Port C 3 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |
| 2 | PC2INTP | RW | 0x0 | Port C 2 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |
| 1 | PC1INTP | RW | 0x0 | Port C 1 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |
| 0 | PC0INTP | RW | 0x0 | Port C 0 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |

8.1.7. GPIOCINTEN

Register 8-6. GPIOCINTEN (GPIO Port C Interrupt Enable, 0x4008 0024)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PC7INTEN | RW | 0x0 | Port C 7 interrupt enable 1b: enabled interrupt 0b: disable interrupt |
| 6 | PC6INTEN | RW | 0x0 | Port C 6 interrupt enable 1b: enabled interrupt 0b: disable interrupt |
| 5 | PC5INTEN | RW | 0x0 | Port C 5 interrupt enable 1b: enabled interrupt 0b: disable interrupt |
| 4 | PC4INTEN | RW | 0x0 | Port C 4 interrupt enable 1b: enabled interrupt 0b: disable interrupt |
| 3 | PC3INTEN | RW | 0x0 | Port C 3 interrupt enable 1b: enabled interrupt 0b: disable interrupt |
| 2 | PC2INTEN | RW | 0x0 | Port C 2 interrupt enable 1b: enabled interrupt 0b: disable interrupt |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|---|
| 1 | PC1INTEN | RW | 0x0 | Port C 1 interrupt enable 1b: enabled interrupt 0b: disable interrupt |
| 0 | PC0INTEN | RW | 0x0 | Port C 0 interrupt enable 1b: enabled interrupt 0b: disable interrupt |

8.1.8. GPIOCINT

Register 8-7. GPIOCINT (GPIO Port C Interrupt, 0x4008 0028)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PC7INT | RW | 0x0 | Port C 7 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |
| 6 | PC6INT | RW | 0x0 | Port C 6 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |
| 5 | PC5INT | RW | 0x0 | Port C 5 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |
| 4 | PC4INT | RW | 0x0 | Port C 4 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |
| 3 | PC3INT | RW | 0x0 | Port C 3 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |
| 2 | PC2INT | RW | 0x0 | Port C 2 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |
| 1 | PC1INT | RW | 0x0 | Port C 1 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |
| 0 | PC0INT | RW | 0x0 | Port C 0 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |

8.1.9. GPIOCINTM

Register 8-8. GPIOCINTM (GPIO Port C Interrupt Mask, 0x4008 002C)


| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|--|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PC7INTM | RW | 0x0 | Port C 7 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |
| 6 | PC6INTM | RW | 0x0 | Port C 6 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|----------------|--------|-------|--|
| 5 | PC5INTM | RW | 0x0 | Port C 5 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |
| 4 | PC4INTM | RW | 0x0 | Port C 4 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |
| 3 | PC3INTM | RW | 0x0 | Port C 3 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |
| 2 | PC2INTM | RW | 0x0 | Port C 2 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |
| 1 | PC1INTM | RW | 0x0 | Port C 1 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |
| 0 | PC0INTM | RW | 0x0 | Port C 0 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |

8.2. Details of Operation

8.2.1. Block Diagram

Figure 8-1. GPIO Port C



8.2.2. Configuration

Following blocks need to be configured for correct use of the GPIO C:

- Nested Vectored Interrupt Controller (NVIC)
- ADC

8.2.3. GPIO C Block

The GPIOC block consists of up to 8 general purpose input output (GPIO). Each GPIO has interrupt capabilities, High-Z output operation, analog ADx input to the ADC Mux. The GPIOC block IO voltage is different from the other GPIO blocks, it is supplied from VCC33.

8.2.4. Analog Input

The digital input state of GPIOC can be monitored with **GPIOCI.PCxI** if **GPIOCIE.PCxIE** is set.

Clear **GPIOCIE.PCxIE** and **GPIOCOE.PCxOE** to disable digital input and output to allow use of analog input ADx to the ADC.

8.2.5. Output and Output Enable

When **GPIOCOE.PCxOE** is enabled, the output state is controlled by **GPIOCO.PCxO**.

When **GPIOCOE.PCxOE** is disabled, the output is in High-Z state.

8.2.6. Interrupt

The interrupt for each GPIO can be enabled with **GPIOCINTEN**. The interrupt can be configured to be rising signal edge or falling signal edge using **GPIOCINTP**. The state of the interrupt can be read from **GPIOCINT**. The individual interrupt bits can be cleared by writing to 1.

When the GPIO interrupts are enabled for the first time after device start-up, it may be in an uncertain state and generate an interrupt. To avoid this the **GPIOCINTM** mask bit need to be set before enabled interrupt bits.

To allow interrupt to be recognized by the CPU the GPIO interrupt need also be enabled in the NVIC.

9. GPIO PORT D

9.1. Register

9.1.1. Register Map

Table 9-1. GPIO Port D Register Map

| ADDRESS | NAME | DESCRIPTION | RESET VALUE |
|--------------------|-------------------|---------------------------------------|-------------|
| GPIO Port D | | | |
| 0x4008 0040 | GPIODO | GPIO Port D output | 0x0000 0000 |
| 0x4008 0044 | GPIODOE | GPIO Port D output enable | 0x0000 0000 |
| 0x4008 0048 | GPIODODS | GPIO Port D output drive strength | 0x0000 0000 |
| 0x4008 004C | GPIODORUP | GPIO Port D output weak pull up | 0x0000 0000 |
| 0x4008 0050 | GPIODORDN | GPIO Port D output weak pull down | 0x0000 0000 |
| 0x4008 0054 | GPIODI | GPIO Port D input | 0x0000 0000 |
| 0x4008 0058 | Reserved | Reserved | 0x0000 0000 |
| 0x4008 005C | GPIODPSEL | GPIO Port D peripheral select | 0x0000 0005 |
| 0x4008 0060 | GPIODINTP | GPIO Port D interrupt polarity select | 0x0000 0000 |
| 0x4008 0064 | GPIODINTEN | GPIO Port D interrupt enable select | 0x0000 0000 |
| 0x4008 0068 | GPIODINT | GPIO Port D interrupt flag | 0x0000 0000 |
| 0x4008 006C | GPIODINTM | GPIO Port D interrupt mask | 0x0000 0000 |

9.1.2. GPIODO

Register 9-1. GPIODO (GPIO Port D Output, 0x4008 0040)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|--|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PD7O | RW | 0x0 | Port D output 7 1b: set output high if GPIODOE.PDOE7 = 1b 0b: set output low if GPIODOE.PDOE7 = 1b |
| 6 | PD6O | RW | 0x0 | Port D output 6 1b: set output high if GPIODOE.PDOE6 = 1b 0b: set output low if GPIODOE.PDOE6 = 1b |
| 5 | PD5O | RW | 0x0 | Port D output 5 1b: set output high if GPIODOE.PDOE5 = 1b 0b: set output low if GPIODOE.PDOE5 = 1b |
| 4 | PD4O | RW | 0x0 | Port D output 4 1b: set output high if GPIODOE.PDOE4 = 1b 0b: set output low if GPIODOE.PDOE4 = 1b |
| 3 | PD3O | RW | 0x0 | Port D output 3 1b: set output high if GPIODOE.PDOE3 = 1b 0b: set output low if GPIODOE.PDOE3 = 1b |
| 2 | PD2O | RW | 0x0 | Port D output 2 1b: set output high if GPIODOE.PDOE2 = 1b 0b: set output low if GPIODOE.PDOE2 = 1b |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-------------|--------|-------|--|
| 1 | PD1O | RW | 0x0 | Port D output 1 1b: set output high if GPIODOE.PDOE1 = 1b 0b: set output low if GPIODOE.PDOE1 = 1b |
| 0 | PD0O | RW | 0x0 | Port D output 0 1b: set output high if GPIODOE.PDOE0 = 1b 0b: set output low if GPIODOE.PDOE0 = 1b |

9.1.3. GPIODOE

Register 9-2. GPIODOE (GPIO Port D Output Enable, 0x4008 0044)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PD7OE | RW | 0x0 | Port D output 7 enable 1b: output state set by GPIODO.PDO7 0b: output disabled, high-impedance state |
| 6 | PD6OE | RW | 0x0 | Port D output 6 enable 1b: output state set by GPIODO.PDO6 0b: output disabled, high-impedance state |
| 5 | PD5OE | RW | 0x0 | Port D output 5 enable 1b: output state set by GPIODO.PDO5 0b: output disabled, high-impedance state |
| 4 | PD4OE | RW | 0x0 | Port D output 4 enable 1b: output state set by GPIODO.PDO4 0b: output disabled, high-impedance state |
| 3 | PD3OE | RW | 0x0 | Port D output 3 enable 1b: output state set by GPIODO.PDO3 0b: output disabled, high-impedance state |
| 2 | PD2OE | RW | 0x0 | Port D output 2 enable 1b: output state set by GPIODO.PDO2 0b: output disabled, high-impedance state |
| 1 | PD1OE | RW | 0x0 | Port D output 1 enable 1b: output state set by GPIODO.PDO1 0b: output disabled, high-impedance state |
| 0 | PD0OE | RW | 0x0 | Port D output 0 enable 1b: output state set by GPIODO.PDO0 0b: output disabled, high-impedance state |

9.1.4. GPIODDS

Register 9-3. GPIODDS (GPIO Port D Output Drive Strength, 0x4008 0048)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|--|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PD7ODS | RW | 0x0 | Port D output 7 drive strength select 1b: high 0b: low |
| 6 | PD6ODS | RW | 0x0 | Port D output 6 drive strength select 1b: high 0b: low |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|---------------|--------|-------|--|
| 5 | PD5ODS | RW | 0x0 | Port D output 5 drive strength select 1b: high 0b: low |
| 4 | PD4ODS | RW | 0x0 | Port D output 4 drive strength select 1b: high 0b: low |
| 3 | PD3ODS | RW | 0x0 | Port D output 3 drive strength select 1b: high 0b: low |
| 2 | PD2ODS | RW | 0x0 | Port D output 2 drive strength select 1b: high 0b: low |
| 1 | PD1ODS | RW | 0x0 | Port D output 1 drive strength select 1b: high 0b: low |
| 0 | PD0ODS | RW | 0x0 | Port D output 0 drive strength select 1b: high 0b: low |

9.1.5. GPIODRUP

Register 9-4. GPIODRUP (GPIO Port D Weak Pull Up, 0x4008 004C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PD7UP | RW | 0x0 | Port D 7 weak pull up select 1b: enable weak pull-up to VCCIO 0b: disable weak pull-up to VCCIO |
| 6 | PD6UP | RW | 0x0 | Port D 6 weak pull up select 1b: enable weak pull-up to VCCIO 0b: disable weak pull-up to VCCIO |
| 5 | PD5UP | RW | 0x0 | Port D 5 weak pull up select 1b: enable weak pull-up to VCCIO 0b: disable weak pull-up to VCCIO |
| 4 | PD4UP | RW | 0x0 | Port D 4 weak pull up select 1b: enable weak pull-up to VCCIO 0b: disable weak pull-up to VCCIO |
| 3 | PD3UP | RW | 0x0 | Port D 3 weak pull up select 1b: enable weak pull-up to VCCIO 0b: disable weak pull-up to VCCIO |
| 2 | PD2UP | RW | 0x0 | Port D 2 weak pull up select 1b: enable weak pull-up to VCCIO 0b: disable weak pull-up to VCCIO |
| 1 | PD1UP | RW | 0x0 | Port D 1 weak pull up select 1b: enable weak pull-up to VCCIO 0b: disable weak pull-up to VCCIO |
| 0 | PD0UP | RW | 0x0 | Port D 0 weak pull up select 1b: enable weak pull-up to VCCIO 0b: disable weak pull-up to VCCIO |

9.1.6. GPIODRDN

Register 9-5. GPIODRDN (GPIO Port D Weak Pull Down, 0x4008 0050)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PD7RDN | RW | 0x0 | Port D 7 weak pull down select 1b: enable weak pull-down to VSS 0b: disable weak pull-down to VSS |
| 6 | PD6RDN | RW | 0x0 | Port D 6 weak pull down select 1b: enable weak pull-down to VSS 0b: disable weak pull-down to VSS |
| 5 | PD5RDN | RW | 0x0 | Port D 5 weak pull down select 1b: enable weak pull-down to VSS 0b: disable weak pull-down to VSS |
| 4 | PD4RDN | RW | 0x0 | Port D 4 weak pull down select 1b: enable weak pull-down to VSS 0b: disable weak pull-down to VSS |
| 3 | PD3RDN | RW | 0x0 | Port D 3 weak pull down select 1b: enable weak pull-down to VSS 0b: disable weak pull-down to VSS |
| 2 | PD2RDN | RW | 0x0 | Port D 2 weak pull down select 1b: enable weak pull-down to VSS 0b: disable weak pull-down to VSS |
| 1 | PD1RDN | RW | 0x0 | Port D 1 weak pull down select 1b: enable weak pull-down to VSS 0b: disable weak pull-down to VSS |
| 0 | PD0RDN | RW | 0x0 | Port D 0 weak pull down select 1b: enable weak pull-down to VSS 0b: disable weak pull-down to VSS |

9.1.7. GPIODI

Register 9-6. GPIODI (GPIO Port D Input, 0x4008 0054)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RW | 0x0 | Reserved |
| 7 | PD7I | RW | 0x0 | Port D 7 input state 1b: input high 0b: input low |
| 6 | PD6I | RW | 0x0 | Port D 6 input state 1b: input high 0b: input low |
| 5 | PD5I | RW | 0x0 | Port D 5 input state 1b: input high 0b: input low |
| 4 | PD4I | RW | 0x0 | Port D 4 input state 1b: input high 0b: input low |
| 3 | PD3I | RW | 0x0 | Port D 3 input state 1b: input high 0b: input low |
| 2 | PD2I | RW | 0x0 | Port D 2 input state 1b: input high 0b: input low |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-------------|--------|-------|---|
| 1 | PD1I | RW | 0x0 | Port D 1 input state 1b: input high 0b: input low |
| 0 | PD0I | RW | 0x0 | Port D 0 input state 1b: input high 0b: input low |

9.1.8. GPIODPSEL

Register 9-7. GPIODPSEL (GPIO Port D Peripheral Select, 0x4008 005C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|---|
| 31:16 | Reserved | RO | 0x0 | Reserved |
| 15:14 | PD7PSEL | RW | 0x0 | Port D 7 peripheral select 11b: reserved 10b: PWMD0 / DTGD0LS output or CD0 capture and compare input 01b: PWMA6 / DTGA2HS output or CA6 capture and compare input 00b: I/O mode PD7 |
| 13:12 | PD6PSEL | RW | 0x0 | Port D 6 peripheral select 11b: reserved 10b: PWMB1 / DTGB0HS output or CB1 capture and compare input 01b: PWMA7 / DTGA3HS output or CA7 capture and compare input 00b: I/O mode PD6 |
| 11:10 | PD5PSEL | RW | 0x0 | Port D 5 peripheral select 11b: reserved 10b: PWMC1 / DTGC0HS output or CC1 capture and compare input 01b: PWMA5 / DTGA1HS output or CA5 capture and compare input 00b: I/O mode PD5 |
| 9:8 | PD4PSEL | RW | 0x0 | Port D 4 peripheral select 11b: reserved 10b: reserved 01b: PWMD1 / DTGD0HS output or CD1 capture and compare input 00b: I/O mode PD4 |
| 7:6 | PD3PSEL | RW | 0x0 | Port D 3 peripheral select 11b: PWMB1 / DTGB0HS output or CB1 capture and compare input 10b: PWMA7 / DTGA3HS output or CA7 capture and compare input 01b: PWMA5 / DTGA1HS output or CA5 capture and compare input 00b: I/O mode PD3 |
| 5:4 | PD2PSEL | RW | 0x0 | Port D 2 peripheral select 11b: PWMB0 / DTGB0LS output or CB0 capture and compare input 10b: PWMA4 / DTGA0HS output or CA4 capture and compare input 01b: PWMA3 / DTGA3LS output or CA3 capture and compare input 00b: I/O mode PD2 |
| 3:2 | PD1PSEL | RW | 0x1 | Port D 1 peripheral select 11b: reserved 10b: EXTCLK input 01b: Serial wire debug SWDCLK 00b: I/O mode PD1 |
| 1:0 | PD0PSEL | RW | 0x1 | Port D 0 peripheral select 11b: reserved 10b: reserved 01b: Serial wire debug SWDDATA 00b: I/O mode PD0 |

9.1.9. GPIOINTP

Register 9-8. GPIOINTP (GPIO Port D Interrupt Polarity, 0x4008 0060)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PD7INTP | RW | 0x0 | Port D 7 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |
| 6 | PD6INTP | RW | 0x0 | Port D 6 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |
| 5 | PD5INTP | RW | 0x0 | Port D 5 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |
| 4 | PD4INTP | RW | 0x0 | Port D 4 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |
| 3 | PD3INTP | RW | 0x0 | Port D 3 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |
| 2 | PD2INTP | RW | 0x0 | Port D 2 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |
| 1 | PD1INTP | RW | 0x0 | Port D 1 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |
| 0 | PD0INTP | RW | 0x0 | Port D 0 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |

9.1.10. GPIOINTEN

Register 9-9. GPIOINTEN (GPIO Port D Interrupt Enable, 0x4008 0064)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PD7INTEN | RW | 0x0 | Port D 7 interrupt enable 1b: enabled interrupt 0b: disable interrupt |
| 6 | PD6INTEN | RW | 0x0 | Port D 6 interrupt enable 1b: enabled interrupt 0b: disable interrupt |
| 5 | PD5INTEN | RW | 0x0 | Port D 5 interrupt enable 1b: enabled interrupt 0b: disable interrupt |
| 4 | PD4INTEN | RW | 0x0 | Port D 4 interrupt enable 1b: enabled interrupt 0b: disable interrupt |
| 3 | PD3INTEN | RW | 0x0 | Port D 3 interrupt enable 1b: enabled interrupt 0b: disable interrupt |
| 2 | PD2INTEN | RW | 0x0 | Port D 2 interrupt enable 1b: enabled interrupt 0b: disable interrupt |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|---|
| 1 | PD1INTEN | RW | 0x0 | Port D 1 interrupt enable 1b: enabled interrupt 0b: disable interrupt |
| 0 | PD0INTEN | RW | 0x0 | Port D 0 interrupt enable 1b: enabled interrupt 0b: disable interrupt |

9.1.11. GPIOINT

Register 9-10. GPIOINT (GPIO Port D Interrupt, 0x4008 0068)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PD7INT | RW | 0x0 | Port D 7 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |
| 6 | PD6INT | RW | 0x0 | Port D 6 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |
| 5 | PD5INT | RW | 0x0 | Port D 5 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |
| 4 | PD4INT | RW | 0x0 | Port D 4 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |
| 3 | PD3INT | RW | 0x0 | Port D 3 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |
| 2 | PD2INT | RW | 0x0 | Port D 2 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |
| 1 | PD1INT | RW | 0x0 | Port D 1 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |
| 0 | PD0INT | RW | 0x0 | Port D 0 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |

9.1.12. GPIOINTM

Register 9-11. GPIOINTM (GPIO Port D Interrupt Mask, 0x4008 006C)


| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|--|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PD7INTM | RW | 0x0 | Port D 7 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |
| 6 | PD6INTM | RW | 0x0 | Port D 6 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|----------------|--------|-------|--|
| 5 | PD5INTM | RW | 0x0 | Port D 5 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |
| 4 | PD4INTM | RW | 0x0 | Port D 4 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |
| 3 | PD3INTM | RW | 0x0 | Port D 3 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |
| 2 | PD2INTM | RW | 0x0 | Port D 2 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |
| 1 | PD1INTM | RW | 0x0 | Port D 1 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |
| 0 | PD0INTM | RW | 0x0 | Port D 0 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |

9.2. Details of Operation

9.2.1. Block Diagram

Figure 9-1. GPIO Port D



9.2.2. Configuration

Following blocks need to be configured for correct use of the GPIO D:

- Nested Vectored Interrupt Controller (NVIC)
- Gate Driver
- Timer A, PWMA, DTGA
- Timer B, PWMB, DTGB
- Timer C, PWMC, DTGC
- Timer D, PWMD, DTGD
- CCS
- SWD Debugger

9.2.3. GPIO D Block

The GPIO D block consists of up to 8 general purpose input output (GPIO). Each GPIO has interrupt capabilities, weak pull-up or pull-down, programmable output drive strength, High-Z output operation. Some of the GPIO can be configured as PWM output, or capture and compare input.

9.2.4. Input

The input state of GPIOD can be monitored with **GPIODI.PDxI**. The input state can be monitored regardless of the peripheral select setting **GPIODPSEL**.

9.2.5. Output and Output Enable

When **GPIOOE.PDxOE** is enabled, the output state is controlled by **GPIOODO.PDxO**.

When **GPIODE.PDxOE** is disabled, the output is in High-Z state.

9.2.6. Output Drive Strength

The output drive strength can be adjusted using **GPIODDS** to meet application needs. Set **GPIODDS.PDxODS** to enable high current drive strength, reset to enable low current drive strength.

9.2.7. Weak Pull Up and Pull Down

Independent from the output settings, weak pull up can be enabled with **GPIODRUP** and weak pull down can be enabled with **GPIODRDN**.

NOTE:

GPIODRUP.PDxRUP or **GPIODRDN.PDxRDN** should never be enabled at the same time for a single GPIO. If switching from weak pull-up to weak pull-down is required, disable weak pull-up first before enable weak pull-down and vice versa.

9.2.8. Peripheral Select

Each GPIO is connected to up to 4 digital peripherals, selectable with **GPIODPSEL**. When a different function than IO is selected the input state can still be read with **GPIODI** and the pull-up and pull-down is still controllable.

9.2.9. Interrupt

The interrupt for each GPIO can be enabled with **GPIODINTEN**. The interrupt can be configured to be rising signal edge or falling signal edge using **GPIODINTP**. The state of the interrupt can be read from **GPIODINT**. The individual interrupt bits can be cleared by writing to 1.

When the GPIO interrupts are enabled for the first time after device start-up, it may be in an uncertain state and generate an interrupt. To avoid this the **GPIODINTM** mask bit need to be set before enabled interrupt bits.

To allow interrupt to be recognized by the CPU the GPIO interrupt need also be enabled in the NVIC.

10. GPIO PORT E

10.1. Register

10.1.1. Register Map

Table 10-1. GPIO Port E Register Map

| ADDRESS | NAME | DESCRIPTION | RESET VALUE |
|--------------------|-------------------|---------------------------------------|-------------|
| GPIO Port E | | | |
| 0x4009 0000 | GPIOEO | GPIO Port E output | 0x0000 0000 |
| 0x4009 0004 | GPIOEOE | GPIO Port E output enable | 0x0000 0000 |
| 0x4009 0008 | GPIOEODS | GPIO Port E output drive strength | 0x0000 0000 |
| 0x4009 000C | GPIOEORUP | GPIO Port E output weak pull up | 0x0000 0000 |
| 0x4009 0010 | GPIOEORDN | GPIO Port E output weak pull down | 0x0000 0000 |
| 0x4009 0014 | GPIOEI | GPIO Port E input | 0x0000 0000 |
| 0x4009 0018 | Reserved | Reserved | 0x0000 0000 |
| 0x4009 001C | GPIOEPSEL | GPIO Port E peripheral select | 0x0000 0000 |
| 0x4009 0020 | GPIOEINTP | GPIO Port E interrupt polarity select | 0x0000 0000 |
| 0x4009 0024 | GPIOEINTEN | GPIO Port E interrupt enable select | 0x0000 0000 |
| 0x4009 0028 | GPIOEINT | GPIO Port E interrupt flag | 0x0000 0000 |
| 0x4009 002C | GPIOEINTM | GPIO Port E interrupt mask | 0x0000 0000 |

10.1.2. GPIOEO

Register 10-1. GPIOEO (GPIO Port E Output, 0x4009 0000)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|--|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PE7O | RW | 0x0 | Port E output 7 1b: set output high if GPIOEOE.PEOE7 = 1b 0b: set output low if GPIOEOE.PEOE7 = 1b |
| 6 | PE6O | RW | 0x0 | Port E output 6 1b: set output high if GPIOEOE.PEOE6 = 1b 0b: set output low if GPIOEOE.PEOE6 = 1b |
| 5 | PE5O | RW | 0x0 | Port E output 5 1b: set output high if GPIOEOE.PEOE5 = 1b 0b: set output low if GPIOEOE.PEOE5 = 1b |
| 4 | PE4O | RW | 0x0 | Port E output 4 1b: set output high if GPIOEOE.PEOE4 = 1b 0b: set output low if GPIOEOE.PEOE4 = 1b |
| 3 | PE3O | RW | 0x0 | Port E output 3 1b: set output high if GPIOEOE.PEOE3 = 1b 0b: set output low if GPIOEOE.PEOE3 = 1b |
| 2 | PE2O | RW | 0x0 | Port E output 2 1b: set output high if GPIOEOE.PEOE2 = 1b 0b: set output low if GPIOEOE.PEOE2 = 1b |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-------------|--------|-------|--|
| 1 | PE1O | RW | 0x0 | Port E output 1 1b: set output high if GPIOEOE.PEOE1 = 1b 0b: set output low if GPIOEOE.PEOE1 = 1b |
| 0 | PE0O | RW | 0x0 | Port E output 0 1b: set output high if GPIOEOE.PEOE0 = 1b 0b: set output low if GPIOEOE.PEOE0 = 1b |

10.1.3. GPIOEOE

Register 10-2. GPIOEOE (GPIO Port E Output Enable, 0x4009 0004)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|--|
| 31:8 | Reserved | RO | 0 | Reserved |
| 7 | PE7OE | RW | 0x0 | Port E output 7 enable 1b: output state set by GPIOEOE.PEO7 0b: output disabled, high-impedance state |
| 6 | PE6OE | RW | 0x0 | Port E output 6 enable 1b: output state set by GPIOEOE.PEO6 0b: output disabled, high-impedance state |
| 5 | PE5OE | RW | 0x0 | Port E output 5 enable 1b: output state set by GPIOEOE.PEO5 0b: output disabled, high-impedance state |
| 4 | PE4OE | RW | 0x0 | Port E output 4 enable 1b: output state set by GPIOEOE.PEO4 0b: output disabled, high-impedance state |
| 3 | PE3OE | RW | 0x0 | Port E output 3 enable 1b: output state set by GPIOEOE.PEO3 0b: output disabled, high-impedance state |
| 2 | PE2OE | RW | 0x0 | Port E output 2 enable 1b: output state set by GPIOEOE.PEO2 0b: output disabled, high-impedance state |
| 1 | PE1OE | RW | 0x0 | Port E output 1 enable 1b: output state set by GPIOEOE.PEO1 0b: output disabled, high-impedance state |
| 0 | PE0OE | RW | 0x0 | Port E output 0 enable 1b: output state set by GPIOEOE.PEO0 0b: output disabled, high-impedance state |

10.1.4. GPIOEDS

Register 10-3. GPIOEDS (GPIO Port E Output Drive Strength, 0x4009 0008)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|--|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PE7ODS | RW | 0x0 | Port E output 7 drive strength select 1b: high 0b: low |
| 6 | PE6ODS | RW | 0x0 | Port E output 6 drive strength select 1b: high 0b: low |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|---------------|--------|-------|--|
| 5 | PE5ODS | RW | 0x0 | Port E output 5 drive strength select 1b: high 0b: low |
| 4 | PE4ODS | RW | 0x0 | Port E output 4 drive strength select 1b: high 0b: low |
| 3 | PE3ODS | RW | 0x0 | Port E output 3 drive strength select 1b: high 0b: low |
| 2 | PE2ODS | RW | 0x0 | Port E output 2 drive strength select 1b: high 0b: low |
| 1 | PE1ODS | RW | 0x0 | Port E output 1 drive strength select 1b: high 0b: low |
| 0 | PE0ODS | RW | 0x0 | Port E output 0 drive strength select 1b: high 0b: low |

10.1.5. GPIOERUP

Register 10-4. GPIOERUP (GPIO Port E Weak Pull Up, 0x4009 000C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PE7RUP | RW | 0x0 | Port E 7 weak pull up select 1b: enable weak pull-up to VCCIO 0b: disable weak pull-up to VCCIO |
| 6 | PE6RUP | RW | 0x0 | Port E 6 weak pull up select 1b: enable weak pull-up to VCCIO 0b: disable weak pull-up to VCCIO |
| 5 | PE5RUP | RW | 0x0 | Port E 5 weak pull up select 1b: enable weak pull-up to VCCIO 0b: disable weak pull-up to VCCIO |
| 4 | PE4RUP | RW | 0x0 | Port E 4 weak pull up select 1b: enable weak pull-up to VCCIO 0b: disable weak pull-up to VCCIO |
| 3 | PE3RUP | RW | 0x0 | Port E 3 weak pull up select 1b: enable weak pull-up to VCCIO 0b: disable weak pull-up to VCCIO |
| 2 | PE2RUP | RW | 0x0 | Port E 2 weak pull up select 1b: enable weak pull-up to VCCIO 0b: disable weak pull-up to VCCIO |
| 1 | PE1RUP | RW | 0x0 | Port E 1 weak pull up select 1b: enable weak pull-up to VCCIO 0b: disable weak pull-up to VCCIO |
| 0 | PE0RUP | RW | 0x0 | Port E 0 weak pull up select 1b: enable weak pull-up to VCCIO 0b: disable weak pull-up to VCCIO |

10.1.6. GPIOERDN

Register 10-5. GPIOERDN (GPIO Port E Weak Pull Down, 0x4009 0010)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PE7RDN | RW | 0x0 | Port E 7 weak pull down select 1b: enable weak pull-down to VSS 0b: disable weak pull-down to VSS |
| 6 | PE6RDN | RW | 0x0 | Port E 6 weak pull down select 1b: enable weak pull-down to VSS 0b: disable weak pull-down to VSS |
| 5 | PE5RDN | RW | 0x0 | Port E 5 weak pull down select 1b: enable weak pull-down to VSS 0b: disable weak pull-down to VSS |
| 4 | PE4RDN | RW | 0x0 | Port E 4 weak pull down select 1b: enable weak pull-down to VSS 0b: disable weak pull-down to VSS |
| 3 | PE3RDN | RW | 0x0 | Port E 3 weak pull down select 1b: enable weak pull-down to VSS 0b: disable weak pull-down to VSS |
| 2 | PE2RDN | RW | 0x0 | Port E 2 weak pull down select 1b: enable weak pull-down to VSS 0b: disable weak pull-down to VSS |
| 1 | PE1RDN | RW | 0x0 | Port E 1 weak pull down select 1b: enable weak pull-down to VSS 0b: disable weak pull-down to VSS |
| 0 | PE0RDN | RW | 0x0 | Port E 0 weak pull down select 1b: enable weak pull-down to VSS 0b: disable weak pull-down to VSS |

10.1.7. GPIOEI

Register 10-6. GPIOEI (GPIO Port E Input, 0x4009 0014)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PE7I | RW | 0x0 | Port E 7 input state 1b: input high 0b: input low |
| 6 | PE6I | RW | 0x0 | Port E 6 input state 1b: input high 0b: input low |
| 5 | PE5I | RW | 0x0 | Port E 5 input state 1b: input high 0b: input low |
| 4 | PE4I | RW | 0x0 | Port E 4 input state 1b: input high 0b: input low |
| 3 | PE3I | RW | 0x0 | Port E 3 input state 1b: input high 0b: input low |
| 2 | PE2I | RW | 0x0 | Port E 2 input state 1b: input high 0b: input low |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-------------|--------|-------|---|
| 1 | PE1I | RW | 0x0 | Port E 1 input state 1b: input high 0b: input low |
| 0 | PE0I | RW | 0x0 | Port E 0 input state 1b: input high 0b: input low |

10.1.8. GPIOEPSEL

Register 10-7. GPIOEPSEL (GPIO Port E Peripheral Select, 0x4009 001C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|---|
| 31:16 | Reserved | RO | 0x0 | Reserved |
| 15:14 | PE7PSEL | RW | 0x0 | Port E 7 peripheral select 11b: reserved 10b: reserved 01b: reserved 00b: I/O mode PE7 |
| 13:12 | PE6PSEL | RW | 0x0 | Port E 6 peripheral select 11b: reserved 10b: reserved 01b: reserved 00b: I/O mode PE6 |
| 11:10 | PE5PSEL | RW | 0x0 | Port E 5 peripheral select 11b: reserved 10b: I2C clock I2CSDA 01b: SPI chip select 2 SPICS2 00b: I/O mode PE5 |
| 9:8 | PE4PSEL | RW | 0x0 | Port E 4 peripheral select 11b: reserved 10b: I2C clock I2CSCL 01b: SPI chip select 1 SPICS1 00b: I/O mode PE4 |
| 7:6 | PE3PSEL | RW | 0x0 | Port E 3 peripheral select 11b: reserved 10b: Device Reset input nRESET1 01b: SPI chip select 0 SPICS0 00b: I/O mode PE3 |
| 5:4 | PE2PSEL | RW | 0x0 | Port E 2 peripheral select 11b: reserved 10b: UART Receive UARTRX 01b: SPI Master in Slave out SPIMISO 00b: I/O mode PE2 |
| 3:2 | PE1PSEL | RW | 0x0 | Port E 1 peripheral select 11b: reserved 10b: UART Transmit UARTTX 01b: SPI Master out Slave in SPIMOSI 00b: I/O mode PE1 |
| 1:0 | PE0PSEL | RW | 0x0 | Port E 0 peripheral select 11b: reserved 10b: reserved 01b: SPI Clock SPICLK 00b: I/O mode PE0 |

10.1.9. GPIOEINTP

Register 10-8. GPIOEINTP (GPIO Port E Interrupt Polarity, 0x4009 0020)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PE7INTP | RW | 0x0 | Port E 7 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |
| 6 | PE6INTP | RW | 0x0 | Port E 6 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |
| 5 | PE5INTP | RW | 0x0 | Port E 5 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |
| 4 | PE4INTP | RW | 0x0 | Port E 4 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |
| 3 | PE3INTP | RW | 0x0 | Port E 3 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |
| 2 | PE2INTP | RW | 0x0 | Port E 2 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |
| 1 | PE1INTP | RW | 0x0 | Port E 1 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |
| 0 | PE0INTP | RW | 0x0 | Port E 0 interrupt polarity select 1b: Rising edge, low to high transition 0b: Falling edge, high to low transition |

10.1.10. GPIOEINTEN

Register 10-9. GPIOEINTEN (GPIO Port E Interrupt Enable, 0x4009 0024)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PE7INTEN | RW | 0x0 | Port E 7 interrupt enable 1b: enabled interrupt 0b: disable interrupt |
| 6 | PE6INTEN | RW | 0x0 | Port E 6 interrupt enable 1b: enabled interrupt 0b: disable interrupt |
| 5 | PE5INTEN | RW | 0x0 | Port E 5 interrupt enable 1b: enabled interrupt 0b: disable interrupt |
| 4 | PE4INTEN | RW | 0x0 | Port E 4 interrupt enable 1b: enabled interrupt 0b: disable interrupt |
| 3 | PE3INTEN | RW | 0x0 | Port E 3 interrupt enable 1b: enabled interrupt 0b: disable interrupt |
| 2 | PE2INTEN | RW | 0x0 | Port E 2 interrupt enable 1b: enabled interrupt 0b: disable interrupt |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|---|
| 1 | PE1INTEN | RW | 0x0 | Port E 1 interrupt enable 1b: enabled interrupt 0b: disable interrupt |
| 0 | PE0INTEN | RW | 0x0 | Port E 0 interrupt enable 1b: enabled interrupt 0b: disable interrupt |

10.1.11. GPIOEINT

Register 10-10. GPIOEINT (GPIO Port E Interrupt, 0x4009 0028)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PE7INT | RW | 0x0 | Port E 7 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |
| 6 | PE6INT | RW | 0x0 | Port E 6 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |
| 5 | PE5INT | RW | 0x0 | Port E 5 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |
| 4 | PE4INT | RW | 0x0 | Port E 4 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |
| 3 | PE3INT | RW | 0x0 | Port E 3 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |
| 2 | PE2INT | RW | 0x0 | Port E 2 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |
| 1 | PE1INT | RW | 0x0 | Port E 1 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |
| 0 | PE0INT | RW | 0x0 | Port E 0 interrupt 1b: interrupt pending, clear with write to 1b 0b: no interrupt pending |

10.1.12. GPIOEINTM

Register 10-11. GPIOEINTM (GPIO Port E Interrupt Mask, 0x4009 002C)


| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|--|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | PE7INTM | RW | 0x0 | Port E 7 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |
| 6 | PE6INTM | RW | 0x0 | Port E 6 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|----------------|--------|-------|--|
| 5 | PE5INTM | RW | 0x0 | Port E 5 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |
| 4 | PE4INTM | RW | 0x0 | Port E 4 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |
| 3 | PE3INTM | RW | 0x0 | Port E 3 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |
| 2 | PE2INTM | RW | 0x0 | Port E 2 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |
| 1 | PE1INTM | RW | 0x0 | Port E 1 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |
| 0 | PE0INTM | RW | 0x0 | Port E 0 interrupt mask 1b: enable interrupt mask 0b: disable interrupt mask |

10.2. Details of Operation

10.2.1. Block Diagram

Figure 10-1. GPIO Port E



10.2.2. Configuration

Following blocks need to be configured for correct use of the GPIO E:

- Nested Vectored Interrupt Controller (NVIC)
- SPI
- I2C
- UART

10.2.3. GPIO E Block

The GPIO E block consists of up to 8 general purpose input output (GPIO). Each GPIO has interrupt capabilities, weak pull-up or pull-down, programmable output drive strength, High-Z output operation.

10.2.4. Input

The input state of GPIOE can be monitored with **GPIOEI.PExI**. The input state can be monitored regardless of the peripheral select setting **GPIOEPSEL**.

10.2.5. Output and Output Enable

When **GPIOEOE.PExOE** is enabled, the output state is controlled by **GPIOEO.PExO**.

When **GPIOEOE.PExOE** is disabled, the output is in High-Z state.

10.2.6. Output Drive Strength

The output drive strength can be adjusted using **GPIOEDS** to meet application needs. Set **GPIOEDS.PExODS** to enable high current drive strength, reset to enable low current drive strength.

10.2.7. Weak Pull Up and Pull Down

Independent from the output settings, weak pull up can be enabled with **GPIOEORUP** and weak pull down can be enabled with **GPIOERDN**.

NOTE:

GPIOERUP.PExRUP or **GPIOERDN.PExRDN** should never be enabled at the same time for a single GPIO. If switching from weak pull-up to weak pull-down is required, disable weak pull-up first before enable weak pull-down and vice versa.

10.2.8. Peripheral Select

Each GPIO is connected to up to 4 digital peripherals, selectable with **GPIOEPSEL**. When a different function than IO is selected the input state can still be read with **GPIOEI** and the pull-up and pull-down is still controllable.

10.2.9. Interrupt

The interrupt for each GPIO can be enabled with **GPIOEINTEN**. The interrupt can be configured to be rising signal edge or falling signal edge using **GPIOEINTP**. The state of the interrupt can be read from **GPIOEINT**. The individual interrupt bits can be cleared by writing to 1.

When the GPIO interrupts are enabled for the first time after device start-up, it may be in an uncertain state and generate an interrupt. To avoid this the **GPIOEINTM** mask bit need to be set before enabled interrupt bits.

To allow interrupt to be recognized by the CPU the GPIO interrupt need also be enabled in the NVIC.

11. TIMER A

11.1. Register

11.1.1. Register Map

Table 11-1. Timer A Register Map

| ADDRESS | NAME | DESCRIPTION | RESET VALUE |
|---|-----------------|---|-------------|
| Timer A | | | |
| 0x400D 0000 | TACTL | Timer A control | 0x0000 0000 |
| 0x400D 0004 | TAPRD | Timer A period | 0x0000 0000 |
| 0x400D 0008 | TACTR | Timer A counter | 0x0000 0000 |
| Timer A PWMA Capture and Compare | | | |
| 0x400D 0040 | TACCTL0 | Timer A capture and compare 0 control | 0x0000 0000 |
| 0x400D 0044 | TACTR0 | Timer A counter 0 | 0x0000 0000 |
| 0x400D 0048 | TACCTL1 | Timer A capture and compare 1 control | 0x0000 0000 |
| 0x400D 004C | TACTR1 | Timer A counter 1 | 0x0000 0000 |
| 0x400D 0050 | TACCTL2 | Timer A capture and compare 2 control | 0x0000 0000 |
| 0x400D 0054 | TACTR2 | Timer A counter 2 | 0x0000 0000 |
| 0x400D 0058 | TACCTL3 | Timer A capture and compare 3 control | 0x0000 0000 |
| 0x400D 005C | TACTR3 | Timer A counter 3 | 0x0000 0000 |
| 0x400D 0060 | TACCTL4 | Timer A capture and compare 4 control | 0x0000 0000 |
| 0x400D 0064 | TACTR4 | Timer A counter 4 | 0x0000 0000 |
| 0x400D 0068 | TACCTL5 | Timer A capture and compare 5 control | 0x0000 0000 |
| 0x400D 006C | TACTR5 | Timer A counter 5 | 0x0000 0000 |
| 0x400D 0070 | TACCTL6 | Timer A capture and compare 6 control | 0x0000 0000 |
| 0x400D 0074 | TACTR6 | Timer A counter 6 | 0x0000 0000 |
| 0x400D 0078 | TACCTL7 | Timer A capture and compare 7 control | 0x0000 0000 |
| 0x400D 007C | TACTR7 | Timer A counter 7 | 0x0000 0000 |
| Timer A Dead Time Generator | | | |
| 0x400D 00A0 | DTGA0CTL | Timer A dead time generator 0 control | 0x0000 0080 |
| 0x400D 00A4 | DTGA0LED | Timer A dead time generator 0 leading edge delay | 0x0000 0000 |
| 0x400D 00A8 | DTGA0TED | Timer A dead time generator 0 trailing edge delay | 0x0000 0000 |
| 0x400D 00B0 | DTGA1CTL | Timer A dead time generator 1 control | 0x0000 0080 |
| 0x400D 00B4 | DTGA1LED | Timer A dead time generator 1 leading edge delay | 0x0000 0000 |
| 0x400D 00B8 | DTGA1TED | Timer A dead time generator 1 trailing edge delay | 0x0000 0000 |
| 0x400D 00C0 | DTGA2CTL | Timer A dead time generator 2 control | 0x0000 0080 |
| 0x400D 00C4 | DTGA2LED | Timer A dead time generator 2 leading edge delay | 0x0000 0000 |
| 0x400D 00C8 | DTGA2TED | Timer A dead time generator 2 trailing edge delay | 0x0000 0000 |
| 0x400D 00D0 | DTGA3CTL | Timer A dead time generator 3 control | 0x0000 0080 |
| 0x400D 00D4 | DTGA3LED | Timer A dead time generator 3 leading edge delay | 0x0000 0000 |

| ADDRESS | NAME | DESCRIPTION | | RESET VALUE |
|-------------|----------|---|--|-------------|
| 0x400D 00D8 | DTGA3TED | Timer A dead time generator 3 trailing edge delay | | 0x0000 0000 |

11.1.2. TACTL

Register 11-1. TACTL (Timer A Control, 0x400D 0000)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|----------|--------|-------|--|
| 31:14 | Reserved | RO | 0x0 | Reserved |
| 13 | DTGCLK | RW | 0x0 | DTGAX clock select 1b: DTGAX use clock after TACTL.CLKDIV 0b: DTGAX use clock selected by TACTL.CLK |
| 12 | Reserved | RW | 0x0 | Reserved, Write to 0x0 |
| 11:10 | MODE | RW | 0x0 | Timer A Mode 11b: reserved 10b: up / down 01b: up 00b: disabled |
| 9 | CLK | RW | 0x0 | Timer A clock input source 1b: ACLK 0b: HCLK |
| 8:6 | CLKDIV | RW | 0x0 | Timer A input clock divider 111b: / 128 110b: / 64 101b: /32 100b: /16 011b: /8 010b: /4 001b: /2 000b: /1 |
| 5 | INTEN | RW | 0x0 | Timer A interrupt enable 1b: enable Timer A interrupt 0b: disable Timer A interrupt |
| 4 | INT | RW | 0x0 | Timer A interrupt 1b: interrupt, clear by write 1b 0b: no interrupt |
| 3 | SS | RW | 0x0 | Timer A single shot 1b: single shot mode 0b: continuous timer mode |
| 2 | CLR | RW | 0x0 | Timer A clear 1b: Clear Timer A, hold Timer A in reset and set SYNC_OUT 0b: Do not clear timer and clear SYNC_OUT |
| 1 | Reserved | RO | 0x0 | Reserved |
| 0 | PRDL | RW | 0x0 | Timer A TAPRD update 1b: Latch new TAPRD value when timer A counting down, TACTR value = 0x1 and TACTL.MODE = 10b 0b: Latch new TAPRD value when timer A counting up and TACTR value = TAPRD – 0x1. |

11.1.3. TAPRD

Register 11-2. TAPRD (Timer A Period, 0x400D 0004)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|----------|--------|-------|----------------------|
| 31:16 | Reserved | RO | 0 | Reserved |
| 15:0 | PERIOD | RW | 0x0 | Timer A period value |

11.1.4. TACTR

Register 11-3. TACTR (Timer A Counter, 0x400D 0008)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|----------|--------|-------|-------------------------------|
| 31:16 | Reserved | RO | 0x0 | Reserved |
| 15:0 | CTR | RO | 0x0 | Current Timer A counter value |

11.1.5. TACC0CTL

Register 11-4. TACC0CTL (Timer A PWMA0 Capture and Compare Control, 0x400D 0040)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|----------|--------|-------|---|
| 31:5 | Reserved | RO | 0x0 | Reserved |
| 4 | CCMODE | RW | 0x0 | Capture and compare mode 1b: Capture mode PWMA0 input 0b: Compare mode PWMA0 output |
| 3 | CCINTEN | RW | 0x0 | Capture and compare interrupt enable 1b: enable interrupt 0b: disable interrupt |
| 2 | CCINT | RW | 0x0 | Capture and compare interrupt 1b: interrupt, clear by write 1b 0b: no interrupt detected |
| 1:0 | CCEDG | RW | 0x0 | Capture mode edge detect PWMA0 11b: reserved 10b: high to low transition and low to high transition 01b: low to high transition only 00b: high to low transition only |

11.1.6. TACC0CTR

Register 11-5. TACC0CTR (Timer A PWMA0 Capture and Compare Counter, 0x400D 0044)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|----------|--------|-------|--|
| 31:16 | Reserved | RO | 0x0 | Reserved |
| 15:0 | CCCTR | RW | 0x0 | Counter value for PWMA0 compare mode or counter value for PWMA0 capture mode |

11.1.7. TACC1CTL

Register 11-6. TACC1CTL (Timer A PWMA1 Capture and Compare Control, 0x400D 0048)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:5 | Reserved | RO | 0x0 | Reserved |
| 4 | CCMODE | RW | 0x0 | Capture and compare mode 1b: Capture mode PWMA1 input 0b: Compare mode PWMA1 output |
| 3 | CCINTEN | RW | 0x0 | Capture and compare interrupt enable 1b: enable interrupt 0b: disable interrupt |
| 2 | CCINT | RW | 0x0 | Capture and compare interrupt 1b: interrupt, clear by write 1b 0b: no interrupt detected |
| 1:0 | CCEDG | RW | 0x0 | Capture mode edge detect PWMA1 11b: reserved 10b: high to low transition and low to high transition 01b: low to high transition only 00b: high to low transition only |

11.1.8. TACC1CTR

Register 11-7. TACC1CTR (Timer A PWMA1 Capture and Compare Counter, 0x400D 004C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|--|
| 31:16 | Reserved | RO | 0x0 | Reserved |
| 15:0 | CCCTR | RW | 0x0 | Counter value for PWMA1 compare mode or counter value for PWMA1 capture mode |

11.1.9. TACC2CTL

Register 11-8. TACC2CTL (Timer A PWMA2 Capture and Compare Control, 0x400D 0050)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:5 | Reserved | RO | 0x0 | Reserved |
| 4 | CCMODE | RW | 0x0 | Capture and compare mode 1b: Capture mode PWMA2 input 0b: Compare mode PWMA2 output |
| 3 | CCINTEN | RW | 0x0 | Capture and compare interrupt enable 1b: enable interrupt 0b: disable interrupt |
| 2 | CCINT | RW | 0x0 | Capture and compare interrupt 1b: interrupt, clear by write 1b 0b: no interrupt detected |
| 1:0 | CCEDG | RW | 0x0 | Capture mode edge detect PWMA2 11b: reserved 10b: high to low transition and low to high transition 01b: low to high transition only 00b: high to low transition only |

11.1.10. TACC2CTR

Register 11-9. TACC2CTR (Timer A PWMA2 Capture and Compare Counter, 0x400D 0054)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|----------|--------|-------|--|
| 31:16 | Reserved | RO | 0x0 | Reserved |
| 15:0 | CCCTR | RW | 0x0 | Counter value for PWMA2 compare mode or counter value for PWMA2 capture mode |

11.1.11. TACC3CTL

Register 11-10. TACC3CTL (Timer A PWMA3 Capture and Compare Control, 0x400D 0058)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|----------|--------|-------|---|
| 31:5 | Reserved | RO | 0x0 | Reserved |
| 4 | CCMODE | RW | 0x0 | Capture and compare mode 1b: Capture mode PWMA3 input 0b: Compare mode PWMA3 output |
| 3 | CCINTEN | RW | 0x0 | Capture and compare interrupt enable 1b: enable interrupt 0b: disable interrupt |
| 2 | CCINT | RW | 0x0 | Capture and compare interrupt 1b: interrupt, clear by write 1b 0b: no interrupt detected |
| 1:0 | CCEDG | RW | 0x0 | Capture mode edge detect PWMA3 11b: reserved 10b: high to low transition and low to high transition 01b: low to high transition only 00b: high to low transition only |

11.1.12. TACC3CTR

Register 11-11. TACC3CTR (Timer A PWMA3 Capture and Compare Counter, 0x400D 005C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|----------|--------|-------|--|
| 31:16 | Reserved | RO | 0x0 | Reserved |
| 15:0 | CCCTR | RW | 0x0 | Counter value for PWMA3 compare mode or counter value for PWMA3 capture mode |

11.1.13. TACC4CTL

Register 11-12. TACC4CTL (Timer A PWMA4 Capture and Compare Control, 0x400D 0060)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|----------|--------|-------|---|
| 31:5 | Reserved | RO | 0x0 | Reserved |
| 4 | CCMODE | RW | 0x0 | Capture and compare mode 1b: Capture mode PWMA4 input 0b: Compare mode PWMA4 output |
| 3 | CCINTEN | RW | 0x0 | Capture and compare interrupt enable 1b: enable interrupt 0b: disable interrupt |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|--------------|--------|-------|---|
| 2 | CCINT | RW | 0x0 | Capture and compare interrupt 1b: interrupt, clear by write 1b 0b: no interrupt detected |
| 1:0 | CCEDG | RW | 0x0 | Capture mode edge detect PWMA4 11b: reserved 10b: high to low transition and low to high transition 01b: low to high transition only 00b: high to low transition only |

11.1.14. TACC4CTR

Register 11-13. TACC4CTR (Timer A PWMA4 Capture and Compare Counter, 0x400D 0064)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|--|
| 31:16 | Reserved | RO | 0x0 | Reserved |
| 15:0 | CCCTR | RW | 0x0 | Counter value for PWMA4 compare mode or counter value for PWMA4 capture mode |

11.1.15. TACC5CTL

Register 11-14. TACC5CTL (Timer A PWMA5 Capture and Compare Control, 0x400D 0068)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:5 | Reserved | RO | 0x0 | Reserved |
| 4 | CCMODE | RW | 0x0 | Capture and compare mode 1b: Capture mode PWMA5 input 0b: Compare mode PWMA5 output |
| 3 | CCINTEN | RW | 0x0 | Capture and compare interrupt enable 1b: enable interrupt 0b: disable interrupt |
| 2 | CCINT | RW | 0x0 | Capture and compare interrupt 1b: interrupt, clear by write 1b 0b: no interrupt detected |
| 1:0 | CCEDG | RW | 0x0 | Capture mode edge detect PWMA5 11b: reserved 10b: high to low transition and low to high transition 01b: low to high transition only 00b: high to low transition only |

11.1.16. TACC5CTR

Register 11-15. TACC5CTR (Timer A PWMA5 Capture and Compare Counter, 0x400D 006C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|--|
| 31:16 | Reserved | RO | 0x0 | Reserved |
| 15:0 | CCCTR | RW | 0x0 | Counter value for PWMA5 compare mode or counter value for PWMA5 capture mode |

11.1.17. TACC6CTL

Register 11-16. TACC6CTL (Timer A PWMA6 Capture and Compare Control, 0x400D 0070)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:5 | Reserved | RO | 0x0 | Reserved |
| 4 | CCMODE | RW | 0x0 | Capture and compare mode 1b: Capture mode PWMA6 input 0b: Compare mode PWMA6 output |
| 3 | CCINTEN | RW | 0x0 | Capture and compare interrupt enable 1b: enable interrupt 0b: disable interrupt |
| 2 | CCINT | RW | 0x0 | Capture and compare interrupt 1b: interrupt, clear by write 1b 0b: no interrupt detected |
| 1:0 | CCEDG | RW | 0x0 | Capture mode edge detect PWMA6 11b: reserved 10b: high to low transition and low to high transition 01b: low to high transition only 00b: high to low transition only |

11.1.18. TACC6CTR

Register 11-17. TACC6CTR (Timer A PWMA6 Capture and Compare Counter, 0x400D 0074)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|--|
| 31:16 | Reserved | RO | 0x0 | Reserved |
| 15:0 | CCCTR | RW | 0x0 | Counter value for PWMA6 compare mode or counter value for PWMA6 capture mode |

11.1.19. TACC7CTL

Register 11-18. TACC7CTL (Timer A PWMA7 Capture and Compare Control, 0x400D 0078)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:5 | Reserved | RO | 0x0 | Reserved |
| 4 | CCMODE | RW | 0x0 | Capture and compare mode 1b: Capture mode PWMA7 input 0b: Compare mode PWMA7 output |
| 3 | CCINTEN | RW | 0x0 | Capture and compare interrupt enable 1b: enable interrupt 0b: disable interrupt |
| 2 | CCINT | RW | 0x0 | Capture and compare interrupt 1b: interrupt, clear by write 1b 0b: no interrupt detected |
| 1:0 | CCEDG | RW | 0x0 | Capture mode edge detect PWMA7 11b: reserved 10b: high to low transition and low to high transition 01b: low to high transition only 00b: high to low transition only |

11.1.20. TACC7CTR

Register 11-19. TACC7CTR (Timer A PWMA7 Capture and Compare Counter, 0x400D 007C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|----------|--------|-------|--|
| 31:16 | Reserved | RO | 0x0 | Reserved |
| 15:0 | CCCTR | RW | 0x0 | Counter value for PWMA7 compare mode or counter value for PWMA7 capture mode |

11.1.21. DTGA0CTL

Register 11-20. DTGA0CTL (Timer A Dead Time Generator 0 Control, 0x400D 00A0)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|----------|--------|-------|---|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | BYPASS | RW | 0x1 | Bypass dead time generator 1b: DTGA0 bypass active, DTGA0LS = PWMA0, DTGA0HS = PWMA4 0b: DTGA0 bypass inactive, dead time inserted to DTGA0LS and DTGA0HS, DTGA0LS = PWMA4, DTGA0HS = PWMA4 |
| 6 | OTP | RW | 0x0 | One Time Preservation 1b: DTGA0HS high time is same as PWMA4 hightime and is shifted by DTGA0LED 0b: DTGA0HS high time is reduced by DTGA0LED |
| 5 | INVHS | RW | 0x0 | Invert DTGA0HS output signal 1b: invert DTGA0HS 0b: do not invert DTGA0HS |
| 4 | INVLS | RW | 0x0 | Invert DTGA0LS output signal 1b: invert DTGA0LS 0b: do not invert DTGA0LS |
| 3:0 | Reserved | RO | 0x0 | Reserved |

11.1.22. DTGA0LED

Register 11-21. DTGA0LED (Timer A Dead Time Generator 0 Leading Edge Delay, 0x400D 00A4)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|----------|--------|-------|---|
| 31:12 | Reserved | RO | 0x0 | Reserved |
| 11:0 | LED | RW | 0x0 | Counter value DTGA0 leading edge dead time in clock cycles defined by TACTL.DTGCLK |

11.1.23. DTGA0TED

Register 11-22. DTGA0TED (Timer A Dead Time Generator 0 Trailing Edge Delay, 0x400D 00A8)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|----------|--------|-------|--|
| 31:12 | Reserved | RO | 0x0 | Reserved |
| 11:0 | TED | RW | 0x0 | Counter value DTGA0 trailing edge dead time in clock cycles defined by TACTL.DTGCLK |

11.1.24. DTGA1CTL

Register 11-23. DTGA1CTL (Timer A Dead Time Generator 1 Control, 0x400D 00B0)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|----------|--------|-------|---|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | BYPASS | RW | 0x1 | Bypass dead time generator 1b: DTGA1 bypass active, DTGA1LS = PWMA1, DTGA1HS = PWMA5 0b: DTGA1 bypass inactive, dead time inserted to DTGA1LS and DTGA1HS, DTGA1LS = PWMA5, DTGA1HS = PWMA5 |
| 6 | OTP | RW | 0x0 | One Time Preservation 1b: DTGA1HS high time is same as PWMA5 hightime and is shifted by DTGA1LED 0b: DTGA1HS high time is reduced by DTGA1LED |
| 5 | INVHS | RW | 0x0 | Invert DTGA1HS output signal 1b: invert DTGA1HS 0b: do not invert DTGA1HS |
| 4 | INVLS | RW | 0x0 | Invert DTGA1LS output signal 1b: invert DTGA1LS 0b: do not invert DTGA1LS |
| 3:0 | Reserved | RO | 0x0 | Reserved |

11.1.25. DTGA1LED

Register 11-24. DTGA1LED (Timer A Dead Time Generator 1 Leading Edge Delay, 0x400D 00B4)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|----------|--------|-------|---|
| 31:12 | Reserved | RO | 0x0 | Reserved |
| 11:0 | LED | RW | 0x0 | Counter value DTGA1 leading edge dead time in clock cycles defined by TACTL.DTGCLK |

11.1.26. DTGA1TED

Register 11-25. DTGA1TED (Timer A Dead Time Generator 1 Trailing Edge Delay, 0x400D 00B8)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|----------|--------|-------|--|
| 31:12 | Reserved | RO | 0x0 | Reserved |
| 11:0 | TED | RW | 0x0 | Counter value DTGA1 trailing edge dead time in clock cycles defined by TACTL.DTGCLK |

11.1.27. DTGA2CTL

Register 11-26. DTGA2CTL (Timer A Dead Time Generator 2 Control, 0x400D 00C0)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|----------|--------|-------|---|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | BYPASS | RW | 0x1 | Bypass dead time generator 1b: DTGA2 bypass active, DTGA2LS = PWMA2, DTGA2HS = PWMA6 0b: DTGA2 bypass inactive, dead time inserted to DTGA2LS and DTGA2HS, DTGA2LS = PWMA6, DTGA2HS = PWMA6 |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|---|
| 6 | OTP | RW | 0x0 | One Time Preservation 1b: DTGA2HS high time is same as PWMA6 hightime and is shifted by DTGA2LED 0b: DTGA2HS high time is reduced by DTGA2LED |
| 5 | INVHS | RW | 0x0 | Invert DTGA2HS output signal 1b: invert DTGA2HS 0b: do not invert DTGA2HS |
| 4 | INVLS | RW | 0x0 | Invert DTGA2LS output signal 1b: invert DTGA2LS 0b: do not invert DTGA2LS |
| 3:0 | Reserved | RO | 0x0 | Reserved |

11.1.28. DTGA2LED

Register 11-27. DTGA2LED (Timer A Dead Time Generator 2 Leading Edge Delay, 0x400D 00C4)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|---|
| 31:12 | Reserved | RO | 0x0 | Reserved |
| 11:0 | LED | RW | 0x0 | Counter value DTGA2 leading edge dead time in clock cycles defined by TACTL.DTGCLK |

11.1.29. DTGA2TED

Register 11-28. DTGA2TED (Timer A Dead Time Generator 2 Trailing Edge Delay, 0x400D 00C8)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|--|
| 31:12 | Reserved | RO | 0x0 | Reserved |
| 11:0 | TED | RW | 0x0 | Counter value DTGA2 trailing edge dead time in clock cycles defined by TACTL.DTGCLK |

11.1.30. DTGA3CTL

Register 11-29. DTGA3CTL (Timer A Dead Time Generator 3 Control, 0x400D 00D0)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | BYPASS | RW | 0x1 | Bypass dead time generator 1b: DTGA3 bypass active, DTGA3LS = PWMA3, DTGA3HS = PWMA7 0b: DTGA3 bypass inactive, dead time inserted to DTGA3LS and DTGA3HS, DTGA3LS = PWMA7, DTGA1HS = PWMA7 |
| 6 | OTP | RW | 0x0 | One Time Preservation 1b: DTGA3HS high time is same as PWMA7 high time and is shifted by DTGA3LED 0b: DTGA3HS high time is reduced by DTGA3LED |
| 5 | INVHS | RW | 0x0 | Invert DTGA3HS output signal 1b: invert DTGA3HS 0b: do not invert DTGA3HS |
| 4 | INVLS | RW | 0x0 | Invert DTGA3LS output signal 1b: invert DTGA3LS 0b: do not invert DTGA3LS |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|----------|--------|-------|-------------|
| 3:0 | Reserved | RO | 0x0 | Reserved |

11.1.31. DTGA3LED

Register 11-30. DTGA3LED (Timer A Dead Time Generator 3 Leading Edge Delay, 0x400D 00D4)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|----------|--------|-------|---|
| 31:12 | Reserved | RO | 0x0 | Reserved |
| 11:0 | LED | RW | 0x0 | Counter value DTGA3 leading edge dead time in clock cycles defined by TACTL.DTGCLK |

11.1.32. DTGA3TED


Register 11-31. DTGA3TED (Timer A Dead Time Generator 3 Trailing Edge Delay, 0x400D 00D8)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|----------|--------|-------|--|
| 31:12 | Reserved | RO | 0x0 | Reserved |
| 11:0 | TED | RW | 0x0 | Counter value DTGA3 trailing edge dead time in clock cycles defined by TACTL.DTGCLK |

11.2. Details of Operation

11.2.1. Block Diagram

Figure 11-1. Timer A



11.2.2. Configuration

Following blocks need to be configured for correct use of the Timer A:

- Clock Control System (CCS)
- Nested Vectored Interrupt Controller (NVIC)
- I/O Controller
- Gate Driver
- Auto sequencing controller (ASC)
- Timer B
- Timer C
- Timer D

11.2.3. Timer A Block

The timer A block consists of a 16-bit timer with up mode or up/down mode with 8 PWM/capture units and 4 dead-time generator units.

11.2.4. Timer

Once enabled the timer counts up to the Timer A period value **TAPRD**. The **TAPRD** register can be written to

while the timer is running, the new **TAPRD** value will be latched when the counter reaches old **TAPRD** value in up mode. In up/down mode there is the option to latch the new **TAPRD** value when counter counts back to zero. **TACTL.PRDL** configures when the timer will be updated with the new **TAPRD** value in up/down mode.

The current timer value is accessible with the timer A counter value register **TACTR**.

11.2.5. Register update

The **TAPRD**, **TACCxCTR** register can be written to while the timer is running, the new **TAPRD**, **TACCxCTR** value will be latched when the counter reaches old **TAPRD** value in up mode. In up/down mode there is the option to latch the new **TAPRD**, **TACCxCTR** values when counter counts back to zero. **TACTL.PRDL** configures when the timer will be updated with the new **TAPRD**, **TACCxCTR** value in up/down mode.

11.2.6. Timer Modes

The timer supports 3 modes of operation: disabled, up and up/down using **TACTL.MODE**.

By default, the timer mode is disabled. When the timer is disabled, the timer counter does not increment or decrement. If the timer is disabled when previously in up or up/down mode, then the timer counter stops where it is. If the timer is re-enabled by putting it back into up or up/down modes, then the counter continues from the point at which it was disabled. To reset the current counter value **TACTR** to zero use **TACTL.CLR**.

In up mode, the timer starts counting from 0 up to the value of **TAPRD**. When the timer counter reaches the value of **TAPRD**, then the timer counter is reset to a value of 0. This mode is typically used for timed events or edge-aligned PWM output.

In up/down mode, the timer starts counting from 0 up to the value of **TAPRD**, and then back down to a value of 0. This timer mode is typically used for center-aligned PWM output. It can also be used for timed events, and will allow a longer timer range due to the fact it counts up and down

11.2.7. Single Shot Mode

The timer can be configured to run either once or continuously.

When the timer is configured in single shot mode using **TACTL.SS** the timer will only count to **TAPRD** value and stops in up mode. In up/down mode the timer will count to **TAPRD** and back to zero only once.

To start the timer in single-shot mode, **TACTL.SS** must be set. The timer will start when **TACTL.CLR** is set. To re-start a single-shot timer, **TACTL.CLR** must be reset, and then set again.

11.2.8. Input Clock And Pre-Scaler

The timer can be configured to use HCLK or ACLK using **TACTL.CLK**. The input clock for the can be divided further down from /1 to /128 using the **TACTL.CLKDIV**.

11.2.9. Timer Synchronization

The Timer A, B, C, D in the system have the ability to have synchronization between them. Each timer has a synchronization in signal (SYNC_IN) and the synchronization out signal (SYNC_OUT).

Timer A can be synchronized with Timer B, C, and D with timer A as master.

The timer asserts the SYNC_OUT pulse when the **TACTL.CLR** bit is set and de-asserts the SYNC_OUT pulse when the **TACTL.CLR** bit is cleared.

Each timer B, C, or D that need to be synchronized as slave with master timer A need to set the **TxCTL.SYNC** bit. If this is bit is not set, then the sync_in signal is ignored and the timer operates independently.

When the **TxCTL.SYNC** bit is set and the SYNC_IN signal is asserted, the timer clears the timer counter. The

timer counter is also cleared anytime the **TxCTL.CLR** bit is set to a 1. When the **TxCTL.SYNC** bit is set and the **SYNC_IN** signal is de-asserted and the timer mode is either up or up/down, then the timer will start counting. The timer will not start counting when the mode is set to up or up/down unless the **SYNC_IN** signal is de-asserted when **TxCTL.SYNC** is set.

NOTE:

In order for this feature to work correctly, all timers that are synchronized must be set to the same mode (up or up/down), with the same timer pre-scaler, timer clock input and timer period.

To enable synchronized timers, the following steps should be followed:

1. All slave timers B, C, or D are configured with the selected timer input clock, timer pre-scaler, timer period and set the **TxCTL.SYNC** bit. The timer should still be set to disabled at this point.
2. The master timer A is configured with the same timer input clock, timer pre-scaler, timer period and sets the **TxCTL.CLR** bit. This should clear all timer counters of the master and slave timers.
3. The slave timers set the timer mode to the desired state (either up or up/down).
4. The master timer sets the timer mode to either up or up/down and clears the **TACTL.CLR** bit. This should start the master and all slave timers simultaneously based on the selected timer clock input.
5. Once configured as above, all timers can be disabled by the master setting **TACTL.CLR** signal, to assert the **SYNC_OUT** signal. The timers can be re-enabled by clearing the **TACTL.CLR** bit, which de-asserts the **SYNC_OUT** signal.

11.2.10. PWM/Compare Units

Timer A supports up to 8 PWM/Capture units PWMA0 to PWMA7. Each PWM/Compare unit can be configured independently in PWM mode or capture mode using **TACCxCTL.CCMODE**.

11.2.10.1. PWM Mode

The PWM mode is enabled with setting **TACCxCTL.CCMODE** to 0.


The timer configuration allows either edge-aligned (timer in up mode) or center-aligned (timer in up/down mode) modes of PWM operation.

In both edge-aligned and center-aligned modes of operation, the timer block outputs a PWM waveform that starts out high at a **TACTR** value of 0 and then transitions to low when **TACTR** counts up to **TACCxCTR** compare value.

To configure a duty cycle of 0%, the **TACCxCTR** should be set to 0; to configure a duty cycle of 100%, the **TACCxCTR** value should be set to a value greater than or equal to **TAPRD**.

The polarity of the timer PWM outputs are not configurable. Adjustments to the polarity of the PWM outputs may be adjusted in the Dead-Time Generator (DTG) unit connected to the timer peripheral for each output independently.

Figure 11-2. PWMA[x] and PWMA[x+4] Example Using Timer A Up Mode and Up/Down Mode




11.2.10.2. Capture Mode

The Capture mode is enabled with setting **TACCxCTL.CCMODE** to 1. The trip condition for capture mode can be configured using **TACCxCTL.CCEDGE**, high-to-low signal edge transition, low-to-high signal edge transition or both.

When trip condition is detected the actual **TACTR** value is copied into **TACCxCTR**.

Figure 11-3. CA[x] and CA[x+4] Capture Example



11.2.11. Timer and PWM/Capture Interrupt

The timer may generate interrupt based on the base timer wrap, or when a capture and compare event occurs.

In the base timer both up and up/down timer modes allow an interrupt to be generated when the count reaches 0. Each time the count reaches zero, the **TACTL.INT** interrupt flag is set. If the interrupt is enabled using the **TACTL.INTEN**, then the Timer IRQ signal will be asserted to the CPU. The interrupt flag may be cleared by writing a 1 to the **TACTL.INT** interrupt flag bit.

In the capture and compare PWM units, each time a compare threshold is reached or each time a capture event is detected the **TACCxCTL.CCINT** bit will be set for that particular timer unit. If the interrupt is enabled via the **TACCxCTL.CCINTEN**, then the Timer IRQ signal will be asserted to the CPU. The interrupt flag may be cleared by writing a 1 to the **TACCxCTL.CCINT** interrupt flag bit.

The timer IRQ signal will be asserted if any of the timer interrupt flags **TACTL.INT** or **TACCxCTL.CCINT** are set. The Timer IRQ signal will be de-asserted when all of the timer interrupt flags are cleared.

11.2.12. Dead-Time Generator

The dead-time generator can be configured to introduce dead-time for a complementary PWM output. The Timer A block supports up to 4 dead time generators.

11.2.12.1. Dead Time Input Clock Selection

The clock source for the DTGAX can be selected using **TACTL.DTGCLK**.

Clear **TACTL.DTGCLK** to 0 to use clock source selected by **TACTL.CLK** directly to use higher resolution for dead time insertion.

Set **TACTL.DTGCLK** to 1 to use divided clock source selected by **TACTL.CLK** and **TACTL.CLKDIV** divider to use the same dead time resolution as Timer A.

11.2.12.2. Dead Time Range

The resolution for leading edge and trailing edge dead time is 12bits. Leading and trailing edge can be set independently for each DTG using **DTGAXLED** and **DTGAXTED**.


11.2.12.3. Bypass Mode

Set **DTGAXCTL.BYPASS** to 0 to enable dead time insertion.

Set **DTGAXCTL.BYPASS** to 1 to enable bypass mode, no deadtime is inserted, PWMA[x+4] is routed to DTGAXHS and PWMAx is routed to DTGAXLS.

The DTGAXHS and DTGAXLS signals can be inverted in bypass mode.

Figure 11-4. DTGAX Bypass Example




11.2.12.4. Inverting PWM Signal

The DTG output signals DTGAXHS and DTGAXLS can be inverted independently.

Set **DTGAXCTL.INVHS** to invert DTGAXHS signal.

Set **DTGAXCTL.INVLS** to invert DTGAXLS signal.

Figure 11-5. DTGAx Bypass and Inverting LS Example



11.2.12.5. Dead Time Insertion


Set **DTGAxCTL.BYPASS** to 0 to enable dead time insertion. In dead time insertion mode only PWM[x+4] signal is used to generate DTGAxHS and DTGAxLS. PWMA[x] signal is ignored and can be used for other purposes.

Set **DTGAxLED** for desired leading-edge and **DTGAxTED** for desired trailing edge in clock-cycles defined by **TACTL.DTGCLK** clock source

NOTE:

In dead time insertion mode the DTGAxLS signal is automatically inverted compared to PWMA[x+4] signal. Set **DTGAxCTL.INVLS** to 0, if this is desired behavior.

Figure 11-6. DTGAx LED and TED Example




11.2.12.6. Dead Time Insertion with On Time Preservation

Set **DTGAxCTL.OTP** to 1 to enable on time preservation. In this mode the DTGAxHS is same as PWM[x+4] on time.

NOTE:

In dead time insertion mode the DTGAxLS signal is automatically inverted compared to PWMA[x+4] signal. Set **DTGAxCTL.INVLS** to 0, if this is desired behavior.

Figure 11-7. DTGAX LED and TED with On Time Preservation Example



11.2.13. PWM Output and Capture Input Pin Selection

Each of the DTGAXHS, DTGAXLS outputs, and CAx inputs can be routed to different I/Os, allowing great flexibility in pin assignments.

In capture mode only one I/O should be enabled as input to the capture. If more than one pin input is enabled, the capture might not work properly.

Note:

Not all pins are available pending package option, consult data sheet for available pins and signals.

Table 11-2. Timer A Signal to Pin Mapping

| PWM | CAPTURE | DEADTIME | PINS |
|-------|---------|----------|--------------------|
| PWMA0 | CA0 | DTGA0LS | PA0 |
| PWMA1 | CA1 | DTGA1LS | PA1 |
| PWMA2 | CA2 | DTGA2LS | PA2 |
| PWMA3 | CA3 | DTGA3LS | PA3, PD2 |
| PWMA4 | CA4 | DTGA0HS | PA3, PA6, PD2 |
| PWMA5 | CA5 | DTGA1HS | PA4, PA7, PD3, PD5 |
| PWMA6 | CA6 | DTGA2HS | PA5, PD7 |
| PWMA7 | CA7 | DTGA3HS | PA7, PD6, PD3 |

12. TIMER B

12.1. Register

12.1.1. Register Map

Table 12-1. Timer B Register Map

| ADDRESS | NAME | DESCRIPTION | RESET VALUE |
|---|-----------------|---|-------------|
| Timer B | | | |
| 0x400E 0000 | TBCTL | Timer B control | 0x0000 0000 |
| 0x400E 0004 | TBPRD | Timer B period | 0x0000 0000 |
| 0x400E 0008 | TBCTR | Timer B counter | 0x0000 0000 |
| Timer B PWMB Capture and Compare | | | |
| 0x400E 0040 | TBCCTL0 | Timer B capture and compare 0 control | 0x0000 0000 |
| 0x400E 0044 | TBCTR0 | Timer B counter 0 | 0x0000 0000 |
| 0x400E 0048 | TBCCTL1 | Timer B capture and compare 1 control | 0x0000 0000 |
| 0x400E 004C | TBCTR1 | Timer B counter 1 | 0x0000 0000 |
| 0x400E 0050 | TBCCTL2 | Timer B capture and compare 2 control | 0x0000 0000 |
| 0x400E 0054 | TBCTR2 | Timer B counter 2 | 0x0000 0000 |
| 0x400E 0058 | TBCCTL3 | Timer B capture and compare 3 control | 0x0000 0000 |
| 0x400E 005C | TBCTR3 | Timer B counter 3 | 0x0000 0000 |
| Timer B Dead Time Generator | | | |
| 0x400E 00A0 | DTGB0CTL | Timer B dead time generator 0 control | 0x0000 0080 |
| 0x400E 00A4 | DTGB0LED | Timer B dead time generator 0 leading edge delay | 0x0000 0000 |
| 0x400E 00A8 | DTGB0TED | Timer B dead time generator 0 trailing edge delay | 0x0000 0000 |

12.1.2. TBCTL

Register 12-1. TBCTL (Timer B Control, 0x400E 0000)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|---|
| 31:14 | Reserved | RO | 0x0 | Reserved |
| 13 | DTGCLK | RW | 0x0 | DTGBx clock select 1b: DTGBx use clock after TBCTL.CLKDIV 0b: DTGBx use clock selected by TBCTL.CLK |
| 12 | SYNC | RW | 0x0 | Timer B synchronization 1b: Synchronize Timer B, enable SYNC_IN 0b: Do not synchronize Timer B, disabled SYNC_IN |
| 11:10 | MODE | RW | 0x0 | Timer B Mode 11b: reserved 10b: up / down 01b: up 00b: disabled |
| 9 | CLK | RW | 0x0 | Timer B clock input source 1b: ACLK 0b: HCLK |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|--|
| 8:6 | CLKDIV | RW | 0x0 | Timer B input clock divider 111b: / 128 110b: / 64 101b: /32 100b: /16 011b: /8 010b: /4 001b: /2 000b: /1 |
| 5 | INTEN | RW | 0x0 | Timer B interrupt enable 1b: enable Timer B interrupt 0b: disable Timer B interrupt |
| 4 | INT | RW1C | 0x0 | Timer B interrupt 1b: interrupt, clear by write 1b 0b: no interrupt |
| 3 | SS | RW | 0x0 | Timer B single shot 1b: single shot mode 0b: continuous timer mode |
| 2 | CLR | RW | 0x0 | Timer B clear 1b: Clear Timer B, hold Timer B in reset and set SYNC_OUT 0b: Do not clear Timer and clear SYNC_OUT |
| 1 | Reserved | RO | 0x0 | Reserved |
| 0 | PRDL | RW | 0x0 | Timer B TBPRD update 1b: Latch new TBPRD value when Timer B counting down, TBCTR value = 0x1 and TBCTL.MODE = 10b 0b: Latch new TBPRD value when Timer B counting up and TBCTR value = TBPRD – 0x1. |

12.1.3. TBPRD

Register 12-2. TBPRD (Timer B Period, 0x400E 0004)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|----------------------|
| 31:16 | Reserved | RO | 0 | Reserved |
| 15:0 | PERIOD | RW | 0x0 | Timer B period value |

12.1.4. TBCTR

Register 12-3. TBCTR (Timer B Counter, 0x400E 0008)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|-------------------------------|
| 31:16 | Reserved | RO | 0x0 | Reserved |
| 15:0 | CTR | RO | 0x0 | Current Timer B counter value |

12.1.5. TBCC0CTL

Register 12-4. TBCC0CTL (Timer B PWMB0 Capture and Compare Control, 0x400E 0040)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|-------------|
| 31:5 | Reserved | RO | 0x0 | Reserved |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|----------------|--------|-------|---|
| 4 | CCMODE | RW | 0x0 | Capture and compare mode 1b: Capture mode PWMB0 input 0b: Compare mode PWMB0 output |
| 3 | CCINTEN | RW | 0x0 | Capture and compare interrupt enable 1b: enable interrupt 0b: disable interrupt |
| 2 | CCINT | RW1C | 0x0 | Capture and compare interrupt 1b: interrupt, clear by write 1b 0b: no interrupt detected |
| 1:0 | CCEDG | RW | 0x0 | Capture mode edge detect PWMB0 11b: reserved 10b: high to low transition and low to high transition 01b: low to high transition only 00b: high to low transition only |

12.1.6. TBCC0CTR

Register 12-5. TBCC0CTR (Timer B PWMB0 Capture and Compare Counter, 0x400E 0044)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|--|
| 31:16 | Reserved | RO | 0x0 | Reserved |
| 15:0 | CCCTR | RW | 0x0 | Counter value for PWMB0 compare mode or counter value for PWMB0 capture mode |

12.1.7. TBCC1CTL

Register 12-6. TBCC1CTL (Timer B PWMB1 Capture and Compare Control, 0x400E 0048)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:5 | Reserved | RO | 0x0 | Reserved |
| 4 | CCMODE | RW | 0x0 | Capture and compare mode 1b: Capture mode PWMB1 input 0b: Compare mode PWMB1 output |
| 3 | CCINTEN | RW | 0x0 | Capture and compare interrupt enable 1b: enable interrupt 0b: disable interrupt |
| 2 | CCINT | RW1C | 0x0 | Capture and compare interrupt 1b: interrupt, clear by write 1b 0b: no interrupt detected |
| 1:0 | CCEDG | RW | 0x0 | Capture mode edge detect PWMB1 11b: reserved 10b: high to low transition and low to high transition 01b: low to high transition only 00b: high to low transition only |

12.1.8. TBCC1CTR

Register 12-7. TBCC1CTR (Timer B PWMB1 Capture and Compare Counter, 0x400E 004C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|-------------|
| 31:16 | Reserved | RO | 0x0 | Reserved |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-------|--------|-------|--|
| 15:0 | CCCTR | RW | 0x0 | Counter value for PWMB1 compare mode or counter value for PWMB1 capture mode |

12.1.9. TBCC2CTL

Register 12-8. TBCC2CTL (Timer B PWMB2 Capture and Compare Control, 0x400E 0050)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|----------|--------|-------|---|
| 31:5 | Reserved | RO | 0x0 | Reserved |
| 4 | CCMODE | RW | 0x0 | Capture and compare mode 1b: Capture mode PWMB2 input 0b: Compare mode PWMB2 output |
| 3 | CCINTEN | RW | 0x0 | Capture and compare interrupt enable 1b: enable interrupt 0b: disable interrupt |
| 2 | CCINT | RW1C | 0x0 | Capture and compare interrupt 1b: interrupt, clear by write 1b 0b: no interrupt detected |
| 1:0 | CCEDG | RW | 0x0 | Capture mode edge detect PWMB2 11b: reserved 10b: high to low transition and low to high transition 01b: low to high transition only 00b: high to low transition only |

12.1.10. TBCC2CTR

Register 12-9. TBCC2CTR (Timer B PWMB2 Capture and Compare Counter, 0x400E 0054)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|----------|--------|-------|--|
| 31:16 | Reserved | RO | 0x0 | Reserved |
| 15:0 | CCCTR | RW | 0x0 | Counter value for PWMB2 compare mode or counter value for PWMB2 capture mode |

12.1.11. TBCC3CTL

Register 12-10. TBCC3CTL (Timer B PWMB3 Capture and Compare Control, 0x400E 0058)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|----------|--------|-------|--|
| 31:5 | Reserved | RO | 0x0 | Reserved |
| 4 | CCMODE | RW | 0x0 | Capture and compare mode 1b: Capture mode PWMB3 input 0b: Compare mode PWMB3 output |
| 3 | CCINTEN | RW | 0x0 | Capture and compare interrupt enable 1b: enable interrupt 0b: disable interrupt |
| 2 | CCINT | RW1C | 0x0 | Capture and compare interrupt 1b: interrupt, clear by write 1b 0b: no interrupt detected |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|--------------|--------|-------|---|
| 1:0 | CCEDG | RW | 0x0 | Capture mode edge detect PWMB3 11b: reserved 10b: high to low transition and low to high transition 01b: low to high transition only 00b: high to low transition only |

12.1.12. TBCC3CTR

Register 12-11. TBCC3CTR (Timer B PWMB3 Capture and Compare Counter, 0x400E 005C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|--|
| 31:16 | Reserved | RO | 0x0 | Reserved |
| 15:0 | CCCTR | RW | 0x0 | Counter value for PWMB3 compare mode or counter value for PWMB3 capture mode |

12.1.13. DTGB0CTL

Register 12-12. DTGB0CTL (Timer B Dead Time Generator 0 Control, 0x400E 00A0)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | BYPASS | RW | 0x1 | Bypass dead time generator 1b: DTGB0 bypass active, DTGB0LS = PWMB0, DTGB0HS = PWMB1 0b: DTGB0 bypass inactive, dead time inserted to DTGB0LS and DTGB0HS, DTGB0LS = PWMB1, DTGB0HS = PWMB1 |
| 6 | OTP | RW | 0x0 | One Time Preservation 1b: DTGB0HS high time is same as PWMB1 high time and is shifted by DTGB0LED 0b: DTGB0HS high time is reduced by DTGB0LED |
| 5 | INVHS | RW | 0x0 | Invert DTGB0HS output signal 1b: invert DTGB0HS 0b: do not invert DTGB0HS |
| 4 | INVLS | RW | 0x0 | Invert DTGB0LS output signal 1b: invert DTGB0LS 0b: do not invert DTGB0LS |
| 3:0 | Reserved | RO | 0x0 | Reserved |

12.1.14. DTGB0LED

Register 12-13. DTGB0LED (Timer B Dead Time Generator 0 Leading Edge Delay, 0x400E 00A4)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|---|
| 31:12 | Reserved | RO | 0x0 | Reserved |
| 11:0 | LED | RW | 0x0 | Counter value DTGB0 leading edge dead time in clock cycles defined by TBCTL.DTGCLK |

12.1.15. DTGB0TED


Register 12-14. DTGB0TED (Timer B Dead Time Generator 0 Trailing Edge Delay, 0x400E 00A8)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|----------|--------|-------|---|
| 31:12 | Reserved | RO | 0x0 | Reserved |
| 11:0 | TED | RW | 0x0 | Counter value DTGB0 trailing edge dead time in clock cycles defined by TBCTL.DTGCLK |

12.2. Details of Operation

12.2.1. Block Diagram

Figure 12-1. Timer B



12.2.2. Configuration

Following blocks need to be configured for correct use of the Timer B:

- Clock Control System (CCS)
- Nested Vectored Interrupt Controller (NVIC)
- IO Controller
- Gate Driver
- Auto sequencing controller (ASC)
- Timer A
- Timer C
- Timer D
-

12.2.3. Timer B Block

The timer B block consist of a 16-bit timer with up mode or up/down mode with 4 PWM/capture units and 1 dead-time generator unit.

12.2.4. Timer

Once enabled the timer counts up to the Timer B period value **TBPRD**. The **TBPRD** register can be written to while the timer is running, the new **TBPRD** value will be latched when the counter reaches old **TBPRD** value in up mode. In up/down mode there is the option to latch the new **TBPRD** value when counter counts back to zero.

TBCTL.PRDL configures when the timer will be updated with the new **TBPRD** value in up/down mode.

The current timer value is accessible with the timer B counter value register **TBCTR**.

12.2.5. Register update

The **TBPRD**, **TBCCxCTR** register can be written to while the timer is running, the new **TBPRD**, **TBCCxCTR** value will be latched when the counter reaches old **TBPRD** value in up mode. In up/down mode there is the option to latch the new **TBPRD**, **TBCCxCTR** values when counter counts back to zero. **TBCTL.PRDL** configures when the timer will be updated with the new **TBPRD**, **TBCCxCTR** value in up/down mode.

12.2.6. Timer Modes

The timer supports 3 modes of operation: disabled, up and up/down using **TBCTL.MODE**.

By default, the timer mode is disabled. When the timer is disabled, the timer counter does not increment or decrement. If the timer is disabled when previously in up or up/down mode, then the timer counter stops where it is. If the timer is re-enabled by putting it back into up or up/down modes, then the counter continues from the point at which it was disabled. To reset the current counter value **TBCTR** to zero use **TBCTL.CLR**.

In up mode, the timer starts counting from 0 up to the value of **TBPRD**. When the timer counter reaches the value of **TBPRD**, then the timer counter is reset to a value of 0. This mode is typically used for timed events or edge-aligned PWM output.

In up/down mode, the timer starts counting from 0 up to the value of **TBPRD**, and then back down to a value of 0. This timer mode is typically used for center-aligned PWM output. It can also be used for timed events, and will allow a longer timer range due to the fact it counts up and down.

12.2.7. Single Shot Mode

The timer can be configured to run either once or continuously.

When the timer is configured in single shot mode using **TBCTL.SS** the timer will only count to **TBPRD** value and stops in up mode. In up/down mode the timer will count to **TBPRD** and back to zero only once.

To start the timer in single-shot mode, **TBCTL.SS** must be set. The timer will start when **TBCTL.CLR** is set. To re-start a single-shot timer, **TBCTL.CLR** must be reset, and then set again.

12.2.8. Input Clock And Pre-Scaler

The timer can be configured to use HCLK or ACLK using **TBCTL.CLK**. The input clock for the can be divided further down from /1 to /128 using the **TBCTL.CLKDIV**.

12.2.9. Timer Synchronization

The Timer A, B, C, D in the system have the ability to have synchronization between them. Each timer has a synchronization in signal (SYNC_IN) and the synchronization out signal (SYNC_OUT).

Timer B can be synchronized with Timer C, and D with timer B as master. Timer B can be synchronized with Timer A as slave.

The timer asserts the SYNC_OUT pulse when the **TBCTL.CLR** bit is set and de-asserts the SYNC_OUT pulse when the **TBCTL.CLR** bit is cleared.

Each timer C, or D that need to be synchronized as slave with master timer B need to set the **TxCTL.SYNC** bit. If this is bit is not set, then the sync_in signal is ignored and the timer operates independently.

When the **TxCTL.SYNC** bit is set and the **SYNC_IN** signal is asserted, the timer clears the timer counter. The timer counter is also cleared anytime the **TxCTL.CLR** bit is set to a 1. When the **TxCTL.SYNC** bit is set and the **SYNC_IN** signal is de-asserted and the timer mode is either up or up/down, then the timer will start counting. The timer will not start counting when the mode is set to up or up/down unless the **SYNC_IN** signal is de-asserted when **TxCTL.SYNC** is set.

NOTE:

In order for this feature to work correctly, all timers that are synchronized must be set to the same mode (up or up/down), with the same timer pre-scaler, timer clock input and timer period.

To enable synchronized timers, the following steps should be followed:

1. All slave timers B, C, or D are configured with the selected timer input clock, timer pre-scaler, timer period and set the **TxCTL.SYNC** bit. The timer should still be set to disabled at this point.
2. The master timer A, or B is configured with the same timer input clock, timer pre-scaler, timer period and sets the **TxCTL.CLR** bit. This should clear all timer counters of the master and slave timers.
3. The slave timers set the timer mode to the desired state (either up or up/down).
4. The master timer sets the timer mode to either up or up/down and clears the **TxCTL.CLR** bit. This should start the master and all slave timers simultaneously based on the selected timer clock input.
5. Once configured as above, all timers can be disabled by the master setting **TxCTL.CLR** signal, to assert the **SYNC_OUT** signal. The timers can be re-enabled by clearing the **TxCTL.CLR** bit, which de-asserts the **SYNC_OUT** signal.
- 6.

12.2.10. PWM/Compare Units

Timer B supports up to 4 PWM/Capture units PWMB0 to PWMB3. Each PWM/Compare unit can be configured independently in PWM mode or capture mode using **TBCCxCTL.CCMODE**.

12.2.10.1. PWM Mode

The PWM mode is enabled with setting **TBCCxCTL.CCMODE** to 0.


The timer configuration allows either edge-aligned (timer in up mode) or center-aligned (timer in up/down mode) modes of PWM operation.

In both edge-aligned and center-aligned modes of operation, the timer block outputs a PWM waveform that starts out high at a **TBCTR** value of 0 and then transitions to low when **TBCTR** counts up to **TBCCxCTR** compare value.

To configure a duty cycle of 0%, the **TBCCxCTR** should be set to 0; to configure a duty cycle of 100%, the **TBCCxCTR** value should be set to a value greater than or equal to **TBPRD**.

The polarity of the timer PWM outputs are not configurable. Adjustments to the polarity of the PWM outputs may be adjusted in the Dead-Time Generator (DTG) unit connected to the timer peripheral for each output independently.

Figure 12-2. PWMB0 and PWMB1 Example Using Timer B Up Mode and Up/Down Mode




12.2.10.2. Capture Mode

The Capture mode is enabled with setting **TBCCxCTL.CCMODE** to 1. The trip condition for capture mode can be configured using **TBCCxCTL.CCEDGE**, high-to-low signal edge transition, low-to-high signal edge transition or both.

When trip condition is detected the actual **TBCTR** value is copied into **TBCCxCTR**.

Figure 12-3. CB0 and CB1 Capture Example



12.2.11. Timer and PWM/Capture Interrupt

The timer may generate interrupt based on the base timer wrap, or when a capture and compare event occurs.

In the base timer both up and up/down timer modes allow an interrupt to be generated when the count reaches 0. Each time the count reaches zero, the **TBCTL.INT** interrupt flag is set. If the interrupt is enabled using the **TBCTL.INTEN**, then the Timer IRQ signal will be asserted to the CPU. The interrupt flag may be cleared by writing a 1 to the **TBCTL.INT** interrupt flag bit.

In the capture and compare PWM units, each time a compare threshold is reached or each time a capture event is detected the **TBCCxCTL.CCINT** bit will be set for that particular timer unit. If the interrupt is enabled via the **TBCCxCTL.CCINTEN**, then the Timer IRQ signal will be asserted to the CPU. The interrupt flag may be cleared by writing a 1 to the **TBCCxCTL.CCINT** interrupt flag bit.

The timer IRQ signal will be asserted if any of the timer interrupt flags **TBCTL.INT** or **TBCCxCTL.CCINT** are set. The Timer IRQ signal will be de-asserted when all of the timer interrupt flags are cleared.

12.2.12. Dead-Time Generator

The dead-time generator can be configured to introduce dead-time for a complementary PWM output. The Timer B block supports up to 1 dead time generator.

12.2.12.1. Dead Time Input Clock Selection

The clock source for the DTGB0 can be selected using **TBCTL.DTGCLK**.

Clear **TBCTL.DTGCLK** to 0 to use clock source selected by **TBCTL.CLK** directly to use higher resolution for dead time insertion.

Set **TBCTL.DTGCLK** to 1 to use divided clock source selected by **TBCTL.CLK** and **TBCTL.CLKDIV** divider to use the same dead time resolution as Timer B.

12.2.12.2. Dead Time Range

The resolution for leading edge and trailing edge dead time is 12bits. Leading and trailing edge can be set independently using **DTGB0LED** and **DTGB0TED**.


12.2.12.3. Bypass Mode

Set **DTGB0CTL.BYPASS** to 0 to enable dead time insertion.

Set **DTGB0CTL.BYPASS** to 1 to enable bypass mode, no dead time is inserted, PWMB1 is routed to DTGB0HS and PWMB0 is routed to DTGB0LS.

The DTGB0HS and DTGB0LS signals can be inverted in bypass mode.

Figure 12-4. DTGB0 Bypass Example




12.2.12.4. Inverting PWM Signal

The DTG output signals DTGB0HS and DTGB0LS can be inverted independently.

Set **DTGB0CTL.INVHS** to invert DTGB0HS signal.

Set **DTGB0CTL.INVLS** to invert DTGB0LS signal.

Figure 12-5. DTGB0 Bypass and Inverting LS Example



12.2.12.5. Dead Time Insertion


Set **DTGB0CTL.BYPASS** to 0 to enable dead time insertion. In dead time insertion mode only PWMB1 signal is used to generate DTGB0HS and DTGB0LS. PWMB0 signal is ignored and can be used for other purposes.

Set **DTGB0LED** for desired leading-edge and **DTGB0TED** for desired trailing edge in clock-cycles defined by **TBCTL.DTGCLK** clock source

NOTE:

In dead time insertion mode the DTGB0LS signal is automatically inverted compared to PWMB1 signal. Set **DTGB0CTL.INVLS** to 0, if this is desired behavior.

Figure 12-6. DTGB0 LED and TED Example




12.2.12.6. Dead Time Insertion with On Time Preservation

Set **DTGB0CTL.OTP** to 1 to enable on time preservation. In this mode the DTGB0HS is same as PWMB1 on time.

NOTE:

In dead time insertion mode the DTGB0LS signal is automatically inverted compared to PWMB1 signal. Set **DTGB0CTL.INVLS** to 0, if this is desired behavior.

Figure 12-7. DTGB0 LED and TED with On Time Preservation Example



12.2.13. PWM Output and Capture Input Pin Selection

Each of the DTGB0HS, DTGB0LS outputs, and CBx inputs can be routed to different I/Os, allowing great flexibility in pin assignments.

In capture mode only one I/O should be enabled as input to the capture. If more than one pin input is enabled, the capture might not work properly.

Note:

Not all pins are available pending package option, consult data sheet for available pins and signals.

Table 12-2. Timer B Signal to Pin Mapping

| PWM | CAPTURE | DEADTIME | PINS |
|-------|---------|----------|---------------|
| PWMB0 | CB0 | DTGB0LS | PA3, PA6, PD2 |
| PWMB1 | CB1 | DTGB0HS | PD3, PD6 |
| PWMB2 | CB2 | N/A | N/A |
| PWMB3 | CB3 | N/A | N/A |

13. TIMER C

13.1. Register

13.1.1. Register Map

Table 13-1. Timer C Register Map

| ADDRESS | NAME | DESCRIPTION | RESET VALUE |
|---|-----------------|---|-------------|
| Timer C | | | |
| 0x400F 0000 | TCCTL | Timer C control | 0x0000 0000 |
| 0x400F 0004 | TCPRD | Timer C period | 0x0000 0000 |
| 0x400F 0008 | TCCTR | Timer C counter | 0x0000 0000 |
| Timer C PWMC Capture and Compare | | | |
| 0x400F 0040 | TCCCTL0 | Timer C capture and compare 0 control | 0x0000 0000 |
| 0x400F 0044 | TCCTR0 | Timer C counter 0 | 0x0000 0000 |
| 0x400F 0048 | TCCCTL1 | Timer C capture and compare 1 control | 0x0000 0000 |
| 0x400F 004C | TCCTR1 | Timer C counter 1 | 0x0000 0000 |
| Timer C Dead Time Generator | | | |
| 0x400F 00A0 | DTGC0CTL | Timer C dead time generator 0 control | 0x0000 0080 |
| 0x400F 00A4 | DTGC0LED | Timer C dead time generator 0 leading edge delay | 0x0000 0000 |
| 0x400F 00A8 | DTGC0TED | Timer C dead time generator 0 trailing edge delay | 0x0000 0000 |

13.1.2. TCCTL

Register 13-1. TCCTL (Timer C Control, 0x400F 0000)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|--|
| 31:14 | Reserved | RO | 0x0 | Reserved |
| 13 | DTGCLK | RW | 0x0 | DTGCx clock select 1b: DTGCx use clock after TCCTL.CLKDIV 0b: DTGCx use clock selected by TCCTL.CLK |
| 12 | SYNC | RW | 0x0 | Timer C synchronization 1b: Synchronize Timer C, enable SYNC_IN 0b: Do not synchronize Timer C, disabled SYNC_IN |
| 11:10 | MODE | RW | 0x0 | Timer C Mode 11b: reserved 10b: up / down 01b: up 00b: disabled |
| 9 | CLK | RW | 0x0 | Timer C clock input source 1b: ACLK 0b: HCLK |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|--|
| 8:6 | CLKDIV | RW | 0x0 | Timer C input clock divider 111b: /128 110b: /64 101b: /32 100b: /16 011b: /8 010b: /4 001b: /2 000b: /1 |
| 5 | INTEN | RW | 0x0 | Timer C interrupt enable 1b: enable Timer C interrupt 0b: disable Timer C interrupt |
| 4 | INT | RW1C | 0x0 | Timer C interrupt 1b: interrupt, clear by write 1b 0b: no interrupt |
| 3 | SS | RW | 0x0 | Timer C single shot 1b: single shot mode 0b: continuous timer mode |
| 2 | CLR | RW | 0x0 | Timer C clear 1b: Clear Timer C, hold Timer C in reset and set SYNC_OUT 0b: Do not clear Timer and clear SYNC_OUT |
| 1 | Reserved | RO | 0x0 | Reserved |
| 0 | PRDL | RW | 0x0 | Timer C TCPRD update 1b: Latch new TCPRD value when Timer C counting down, TCCTR value = 0x1 and TCCTL.MODE = 10b 0b: Latch new TCPRD value when Timer C counting up and TCCTR value = TCPRD – 0x1. |

13.1.3. TCPRD

Register 13-2. TCPRD (Timer C Period, 0x400F 0004)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|----------------------|
| 31:16 | Reserved | RO | 0 | Reserved |
| 15:0 | PERIOD | RW | 0x0 | Timer C period value |

13.1.4. TCCTR

Register 13-3. TCCTR (Timer C Counter, 0x400F 0008)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|-------------------------------|
| 31:16 | Reserved | RO | 0x0 | Reserved |
| 15:0 | CTR | RW | 0x0 | Current Timer C counter value |

13.1.5. TCCC0CTL

Register 13-4. TCCC0CTL (Timer C PWM0 Capture and Compare Control, 0x400F 0040)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|-------------|
| 31:5 | Reserved | RO | 0x0 | Reserved |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|----------------|--------|-------|---|
| 4 | CCMODE | RW | 0x0 | Capture and compare mode 1b: Capture mode PWMCO input 0b: Compare mode PWMCO output |
| 3 | CCINTEN | RW | 0x0 | Capture and compare interrupt enable 1b: enable interrupt 0b: disable interrupt |
| 2 | CCINT | RW1C | 0x0 | Capture and compare interrupt 1b: interrupt, clear by write 1b 0b: no interrupt detected |
| 1:0 | CCEDG | RW | 0x0 | Capture mode edge detect PWMCO 11b: reserved 10b: high to low transition and low to high transition 01b: low to high transition only 00b: high to low transition only |

13.1.6. TCCC0CTR

Register 13-5. TCCC0CTR (Timer C PWMCO Capture and Compare Counter, 0x400F 0044)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|--|
| 31:16 | Reserved | RO | 0x0 | Reserved |
| 15:0 | CCCTR | RW | 0x0 | Counter value for PWMCO compare mode or counter value for PWMCO capture mode |

13.1.7. TCCC1CTL

Register 13-6. TCCC1CTL (Timer C PWMCO Capture and Compare Control, 0x400F 0048)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:5 | Reserved | RO | 0x0 | Reserved |
| 4 | CCMODE | RW | 0x0 | Capture and compare mode 1b: Capture mode PWMCO input 0b: Compare mode PWMCO output |
| 3 | CCINTEN | RW | 0x0 | Capture and compare interrupt enable 1b: enable interrupt 0b: disable interrupt |
| 2 | CCINT | RW1C | 0x0 | Capture and compare interrupt 1b: interrupt, clear by write 1b 0b: no interrupt detected |
| 1:0 | CCEDG | RW | 0x0 | Capture mode edge detect PWMCO 11b: reserved 10b: high to low transition and low to high transition 01b: low to high transition only 00b: high to low transition only |

13.1.8. TCCC1CTR

Register 13-7. TCCC1CTR (Timer C PWMCO Capture and Compare Counter, 0x400F 004C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|-------------|
| 31:16 | Reserved | RO | 0x0 | Reserved |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-------|--------|-------|--|
| 15:0 | CCCTR | RW | 0x0 | Counter value for PWMC1 compare mode or counter value for PWMC1 capture mode |

13.1.9. DTGC0CTL

Register 13-8. DTGC0CTL (Timer C Dead Time Generator 0 Control, 0x400F 00A0)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|----------|--------|-------|---|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | BYPASS | RW | 0x1 | Bypass dead time generator 1b: DTGC0 bypass active, DTGC0LS = PWMC0, DTGC0HS = PWMC1 0b: DTGC0 bypass inactive, dead time inserted to DTGC0LS and DTGC0HS, DTGC0LS = PWMC1, DTGC0HS = PWMC1 |
| 6 | OTP | RW | 0x0 | One Time Preservation 1b: DTGC0HS high time is same as PWMC1 high time is shifted by DTGC0LED 0b: DTGC0HS high time is reduced by DTGC0LED |
| 5 | INVHS | RW | 0x0 | Invert DTGC0HS output signal 1b: invert DTGC0HS 0b: do not invert DTGC0HS |
| 4 | INVLS | RW | 0x0 | Invert DTGC0LS output signal 1b: invert DTGC0LS 0b: do not invert DTGC0LS |
| 3:0 | Reserved | RO | 0x0 | Reserved |

13.1.10. DTGC0LED

Register 13-9. DTGC0LED (Timer C Dead Time Generator 0 Leading Edge Delay, 0x400F 00A4)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|----------|--------|-------|---|
| 31:12 | Reserved | RO | 0x0 | Reserved |
| 11:0 | LED | RW | 0x0 | Counter value DTGC0 leading edge dead time in clock cycles defined by TCCTL.DTGCLK |

13.1.11. DTGC0TED


Register 13-10. DTGC0TED (Timer C Dead Time Generator 0 Trailing Edge Delay, 0x400F 00A8)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|----------|--------|-------|--|
| 31:12 | Reserved | RO | 0x0 | Reserved |
| 11:0 | TED | RW | 0x0 | Counter value DTGC0 trailing edge dead time in clock cycles defined by TCCTL.DTGCLK |

13.2. Details of Operation

13.2.1. Block Diagram

Figure 13-1. Timer C



13.2.2. Configuration

Following blocks need to be configured for correct use of the Timer C:

- Clock Control System (CCS)
- Nested Vectored Interrupt Controller (NVIC)
- IO Controller
- Gate Driver
- Auto sequencing controller (ASC)
- Timer A
- Timer B
- Timer D
-

13.2.3. Timer C Block

The timer C block consist of a 16-bit timer with up mode or up/down mode with 2 PWM/capture units and 1 dead-time generator unit.

13.2.4. Timer

Once enabled the timer counts up to the Timer C period value **TCPRD**. The **TCPRD** register can be written to while the timer is running, the new **TCPRD** value will be latched when the counter reaches old **TCPRD** value in up mode. In up/down mode there is the option to latch the new **TCPRD** value when counter counts back to zero.

TCCTL.PRDL configures when the timer will be updated with the new **TCPRD** value in up/down mode.

The current timer value is accessible with the timer C counter value register **TCCTR**.

13.2.5. Register update

The **TCPRD**, **TCCCxCTR** register can be written to while the timer is running, the new **TCPRD**, **TCCCxCTR** value will be latched when the counter reaches old **TCPRD** value in up mode. In up/down mode there is the option to latch the new **TCPRD**, **TCCCxCTR** values when counter counts back to zero. **TCCTL.PRDL** configures when the timer will be updated with the new **TCPRD**, **TCCCxCTR** value in up/down mode.

13.2.6. Timer Modes

The timer supports 3 modes of operation: disabled, up and up/down using **TCCTL.MODE**.

By default, the timer mode is disabled. When the timer is disabled, the timer counter does not increment or decrement. If the timer is disabled when previously in up or up/down mode, then the timer counter stops where it is. If the timer is re-enabled by putting it back into up or up/down modes, then the counter continues from the point at which it was disabled. To reset the current counter value **TCCTR** to zero use **TCCTL.CLR**.

In up mode, the timer starts counting from 0 up to the value of **TCPRD**. When the timer counter reaches the value of **TCPRD**, then the timer counter is reset to a value of 0. This mode is typically used for timed events or edge-aligned PWM output.

In up/down mode, the timer starts counting from 0 up to the value of **TCPRD**, and then back down to a value of 0. This timer mode is typically used for center-aligned PWM output. It can also be used for timed events, and will allow a longer timer range due to the fact it counts up and down

13.2.7. Single Shot Mode

The timer can be configured to run either once or continuously.

When the timer is configured in single shot mode using **TCCTL.SS** the timer will only count to **TCPRD** value and stops in up mode. In up/down mode the timer will count to **TCPRD** and back to zero only once.

To start the timer in single-shot mode, **TCCTL.SS** must be set. The timer will start when **TCCTL.CLR** is set. To re-start a single-shot timer, **TCCTL.CLR** must be reset, and then set again.

13.2.8. Input clock and Pre-scaler

The timer can be configured to use HCLK or ACLK using **TCCTL.CLK**. The input clock for the can be divided further down from /1 to /128 using the **TCCTL.CLKDIV**.

13.2.9. Timer synchronization

The Timer A, B, C, D in the system have the ability to have synchronization between them. Each timer has a synchronization in signal (SYNC_IN) and the synchronization out signal (SYNC_OUT).

Timer C can be synchronized with Timer D as master. Timer B can be synchronized with Timer A, and B as slave.

The timer asserts the SYNC_OUT pulse when the **TCCTL.CLR** bit is set and de-asserts the SYNC_OUT pulse when the **TCCTL.CLR** bit is cleared.

If timer D that need to be synchronized as slave with master timer C need to set the **TxCTL.SYNC** bit. If this is bit is not set, then the sync_in signal is ignored and the timer operates independently.

When the **TxCTL.SYNC** bit is set and the **SYNC_IN** signal is asserted, the timer clears the timer counter. The timer counter is also cleared anytime the **TxCTL.CLR** bit is set to a 1. When the **TxCTL.SYNC** bit is set and the **SYNC_IN** signal is de-asserted and the timer mode is either up or up/down, then the timer will start counting. The timer will not start counting when the mode is set to up or up/down unless the **SYNC_IN** signal is de-asserted when **TxCTL.SYNC** is set.

NOTE:

In order for this feature to work correctly, all timers that are synchronized must be set to the same mode (up or up/down), with the same timer pre-scaler, timer clock input and timer period.

To enable synchronized timers, the following steps should be followed:

1. The slave timer C, D is configured with the selected timer input clock, timer pre-scaler, timer period and set the **TxCTL.SYNC** bit. The timer should still be set to disabled at this point.
2. The master timer A, or B is configured with the same timer input clock, timer pre-scaler, timer period and sets the **TxCTL.CLR** bit. This should clear all timer counters of the master and slave timers.
3. The slave timers set the timer mode to the desired state (either up or up/down).
4. The master timer sets the timer mode to either up or up/down and clears the **TxCTL.CLR** bit. This should start the master and all slave timers simultaneously based on the selected timer clock input.
5. Once configured as above, all timers can be disabled by the master setting **TxCTL.CLR** signal, to assert the **SYNC_OUT** signal. The timers can be re-enabled by clearing the **TxCTL.CLR** bit, which de-asserts the **SYNC_OUT** signal.

13.2.10. PWM/Compare Units

Timer C supports up to 2 PWM/Capture units PWMC0 to PWMC1. Each PWM/Compare unit can be configured independently in PWM mode or capture mode using **TCCCxCTL.CCMODE**.

13.2.10.1. PWM Mode

The PWM mode is enabled with setting **TCCCxCTL.CCMODE** to 0.


The timer configuration allows either edge-aligned (timer in up mode) or center-aligned (timer in up/down mode) modes of PWM operation.

In both edge-aligned and center-aligned modes of operation, the timer block outputs a PWM waveform that starts out high at a **TCCTR** value of 0 and then transitions to low when **TCCTR** counts up to **TCCCxCTR** compare value.

To configure a duty cycle of 0%, the **TCCCxCTR** should be set to 0; to configure a duty cycle of 100%, the **TCCCxCTR** value should be set to a value greater than or equal to **TCPRD**.

The polarity of the timer PWM outputs are not configurable. Adjustments to the polarity of the PWM outputs may be adjusted in the Dead-Time Generator (DTG) unit connected to the timer peripheral for each output independently.

Figure 13-2. PWM0 and PWM1 Example Using Timer C Up Mode and Up/Down Mode




13.2.10.2. Capture Mode

The Capture mode is enabled with setting **TCCCxCTL.CCMODE** to 1. The trip condition for capture mode can be configured using **TCCCxCTL.CCEDGE**, high-to-low signal edge transition, low-to-high signal edge transition or both.

When trip condition is detected the actual **TCCTR** value is copied into **TCCCxCTR**.

Figure 13-3. CC0 and CC1 Capture Example



13.2.11. Timer and PWM/Capture Interrupt

The timer may generate interrupt based on the base timer wrap, or when a capture and compare event occurs.

In the base timer both up and up/down timer modes allow an interrupt to be generated when the count reaches 0. Each time the count reaches zero, the **TCCTL.INT** interrupt flag is set. If the interrupt is enabled using the **TCCTL.INTEN**, then the Timer IRQ signal will be asserted to the CPU. The interrupt flag may be cleared by writing a 1 to the **TCCTL.INT** interrupt flag bit.

In the capture and compare PWM units, each time a compare threshold is reached or each time a capture event is detected the **TCCCxCTL.CCINT** bit will be set for that particular timer unit. If the interrupt is enabled via the **TCCCxCTL.CCINTEN**, then the Timer IRQ signal will be asserted to the CPU. The interrupt flag may be cleared by writing a 1 to the **TCCCxCTL.CCINT** interrupt flag bit.

The timer IRQ signal will be asserted if any of the timer interrupt flags **TCCTL.INT** or **TCCCxCTL.CCINT** are set. The Timer IRQ signal will be de-asserted when all of the timer interrupt flags are cleared.

13.2.12. Dead-Time Generator

The dead-time generator can be configured to introduce dead-time for a complementary PWM output. The Timer C block supports up to 1 dead time generator.

13.2.12.1. Dead Time Input Clock Selection

The clock source for the DTGC0 can be selected using **TCCTL.DTGCLK**.

Clear **TCCTL.DTGCLK** to 0 to use clock source selected by **TCCTL.CLK** directly to use higher resolution for dead time insertion.

Set **TCCTL.DTGCLK** to 1 to use divided clock source selected by **TCCTL.CLK** and **TCCTL.CLKDIV** divider to use the same dead time resolution as Timer C.

13.2.12.2. Dead Time Range

The resolution for leading edge and trailing edge dead time is 12bits. Leading and trailing edge can be set independently using **DTGC0LED** and **DTGC0TED**.


13.2.12.3. Bypass Mode

Set **DTGC0CTL.BYPASS** to 0 to enable dead time insertion.

Set **DTGC0CTL.BYPASS** to 1 to enable bypass mode, no dead time is inserted, PWMC1 is routed to DTGC0HS and PWMC0 is routed to DTGC0LS.

The DTGC0HS and DTGC0LS signals can be inverted in bypass mode.

Figure 13-4. DTGC0 Bypass Example




13.2.12.4. Inverting PWM Signal

The DTG output signals DTGC0HS and DTGC0LS can be inverted independently.

Set **DTGC0CTL.INVHS** to invert DTGC0HS signal.

Set **DTGC0CTL.INVLS** to invert DTGC0LS signal.

Figure 13-5. DTGC0 Bypass and Inverting LS Example



13.2.12.5. Dead Time Insertion


Set **DTGC0CTL.BYPASS** to 0 to enable dead time insertion. In dead time insertion mode only PWMC1 signal is used to generate DTGC0HS and DTGC0LS. PWMC0 signal is ignored and can be used for other purposes.

Set **DTGC0LED** for desired leading-edge and **DTGC0TED** for desired trailing edge in clock-cycles defined by **TCCTL.DTGCLK** clock source

NOTE:

In dead time insertion mode the DTGC0LS signal is automatically inverted compared to PWMC1 signal. Set **DTGC0CTL.INVLS** to 0, if this is desired behavior.

Figure 13-6. DTGC0 LED and TED Example




13.2.12.6. Dead Time Insertion With On Time Preservation

Set **DTGC0CTL.OTP** to 1 to enable on time preservation. In this mode the DTGC0HS is same as PWMC1 on time.

NOTE:

In dead time insertion mode the DTGC0LS signal is automatically inverted compared to PWMC1 signal. Set **DTGC0CTL.INVLS** to 0, if this is desired behavior.

Figure 13-7. DTGC0 LED and TED with On Time Preservation Example



13.2.13. PWM Output and Capture Input Pin Selection

Each of the DTGC0HS, DTGC0LS outputs, and CCx inputs can be routed to different I/Os, allowing great flexibility in pin assignments.

In capture mode only one I/O should be enabled as input to the capture. If more than one pin input is enabled, the capture might not work properly.

Note:

Not all pins are available pending package option, consult data sheet for available pins and signals.

Table 13-2. Timer C Signal to Pin Mapping

| PWM | CAPTURE | DEADTIME | PINS |
|--------|---------|----------|----------|
| PWM C0 | CC0 | DTGC0LS | PA4 |
| PWM C1 | CC1 | DTGC1LS | PA7, PD5 |

14. TIMER D

14.1. Register

14.1.1. Register Map

Table 14-1. Timer D Register Map

| ADDRESS | NAME | DESCRIPTION | RESET VALUE |
|---|-----------------|---|-------------|
| Timer D | | | |
| 0x4010 0000 | TDCTL | Timer D control | 0x0000 0000 |
| 0x4010 0004 | TDPRD | Timer D period | 0x0000 0000 |
| 0x4010 0008 | TDCTR | Timer D counter | 0x0000 0000 |
| Timer D PWMD Capture and Compare | | | |
| 0x4010 0040 | TDCCTL0 | Timer D capture and compare 0 control | 0x0000 0000 |
| 0x4010 0044 | TDCTR0 | Timer D counter 0 | 0x0000 0000 |
| 0x4010 0048 | TDCCTL1 | Timer D capture and compare 1 control | 0x0000 0000 |
| 0x4010 004C | TDCTR1 | Timer D counter 1 | 0x0000 0000 |
| Timer D Dead Time Generator | | | |
| 0x4010 00A0 | DTGD0CTL | Timer D dead time generator 0 control | 0x0000 0080 |
| 0x4010 00A4 | DTGD0LED | Timer D dead time generator 0 leading edge delay | 0x0000 0000 |
| 0x4010 00A8 | DTGD0TED | Timer D dead time generator 0 trailing edge delay | 0x0000 0000 |

14.1.2. TDCTL

Register 14-1. TDCTL (Timer D Control, 0x4010 0000)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|--|
| 31:14 | Reserved | RO | 0x0 | Reserved |
| 13 | DTGCLK | RW | 0x0 | DTGDx clock select 1b: DTGDx use clock after TDCTL.CLKDIV 0b: DTGDx use clock selected by TDCTL.CLK |
| 12 | SYNC | RW | 0x0 | Timer D synchronization 1b: Synchronize Timer D, enable SYNC_IN 0b: Do not synchronize Timer D, disabled SYNC_IN |
| 11:10 | MODE | RW | 0x0 | Timer D Mode 11b: reserved 10b: up / down 01b: up 00b: disabled |
| 9 | CLK | RW | 0x0 | Timer D clock input source 1b: ACLK 0b: HCLK |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|---|
| 8:6 | CLKDIV | RW | 0x0 | Timer D input clock divider 111b: / 128 110b: / 64 101b: /32 100b: /16 011b: /8 010b: /4 001b: /2 000b: /1 |
| 5 | INTEN | RW | 0x0 | Timer D interrupt enable 1b: enable Timer D interrupt 0b: disable Timer D interrupt |
| 4 | INT | RW1C | 0x0 | Timer D interrupt 1b: interrupt, clear by write 1b 0b: no interrupt |
| 3 | SS | RW | 0x0 | Timer D single shot 1b: single shot mode 0b: continuous timer mode |
| 2 | CLR | RW | 0x0 | Timer D clear 1b: Clear Timer D, hold Timer D in reset and set SYNC_OUT 0b: Do not clear Timer and clear SYNC_OUT |
| 1 | Reserved | RO | 0x0 | Reserved |
| 0 | PRDL | RW | 0x0 | Timer D TDPRD update 1b: Latch new TDPRD value when Timer D counting down, TDCTR value = 0x1 and TDCTL.MODE = 10b 0b: Latch new TDPRD value when Timer D counting up and TDCTR value = TDPRD – 0x1. |

14.1.3. TDPRD

Register 14-2. TDPRD (Timer D Period, 0x4010 0004)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|----------------------|
| 31:16 | Reserved | RO | 0 | Reserved |
| 15:0 | PERIOD | RW | 0x0 | Timer D period value |

14.1.4. TDCTR

Register 14-3. TDCTR (Timer D Counter, 0x4010 0008)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|-------------------------------|
| 31:16 | Reserved | RO | 0x0 | Reserved |
| 15:0 | CTR | RW | 0x0 | Current Timer D counter value |

14.1.5. TDCC0CTL

Register 14-4. TDCC0CTL (Timer D PWMD0 Capture and Compare Control, 0x4010 0040)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|-------------|
| 31:5 | Reserved | RO | 0x0 | Reserved |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|----------------|--------|-------|---|
| 4 | CCMODE | RW | 0x0 | Capture and compare mode 1b: Capture mode PWMD0 input 0b: Compare mode PWMD0 output |
| 3 | CCINTEN | RW | 0x0 | Capture and compare interrupt enable 1b: enable interrupt 0b: disable interrupt |
| 2 | CCINT | RW1C | 0x0 | Capture and compare interrupt 1b: interrupt, clear by write 1b 0b: no interrupt detected |
| 1:0 | CCEDG | RW | 0x0 | Capture mode edge detect PWMD0 11b: reserved 10b: high to low transition and low to high transition 01b: low to high transition only 00b: high to low transition only |

14.1.6. TDCC0CTR

Register 14-5. TDCC0CTR (Timer D PWMD0 Capture and Compare Counter, 0x4010 0044)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|--|
| 31:16 | Reserved | RO | 0x0 | Reserved |
| 15:0 | CCCTR | RW | 0x0 | Counter value for PWMD0 compare mode or counter value for PWMD0 capture mode |

14.1.7. TDCC1CTL

Register 14-6. TDCC1CTL (Timer D PWMD1 Capture and Compare Control, 0x4010 0048)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:5 | Reserved | RO | 0x0 | Reserved |
| 4 | CCMODE | RW | 0x0 | Capture and compare mode 1b: Capture mode PWMD1 input 0b: Compare mode PWMD1 output |
| 3 | CCINTEN | RW | 0x0 | Capture and compare interrupt enable 1b: enable interrupt 0b: disable interrupt |
| 2 | CCINT | RW1C | 0x0 | Capture and compare interrupt 1b: interrupt, clear by write 1b 0b: no interrupt detected |
| 1:0 | CCEDG | RW | 0x0 | Capture mode edge detect PWMD1 11b: reserved 10b: high to low transition and low to high transition 01b: low to high transition only 00b: high to low transition only |

14.1.8. TDCC1CTR

Register 14-7. TDCC1CTR (Timer D PWMD1 Capture and Compare Counter, 0x4010 004C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|-------------|
| 31:16 | Reserved | RO | 0x0 | Reserved |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-------|--------|-------|--|
| 15:0 | CCCTR | RW | 0x0 | Counter value for PWMD1 compare mode or counter value for PWMD1 capture mode |

14.1.9. DTGD0CTL

Register 14-8. DTGD0CTL (Timer D Dead Time Generator 0 Control, 0x4010 00A0)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|----------|--------|-------|---|
| 31:8 | Reserved | RO | 0x0 | Reserved |
| 7 | BYPASS | RW | 0x1 | Bypass dead time generator 1b: DTGD0 bypass active, DTGD0LS = PWMD0, DTGD0HS = PWMD1 0b: DTGD0 bypass inactive, dead time inserted to DTGD0LS and DTGD0HS, DTGD0LS = PWMD1, DTGD0HS = PWMD1 |
| 6 | OTP | RW | 0x0 | One Time Preservation 1b: DTGD0HS high time is same as PWMD1 high time and is shifted by DTGD0LED 0b: DTGD0HS high time is reduced by DTGD0LED |
| 5 | INVHS | RW | 0x0 | Invert DTGD0HS output signal 1b: invert DTGD0HS 0b: do not invert DTGD0HS |
| 4 | INVLS | RW | 0x0 | Invert DTGD0LS output signal 1b: invert DTGD0LS 0b: do not invert DTGD0LS |
| 3:0 | Reserved | RO | 0x0 | Reserved |

14.1.10. DTGD0LED

Register 14-9. DTGD0LED (Timer D Dead Time Generator 0 Leading Edge Delay, 0x4010 00A4)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|----------|--------|-------|--|
| 31:12 | Reserved | RO | 0x0 | Reserved |
| 11:0 | LED | RW | 0x0 | Counter value DTGD0 leading edge dead time in clock cycles defined by TDCTL.DTGCLK |

14.1.11. DTGD0TED


Register 14-10. DTGD0TED (Timer D Dead Time Generator 0 Trailing Edge Delay, 0x4010 00A8)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|----------|--------|-------|---|
| 31:12 | Reserved | RO | 0x0 | Reserved |
| 11:0 | TED | RW | 0x0 | Counter value DTGD0 trailing edge dead time in clock cycles defined by TDCTL.DTGCLK |

14.2. Details of Operation

14.2.1. Block Diagram

Figure 14-1. Timer D



14.2.2. Configuration

Following blocks need to be configured for correct use of the Timer D:

- Clock Control System (CCS)
- Nested Vectored Interrupt Controller (NVIC)
- IO Controller
- Gate Driver
- Auto sequencing controller (ASC)
- Timer A
- Timer B
- Timer C

14.2.3. Timer D Block

The timer D block consist of a 16-bit timer with up mode or up/down mode with 2 PWM/capture units and 1 dead-time generator unit.

14.2.4. Timer

Once enabled the timer counts up to the Timer D period value **TDPRD**. The **TDPRD** register can be written to while the timer is running, the new **TDPRD** value will be latched when the counter reaches old **TDPRD** value in up mode. In up/down mode there is the option to latch the new **TDPRD** value when counter counts back to zero. **TDCTL.PRDL** configures when the timer will be updated with the new **TDPRD** value in up/down mode.

The current timer value is accessible with the timer D counter value register **TDCTR**.

14.2.5. Register Update

The **TDPRD**, **TDCCxCTR** register can be written to while the timer is running, the new **TDPRD**, **TDCCxCTR** value will be latched when the counter reaches old **TDPRD** value in up mode. In up/down mode there is the option to latch the new **TDPRD**, **TDCCxCTR** values when counter counts back to zero. **TDCTL.PRDL** configures when the timer will be updated with the new **TDPRD**, **TDCCxCTR** value in up/down mode.

14.2.6. Timer Modes

The timer supports 3 modes of operation: disabled, up and up/down using **TDCTL.MODE**.

By default, the timer mode is disabled. When the timer is disabled, the timer counter does not increment or decrement. If the timer is disabled when previously in up or up/down mode, then the timer counter stops where it is. If the timer is re-enabled by putting it back into up or up/down modes, then the counter continues from the point at which it was disabled. To reset the current counter value **TDCTR** to zero use **TDCTL.CLR**.

In up mode, the timer starts counting from 0 up to the value of **TDPRD**. When the timer counter reaches the value of **TDPRD**, then the timer counter is reset to a value of 0. This mode is typically used for timed events or edge-aligned PWM output.

In up/down mode, the timer starts counting from 0 up to the value of **TDPRD**, and then back down to a value of 0. This timer mode is typically used for center-aligned PWM output. It can also be used for timed events, and will allow a longer timer range due to the fact it counts up and down

14.2.7. Single Shot Mode

The timer can be configured to run either once or continuously.

When the timer is configured in single shot mode using **TDCTL.SS** the timer will only count to **TDPRD** value and stops in up mode. In up/down mode the timer will count to **TDPRD** and back to zero only once.

To start the timer in single-shot mode, **TDCTL.SS** must be set. The timer will start when **TDCTL.CLR** is set. To re-start a single-shot timer, **TDCTL.CLR** must be reset, and then set again.

14.2.8. Input Clock And Pre-Scaler

The timer can be configured to use HCLK or ACLK using **TDCTL.CLK**. The input clock for the can be divided further down from /1 to /128 using the **TDCTL.CLKDIV**.

14.2.9. Timer Synchronization

The Timer A, B, C, D in the system have the ability to have synchronization between them. Each timer has a synchronization in signal (SYNC_IN) and the synchronization out signal (SYNC_OUT).

Timer D can be synchronized with Timer A, B, or C as slave.

The timer asserts the SYNC_OUT pulse when the **TDCTL.CLR** bit is set and de-asserts the SYNC_OUT pulse when the **TDCTL.CLR** bit is cleared.

If timer D that need to be synchronized as slave with master timer C need to set the **TxCTL.SYNC** bit. If this is bit is not set, then the sync_in signal is ignored and the timer operates independently.

When the **TxCTL.SYNC** bit is set and the SYNC_IN signal is asserted, the timer clears the timer counter. The timer counter is also cleared anytime the **TxCTL.CLR** bit is set to a 1. When the **TxCTL.SYNC** bit is set and the SYNC_IN signal is de-asserted and the timer mode is either up or up/down, then the timer will start counting. The timer will not start counting when the mode is set to up or up/down unless the SYNC_IN signal is de-asserted when **TxCTL.SYNC** is set.

NOTE:

In order for this feature to work correctly, all timers that are synchronized must be set to the same mode (up or up/down), with the same timer pre-scaler, timer clock input and timer period.

To enable synchronized timers, the following steps should be followed:

1. The slave timer B, C, D is configured with the selected timer input clock, timer pre-scaler, timer period and set the **TxCTL.SYNC** bit. The timer should still be set to disabled at this point.
2. The master timer A, B or C is configured with the same timer input clock, timer pre-scaler, timer period and sets the **TxCTL CLR** bit. This should clear all timer counters of the master and slave timers.
3. The slave timers set the timer mode to the desired state (either up or up/down).
4. The master timer sets the timer mode to either up or up/down and clears the **TxCTL CLR** bit. This should start the master and all slave timers simultaneously based on the selected timer clock input.
5. Once configured as above, all timers can be disabled by the master setting **TxCTL CLR** signal, to assert the **SYNC_OUT** signal. The timers can be re-enabled by clearing the **TxCTL CLR** bit, which de-asserts the **SYNC_OUT** signal.

14.2.10. PWM/Compare Units

Timer D supports up to 2 PWM/Capture units PWMD0 to PWMD1. Each PWM/Compare unit can be configured independently in PWM mode or capture mode using **TDCCxCTL.CCMODE**.

14.2.10.1. PWM Mode

The PWM mode is enabled with setting **TDCCxCTL.CCMODE** to 0.


The timer configuration allows either edge-aligned (timer in up mode) or center-aligned (timer in up/down mode) modes of PWM operation.

In both edge-aligned and center-aligned modes of operation, the timer block outputs a PWM waveform that starts out high at a **TDCTR** value of 0 and then transitions to low when **TDCTR** counts up to **TDCCxCTR** compare value.

To configure a duty cycle of 0%, the **TDCCxCTR** should be set to 0; to configure a duty cycle of 100%, the **TDCCxCTR** value should be set to a value greater than or equal to **TDPRD**.

The polarity of the timer PWM outputs are not configurable. Adjustments to the polarity of the PWM outputs may be adjusted in the Dead-Time Generator (DTG) unit connected to the timer peripheral for each output independently.

Figure 14-2. PWMD0 and PWMD1 Example Using Timer D Up Mode and Up/Down Mode




14.2.10.2. Capture Mode

The Capture mode is enabled with setting **TDCCxCTL.CCMODE** to 1. The trip condition for capture mode can be configured using **TDCCxCTL.CCEDGE**, high-to-low signal edge transition, low-to-high signal edge transition or both.

When trip condition is detected the actual **TDCTR** value is copied into **TDCCxCTR**.

Figure 14-3. CD0 and CD1 Capture Example



14.2.11. Timer and PWM/Capture Interrupt

The timer may generate interrupt based on the base timer wrap, or when a capture and compare event occurs.

In the base timer both up and up/down timer modes allow an interrupt to be generated when the count reaches 0. Each time the count reaches zero, the **TDCTL.INT** interrupt flag is set. If the interrupt is enabled using the **TDCTL.INTEN**, then the Timer IRQ signal will be asserted to the CPU. The interrupt flag may be cleared by writing a 1 to the **TDCTL.INT** interrupt flag bit.

In the capture and compare PWM units, each time a compare threshold is reached or each time a capture event is detected the **TDCCxCTL.CCINT** bit will be set for that particular timer unit. If the interrupt is enabled via the **TDCCxCTL.CCINTEN**, then the Timer IRQ signal will be asserted to the CPU. The interrupt flag may be cleared by writing a 1 to the **TDCCxCTL.CCINT** interrupt flag bit.

The timer IRQ signal will be asserted if any of the timer interrupt flags **TDCTL.INT** or **TDCCxCTL.CCINT** are set. The Timer IRQ signal will be de-asserted when all of the timer interrupt flags are cleared.

14.2.12. Dead-Time Generator

The dead-time generator can be configured to introduce dead-time for a complementary PWM output. The Timer D block supports up to 1 dead time generator.

14.2.12.1. Dead Time Input Clock Selection

The clock source for the DTGD0 can be selected using **TDCTL.DTGCLK**.

Clear **TDCTL.DTGCLK** to 0 to use clock source selected by **TDCTL.CLK** directly to use higher resolution for dead time insertion.

Set **TDCTL.DTGCLK** to 1 to use divided clock source selected by **TDCTL.CLK** and **TDCTL.CLKDIV** divider to use the same dead time resolution as Timer D.

14.2.12.2. Dead Time Range

The resolution for leading edge and trailing edge dead time is 12bits. Leading and trailing edge can be set independently using **DTGD0LED** and **DTGD0TED**.


14.2.12.3. Bypass Mode

Set **DTGD0CTL.BYPASS** to 0 to enable dead time insertion.

Set **DTGD0CTL.BYPASS** to 1 to enable bypass mode, no dead time is inserted, PWMD1 is routed to DTGD0HS and PWMD0 is routed to DTGD0LS.

The DTGD0HS and DTGD0LS signals can be inverted in bypass mode.

Figure 14-4. DTGD0 Bypass Example




14.2.12.4. Inverting PWM Signal

The DTG output signals DTGD0HS and DTGD0LS can be inverted independently.

Set **DTGD0CTL.INVHS** to invert DTGD0HS signal.

Set **DTGD0CTL.INVLS** to invert DTGD0LS signal.

Figure 14-5. DTGD0 Bypass and Inverting LS Example



14.2.12.5. Dead Time Insertion


Set **DTGD0CTL.BYPASS** to 0 to enable dead time insertion. In dead time insertion mode only PWMD1 signal is used to generate DTGD0HS and DTGD0LS. PWMD0 signal is ignored and can be used for other purposes.

Set **DTGD0LED** for desired leading-edge and **DTGD0TED** for desired trailing edge in clock-cycles defined by **TDCTL.DTGCLK** clock source

NOTE:

In dead time insertion mode the DTGD0LS signal is automatically inverted compared to PWMD1 signal. Set **DTGD0CTL.INVLS** to 0, if this is desired behavior.

Figure 14-6. DTGD0 LED and TED Example




14.2.12.6. Dead Time Insertion with On Time Preservation

Set **DTGD0CTL.OTP** to 1 to enable on time preservation. In this mode the DTGD0HS is same as PWMD1 on time.

NOTE:

In dead time insertion mode the DTGD0LS signal is automatically inverted compared to PWMD1 signal. Set **DTGD0CTL.INVLS** to 0, if this is desired behavior.

Figure 14-7. DTGD0 LED and TED with On Time Preservation Example



14.2.13. PWM Output and Capture Input Pin Selection

Each of the DTGD0HS, DTGD0LS outputs, and CDx inputs can be routed to different I/Os, allowing great flexibility in pin assignments.

In capture mode only one I/O should be enabled as input to the capture. If more than one pin input is enabled, the capture might not work properly.

Note:

Not all pins are available pending package option, consult data sheet for available pins and signals.

Table 14-2. Timer D Signal to Pin Mapping

| PWM | CAPTURE | DEADTIME | PINS |
|-------|---------|----------|----------|
| PWMD0 | CD0 | DTGD0LS | PA5, PD7 |
| PWMD1 | CD1 | DTGD1LS | PD4 |

15. FLASH MEMORY CONTROLLER

15.1. Register

15.1.1. Register Map

Table 15-1. FLASH Memory Controller Register Map

| ADDRESS | NAME | DESCRIPTION | RESET VALUE |
|--------------------------------|--------------------|---------------------------------------|-------------|
| FLASH Memory Controller | | | |
| 0x4002 0000 | FLASHLOCK | FLASH lock | 0x0000 0000 |
| 0x4002 0004 | FLASHSTATUS | FLASH status | 0x0000 0000 |
| 0x4002 0008 | FLASHPAGE | FLASH page selection | 0x0000 0000 |
| 0x4002 000C | Reserved | Reserved | 0x0000 0000 |
| 0x4002 0010 | Reserved | Reserved | 0x0000 0000 |
| 0x4002 0014 | FLASHPERASE | FLASH page erase | 0x0000 0000 |
| 0x4002 0018 | Reserved | Reserved | 0x0000 0000 |
| 0x4002 001C | Reserved | Reserved | 0x0000 0000 |
| 0x4002 0020 | Reserved | Reserved | 0x0000 0000 |
| 0x4002 0024 | SWDACCESS | SWD access control | 0x0000 0000 |
| 0x4002 0028 | FLASHWSTATE | FLASH wait state control | 0x0000 0003 |
| 0x4002 002C | FLASHBWRITE | FLASH buffered write enable | 0x0000 0000 |
| 0x4002 0030 | FLASHBWDATA | FLASH buffered write data and address | 0x0000 0000 |

15.1.2. FLASHLOCK

Register 15-1. FLASHLOCK (FLASH Lock, 0x4002 0000)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-------------|--------|-------|---|
| 31:0 | LOCK | RW | 0x0 | Unlock access to FLASH registers and FLASH memory 0xAAAA AAAA: allow write and erase to FLASH pages 0x1234 5678: allow write of FLASHWSTATE register 0xF983 62AB: allow write access to address 0x0010 0008 to disable SWD |

15.1.3. FLASHSTATUS

Register 15-2. FLASHSTATUS (FLASH Status, 0x4002 0004)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|--|
| 31:5 | Reserved | R | 0x0 | Reserved |
| 4 | Reserved | R | 0x0 | Reserved |
| 3 | Reserved | R | 0x0 | Reserved |
| 2 | Reserved | R | 0x0 | Reserved |
| 1 | PERASE | R | 0x0 | Page erase active 1b: page erase in progress 0b: page erase finished or no page erase in progress |
| 0 | WRITE | R | 0x0 | Buffered write active, only used in conjunction with FLASHBWRITE 1b: buffered write in progress 0b: buffered write finished or no buffered write in progress |

15.1.4. FLASHPAGE

Register 15-3. FLASHPAGE (FLASH Page Selector, 0x4002 0008)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|--|
| 31:5 | Reserved | R | 0x0 | Reserved |
| 4:0 | PAGE | RW | 0x0 | FLASH page selector for page erase 0x1F: page 31, 0x0000 7C00 to 0x0000 7FFF 0x1E: page 30, 0x0000 7800 to 0x0000 7BFF 0x1D: page 29, 0x0000 7400 to 0x0000 73FF 0x1C: page 28, 0x0000 7000 to 0x0000 73FF 0x1B: page 27, 0x0000 6C00 to 0x0000 6FFF 0x1A: page 26, 0x0000 6800 to 0x0000 6BFF 0x19: page 25, 0x0000 6400 to 0x0000 67FF 0x18: page 24, 0x0000 6000 to 0x0000 63FF 0x17: page 23, 0x0000 5C00 to 0x0000 5FFF 0x16: page 22, 0x0000 5800 to 0x0000 5BFF 0x15: page 21, 0x0000 5400 to 0x0000 57FF 0x14: page 20, 0x0000 5000 to 0x0000 53FF 0x13: page 19, 0x0000 4C00 to 0x0000 4FFF 0x12: page 18, 0x0000 4800 to 0x0000 4BFF 0x11: page 17, 0x0000 4400 to 0x0000 47FF 0x10: page 16, 0x0000 4000 to 0x0000 43FF 0x0F: page 15, 0x0000 3C00 to 0x0000 3FFF 0x0E: page 14, 0x0000 3800 to 0x0000 3BFF 0x0D: page 13, 0x0000 3400 to 0x0000 37FF 0x0C: page 12, 0x0000 3000 to 0x0000 33FF 0x0B: page 11, 0x0000 2C00 to 0x0000 2FFF 0x0A: page 10, 0x0000 2800 to 0x0000 2BFF 0x09: page 9, 0x0000 2400 to 0x0000 27FF 0x08: page 8, 0x0000 2000 to 0x0000 23FF 0x07: page 7, 0x0000 1C00 to 0x0000 1FFF 0x06: page 6, 0x0000 1800 to 0x0000 1BFF 0x05: page 5, 0x0000 1400 to 0x0000 17FF 0x04: page 4, 0x0000 1000 to 0x0000 13FF 0x03: page 3, 0x0000 0C00 to 0x0000 0FFF 0x02: page 2, 0x0000 0800 to 0x0000 0BFF 0x01: page 1, 0x0000 0400 to 0x0000 07FF 0x00: page 0, 0x0000 0000 to 0x0000 03FF |

15.1.5. FLASHPERASE

Register 15-4. FLASHPERASE (FLASH Page Erase, 0x4002 0014)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|---------------|--------|-------|--|
| 31:0 | PERASE | R | 0x0 | Write of correct key value to this register starts FLASH page erase selected in FLASHPAGE.PAGE 0xA5A5 5A5A: start FLASH page erase selected by FLASHPAGE.PAGE |

15.1.6. SWDACCESS

Register 15-5. SWDACCESS (SDW Access Status, 0x4002 0024)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|--------------|--------|-------|--|
| 31:0 | DEBUG | R | 0x0 | Status of SWD debug 0xFFFFFFFF: SWD access is enabled 0x69696969: SWD access is disabled |

15.1.7. FLASHWSTATE

Register 15-6. FLASHWSTATE (FLASH Access Wait State, 0x4002 0028)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|--|
| 31:2 | Reserved | RW | 0x0 | Reserved, must be set to 0x0 |
| 1:0 | WSTATE | RW | 0x3 | FLASH access wait state 11b: 3 wait states for 75MHz < HCLK < 100MHz 10b: 2 wait states for 50MHz < HCLK < 75MHz 01b: 1 wait state for 25MHz < HCLK < 50MHz 00b: 0 wait state for HCLK < 25MHz |

15.1.8. FLASHBWRITE

Register 15-7. FLASHBWRITE (Buffered FLASH Write, 0x4002 002C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|---------------|--------|-------|---|
| 31:0 | BWRITE | RW | 0x0 | Write of correct key value to this register starts buffered write operation 0xCA72 6B18: start buffered write of FLASHBWDATA |

15.1.9. FLASHBWDATA


Register 15-8. FLASHBWDATA (Buffered FLASH Write Data, 0x4002 0030)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|---|
| 31 | Reserved | RW | 0x0 | Reserved, must be set to 0x0 |
| 30 | Reserved | RW | 0x0 | Reserved, must be set to 0x0 |
| 29:25 | PAGE | RW | 0x0 | FLASH page selector to write to 0x1F: page 31, 0x0000 7C00 to 0x0000 7FFF 0x1E: page 30, 0x0000 7800 to 0x0000 7BFF 0x1D: page 29, 0x0000 7400 to 0x0000 73FF 0x1C: page 28, 0x0000 7000 to 0x0000 73FF 0x1B: page 27, 0x0000 6C00 to 0x0000 6FFF 0x1A: page 26, 0x0000 6800 to 0x0000 6BFF 0x19: page 25, 0x0000 6400 to 0x0000 67FF 0x18: page 24, 0x0000 6000 to 0x0000 63FF 0x17: page 23, 0x0000 5C00 to 0x0000 5FFF 0x16: page 22, 0x0000 5800 to 0x0000 5BFF 0x15: page 21, 0x0000 5400 to 0x0000 57FF 0x14: page 20, 0x0000 5000 to 0x0000 53FF 0x13: page 19, 0x0000 4C00 to 0x0000 4FFF 0x12: page 18, 0x0000 4800 to 0x0000 4BFF 0x11: page 17, 0x0000 4400 to 0x0000 47FF 0x10: page 16, 0x0000 4000 to 0x0000 43FF 0x0F: page 15, 0x0000 3C00 to 0x0000 3FFF 0x0E: page 14, 0x0000 3800 to 0x0000 3BFF 0x0D: page 13, 0x0000 3400 to 0x0000 37FF 0x0C: page 12, 0x0000 3000 to 0x0000 33FF 0x0B: page 11, 0x0000 2C00 to 0x0000 2FFF 0x0A: page 10, 0x0000 2800 to 0x0000 2BFF 0x09: page 9, 0x0000 2400 to 0x0000 27FF 0x08: page 8, 0x0000 2000 to 0x0000 23FF 0x07: page 7, 0x0000 1C00 to 0x0000 1FFF 0x06: page 6, 0x0000 1800 to 0x0000 1BFF 0x05: page 5, 0x0000 1400 to 0x0000 17FF 0x04: page 4, 0x0000 1000 to 0x0000 13FF 0x03: page 3, 0x0000 0C00 to 0x0000 0FFF 0x02: page 2, 0x0000 0800 to 0x0000 0BFF 0x01: page 1, 0x0000 0400 to 0x0000 07FF 0x00: page 0, 0x0000 0000 to 0x0000 03FF |
| 24:16 | ADDRESS | RW | 0x0 | Relative half word address within selected FLASHBWDATA.PAGE |
| 15:0 | DATA | RW | 0x0 | Data to write |

15.2. Details of Operation

15.2.1. Block Diagram

Figure 15-1. FLASH Memory Controller



15.2.2. Configuration

Following blocks need to be configured for correct use of the FLASH:

- Clock Control System (CCS)

15.2.3. FLASH Memory

The Flash memory controller allows configuration of the FLASH memory. FLASH wait states, FLASH erase, buffered FLASH write, and SWD debug access can be configured. The FLASH memory has up to 32 pages of 1kByte each.

15.2.4. Writing to FLASH Controller Registers

The FLASH Controller registers are write protected to reduce chances of accidental erase or modification of FLASH memory. Each write to a FLASH controller register is a 2 step process. The first step is to write the correct key into **FLASHLOCK** followed by a FLASH controller register write.

Without correct key any writes to FLASH controller register will be ignored. Flash controller reads are always possible.

15.2.5. FLASH Wait State

After device reset, the **FLASHWSTATE** is set to 0x3. To allow optimal FLASH access time without delay, the FLASH wait state need to be set according to HCLK frequency used. See register table for correct setting.

To write to **FLASHWSTATE** register, **FLASHLOCK** need to be set to 0x1234 5678.

15.2.6. FLASH Page Erase

To erase a page of FLASH memory, set **FLASHLOCK** to 0xAAAA AAAA first, then set **FLASHBWDATA.PAGE** to the page to be erased and then set **FLASHPERASE** to 0xA5A5 5A5A. The FLASH page operation will start, **FLASHSTATUS.PERASE** is set to 1b and any access to FLASH memory address space is stalled until erase operation is finished. **FLASHSTATUS.PERASE** is set to 0b when erase operation is finished.

It is not recommended to erase FLASH pages while executing from FLASH as any access to FLASH is stalled until the erase operation is finished. Either execute from SRAM or use SWD debug interface.

15.2.7. Write to FLASH

Only half-word address aligned half-word writes are supported. To write a half word to FLASH memory, make sure the memory location is erased by doing a read, it should return 0xFFFF. Set **FLASHLOCK** to 0xAAAA AAAA first, then write a half-word to the memory address directly.

It is not recommended to write to FLASH while executing from FLASH as any access to FLASH is stalled until the erase operation is finished. Either execute from SRAM or use SWD debug interface.

15.2.8. Buffered Write to FLASH

Only half-word address aligned half-word writes are supported. The FLASH memory controller also allows buffered write to FLASH, to allow CPU still react to interrupts or perform other tasks while waiting for FLASH write to finish when executing from SRAM.

To write a half word to FLASH memory, make sure the memory location is erased by doing a read, it should return 0xFFFF. Set **FLASHLOCK** to 0xAAAA AAAA first, then write to **FLASHBWDATA**, with **FLASHBWDATA.DATA** the half-word you want to write, and **FLASHBWDATA.PAGE** the page where the memory location resides and **FLASHBWDATA.ADDRESS** the relative address of the memory location.

The FLASH page operation will start, **FLASHSTATUS.WRITE** is set to 1b, AHB bus control will be given back to CPU to allow execution of other commands. Any access to FLASH memory while buffered write operation is active will stall. **FLASHSTATUS.WRITE** is set to 0b when buffered write operation is finished.

To calculate **FLASHBWDATA.PAGE** use:

$$PAGE = \frac{\text{Memoryaddress}}{\text{pagesize}} \quad (4)$$

Where:

PAGE: integer value for **FLASHBWDATA.PAGE**

Memoryaddress: Word memory address

pagesize: FLASH page size: 0x400

Then to calculate **FLASHBWDATA.ADDRESS** use:

$$ADDRESS = \frac{(\text{Memoryaddress} - PAGE * \text{pagesize})}{2} \quad (5)$$

Where:

ADDRESS: integer value for **FLASHBWDATA.ADDRESS**

PAGE: integer value for **FLASHBWDATA.PAGE**

Memoryaddress: Word memory address

pagesize: FLASH page size: 0x400

Example:

memoryaddress: 0x0000 0438

PAGE = 0x0000 0438 / 0x400 = 0x01

ADDRESS = (0x0000 0438 – 0x01*0x400)/0x2 = 0x38/0x2 = 0x1C

It is not recommended to write to FLASH while executing from FLASH as any access to FLASH is stalled until the erase operation is finished. Either execute from SRAM or use SWD debug interface.

15.2.9. SWD Debug Access Disable

The SWD debug access is enabled by default and can be disabled by a FUSE to prevent access of device memory.

Caution need to be taken. This action is not reversible.

To disable SWD set **FLASHLOCK** to 0xF983 62AB first, then write 0x6969 6969 to address 0x0010 0008 will disable the SWD debug access.

16. ADC AND AUTO SEQUENCER

16.1. Register

16.1.1. Register Map

Table 16-1. Register Map – EMUX

| ADDRESS | NAME | DESCRIPTION | RESET VALUE |
|-------------|----------|-----------------------------------|-------------|
| EMUX | | | |
| 0x4015 0000 | EMUXCTL | ADC external MUX control register | 0x0000 0000 |
| 0x4015 0004 | EMUXDATA | ADC external MUX data register | 0x0000 0000 |

Table 16-2. Register Map – ADC

| ADDRESS | NAME | DESCRIPTION | RESET VALUE |
|-------------|--------|--------------------------------|-------------|
| ADC | | | |
| 0x4015 0008 | ADCCTL | ADC control register | 0x0000 0000 |
| 0x4015 000C | ADCR | ADC conversion result register | 0x0000 0000 |
| 0x4015 0010 | ADCINT | ADC Interrupt register | 0x0000 0000 |

Table 16-3. Register Map – ADC Auto Sequencer 0

| ADDRESS | NAME | DESCRIPTION | RESET VALUE |
|------------------------------|--------|---|-------------|
| ADC Auto Sequencer -0 | | | |
| 0x4015 0040 | AS0CTL | Automated ADC sampling 0 control register | 0x0000 0000 |
| 0x4015 0044 | AS0S0 | Automated Sampling 0 Sequence 0 register | 0x0000 0000 |
| 0x4015 0048 | AS0R0 | Automated Sampling 0 Sample result 0 register | 0x0000 0000 |
| 0x4015 004C | AS0S1 | Automated Sampling 0 Sequence 1 register | 0x0000 0000 |
| 0x4015 0050 | AS0R1 | Automated Sampling 0 Sample result 1 register | 0x0000 0000 |
| 0x4015 0054 | AS0S2 | Automated Sampling 0 Sequence 2 register | 0x0000 0000 |
| 0x4015 0058 | AS0R2 | Automated Sampling 0 Sample result 2 register | 0x0000 0000 |
| 0x4015 005C | AS0S3 | Automated Sampling 0 Sequence 3 register | 0x0000 0000 |
| 0x4015 0060 | AS0R3 | Automated Sampling 0 Sample result 3 register | 0x0000 0000 |
| 0x4015 0064 | AS0S4 | Automated Sampling 0 Sequence 4 register | 0x0000 0000 |
| 0x4015 0068 | AS0R4 | Automated Sampling 0 Sample result 4 register | 0x0000 0000 |
| 0x4015 006C | AS0S5 | Automated Sampling 0 Sequence 5 register | 0x0000 0000 |
| 0x4015 0070 | AS0R5 | Automated Sampling 0 Sample result 5 register | 0x0000 0000 |
| 0x4015 0074 | AS0S6 | Automated Sampling 0 Sequence 6 register | 0x0000 0000 |
| 0x4015 0078 | AS0R6 | Automated Sampling 0 Sample result 6 register | 0x0000 0000 |
| 0x4015 007C | AS0S7 | Automated Sampling 0 Sequence 7 register | 0x0000 0000 |
| 0x4015 0080 | AS0R7 | Automated Sampling 0 Sample result 7 register | 0x0000 0000 |

Table 16-4. Register Map – ADC Auto Sequencer 1

| ADDRESS | NAME | DESCRIPTION | RESET VALUE |
|------------------------------|--------|---|-------------|
| ADC Auto Sequencer -1 | | | |
| 0x4015 0100 | AS1CTL | Automated ADC sampling 1 control register | 0x0000 0000 |
| 0x4015 0104 | AS1S0 | Automated Sampling 1 Sequence 0 register | 0x0000 0000 |
| 0x4015 0108 | AS1R0 | Automated Sampling 1 Sample result 0 register | 0x0000 0000 |
| 0x4015 010C | AS1S1 | Automated Sampling 1 Sequence 1 register | 0x0000 0000 |
| 0x4015 0110 | AS1R1 | Automated Sampling 1 Sample result 1 register | 0x0000 0000 |
| 0x4015 0114 | AS1S2 | Automated Sampling 1 Sequence 2 register | 0x0000 0000 |
| 0x4015 0118 | AS1R2 | Automated Sampling 1 Sample result 2 register | 0x0000 0000 |
| 0x4015 011C | AS1S3 | Automated Sampling 1 Sequence 3 register | 0x0000 0000 |
| 0x4015 0120 | AS1R3 | Automated Sampling 1 Sample result 3 register | 0x0000 0000 |
| 0x4015 0124 | AS1S4 | Automated Sampling 1 Sequence 4 register | 0x0000 0000 |
| 0x4015 0128 | AS1R4 | Automated Sampling 1 Sample result 4 register | 0x0000 0000 |
| 0x4015 012C | AS1S5 | Automated Sampling 1 Sequence 5 register | 0x0000 0000 |
| 0x4015 0130 | AS1R5 | Automated Sampling 1 Sample result 5 register | 0x0000 0000 |
| 0x4015 0134 | AS1S6 | Automated Sampling 1 Sequence 6 register | 0x0000 0000 |
| 0x4015 0138 | AS1R6 | Automated Sampling 1 Sample result 6 register | 0x0000 0000 |
| 0x4015 013C | AS1S7 | Automated Sampling 1 Sequence 7 register | 0x0000 0000 |
| 0x4015 0140 | AS1R7 | Automated Sampling 1 Sample result 7 register | 0x0000 0000 |

16.1.2. EMUXCTL

Register 16-1. EMUXCTL (ADC external MUX control register 0x4015 0000)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|--|
| 31:6 | Reserved | R | 0x0 | Reserved |
| 5 | EMUXC | RW | 0x0 | ADC external MUX control 1b: EMUX is controlled by auto-sequencer unit 0b: EMUX manual control |
| 4 | EMUXBUSY | RW | 0x0 | ADC external MUX status 1b: ADC external MUX sending data 0b: ADC external MUX not busy or not used |
| 3 | EMUXDONE | RW | 0x0 | ADC external MUX data send done, auto-clear with read or when new data is sent over EMUX 1b: ADC external MUX data sent 0b: ADC external MUX busy |
| 2:0 | EMUXCDIV | RW | 0x0 | ADC external mux clock to FCLK divider 111b: FCLK/8 110b: FCLK/7 101b: FCLK.6 100b: FCLK/5 011b: FCLK/4 010b: FCLK/3 001b: FCLK/2 000b: FCLK/1 |

16.1.3. EMUXDATA

Register 16-2. EMUXDATA (EMUX data register 0x4015 0004)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|--|
| 31:8 | Reserved | R | 0x0 | Reserved |
| 7:0 | DATA | RW | 0x0 | EMUX data, writing this register will start transmission over EMUX |

16.1.4. ADCCTL

Register 16-3. ADCCTL (ADC control register 0x4015 0008)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|------------------|--------|-------|---|
| 31:16 | Reserved | R | 0x0 | Reserved |
| 15 | ADCEN | RW | 0x0 | ADC module enable 1b: enable ADC module 0b: turn off ADC module |
| 14 | ADCSTART | R/W | 0x0 | Start ADC conversion. A write of 1b will start ADC conversion if ADCCTL.ADCBUSY = 0b and ADCCTL.ADCMODE = 00b. 1b: start ADC conversion 0b: stop ADC conversion, also stop repeated ADC conversions ADCCTL.ADCREPEAT = 1b. |
| 13 | ADCREPEAT | R/W | 0x0 | ADC repeat mode 1b: repeated conversion, also auto rearms auto sequencer 0b: single shot conversion |
| 12:10 | ADCMODE | R/W | 0x0 | ADC conversion mode 111b: automated sequencer 0 and 1 independently triggered 110b: automated sequencer 0 and 1 daisy chained trigger on AS0 101b: automated sequencer 1 only trigger condition 100b: automated sequencer 0 only trigger condition 011b: automated sequencer 0 and 1 daisy chained 010b: automated sequencer 1 only 001b: automated sequencer 0 only 000b: single channel |
| 9:8 | Reserved | R | 0x0 | Reserved |
| 7 | ADCBUSY | R | 0x0 | ADC busy 1b: ADC conversion or auto sequencer active 0b: ADC no operation |
| 6:4 | ADCMUX | R/W | 0x0 | ADC MUX input select 111b: VSSA 110b: reserved 101b: AD5 100b: AD4 011b: AD3 010b: AD2 001b: reserved 000b: AD0 |
| 3 | Reserved | R | 0x0 | Reserved |
| 2:0 | ADCCDIV | R/W | 0x0 | ADC input clock FCLK divider 111b: FCLK/8 110b: FCLK/7 101b: FCLK.6 100b: FCLK/5 011b: FCLK/4 010b: FCLK/3 001b: FCLK/2 000b: FCLK/1 |

16.1.5. ADCCR

Register 16-4. ADCCR (ADC conversion result register 0x4015 000C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|------------------|--------|-------|-----------------------|
| 31:10 | Reserved | R | 0x0 | Reserved |
| 9:0 | ADCRESULT | R | 0x0 | ADC conversion result |

16.1.6. ADCINT

Register 16-5. ADCINT (ADC Interrupt register 0x4015 0010)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-------------------|--------|-------|--|
| 31:13 | Reserved | R | 0x0 | Reserved |
| 19:18 | ASCINTTR | RW | 0x0 | Last Auto sequencer to run 11b: reserved 10b: auto sequencer 1 to run 01b: auto sequencer 0 to run 00b: no sequencer to r |
| 17:16 | ASCINTSEQ | RW | 0x0 | Last Auto sequencer to trigger ADCINT.ASCINT 11b: Auto sequencer 1 and 0 triggered interrupt 10b: Auto sequencer 1 triggered interrupt 01b: Auto sequencer 0 triggered interrupt 00b: no trigger |
| 15:13 | Reserved | R | 0x0 | Reserved |
| 12 | ASCINT_EN | RW | 0x0 | Enable auto sequencer collision interrupt 1b: enable ASCINT 0b: disable ASCINT |
| 11 | AS1INT_EN | RW | 0x0 | Enable auto sequencer 1 conversions finished interrupt 1b: enable AS1INT 0b: disable AS1INT |
| 10 | AS0INT_EN | RW | 0x0 | Enable auto sequencer 0 conversions finished interrupt 1b: enable AS0INT 0b: disable AS0INT |
| 9 | EMUXINT_EN | RW | 0x0 | Enable EMUX transfer finished interrupt 1b: enable EMUXINT 0b: disable EMUXINT |
| 8 | ADCINT_EN | RW | 0x0 | Enable ADC conversion finished interrupt 1b: enable ADCINT 0b: disable ADCINT |
| 7:5 | Reserved | RW | 0x0 | Reserved, must be set to 0 |
| 4 | ASCINT | RW | 0x0 | Auto sequencer collision interrupt 1b: interrupt, clear by writing 1b to it 0b: no interrupt NOTE: This bit is cleared by writing a 1b to it. |
| 3 | AS1INT | RW | 0x0 | Auto sequencer 1 conversions finished interrupt 1b: interrupt, clear by writing 1b to it 0b: no interrupt NOTE: This bit is cleared by writing a 1b to it. |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|----------------|--------|-------|---|
| 2 | AS0INT | RW | 0x0 | Auto sequencer 0 conversions finished interrupt 1b: interrupt, clear by writing 1b to it 0b: no interrupt NOTE: This bit is cleared by writing a 1b to it. |
| 1 | EMUXINT | RW | 0x0 | EMUX data transfer finished interrupt 1b: interrupt, clear by writing 1b to it 0b: no interrupt NOTE: This bit is cleared by writing a 1b to it. |
| 0 | ADCINT | RW | 0x0 | ADC conversion finished interrupt 1b: interrupt, clear by writing 1b to it 0b: no interrupt NOTE: This bit is cleared by writing a 1b to it. |

16.1.7. AS0CTL

Register 16-6. AS0CTL (Auto Sequencer 0 control register 0x4015 0040)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|--|
| 31:13 | Reserved | R | 0x0 | Reserved |
| 12 | AS0BUSY | RW | 0x0 | Auto sequencer 0 busy 1b: auto sequencer 0 sampling active 0b: auto sequencer 0 not active |
| 11 | AS0EN | RW | 0x0 | Auto sequencer 0 enable 1b: auto sequencer 0 enabled 0b: auto sequencer 0 not enabled |
| 10:8 | AS0D | RW | 0x0 | Auto sequencer 0 sampling depth 111b: 8 samples 110b: 7 samples 101b: 6 samples 100b: 5 samples 011b: 4 samples 010b: 3 samples 001b: 2 samples 000b: 1 sample |
| 7 | AS0TR | RW | 0x0 | Auto sequencer 0 trigger source 1b: Timer, as defined by AS0CTL.AS0TRTMR 0b: PWM, as defined by AS0CTL.AS0TRPWM |
| 6 | AS0TRE | RW | 0x0 | Auto sequencer 0 trigger source AS0CTL.AS0TR edge 1b: high to low edge 0b: low to high edge |
| 5:4 | AS0TRTMR | RW | 0x0 | Auto sequencer 0 timer trigger source 11b: Timer D 10b: Timer C 01b: Timer B 00b: Timer A |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|------------------|--------|-------|---|
| 3:0 | ASA0TRPWM | RW | 0x0 | Auto sequencer 0 PWM trigger source 1111b: reserved 1110b: reserved 1101b: PWMD1 1100b: PWMD0 1011b: PWMC1 1010b: PWMC0 1001b: PWMB1 1000b: PWMB0 0111b: PWMA7 0110b: PWMA6 0101b: PWMA5 0100b: PWMA4 0011b: PWMA3 0010b: PWMA2 0001b: PWMA1 0000b: PWMA0 |

16.1.8. AS0S0

Register 16-7. AS0S0 (Auto sequencer 0-sample 0 control 0x4015 0044)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|--|
| 31:15 | Reserved | R | 0x0 | Reserved |
| 14:12 | ADCMUX | RW | 0x0 | ADC MUX input select 111b: VSSA 110b: reserved 101b: AD5 100b: AD4 011b: AD3 010b: AD2 001b: reserved 000b: EMUX |
| 11:10 | DELAY | RW | 0x0 | Delay between start of sample sequence and start of ADC conversion in ADC input clocks FLCK/ADCCTL.ADCCDIV 11b: 16 ADC input clock cycles 10b: 8 ADC input clock cycles 01b: 4 ADC input clock cycles 00b: 0 ADC input clock |
| 9:8 | EMUXS | RW | 0x0 | EMUX transmission start 11b: reserved 10b: send AS0S0.EMUXD data after S/H of ADC 01b: send AS0S0.EMUXD data at beginning of this sample sequence 00b: do not send AS0S0.EMUXD data |
| 7:0 | EMUXD | RW | 0x0 | EMUX data to transmit |

16.1.9. AS0R0

Register 16-8. AS0R0 (Auto sequencer 0-sample 0 result register 0x4015 0048)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|------------------|--------|-------|-----------------------|
| 31:10 | Reserved | R | 0x0 | Reserved |
| 9:0 | ADCRESULT | R | 0x0 | ADC conversion result |

16.1.10. AS0S1

Register 16-9. AS0S1 (Auto sequencer 0-sample 1 control 0x4015 004C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|--|
| 31:15 | Reserved | R | 0x0 | Reserved |
| 14:12 | ADCMUX | RW | 0x0 | ADC MUX input select 111b: VSSA 110b: reserved 101b: AD5 100b: AD4 011b: AD3 010b: AD2 001b: reserved 000b: EMUX |
| 11:10 | DELAY | RW | 0x0 | Delay between start of sample sequence and start of ADC conversion in ADC input clocks FLCK/ADCCTL.ADCCDIV 11b: 16 ADC input clock cycles 10b: 8 ADC input clock cycles 01b: 4 ADC input clock cycles 00b: 0 ADC input clock |
| 9:8 | EMUXS | RW | 0x0 | EMUX transmission start 11b: reserved 10b: send AS0S1.EMUXD data after S/H of ADC 01b: send AS0S1.EMUXD data at beginning of this sample sequence 00b: do not send AS0S1.EMUXD data |
| 7:0 | EMUXD | RW | 0x0 | EMUX data to transmit |

16.1.11. AS0R1

Register 16-10. AS0R1 (Auto sequencer 0-sample 1 result register 0x4015 0050)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|------------------|--------|-------|-----------------------|
| 31:10 | Reserved | R | 0x0 | Reserved |
| 9:0 | ADCRESULT | R | 0x0 | ADC conversion result |

16.1.12. AS0S2

Register 16-11. AS0S2 (Auto sequencer 0-sample 2 control 0x4015 0054)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|--|
| 31:15 | Reserved | R | 0x0 | Reserved |
| 14:12 | ADCMUX | RW | 0x0 | ADC MUX input select 111b: VSSA 110b: reserved 101b: AD5 100b: AD4 011b: AD3 010b: AD2 001b: reserved 000b: EMUX |
| 11:10 | DELAY | RW | 0x0 | Delay between start of sample sequence and start of ADC conversion in ADC input clocks FLCK/ADCCTL.ADCCDIV 11b: 16 ADC input clock cycles 10b: 8 ADC input clock cycles 01b: 4 ADC input clock cycles 00b: 0 ADC input clock |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|--------------|--------|-------|---|
| 9:8 | EMUXS | RW | 0x0 | EMUX transmission start 11b: reserved 10b: send AS0S2.EMUXD data after S/H of ADC 01b: send AS0S2.EMUXD data at beginning of this sample sequence 00b: do not send AS0S2.EMUXD data |
| 7:0 | EMUXD | RW | 0x0 | EMUX data to transmit |

16.1.13. AS0R2

Register 16-12. AS0R2 (Auto sequencer 0-sample 2 result register 0x4015 0058)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|------------------|--------|-------|-----------------------|
| 31:10 | Reserved | R | 0x0 | Reserved |
| 9:0 | ADCRESULT | R | 0x0 | ADC conversion result |

16.1.14. AS0S3

Register 16-13. AS0S3 (Auto sequencer 0-sample 3 control 0x4015 005C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|--|
| 31:15 | Reserved | R | 0x0 | Reserved |
| 14:12 | ADCMUX | RW | 0x0 | ADC MUX input select 111b: VSSA 110b: reserved 101b: AD5 100b: AD4 011b: AD3 010b: AD2 001b: reserved 000b: EMUX |
| 11:10 | DELAY | RW | 0x0 | Delay between start of sample sequence and start of ADC conversion in ADC input clocks FLCK/ADCCTL.ADCCDIV 11b: 16 ADC input clock cycles 10b: 8 ADC input clock cycles 01b: 4 ADC input clock cycles 00b: 0 ADC input clock |
| 9:8 | EMUXS | RW | 0x0 | EMUX transmission start 11b: reserved 10b: send AS0S3.EMUXD data after S/H of ADC 01b: send AS0S3.EMUXD data at beginning of this sample sequence 00b: do not send AS0S3.EMUXD data |
| 7:0 | EMUXD | RW | 0x0 | EMUX data to transmit |

16.1.15. AS0R3

Register 16-14. AS0R3 (Auto sequencer 0-sample 3 result register 0x4015 0060)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|------------------|--------|-------|-----------------------|
| 31:10 | Reserved | R | 0x0 | Reserved |
| 9:0 | ADCRESULT | R | 0x0 | ADC conversion result |

16.1.16. AS0S4

Register 16-15. AS0S4 (Auto sequencer 0-sample 4 control 0x4015 0064)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|--|
| 31:15 | Reserved | R | 0x0 | Reserved |
| 14:12 | ADCMUX | RW | 0x0 | ADC MUX input select 111b: VSSA 110b: reserved 101b: AD5 100b: AD4 011b: AD3 010b: AD2 001b: reserved 000b: EMUX |
| 11:10 | DELAY | RW | 0x0 | Delay between start of sample sequence and start of ADC conversion in ADC input clocks FLCK/ADCCTL.ADCCDIV 11b: 16 ADC input clock cycles 10b: 8 ADC input clock cycles 01b: 4 ADC input clock cycles 00b: 0 ADC input clock |
| 9:8 | EMUXS | RW | 0x0 | EMUX transmission start 11b: reserved 10b: send AS0S4.EMUXD data after S/H of ADC 01b: send AS0S4.EMUXD data at beginning of this sample sequence 00b: do not send AS0S4.EMUXD data |
| 7:0 | EMUXD | RW | 0x0 | EMUX data to transmit |

16.1.17. AS0R4

Register 16-16. AS0R4 (Auto sequencer 0-sample 4 result register 0x4015 0068)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|------------------|--------|-------|-----------------------|
| 31:10 | Reserved | R | 0x0 | Reserved |
| 9:0 | ADCRESULT | R | 0x0 | ADC conversion result |

16.1.18. AS0S5

Register 16-17. AS0S5 (Auto sequencer 0-sample 5 control 0x4015 006C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|--|
| 31:15 | Reserved | R | 0x0 | Reserved |
| 14:12 | ADCMUX | RW | 0x0 | ADC MUX input select 111b: VSSA 110b: reserved 101b: AD5 100b: AD4 011b: AD3 010b: AD2 001b: reserved 000b: EMUX |
| 11:10 | DELAY | RW | 0x0 | Delay between start of sample sequence and start of ADC conversion in ADC input clocks FLCK/ADCCTL.ADCCDIV 11b: 16 ADC input clock cycles 10b: 8 ADC input clock cycles 01b: 4 ADC input clock cycles 00b: 0 ADC input clock |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|--------------|--------|-------|---|
| 9:8 | EMUXS | RW | 0x0 | EMUX transmission start 11b: reserved 10b: send AS0S5.EMUXD data after S/H of ADC 01b: send AS0S5.EMUXD data at beginning of this sample sequence 00b: do not send AS0S5.EMUXD data |
| 7:0 | EMUXD | RW | 0x0 | EMUX data to transmit |

16.1.19. AS0R5

Register 16-18. AS0R5 (Auto sequencer 0-sample 5 result register 0x4015 0070)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|------------------|--------|-------|-----------------------|
| 31:10 | Reserved | R | 0x0 | Reserved |
| 9:0 | ADCRESULT | R | 0x0 | ADC conversion result |

16.1.20. AS0S6

Register 16-19. AS0S6 (Auto sequencer 0-sample 6 control 0x4015 0074)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|--|
| 31:15 | Reserved | R | 0x0 | Reserved |
| 14:12 | ADCMUX | RW | 0x0 | ADC MUX input select 111b: VSSA 110b: reserved 101b: AD5 100b: AD4 011b: AD3 010b: AD2 001b: reserved 000b: EMUX |
| 11:10 | DELAY | RW | 0x0 | Delay between start of sample sequence and start of ADC conversion in ADC input clocks FLCK/ADCCTL.ADCCDIV 11b: 16 ADC input clock cycles 10b: 8 ADC input clock cycles 01b: 4 ADC input clock cycles 00b: 0 ADC input clock |
| 9:8 | EMUXS | RW | 0x0 | EMUX transmission start 11b: reserved 10b: send AS0S6.EMUXD data after S/H of ADC 01b: send AS0S6.EMUXD data at beginning of this sample sequence 00b: do not send AS0S6.EMUXD data |
| 7:0 | EMUXD | RW | 0x0 | EMUX data to transmit |

16.1.21. AS0R6

Register 16-20. AS0R6 (Auto sequencer 0-sample 6 result register 0x4015 0078)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|------------------|--------|-------|-----------------------|
| 31:10 | Reserved | R | 0x0 | Reserved |
| 9:0 | ADCRESULT | R | 0x0 | ADC conversion result |

16.1.22. AS0S7

Register 16-21. AS0S7 (Auto sequencer 0-sample 7 control 0x4015 007C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|--|
| 31:15 | Reserved | R | 0x0 | Reserved |
| 14:12 | ADCMUX | RW | 0x0 | ADC MUX input select 111b: VSSA 110b: reserved 101b: AD5 100b: AD4 011b: AD3 010b: AD2 001b: reserved 000b: EMUX |
| 11:10 | DELAY | RW | 0x0 | Delay between start of sample sequence and start of ADC conversion in ADC input clocks FLCK/ADCCTL.ADCCDIV 11b: 16 ADC input clock cycles 10b: 8 ADC input clock cycles 01b: 4 ADC input clock cycles 00b: 0 ADC input clock |
| 9:8 | EMUXS | RW | 0x0 | EMUX transmission start 11b: reserved 10b: send AS0S7.EMUXD data after S/H of ADC 01b: send AS0S7.EMUXD data at beginning of this sample sequence 00b: do not send AS0S7.EMUXD data |
| 7:0 | EMUXD | RW | 0x0 | EMUX data to transmit |

16.1.23. AS0R7

Register 16-22. AS0R7 (Auto sequencer 0-sample 7 result register 0x4015 0080)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|------------------|--------|-------|-----------------------|
| 31:10 | Reserved | R | 0x0 | Reserved |
| 9:0 | ADCRESULT | R | 0x0 | ADC conversion result |

16.1.24. AS1CTL

Register 16-23. AS1CTL (Auto Sequencer 1 control register 0x4015 0100)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|--|
| 31:13 | Reserved | R | 0x0 | Reserved |
| 12 | AS1BUSY | RW | 0x0 | Auto sequencer 1 busy 1b: auto sequencer 1 sampling active 0b: auto sequencer 1 not active |
| 11 | AS1EN | RW | 0x0 | Auto sequencer 1 enable 1b: auto sequencer 1 enabled 0b: auto sequencer 1 not enabled |
| 10:8 | AS1D | RW | 0x0 | Auto sequencer 1 sampling depth 111b: 8 samples 110b: 7 samples 101b: 6 samples 100b: 5 samples 011b: 4 samples 010b: 3 samples 001b: 2 samples 000b: 1 sample |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|---|
| 7 | AS1TR | RW | 0x0 | Auto sequencer 1 trigger source 1b: Timer, as defined by AS1CTL.AS1TRTMR 0b: PWM, as defined by AS1CTL.AS1TRPWM |
| 6 | AS1TRE | RW | 0x0 | Auto sequencer 1 trigger source AS1CTL.AS1TR edge 1b: high to low edge 0b: low to high edge |
| 5:4 | AS1TRTMR | RW | 0x0 | Auto sequencer 1 timer trigger source 11b: Timer D 10b: Timer C 01b: Timer B 00b: Timer A |
| 3:0 | AS1TRPWM | RW | 0x0 | Auto sequencer 1 PWM trigger source 1111b: reserved 1110b: reserved 1101b: PWMD1 1100b: PWMD0 1011b: PWMC1 1010b: PWMC0 1001b: PWMB1 1000b: PWMB0 0111b: PWMA7 0110b: PWMA6 0101b: PWMA5 0100b: PWMA4 0011b: PWMA3 0010b: PWMA2 0001b: PWMA1 0000b: PWMA0 |

16.1.25. AS1S0

Register 16-24. AS1S0 (Auto sequencer 1-sample 0 control 0x4015 0104)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|--|
| 31:15 | Reserved | R | 0x0 | Reserved |
| 14:12 | ADCMUX | RW | 0x0 | ADC MUX input select 111b: VSSA 110b: reserved 101b: AD5 100b: AD4 011b: AD3 010b: AD2 001b: reserved 000b: EMUX |
| 11:10 | DELAY | RW | 0x0 | Delay between start of sample sequence and start of ADC conversion in ADC input clocks FLCK/ADCCTL.ADCCDIV 11b: 16 ADC input clock cycles 10b: 8 ADC input clock cycles 01b: 4 ADC input clock cycles 00b: 0 ADC input clock |
| 9:8 | EMUXS | RW | 0x0 | EMUX transmission start 11b: reserved 10b: send AS1S0.EMUXD data after S/H of ADC 01b: send AS1S0.EMUXD data at beginning of this sample sequence 00b: do not send AS1S0.EMUXD data |
| 7:0 | EMUXD | RW | 0x0 | EMUX data to transmit |

16.1.26. AS1R0

Register 16-25. AS1R0 (Auto sequencer 1-sample 0 result register 0x4015 0108)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------|--------|-------|-----------------------|
| 31:10 | Reserved | R | 0x0 | Reserved |
| 9:0 | ADCRESULT | R | 0x0 | ADC conversion result |

16.1.27. AS1S1

Register 16-26. AS1S1 (Auto sequencer 1-sample 1 control 0x4015 010C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|----------|--------|-------|--|
| 31:15 | Reserved | R | 0x0 | Reserved |
| 14:12 | ADCMUX | RW | 0x0 | ADC MUX input select 111b: VSSA 110b: reserved 101b: AD5 100b: AD4 011b: AD3 010b: AD2 001b: reserved 000b: EMUX |
| 11:10 | DELAY | RW | 0x0 | Delay between start of sample sequence and start of ADC conversion in ADC input clocks FLCK/ADCCTL.ADCCDIV 11b: 16 ADC input clock cycles 10b: 8 ADC input clock cycles 01b: 4 ADC input clock cycles 00b: 0 ADC input clock |
| 9:8 | EMUXS | RW | 0x0 | EMUX transmission start 11b: reserved 10b: send AS1S1.EMUXD data after S/H of ADC 01b: send AS1S1.EMUXD data at beginning of this sample sequence 00b: do not send AS1S1.EMUXD data |
| 7:0 | EMUXD | RW | 0x0 | EMUX data to transmit |

16.1.28. AS1R1

Register 16-27. AS1R1 (Auto sequencer 1-sample 1 result register 0x4015 0110)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------|--------|-------|-----------------------|
| 31:10 | Reserved | R | 0x0 | Reserved |
| 9:0 | ADCRESULT | R | 0x0 | ADC conversion result |

16.1.29. AS1S2

Register 16-28. AS1S2 (Auto sequencer 1-sample 2 control 0x4015 0114)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|----------|--------|-------|-------------|
| 31:15 | Reserved | R | 0x0 | Reserved |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|---------------|--------|-------|--|
| 14:12 | ADCMUX | RW | 0x0 | ADC MUX input select 111b: VSSA 110b: reserved 101b: AD5 100b: AD4 011b: AD3 010b: AD2 001b: reserved 000b: EMUX |
| 11:10 | DELAY | RW | 0x0 | Delay between start of sample sequence and start of ADC conversion in ADC input clocks FLCK/ADCCTL.ADCCDIV 11b: 16 ADC input clock cycles 10b: 8 ADC input clock cycles 01b: 4 ADC input clock cycles 00b: 0 ADC input clock |
| 9:8 | EMUXS | RW | 0x0 | EMUX transmission start 11b: reserved 10b: send AS1S2.EMUXD data after S/H of ADC 01b: send AS1S2.EMUXD data at beginning of this sample sequence 00b: do not send AS1S2.EMUXD data |
| 7:0 | EMUXD | RW | 0x0 | EMUX data to transmit |

16.1.30. AS1R2

Register 16-29. AS1R2 (Auto sequencer 1-sample 2 result register 0x4015 0118)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|------------------|--------|-------|-----------------------|
| 31:10 | Reserved | R | 0x0 | Reserved |
| 9:0 | ADCRESULT | R | 0x0 | ADC conversion result |

16.1.31. AS1S3

Register 16-30. AS1S3 (Auto sequencer 1-sample 3 control 0x4015 011C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|--|
| 31:15 | Reserved | R | 0x0 | Reserved |
| 14:12 | ADCMUX | RW | 0x0 | ADC MUX input select 111b: VSSA 110b: reserved 101b: AD5 100b: AD4 011b: AD3 010b: AD2 001b: reserved 000b: EMUX |
| 11:10 | DELAY | RW | 0x0 | Delay between start of sample sequence and start of ADC conversion in ADC input clocks FLCK/ADCCTL.ADCCDIV 11b: 16 ADC input clock cycles 10b: 8 ADC input clock cycles 01b: 4 ADC input clock cycles 00b: 0 ADC input clock |
| 9:8 | EMUXS | RW | 0x0 | EMUX transmission start 11b: reserved 10b: send AS1S3.EMUXD data after S/H of ADC 01b: send AS1S3.EMUXD data at beginning of this sample sequence 00b: do not send AS1S3.EMUXD data |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-------|--------|-------|-----------------------|
| 7:0 | EMUXD | RW | 0x0 | EMUX data to transmit |

16.1.32. AS1R3

Register 16-31. AS1R3 (Auto sequencer 1-sample 3 result register 0x4015 0120)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------|--------|-------|-----------------------|
| 31:10 | Reserved | R | 0x0 | Reserved |
| 9:0 | ADCRESULT | R | 0x0 | ADC conversion result |

16.1.33. AS1S4

Register 16-32. AS1S4 (Auto sequencer 1-sample 4 control 0x4015 0124)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|----------|--------|-------|--|
| 31:15 | Reserved | R | 0x0 | Reserved |
| 14:12 | ADCMUX | RW | 0x0 | ADC MUX input select 111b: VSSA 110b: reserved 101b: AD5 100b: AD4 011b: AD3 010b: AD2 001b: reserved 000b: EMUX |
| 11:10 | DELAY | RW | 0x0 | Delay between start of sample sequence and start of ADC conversion in ADC input clocks FLCK/ADCCTL.ADCCDIV 11b: 16 ADC input clock cycles 10b: 8 ADC input clock cycles 01b: 4 ADC input clock cycles 00b: 0 ADC input clock |
| 9:8 | EMUXS | RW | 0x0 | EMUX transmission start 11b: reserved 10b: send AS1S4.EMUXD data after S/H of ADC 01b: send AS1S4.EMUXD data at beginning of this sample sequence 00b: do not send AS1S4.EMUXD data |
| 7:0 | EMUXD | RW | 0x0 | EMUX data to transmit |

16.1.34. AS1R4

Register 16-33. AS1R4 (Auto sequencer 1-sample 4 result register 0x4015 0128)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------|--------|-------|-----------------------|
| 31:10 | Reserved | R | 0x0 | Reserved |
| 9:0 | ADCRESULT | R | 0x0 | ADC conversion result |

16.1.35. AS1S5

Register 16-34. AS1S5 (Auto sequencer 1-sample 5 control 0x4015 012C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|----------|--------|-------|-------------|
| 31:15 | Reserved | R | 0x0 | Reserved |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|---------------|--------|-------|--|
| 14:12 | ADCMUX | RW | 0x0 | ADC MUX input select 111b: VSSA 110b: reserved 101b: AD5 100b: AD4 011b: AD3 010b: AD2 001b: reserved 000b: EMUX |
| 11:10 | DELAY | RW | 0x0 | Delay between start of sample sequence and start of ADC conversion in ADC input clocks FLCK/ADCCTL.ADCCDIV 11b: 16 ADC input clock cycles 10b: 8 ADC input clock cycles 01b: 4 ADC input clock cycles 00b: 0 ADC input clock |
| 9:8 | EMUXS | RW | 0x0 | EMUX transmission start 11b: reserved 10b: send AS1S5.EMUXD data after S/H of ADC 01b: send AS1S5.EMUXD data at beginning of this sample sequence 00b: do not send AS1S5.EMUXD data |
| 7:0 | EMUXD | RW | 0x0 | EMUX data to transmit |

16.1.36. AS1R5

Register 16-35. AS1R5 (Auto sequencer 1-sample 5 result register 0x4015 0130)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|------------------|--------|-------|-----------------------|
| 31:10 | Reserved | R | 0x0 | Reserved |
| 9:0 | ADCRESULT | R | 0x0 | ADC conversion result |

16.1.37. AS1S6

Register 16-36. AS1S6 (Auto sequencer 1-sample 6 control 0x4015 0134)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|--|
| 31:15 | Reserved | R | 0x0 | Reserved |
| 14:12 | ADCMUX | RW | 0x0 | ADC MUX input select 111b: VSSA 110b: reserved 101b: AD5 100b: AD4 011b: AD3 010b: AD2 001b: reserved 000b: EMUX |
| 11:10 | DELAY | RW | 0x0 | Delay between start of sample sequence and start of ADC conversion in ADC input clocks FLCK/ADCCTL.ADCCDIV 11b: 16 ADC input clock cycles 10b: 8 ADC input clock cycles 01b: 4 ADC input clock cycles 00b: 0 ADC input clock |
| 9:8 | EMUXS | RW | 0x0 | EMUX transmission start 11b: reserved 10b: send AS1S6.EMUXD data after S/H of ADC 01b: send AS1S6.EMUXD data at beginning of this sample sequence 00b: do not send AS1S6.EMUXD data |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-------|--------|-------|-----------------------|
| 7:0 | EMUXD | RW | 0x0 | EMUX data to transmit |

16.1.38. AS1R6

Register 16-37. AS1R6 (Auto sequencer 1-sample 6 result register 0x4015 0138)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------|--------|-------|-----------------------|
| 31:10 | Reserved | R | 0x0 | Reserved |
| 9:0 | ADCRESULT | R | 0x0 | ADC conversion result |

16.1.39. AS1S7

Register 16-38. AS1S7 (Auto sequencer 1-sample 7 control 0x4015 013C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|----------|--------|-------|--|
| 31:15 | Reserved | R | 0x0 | Reserved |
| 14:12 | ADCMUX | RW | 0x0 | ADC MUX input select 111b: VSSA 110b: reserved 101b: AD5 100b: AD4 011b: AD3 010b: AD2 001b: reserved 000b: EMUX |
| 11:10 | DELAY | RW | 0x0 | Delay between start of sample sequence and start of ADC conversion in ADC input clocks FLCK/ADCCTL.ADCCDIV 11b: 16 ADC input clock cycles 10b: 8 ADC input clock cycles 01b: 4 ADC input clock cycles 00b: 0 ADC input clock |
| 9:8 | EMUXS | RW | 0x0 | EMUX transmission start 11b: reserved 10b: send AS1S7.EMUXD data after S/H of ADC 01b: send AS1S7.EMUXD data at beginning of this sample sequence 00b: do not send AS1S7.EMUXD data |
| 7:0 | EMUXD | RW | 0x0 | EMUX data to transmit |

16.1.40. AS1R7


Register 16-39. AS1R7 (Auto sequencer 1-sample 7 result register 0x4015 0140)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------|--------|-------|-----------------------|
| 31:10 | Reserved | R | 0x0 | Reserved |
| 9:0 | ADCRESULT | R | 0x0 | ADC conversion result |

16.2. Details of Operation

16.2.1. Block Diagram

Figure 16-1. ADC, EMUX, ASC0, ASC1



16.3. Details of Operation

16.3.1. Basic Configuration

Following blocks need to be configured for correct operation of the ADC

- CCS
- Timer A, B, C or D
- GPIOB
- GPIOC
- NVIC

16.3.2. ADC, Autosequencer and EMUX

The ADC is a 10-bit SAR ADC. It can be used standalone or together with up to 2 independent low latency auto sequencer state machines to take series of up to 8 samples each into dedicated sample result registers, triggered by either PWM or timer signals. Each sample setup can be programmed with dedicated ADC-MUX setting and settling time delay. A dedicated, programmable high speed low latency communication interface is available to set analog both MUX, sample and hold circuits in the analog peripherals.

16.3.3. Clock Setting

The ADC clock is derived from FCLK and can be set with **ADCCTL.ADCCDIV**. The ADC clock should not exceed 16MHz for correct operation.

The EMUX clock is derived from HCLK and can be set with **EMUXCTL.EMUXCDIV**.

16.3.4. ADC

The ADC, ASC0, ASC1 and EMUX block is enabled with **ADCCTL.ADCEN**. In manual conversion mode set **ADCCTL.ADCMODE** to 0b. Set the ADx channel with **ADCCTL.ADCMUX**. For single conversion, set **ADCCTL.REPEAT** to 0b, for repeated conversion set **ADCCTL.REPEAT** to 1b. To start a conversion set **ADCCTL.ADCSTART** to 1b. The ADC will start sampling the analog input channel for 3 clock cycles and holds the analog value in its internal S/H for conversion. It is safe to switch ADC input channel 4 clocks after ADC start without affecting the ADC result.

One complete ADC conversion will take 16 ADC clock cycles and the ADC conversion result will be available in **ADCCR**. In repeated mode **ADCCR** will be overwritten every 16 ADC clock cycles.. The **ADCCTL.ADCBUSY** flag will be 1b as long as conversions are active. **ADCCTL.ADCSTART** will auto clear in single conversion mode. To stop a conversion manually clear **ADCCTL.ADCSTART**.

Figure 16-2. ADC Conversion (Single Shot)





Figure 16-3. ADC Conversion (Repeat Mode)



16.3.5. EMUX

The EMUX is a low latency high speed serial interface with 8-bit data message to control the external ADC MUX and S/H in the analog front end. The EMUX interface is independent from the SOC BUS bridge.

The clock frequency of the EMUX can be adjusted with **EMUXCTL.EMUXCDIV** from HCLK/1 to HCLK/8.

To allow use of EMUX with auto sequencer ASC0 and ASC1, **EMUXCTL.EMUXC** must be set to 1b.

In manual mode with **EMUXCTL.EMUXC** = 0b, the EMUX will start sending the message MSB first as soon as a 8-bit message is written to **EMUXDATA**. While the message is transferred, **EMUXCTL.EMUXDONE** is cleared and is set to 1b when the message transfer is complete.

16.3.6. Auto Sequencer ASC0, ASC1

The ADC and EMUX can be controlled with 2 independent auto sequencer state machines ASC0 and ASC01 to offload the CPU from high speed, low latency sampling. Each sequencer can be programmed to take up to 8 consecutive ADC samples from different analog inputs.

16.3.6.1. Auto Sequencer Modes

The AC0, ASC1 support 8 different modes, configurable with **ADCCTL.ADCMODE**.

With **ADCCTL.ADCMODE** = 000b ASC0 and ASC1 are disabled and the ADC is used in manual mode.

With **ADCCTL.ADCMODE** = 001b only ASC0 is active and manually triggered with **AS0CTL.AS0EN**.

With **ADCCTL.ADCMODE** = 010b only ASC1 is enabled and manually triggered with **AS1CTL.AS1EN**.

With **ADCCTL.ADCMODE** = 011b ASC0 and ASC1 are enabled and daisy chained. When manually triggered with **AS0CTL.AS0EN**, ASC0 will convert all programmed samples, when finished ASC0 will automatically trigger ASC1.

With **ADCCTL.ADCMODE** = 100b only ASC0 is active and triggered with trigger source configured in **AS0CTL.AS0TR**.

With **ADCCTL.ADCMODE** = 101b only ASC1 is active and triggered with trigger source configured in **AS1CTL.AS1TR**.

With **ADCCTL.ADCMODE** = 110b ASC0 and ASC1 are enabled and daisy chained. When triggered with source defined in **AS0CTL.AS0TR**, ASC0 will convert all programmed samples, when finished ASC0 will automatically trigger ASC1.

With **ADCCTL.ADCMODE** = 111b ASC0 and ASC1 are enabled and run independently. ASC0 is triggered with **AS0CTL.AS0TR**, ASC1 is triggered with **AS1CTL.AS1TR**.


Figure 16-4. ASCx, ADCCTL.ADCMODE = 001b, 010b, 100b, 101b



Figure 16-5. ASCx, ADCCTL.ADCMODE = 011b, 110b



Figure 16-6. ASCx, ADCCTL.ADCMODE = 111b



16.3.6.2. Sequencer trigger

Each sequencer ASC0 and ASC1 can use 2 different trigger modes, manual mode or automated mode.

In automated mode use **ASxCTL.ASxTR** to set the trigger source either to timer A, B, C, or D or PWMAX, PWMBx, PWMCx or PWMDx. Use **AS0xCTL.ASxTRE** to set rising or falling edge trigger. Use **AS0xCTL.ASxTMR** to select timer source or **AS0xCTL.AsxTRPWM** to PWM source.

16.3.6.3. ASC Samples

Each sequencer can be programmed to take 1 to 8 samples up on triggering using **ASxCTL.AsxD**. For each sample, the ADC channel can be programmed with **ASxSy.ADCMUX**, a delay between MUX change and ADC start using **ASxSy.DELAY**, a EMUX message to be send with **ASxSy.EMUXD**, and a configuration with **ASxSy.EMUXS** to not send EMUXD, send right after ADCMUX change or send right after start of delay.

NOTE:

Make sure that the EMUX transmission is finished within delay time or ADC conversion time by choosing the correct EMUX clock divider setting.

Figure 16-7. ASxSy Sample with ASxSy.EMUXS = 00b and ASxSy.DELAY = 11b




Figure 16-8. ASxSy Sample with ASxSy.EMUXS = 01b and ASxSy.DELAY = 11b





Figure 16-9. ASxSy Sample with ASxSy.EMUXS = 10b and ASxSy.DELAY = 11b



16.3.6.4. ASC0, ASC1 Priority and Collision

In **ADCCTL.ADCMODE** = 100b, 101b, 110b the ASC are triggered with external trigger timer or PWM. Care has to be taken to space the trigger wide enough to allow sequencer ASCx to finish all samples. In case the sequencer trigger event happens before ASC sequencer finishes all samples, the **ADCINT.ASCINT** collision interrupt will be set and the trigger will be ignored. When **ADCINT.ASCINT** is set, **ADCINT.ASCINTSEQ** shows the ASC0 or ASC1 trigger causing the collision interrupt and **ADCINT.ASCINTR** the actual running sequencer.

Figure 16-10. ASCx, 8 samples, No Collision





Figure 16-11. ASCx 8 samples, Collision




In **ADCCTL.ADCMODE = 111b**, the ASC0 and ASC1 sequencer are triggered independently but are accessing the same ADC.

In case of both ASC0 and ASC1 are triggered at the same time, ASC0 has always higher priority and will be executed while ASC1 is skipped and ignored. **ADCINT.ASCINT** will be set, **ADCINT.ASCINTSEQ** shows the ASC0 or ASC1 trigger causing the collision interrupt and **ADCINT.ASCINTR** the actual running sequencer.

In case of ASC0 or ASC1 sequencer running while the other is triggered, the second sequencer trigger is skipped and ignored, **ADCINT.ASCINT** will be set, **ADCINT.ASCINTSEQ** shows the ASC0 or ASC1 trigger causing the collision interrupt and **ADCINT.ASCINTR** the actual running sequencer.

Figure 16-12. ASC0 8 samples, ASC1 4 samples, Collision



17. I²C

17.1. Register

17.1.1. Register Map

Table 17-1. I²C Register Map

| ADDRESS | NAME | DESCRIPTION | RESET VALUE |
|-----------------------|-------------------|--|-------------|
| I²C | | | |
| 0x401B 0000 | I2CCFG | I ² C configuration | 0x0000 0000 |
| 0x401B 0004 | I2CINTSTAT | I ² C interrupt and status | 0x0000 0000 |
| 0x401B 0008 | I2CINTEN | I ² C interrupt enable | 0x0000 0000 |
| 0x401B 0030 | I2CMCTL | I ² C master access control | 0x0000 0000 |
| 0x401B 0034 | I2CMRXDATA | I ² C master receive data | 0x0000 0000 |
| 0x401B 0038 | I2CMTXDATA | I ² C master transmit data | 0x0000 0000 |
| 0x401B 0040 | I2CBAUD | I ² C master baud rate | 0x01EC 01EC |
| 0x401B 0070 | I2CSRXDATA | I ² C slave receive data | 0x0000 0000 |
| 0x401B 0074 | I2CSTXDATA | I ² C slave transmit data | 0x0000 0000 |
| 0x401B 0078 | I2CSADDR | I ² C slave address | 0x0000 0000 |

17.1.2. I2CCFG

Register 17-1. I2CCFG (I²C Configuration, 0x401B 0000)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:6 | Reserved | R | 0x0 | Reserved |
| 5 | Reserved | RW | 0x1 | Reserved, must be set to 1b |
| 4 | ADDRMODE | RW | 0x0 | Address Mode 1b: 10-bit addressing 0b: 7-bit addressing |
| 3 | Reserved | RW | 0x0 | Reserved, must be set to 0b |
| 2 | MAEN | RW | 0x0 | Master 1b: I2C Master enable 0b: I2C Master enable |
| 1 | Reserved | RW | 0x0 | Reserved, must be set to 0b |
| 0 | SLEN | RW | 0x0 | Slave Enable 1b: I2C Slave enable 0b: I2C Slave disable |

17.1.3. I2CINT

Register 17-2. I2CINT (I²C Interrupt, 0x401B 0004)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|-------------|
| 31:25 | Reserved | R | 0x0 | Reserved |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|----------------------|--------|-------|--|
| 24 | SLXFERDONEINT | R | 0x0 | Slave Transfer 1b = Slave transfer complete, clears on read 0b = Slave transfer not done |
| 23:19 | Reserved | R | 0x0 | Reserved |
| 18 | SLRXFINT | R | 0x0 | Slave receive data register SLRXDATA full 1b: SLRXDATA received data from I2C bus, clears on read 0b: SLRXDATA did not receive data since last read of I2CINT |
| 17 | SLTXEINT | R | 0x0 | Slave transmit data register SLTXDATA empty 1b: SLTXDATA transmitted to I2C bus, clears on read 0b: SLTXDATA not transmitted since last read of I2CINT |
| 16 | SLADDRMINT | R | 0x0 | Slave Address match 1b: Slave address match detected, clears on read 0b: no match |
| 15:12 | Reserved | R | 0x0 | Reserved |
| 11 | MADACKINT | R | 0x0 | Master data acknowledge 1b: Master data NACK'd, clears on read 0b: Master data ACK'd |
| 10 | MAARBLINT | R | 0x0 | Master lost arbitration 1b: Master lost arbitration, clear on read 0b: no error |
| 9 | MAADDRACKINT | R | 0x0 | Master address acknowledge 1b: Master address NACK'd, clears on read 0b: Master address ACK'd |
| 8 | MAXFERDONEINT | RW | 0x0 | Master transfer complete 1b: Master transfer complete, clears on read 0b: not done |
| 7:3 | Reserved | R | 0x0 | Reserved |
| 2 | MARXF | R | 0x0 | Master receive data register MARXDATA full 1b: MARXDATA received data from I2C bus, clears on read 0b: MARXDATA did not receive data since last read of I2CINT |
| 1 | MACTLE | RW | 0x0 | MACCTL access register accessed 1b: I2CMACTL processed by I2C engine, clears on read 0b: I2CMACTL not accessed by I2C engine since last read of I2CINT |
| 0 | MATXE | R | 0x0 | Master transmit data register MATXDATA empty 1b: MATXDATA transmitted to I2C bus, clears on read 0b: MATXDATA not transmitted since last read of I2CINT |

17.1.4. I2CINTEN

Register 17-3. I2CINTEN (I²C Interrupt Enable, 0x401B 0008)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------------------|--------|-------|---|
| 31:25 | Reserved | R | 0x0 | Reserved |
| 24 | SLXFERDONEIN TEN | RW | 0x0 | SLXFERDONE Interrupt enable 1b: interrupt enable 0b: interrupt disabled |
| 23:19 | Reserved | R | 0x0 | Reserved |
| 18 | SLRXF | R | 0x0 | SLRXF Interrupt enable 1b: interrupt enable 0b: interrupt disabled |
| 17 | SLTXE | R | 0x0 | SLTXE Interrupt enable 1b: interrupt enable 0b: interrupt disabled |
| 16 | SLADDRM | R | 0x0 | SLADDRM Interrupt enable 1b: interrupt enable 0b: interrupt disabled |
| 15:9 | Reserved | R | 0x0 | Reserved |
| 8 | MAXFERDONE | R | 0x0 | MAXFERDONE Interrupt enable 1b: interrupt enable 0b: interrupt disabled |
| 7:3 | Reserved | R | 0x0 | Reserved |
| 2 | MARXF | R | 0x0 | MARXF Interrupt enable 1b: interrupt enable 0b: interrupt disabled |
| 1 | MACTLE | R | 0x0 | MACTLE Interrupt enable 1b: interrupt enable 0b: interrupt disabled |
| 0 | MATXE | R | 0x0 | MATXE Interrupt enable 1b: interrupt enable 0b: interrupt disabled |

17.1.5. I2CMACTL

Register 17-4. I2CMACTL (I²C Master Access Control, 0x401B 0030)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|------------------|--------|-------|---|
| 31:14 | Reserved | R | 0x0 | Reserved |
| 13 | I2CMACTLF | R | 0x0 | I2CMACTL full 1b: I2CMACTL full, write not allowed, read to clear 0b: I2CMACTL processed, write allowed |
| 12 | Reserved | R | 0x0 | Reserved |
| 11 | XFERTYPE | RW | 0x0 | Master transfer type 1b: I ² C Master Read 0b: I ² C Master Write |
| 10 | RSTART | RW | 0x0 | Repeated start 1b: No STOP at end of transfer Repeated START 0b: STOP at end of transfer |
| 9:7 | I2CADDRU | RW | 0x0 | Upper I ² C address bit 9:7 |
| 6:0 | I2CADDRL | RW | 0x0 | Lower I ² C address bit 6:0 |

17.1.6. I2CMARXDATA

Register 17-5. I2CMARXDATA (I²C Master Receive Data, 0x401B 0034)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|---------------------|--------|-------|--|
| 31:9 | Reserved | RW | 0x0 | Reserved |
| 8 | I2CMARXDATAF | R | 0x0 | I2CMARXDATA full 1b: I2CMARXDATA register full, clear by read 0b: I2CMARXDATA register empty |
| 7:0 | MARXDATA | RW | 0x0 | Master Data Byte received |

17.1.7. I2CMATXDATA

Register 17-6. I2CMATXDATA (I²C Master Transmit Data, 0x401B 0038)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|---------------------|--------|-------|---|
| 31:9 | Reserved | RW | 0x0 | Reserved |
| 9 | LBYTE | RW | 0x0 | Last Byte of Transfer 1b: Last byte of READ or WRITE indicator, initiate STOP after data transfer |
| 8 | I2CMATXDATAF | R | 0x0 | I2CMATXDATA full 1b: I2CMATXDATA register full, data not transmitted 0b: I2CMATXDATA register empty |
| 7:0 | MATXDATA | RW | 0x0 | Master Data Byte to transmit |

17.1.8. I2CBAUD

Register 17-7. I2CBAUD (I²C Baud Rate, 0x401B 0040)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|---|
| 31:27 | Reserved | R | 0x0 | Reserved |
| 26:16 | SCLH | RW | 0x1EC | Number of HCLK cycles for I2CCL high time |
| 15:11 | Reserved | R | 0x0 | Reserved |
| 10:0 | SCLL | RW | 0x1EC | Number of HCLK cycles for I2CCL low time |

17.1.9. I2CSLRXDATA

Register 17-8. I2CSLRXDATA (I²C Slave Receive Data, 0x401B 0070)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|---------------------|--------|-------|---|
| 31:9 | Reserved | RW | 0x0 | Reserved |
| 8 | I2CSLRXDATAF | R | 0x0 | I2CSLRXDATA full 1b: I2CSLRXDATA register full, data not transmitted 0b: I2CSLRXDATA register empty |
| 7:0 | SLRXDATA | RW | 0x0 | Slave Data Byte received |

17.1.10. I2CSLTXDATA

Register 17-9. I2CSLTXDATA (I²C Slave Transmit Data, 0x401B 0074)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|---------------------|--------|-------|---|
| 31:9 | Reserved | RW | 0x0 | Reserved |
| 9 | I2CSLTXDATAF | R | 0x0 | I2CSLTXDATA full 1b: I2CSLTXDATA register full, data not transmitted 0b: I2CSLTXDATA register empty |
| 8 | NACK | RW | 0x0 | Slave ACK or NACK 1b: Issue NACK on I ² C Write 0b: Issue ACK on I ² C Write |
| 7:0 | SLTXDATA | RW | 0x0 | Slave Data Byte to transmit |

17.1.11. I2CSLADDR


Register 17-10. I2CSLADDR (I²C Slave Address, 0x401B 0074)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|------------------------------|
| 31:10 | Reserved | RW | 0x0 | Reserved |
| 9:7 | SLADDRH | R | 0x0 | Higher Slave address bit 9:7 |
| 6:0 | SLADDRL | RW | 0x0 | Lower Slave address bit 6:0 |

17.2. Details of Operation

17.2.1. Block Diagram

Figure 17-1. I2C



17.2.2. Configuration

Following blocks need to be configured for correct use of the I2C:

- Clock Control System (CCS)
- Nested Vectored Interrupt Controller (NVIC)
- IO Controller

17.2.3. I2C

The I2C Controller has one master and one slave connected to the same I/O that can be configured to be master only, slave only or concurrent master/slave. The I2C controller supports Normal mode (100kHz), Fast mode (400kHz), and Fast Mode+ (1MHz) operation. And 7-bit/ 10-bit addressing.

The master supports both single master and multi-master, multi-master sync and multi-master arbitration.

The slave supports clock stretching as well.

17.2.4. I2C Clock setting

The I2C SCLK frequency is derived from HCLK, **I2CBAUD.SCLH** sets the SCLK high pulse and **I2CBAUD.SCLL** sets the SCLK low pulse in HCLK cycles and need to be set correctly for different I2C mode.

The minimum HCLK for correct function of the I2C block is: 2.8MHz for normal mode, 3.2MHz for fast mode and 6.14MHz for fast+ mode.

The table below shows pre-calculated **I2CBAUD** settings for normal, fast and fast+ mode with 50MHz HCLK.

Table 17-11. I2CBAUD settings for different HCLK

| I2C Mode | SCLK Frequency | HLCK | I2CBAUD.SCLH | I2CBAUD.SCLL |
|----------|----------------|---------|--------------|--------------|
| Normal | 100kHz | 50MHz | 0xFA | 0xFA |
| Normal | 100kHz | 4MHz | 0x14 | 0x14 |
| Normal | 100kHz | 2.8MHz | 0x0E | 0x0E |
| Fast | 400kHz | 50MHz | 0x3E | 0x3E |
| Fast | 400kHz | 4MHz | 0x3E | 0x3E |
| Fast | 400kHz | 3.2MHz | 0x04 | 0x04 |
| Fast+ | 1000kHz | 50MHz | 0x18 | 0x18 |
| Fast+ | 1000kHz | 6.14MHz | 0x03 | 0x03 |

17.2.5. I2C Addressing

The I2C address is for I2C master is set in **I2CMACTL.I2CADDRL** and **I2CMACTL.I2CADDRH**. The slave address is set **I2CSLADDR.SLADDRL** and **I2CSLADDR.SLADDRH**.

18. UART

18.1. Register

18.1.1. Register Map

Table 18-1. UART Register Map

| ADDRESS | NAME | DESCRIPTION | RESET VALUE |
|-------------|------------------|-------------------------------|-------------|
| UART | | | |
| 0x401D 0000 | UARTRXTX | UART receive/transmit FIFO | 0x0000 0000 |
| 0x401D 0004 | UARTIEN | UART interrupt enable | 0x0000 0000 |
| 0x401D 0008 | UARTII | UART interrupt identification | 0x0000 0001 |
| 0x401D 000C | UARTLC | UART line control | 0x0000 0000 |
| 0x401D 0010 | Reserved | Reserved | 0x0000 0000 |
| 0x401D 0014 | UARTLS | UART line status | 0x0000 0060 |
| 0x401D 0018 | Reserved | Reserved | unknown |
| 0x401D 001C | Reserved | Reserved | 0x0000 0000 |
| 0x401D 0020 | UARTFCTL | UART FIFO control | 0x0000 0000 |
| 0x401D 0024 | UARTIEN | UART interrupt enable | 0x0000 0000 |
| 0x401D 0028 | UARTDL_L | UART divisor latch low byte | 0x0000 0000 |
| 0x401D 002C | UARTDL_H | UART divisor latch high byte | 0x0000 0000 |
| 0x401D 0038 | UARTFD_F | UART fractional divisor value | 0x0000 0000 |
| 0x401D 003C | Reserved | Reserved | 0x0000 0000 |
| 0x401D 0040 | UARTFSTAT | UART FIFO status | 0x0000 0005 |

18.1.2. UARTRXTX/UARTDL_L

Register 18-1. UARTRXTX (UART Receive/Transmit FIFO, 0x401D 0000)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | R | 0x0 | Reserved |
| 7:0 | RXTX | RW | 0x0 | Receive and Transmit FIFO buffer on READ: RX FIFO on WRITE: TX FIFO |

18.1.3. UARTIEN/UARTDL_H

Register 18-2. UARTIEN (UART Interrupt Enable, 0x401D 0004)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|--|
| 31:4 | Reserved | R | 0x0 | Reserved |
| 3 | MSINTEN | RW | 0x0 | Modem Status interrupt enable 1b: enable interrupt 0b: disable interrupt |
| 2 | RSINTEN | RW | 0x0 | Receive interrupt enable 1b: enable interrupt 0b: disable interrupt |
| 1 | TXINTEN | RW | 0x0 | TX register empty interrupt enable 1b: enable interrupt 0b: disable interrupt |
| 0 | RXINTEN | RW | 0x0 | RX register data available interrupt enable 1b: enable interrupt 0b: disable interrupt |

18.1.4. UARTII

Register 18-3. UARTII (UART Interrupt Identification, 0x401D 0008)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|------------------|--------|-------|---|
| 31:8 | Reserved | R | 0x0 | Reserved |
| 7 | RXFEN | R | 0x0 | RX FIFO enable flag 1b: enabled 0b: disabled |
| 6 | TXFEN | R | 0x0 | TX FIFO enable flag 1b: enabled 0b: disabled |
| 5:4 | Reserved | R | 0x0 | Reserved |
| 3:1 | UARTINTID | R | 0x0 | UART Interrupt type 111b: reserved 110b: Timeout 101b: reserved 100b: reserved 011b: RX Line Status 010b: RX Data Available 001b: TX Hold register empty 000b: Modem Status |
| 0 | UARTINT | R | 0x1 | UART Interrupt 1b: UART interrupt 0b: no UART interrupt |

18.1.5. UARTLC

Register 18-4. UARTLC (UART Line Control, 0x401D 000C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|--|
| 31:8 | Reserved | R | 0x0 | Reserved |
| 7 | Reserved | RW | 0x0 | Reserved, write to 0x0 |
| 6 | SB | RW | 0x0 | Break Control 1b: force TX to 0b 0b: normal operation |
| 5 | SP | RW | 0x0 | Stick Parity 1b: enable 0b: disable |
| 4 | EPS | RW | 0x0 | Parity type 1b: generate EVEN parity 0b: generate ODD parity |
| 3 | PEN | RW | 0x0 | Parity Bit 1b: enable Parity 0b: disable Parity |
| 2 | STB | RW | 0x0 | Stop Bits 1b: 2 STOP bits (1.5 STOP bits for BPC=00) 0b: 1 STOP bit |
| 1:0 | BPC | RW | 0x0 | Bits per Character 11b: 8 bits 10b: 7 bits 01b: 6 bits 00b: 5 bits |

18.1.6. UARTLS

Register 18-5. UARTLS (UART Line Status, 0x401D 0014)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|--|
| 31:8 | Reserved | R | 0x0 | Reserved |
| 7 | RXE | R | 0x0 | RX FIFO Error 1b: at least 1 parity, framing or break error active in FIFO 0b: no error in RX FIFO |
| 6 | TXE | R | 0x1 | TX Empty 1b: TX shift register and TX FIFO are empty 0b: not empty |
| 5 | TCFE | R | 0x1 | TX FIFO Empty 1b: TX FIFO are empty 0b: not empty |
| 4 | RXBE | R | 0x0 | RX Break 1b: entry on top of RX FIFO has break error, bit clears on read 0b: error cleared |
| 3 | RXFE | R | 0x0 | RX Framing Error 1b: entry on top of RX FIFO has framing error, bit clears on read 0b: error cleared |
| 2 | RXPE | R | 0x0 | RX Parity Error 1b: entry on top of RX FIFO has parity error, bit clears on read 0b: error cleared |
| 1 | RXOE | R | 0x0 | RX Overrun error 1b: RX FIFO full and last entry overwritten, bit clears on read 0b: error cleared |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-------------|--------|-------|---|
| 0 | RXDR | R | 0x0 | RX Data ready 1b: at least 1 entry in RX FIFO 0b: RX FIFO empty |

18.1.7. UARTFCTL

Register 18-6. UARTFCTL (FIFO Control, 0x401D 0020)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:8 | Reserved | R | 0x0 | Reserved |
| 7:6 | RXFT | RW | 0x1 | RX FIFO Threshold 11b: 14 Bytes in FIFO 10b: 8 Bytes in FIFO 01b: 4 Bytes in FIFO 00b: 1 Byte in FIFO |
| 5:3 | Reserved | R | 0x0 | Reserved |
| 2 | TXFRESET | RW | 0x0 | TX FIFO reset 1b: clear TX FIFO, bit auto clears 0b: no action |
| 1 | RXFRESET | RW | 0x0 | RX FIFO reset 1b: clear RX FIFO, bit auto clears 0b: no action |
| 0 | FEN | RW | 0x0 | FIFO enable 1b: enable RX, TX FIFO 0b: disable RX, TX FIFO |

18.1.8. UARTIEN

Register 18-7. UARTIEN (UART Interrupt Enable, 0x401D 0024)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|--|
| 31:4 | Reserved | R | 0x0 | Reserved |
| 3 | MSINTEN | RW | 0x0 | Modem Status interrupt enable 1b: enable interrupt 0b: disable interrupt |
| 2 | RSINTEN | RW | 0x0 | Receive interrupt enable 1b: enable interrupt 0b: disable interrupt |
| 1 | TXINTEN | RW | 0x0 | TX register empty interrupt enable 1b: enable interrupt 0b: disable interrupt |
| 0 | RXINTEN | RW | 0x0 | RX register data available interrupt enable 1b: enable interrupt 0b: disable interrupt |

18.1.9. UARSDL_L

Register 18-8. UARSDL_L (UART Divisor Latch Low Byte, 0x401D 0028)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|-------------------------|
| 31:8 | Reserved | R | 0x0 | Reserved |
| 7:0 | DL_L | RW | 0x0 | Divisor value, low byte |

18.1.10. UARTDL_H

Register 18-9. UARTDL_H (UART Divisor Latch High Byte, 0x401D 002C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|--------------------------|
| 31:8 | Reserved | R | 0x0 | Reserved |
| 7:0 | DL_H | RW | 0x0 | Divisor value, high byte |

18.1.11. UARTFD_F

Register 18-10. UARTFD_F (UART Fractional Divisor Value, 0x401D 0038)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|--------------------------|
| 31:8 | Reserved | R | 0x0 | Reserved |
| 7:0 | FRAC | RW | 0x0 | Fractional divisor value |

18.1.12. UARTFSTAT


Register 18-11. UARTFSTAT (UART FIFO Status, 0x401D 0040)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|---|
| 31:4 | Reserved | R | 0x0 | Reserved |
| 3 | RXFF | R | 0x0 | RX FIFO full 1b: RX FIFO full 0b: RX FIFO not full |
| 2 | RXFE | R | 0x1 | RX FIFO empty 1b: RX FIFO empty 0b: RX FIFO not empty |
| 1 | TXFF | R | 0x0 | TX FIFO full 1b: TX FIFO full 0b: TX FIFO not full |
| 0 | TXFE | R | 0x1 | TX FIFO empty 1b: TX FIFO empty 0b: TX FIFO not empty |

18.2. Details of Operation

18.2.1. Block Diagram

Figure 18-1. UART



18.2.2. Configuration

Following blocks need to be configured for correct use of the UART:

- Clock Control System (CCS)
- Nested Vectored Interrupt Controller (NVIC)
- I/O Controller

18.2.3. UART

The UART supports up to 115,200 k-bit communication speed, has programmable clock selection with fractional divider, loop back mode for testing, 16 Byte transmit and 16 Byte receive FIFO with programmable receive interrupt threshold.

18.2.4. UART Clock Rate Setting

The UART block has a fractional divider to set up the baud rate. The UART clock is fed by the HCLK. The UART clock must be set to 16x the desired RX/TX baud rate setting for correct functioning.

To calculate settings for **UARTDL_H**, **UARTDL_L**, **UARTFD_F**, first calculate the desired divisor setting using following formula:

$$UARTDivisor = \frac{HCLK}{BAUDRATE * 16} \quad (6)$$

Where:

UARTDivisor: calculated divisor

HCLK: HCLK frequency in Hz

BAUDRATE: desired Baud rate

The integer portion of UARTDivisor is used to set **UARTDL_H**, **UARTDL_L**.

To calculate the value of **UARTFD_F**, use formula below and round to the nearest integer.

$$UARTFD = UARTDivisor_{frac} * 256 \quad (7)$$

Where:

UARTFD: calculated UARTFD value

UARTDIVISOR_FRAC: UARTDivisor fractional value

To calculate Baud rate error use following:

$$BAUDRATEERROR = BAUDRATE - (HCLK / (UARTDivisor + UARTDivisor_{frac} / 256)) / 16 \quad (8)$$

Where:

BAUDRATEERROR: absolute baud rate error

BAUDRATE: Baudrate

HCLK: HCLK frequency in Hz

UARTDivisor: UART divisor integer value

UARTDivisor_fraC: UART divisor fractional value

To calculate relative Baud rate error use following:

$$Relative\ BAUDRATEERROR = BAUDRATEERROR / BAUDRATE * 100 \quad (9)$$

Where:

Relative BAUDRATE ERROR: relative BAUD rate error in %.

BAUDRATEERROR: absolute Baudrateerror

BAUDRATE: desired baudrate setting

The table below shows pre-calculated divisor settings for common Baud rates with 50MHz HCLK.

Register 18-12. UART Divisor Settings for 50 MHz HCLK

| Baud Rate | Desired Divisor | Int | frac | UARTDL_H | UARTDL_L | UARTFD_F | Absolute BAUD rate error | BAUD rate error % |
|-----------|-----------------|-------|------|----------|----------|----------|--------------------------|-------------------|
| 300 | 10416.667 | 10416 | 171 | 0x28 | 0xB0 | 0xAB | 0.000010 | 0.0000% |
| 600 | 5208.333 | 5208 | 85 | 0x14 | 0x58 | 0x55 | -0.000038 | 0.0000% |
| 900 | 3472.222 | 3472 | 57 | 0x0D | 0x90 | 0x39 | -0.000058 | 0.0000% |
| 1200 | 2604.167 | 2604 | 43 | 0x0A | 0x2C | 0x2B | 0.000154 | 0.0000% |
| 2400 | 1302.083 | 1302 | 21 | 0x05 | 0x16 | 0x15 | -0.000614 | 0.0000% |
| 4800 | 651.042 | 651 | 11 | 0x02 | 0x8B | 0x0B | 0.002458 | 0.0001% |
| 9600 | 325.521 | 325 | 133 | 0x01 | 0x45 | 0x85 | 0.004915 | 0.0001% |
| 19200 | 162.760 | 162 | 195 | 0x00 | 0xA2 | 0xC3 | -0.049152 | -0.0003% |
| 38400 | 81.380 | 81 | 97 | 0x00 | 0x51 | 0x61 | -0.1 | -0.0003% |
| 57600 | 54.253 | 54 | 65 | 0x00 | 0x41 | 0x41 | -0.501355 | -0.0009% |
| 115200 | 27.127 | 27 | 33 | 0x00 | 0x21 | 0x21 | 1.120655 | 0.0010% |

18.2.5. Data settings

The **UARTLC** register defines the character settings like number of data bits, parity and number of stop bits

18.2.6. FIFO Settings

The FIFO can be configured with the **UARTFCTL** register. FIFO enable, depth and TX/RX FIFO reset can be configured. The FIFO status can be monitored in the **UARTLS** register. A write to **UARTRXTX** writes to the TX FIFO, while a read from **UARTRXTX** reads from RX FIFO.

18.2.7. Error Checking on Received Data

The character specific error does not show up in **UARTLS** until the character is at the top of the RX FIFO.

Each captured character is checked for following errors

- Break Error **UARTLS.RXBE** – there was a logic '0' detected on the RX input for more than one character transmission period (BAUD RATE *(1 startbit + **UARTLC.BPC** data bits + 1 parity bit + **UARTLC.STB** stopbits)
- Framing Error **UARTLS.RXFE** – there was a logic '0' detected where there should be a STOP bit
- Parity Error **UARTLS.PE** – received parity and calculated parity do not match.

19. SOC BUS BRIDGE

19.1. Register

19.1.1. Register Map

Table 19-1. SOC Bus Bridge Register Map

| ADDRESS | NAME | DESCRIPTION | RESET VALUE |
|-----------------------|-------------------|---------------------------------|-------------|
| SOC Bus Bridge | | | |
| 0x4020 0000 | SOCBCTL | SOC Bus Bridge control | 0x0000 0000 |
| 0x4020 0004 | SOCBCFG | SOC Bus Bridge configuration | 0x0000 0200 |
| 0x4020 0008 | SOCBCLKDIV | SOC Bus Bridge clock divider | 0x0000 0008 |
| 0x4000 000C | Reserved | Reserved | 0x0000 0000 |
| 0x4000 0010 | Reserved | Reserved | 0x0000 0000 |
| 0x4020 0014 | SOCBSTAT | SOC Bus Bridge status | 0x0000 0000 |
| 0x4020 0018 | Reserved | Reserved | 0x0000 0000 |
| 0x4020 001C | SOCBD | SOC Bus Bridge data | 0x0000 0000 |
| 0x4020 0020 | SOCBINT_EN | SOC Bus Bridge interrupt enable | 0x0000 0034 |

19.1.2. SOCBCTL

Register 19-1. SOCBCTL (SOC Bus Bridge Control, 0x4020 0000)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|--|
| 31:9 | Reserved | R | 0x0 | Reserved |
| 8 | Reserved | RW | 0x0 | Reserved, set to 0x0 |
| 7 | Reserved | RW | 0x0 | Reserved, set to 0x1 |
| 6 | Reserved | RW | 0x0 | Reserved, set to 0x1 |
| 5 | MTRARM | W | 0x0 | MTRANS re-arm Writing a 1b to this bit re-arms the SOCBCTL.MTRANS operation by de-asserting the CSx chip select and returning the master mode state machine to IDLE. |
| 3 | Reserved | RW | 0x0 | Reserved, set to 0x0 |
| 2 | Reserved | RW | 0x0 | Reserved, set to 0x0 |
| 1 | SIE | RW | 0x0 | SOC Bus Bridge interrupt enable. 1b = Enable the interrupt 0b = Disable the interrupt |
| 0 | SSEN | RW | 0x0 | SOC Bus Bridge enable: 1b = Enable this module. 0b = Disable this module. |

19.1.3. SOCBCFG

Register 19-2. SOCBCFG (SOC Bus Bridge Configuration, 0x4020 0004)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|-------------|
| 31:14 | Reserved | R | 0x0 | Reserved |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|---|
| 13 | Reserved | RW | 0x0 | Reserved, set to 0x0 |
| 12 | Reserved | RW | 0x0 | Reserved, be set to 0x0 |
| 11 | Reserved | RW | 0x0 | Reserved, be set to 0x1 |
| 10 | Reserved | RW | 0x0 | Reserved, be set to 0x1 |
| 9:6 | Reserved | RW | 0x0 | Reserved, be set to 0x0 |
| 5 | Reserved | RW | 0x0 | Reserved, be set to 0x0 |
| 4 | Reserved | RW | 0x0 | Reserved, be set to 0x0 |
| 3 | Reserved | RW | 0x0 | Reserved, mbe set to 0x0 |
| 2 | MRST | RW | 0x0 | Module reset. 1b: Force soft reset of module. The internal state machines are reset; Status register is cleared; However, the soft reset doesn't affect control register values. 0b: do not hold the module in reset. |
| 1:0 | Reserved | RW | 0x0 | Reserved, set to 0x0 |

19.1.4. SOCBCLKDIV

Register 19-3. SOCBCLK (SOC Bus Bridge Clock Divider, 0x4020 0008)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|---|
| 31:16 | Reserved | R | 0x0 | Reserved |
| 15:0 | CLKDIV | RW | 0x8 | Clock divisor for SCLK: SCLK = HCLK / [(CLKDIV+1)*2] the minimum divider is /2 |

19.1.5. SOCBSTAT

Register 19-4. SOCBSTAT (SOC Bus Bridge Status, 0x4020 0014)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|---|
| 31:15 | Reserved | R | 0x0 | Reserved |
| 14:12 | CURSTATE | RW | 0x0 | Raw status of the SOC bus bridge master state machine's "current_state" register. 111b: CSBEGIN 110b: MTRANS 101b: CKWAIT 100b: CSWAIT 011b: CSHOLD 010b: TRANSFER 001b: CSSETUP 000b: IDLE |
| 11 | Reserved | R | 0x0 | Reserved |
| 10 | RXFULL | R | 0x0 | Raw indicator that the Rx incoming holding register contains a valid data word. 1b: Rx incoming holding register contains a valid data word. 0b: Rx incoming holding register contains no valid data word. |
| 9 | TXFULL | R | 0x0 | Raw indicator that the Tx outgoing holding register is still in use, and not ready to accept another data word. 1b: Tx outgoing holding register is still in use not ready to accept another data word. 0b: Tx outgoing register is ready to accept another data word |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|--|
| 8 | WRUFL | RW | 0x0 | <p>Write Buffer Underflow: set on the start of a second outgoing transfer if data hasn't been written to the SOCBD after the previous transfer 1b: Write Underflow detected, clear by writing 1b to it 0b: No Write Underflow since this bit was cleared</p> <p>Note: This bit is cleared by writing a 1b to it. This bit is a sticky status bit, and will set upon meeting the condition regardless of the state of its corresponding interrupt enable SOCBINT_EN.WRUFL_EN.</p> |
| 7:6 | Reserved | RW | 0x0 | Reserved, must be set to 0x0 |
| 5 | CYC_DONE | RW | 0x0 | <p>Cycle Done: this bit will set when the current transfer of 8 bits is complete. It indicates that 8 bits were sent on the transmit port and 8 bits were sampled on the receive port. 1b: Cycle done detected, clear by writing 1b to it 0b: No Cycle Done detected since this bit was cleared</p> <p>Note: This bit is cleared by writing a 1b to it. This bit is a sticky status bit, and will set upon meeting the condition regardless of the state of its corresponding interrupt enable SOCBINT_EN.CYC_DONE_EN.</p> |
| 4:3 | Reserved | RW | 0x0 | Reserved, must be set to 0x0 |
| 2 | RDOFL | RW | 0x0 | <p>Read Buffer Overflow: set on the completion of a second incoming transfer if data hasn't been read from the SOCBD from the previous transfer 1b: Read Overflow detected, clear by writing 1b to it 0b: No Read Overflow since this bit was cleared</p> <p>Note: This bit is cleared by writing a 1b to it. This bit is a sticky status bit, and will set upon meeting the condition regardless of the state of its corresponding interrupt enable SOCBINT_EN.RDOFL_EN.</p> |
| 1 | Reserved | R | 0x0 | Reserved |
| 0 | SOCB_INT | R | 0x0 | <p>SOC bus bridge Interrupt Logical OR of each raw status bit WRUFL, RDOFL, and CYC_DONE, qualified with its corresponding SOCBINT_EN enable. 1b: interrupt 0b: no interrupt</p> <p>Note that if the corresponding SOCBINT_EN of those status bits is reset to '0', those status bits themselves will still assert upon meeting the condition, but will not contribute to the assertion of SOCB_INT. The status bits are true "raw" status bits, and the corresponding SOCBINT_EN simply allows them to cause an interrupt.</p> |

19.1.6. SOCBD

Register 19-5. SOCBD (SOC Bus Bridge Data, 0x4020 001C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|--|
| 31:8 | Reserved | RW | 0x0 | Reserved, must be set to 0x0 |
| 7:0 | DATA | RW | 0x0 | <p>SOC bus bridge data On READ: retrieve received data word from the incoming holding buffer. On WRITE: write a address or data word to the outgoing holding buffer.</p> |

19.1.7. SOCBINT_EN


Register 19-6. SOCBINT_EN (SOC Bus Bridge Interrupt Enable, 0x4020 0020)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|--|
| 31:9 | Reserved | RW | 0x0 | Reserved |
| 8 | WRUFL_EN | RW | 0x0 | Write buffer underflow WRUFL interrupt enable 1b: enable SOCBSTAT.WRUFL interrupt 0b: disable SOCBSTAT.WRUFL interrupt |
| 7:6 | Reserved | RW | 0x0 | Reserved, set to 0x0 |
| 5 | Reserved | RW | 0x1 | Reserved, set to 0x0 |
| 4:3 | Reserved | RW | 0x1 | Reserved, set to 0x0 |
| 2 | Reserved | RW | 0x1 | Read buffer overflow RDOFL interrupt enable 1b: enable SOCBSTAT.RDOFL interrupt 0b: disable SOCBSTAT.RDOFL interrupt |
| 1:0 | Reserved | RW | 0x0 | Reserved |

19.2. Details of Operation

19.2.1. Block Diagram

Figure 19-1. SOC Bridge



19.2.2. Configuration

Following blocks need to be configured for correct use of the SPI:

- Clock Control System (CCS)
- Nested Vectored Interrupt Controller (NVIC)
- IO Controller

19.2.3. SOC Bridge

The SOC bridge is used to set and read registers in the analog section of the device.

19.2.4. SOC Bridge Clock Rate Setting

The SOC bridge Module SOCCLK is derived from HCLK to drive the SPI logic, generate setup, hold and wait timings for CSx signals, and SOCCLK.

The SPICLK clock is derived from HCLK using a clock divider configurable with **SOCCLKDIV**. The lowest clock allowable divider in SPI slave mode is HCLK/8. In SPI Master mode the lowest allowable clock divider is HCLK/2.

To calculate SOCCLK use

$$SOCCLK = \frac{HCLK}{(SOCCLKDIV+1)*2} \quad (10)$$

Where:

SOCCLK: SOCCLK in Hz

HCLK: HLCK in Hz

SOCCLKDIV: **SOCCLKDIV** setting

19.2.5. Enable and Setup of SOC Bridge

19.2.6. SOC Interrupt

The SOC bridge engine interrupt is enabled with **SOCCTL.SIE**. Then any sub interrupts are enabled in **SINT_EN**.


19.2.7. SOC Bridge Protocol

The SOC bridge protocol is a 2 byte protocol, the first byte is the address packet including a 7-bit address [7:1] and a write bit [0], the second packet is an 8bit data packet.

19.2.8. Reading from SOC Bridge

To read to the SOC bridge, start with writing the address packet to **SOCBD** first. Wait for **SOCBSTAT.CYC_DONE** = 1b. Clear **SOCBSTAT.CYC_DONE** by set to 1b. Then write a second dummy address packet to **SOCBD** to clock out the data packet. Wait for **SOCBSTAT.CYC_DONE** = 1b. Clear **SOCBSTAT.CYC_DONE** by set to 1b. Set **SOCBCTL.MTRARM** to 1b to deassert SOCBCS0. Then read from **SOCBD** to get the data packet content


Figure 19-2. Single Read from SOC Bridge



19.2.9. Writing to SOC Bridge

To write to the SOC bridge, start with writing the address packet to **SOCBD** first. Wait for **SOCBSTAT.CYC_DONE** = 1b. Clear **SOCBSTAT.CYC_DONE** by set to 1b. Then write the data packet to **SOCBD**. Wait for **SOCBSTAT.CYC_DONE** = 1b. Clear **SOCBSTAT.CYC_DONE** by set to 1b. Set **SOCBCTL.MTRARM** to 1b to deassert SOCBCS0. Optional you read from **SOCBD** to get the data packet content with old data content of the register address.

Figure 19-3. Single Write to SOC Bridge



20. SPI

20.1. Register

20.1.1. Register Map

Table 20-1. SPI Register Map

| ADDRESS | NAME | DESCRIPTION | RESET VALUE |
|-------------|------------------|--------------------------|-------------|
| SPI | | | |
| 0x4021 0000 | SPICTL | SPI control | 0x0000 0000 |
| 0x4021 0004 | SPICFG | SPI configuration | 0x0000 0200 |
| 0x4021 0008 | SPICLKDIV | SPI clock divider | 0x0000 0008 |
| 0x4021 000C | Reserved | Reserved | 0x0000 0000 |
| 0x4021 0010 | Reserved | Reserved | 0x0000 0000 |
| 0x4021 0014 | SPISTAT | SPI status | 0x0000 0000 |
| 0x4021 0018 | SPICSSTR | SPI chip select steering | 0x0000 0000 |
| 0x4021 001C | SPID | SPI data | 0x0000 0000 |
| 0x4021 0020 | SPIINT_EN | SPI interrupt enable | 0x0000 0000 |

20.1.2. SPICTL

Register 20-1. SPICTL (SPI Control, 0x4021 0000)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-----------------|--------|-------|--|
| 31:9 | Reserved | R | 0x0 | Reserved |
| 8 | RTRANS | RW | 0x0 | Auto-retransmit on UCLK error. 1b: On a UCLK error, the transmit holding register does NOT get reset, so the word that was transmitting when the UCLK error occurred remains queued. 0b: On a UCLK error, the transmit holding register is reset, and the word that was transmitting when the UCLK error occurred is lost. |
| 7 | MMST_N | RW | 0x0 | Multi-master mode (MASTER ONLY) 1b: Single-Master mode, always drive a value onto CSx, SPICLK and MOSI. 0b: Multi-master mode, always tri-state the CSx, SPICLK and MOSI lines when a transfer is complete. |
| 6 | MTRANS | RW | 0x0 | Multiple Transfer Mode (MASTER ONLY) 1b: Generate multiple transfers of [SPICFG.WL] bits within a single CSx assertion. 0b: Generate single transfers (assert CSx, transfer data word of [SPICFG.WL] bits, de-assert CSx). |
| 5 | MTRARM | W | 0x0 | MTRANS re-arm (MASTER ONLY): Writing a 1b to this bit re-arms the SPICTL.MTRANS operation by de-asserting the CSx chip select and returning the master mode state machine to IDLE. |
| 4 | Reserved | RW | 0x0 | Reserved, must be set to 0x0 |
| 3 | SE | RW | 0x0 | Slave Enable 1b: SPI is a SLAVE. 0b: SPI is a MASTER. |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-------------|--------|-------|---|
| 2 | LPBK | RW | 0x0 | Internal loop back Mode 1b: Tie the serial out source to the serial in line (internal signaling, does not traverse the chip IO bi-di buffers). 0b = Normal operation. |
| 1 | SIE | RW | 0x0 | SPI Interrupt enable. 1b = Enable the interrupt 0b = Disable the interrupt |
| 0 | SSEN | RW | 0x0 | SPI enable: 1b = Enable this module. 0b = Disable this module. |

20.1.3. SPICFG

Register 20-2. SPICFG (SPI Configuration, 0x4021 0004)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|---|
| 31:14 | Reserved | R | 0x0 | Reserved |
| 13 | Reserved | RW | 0x0 | Reserved, must be set to 0x0 |
| 12 | Reserved | RW | 0x0 | Reserved, must be set to 0x0 |
| 11 | MTURBO | RW | 0x0 | Master “turbo” operation mode: 1b: Enable master turbo mode, using HCLK-based bit count, allowing operation down to max 2:1 HCLK:SPICLK ratio 0b: Disable master turbo mode, legacy operation down to max 8:1 HCLK:SPICLK ratio. |
| 10 | TXDBUF | RW | 0x0 | Transmit Double-Buffer mode: 1b: enable double-buffer “ping-pong” on shift register transmit output path (keep up with back-to-back words at faster HCLK:SPICLK ratios) 0b: disable double-buffer, legacy operation with a single shift register buffer and single queuing buffer |
| 9 | TXDATPH | RW | 0x0 | Early Transmit Data Phase. 1b: Enable: MISO (slave mode) or MOSI(master mode) transitions occur ½ an SPICLK period sooner than the normal protocol (i.e. transition on capture edge instead of launch edge) 0b: Disable: normal transmit data phase, transitions are on the launch edge of SPICLK |
| 8 | Reserved | RW | 0x0 | Reserved, must be set to 0x0 |
| 7 | RCVCPH | RW | 0x0 | SLAVE MODE Clock Phase 1b: Second clock transition of a new transfer is used to sample data 0b: First clock transition of a new transfer is used to sample data |
| 6 | RCVCP | RW | 0x0 | SLAVE MODE Clock Polarity 1b: SPICLK is HI in its inactive state 0b: SPICLK is LO in its inactive state |
| 5 | CPH | RW | 0x0 | MASTER MODE Clock Phase 1b: Second clock transition of a new transfer is used to sample data 0b: First clock transition of a new transfer is used to sample data |
| 4 | CP | RW | 0x0 | MASTER MODE Clock Polarity 1b: SPICLK is HI in its inactive state 0b: SPICLK is LO in its inactive state |
| 3 | LB1ST | RW | 0x0 | Least Bit First 1b: LSB is the first serial bit of a transfer 0b: MSB is the first serial bit of a transfer |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-------------|--------|-------|---|
| 2 | MRST | RW | 0x0 | Module reset. 1b: Force soft reset of module. The internal state machines are reset; Status register is cleared; However, the soft reset doesn't affect control register values. 0b: do not hold the module in reset. |
| 1:0 | WL | RW | 0x0 | Word Length select 11b: Word Length = 32-bits 10b: Word Length = 24-bits 01b: Word Length = 16-bits 00b: Word Length = 8-bits |

20.1.4. SPICLKDIV

Register 20-3. SPICLKDIV (SPI Clock Divider, 0x4021 0008)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|--|
| 31:16 | Reserved | R | 0x0 | Reserved |
| 15:0 | CLKDIV | RW | 0x8 | Clock divisor for SCLK: SCLK = HCLK / [(CLKDIV+1)*2] In Master/Slave mode with SPICFG.MTURBO = 0b, minimum divider is /8. In Master mode with SPICFG.MTURBO =1b, minimum divider is /2 |

20.1.5. SPISTAT

Register 20-4. SPISTAT (SPI Status, 0x4021 0014)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|---|
| 31:15 | Reserved | R | 0x0 | Reserved |
| 14:12 | CURSTATE | RW | 0x0 | Raw status of the SOC bus bridge master state machine's "current_state" register. 111b: CSBEGIN 110b: MTRANS 101b: CKWAIT 100b: CSWAIT 011b: CSHOLD 010b: TRANSFER 001b: CSSETUP 000b: IDLE |
| 11 | Reserved | R | 0x0 | Reserved |
| 10 | RXFULL | R | 0x0 | Raw indicator that the Rx incoming holding register contains a valid data word. 1b: Rx incoming holding register contains a valid data word. 0b: Rx incoming holding register contains no valid data word. |
| 9 | TXFULL | R | 0x0 | Raw indicator that the Tx outgoing holding register is still in use, and not ready to accept another data word. 1b: Tx outgoing holding register is still in use not ready to accept another data word. 0b: Tx outgoing register is ready to accept another data word |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|---|
| 8 | WRUFL | RW | 0x0 | <p>Write Buffer Underflow Set on the start of a second outgoing transfer if data hasn't been written to the SD register after the previous transfer 1b: Write Underflow detected, clear by writing 1b to it 0b: No Write Underflow since this bit was cleared</p> <p>Note: This bit is cleared by writing a 1b to it. This bit is a sticky status bit, and will set upon meeting the condition regardless of the state of its corresponding interrupt enable SPIINT_EN.WRUFL_EN.</p> |
| 7 | Reserved | RW | 0x0 | Reserved, must be set to 0x0 |
| 6 | TE | RW | 0x0 | <p>Chip Select Trailing Edge Detect 1b: a chip select de-assertion was detected, clear by writing 1b to it 0b: no chip select de-assertion detected since this bit was cleared</p> <p>NOTE: This bit is cleared by writing a 1b to it. This bit is a sticky status bit, and will set upon meeting the condition regardless of the state of its corresponding interrupt enable SPIINT_EN.TE_EN.</p> |
| 5 | CYC_DONE | RW | 0x0 | <p>Cycle Done: this bit will set when the current transfer of 8 bits is complete. It indicates that 8 bits were sent on the transmit port and 8 bits were sampled on the receive port. 1b: Cycle done detected, clear by writing 1b to it 0b: No Cycle Done detected since this bit was cleared</p> <p>NOTE: This bit is cleared by writing a 1b to it. This bit is a sticky status bit, and will set upon meeting the condition regardless of the state of its corresponding interrupt enable SPIINT_EN.CYC_DONE_EN.</p> |
| 4 | UCLK | RW | 0x0 | <p>Underclock Condition Set if the current transfer received less than word-length "WL" clocks on the SPICLK line prior to CSx de-assertion. 1b: Underclock condition detected, clear by writing 1b to it 0b: No underclock condition detected since this bit was cleared.</p> <p>NOTE: This bit is cleared by writing a 1b to it. This bit is a sticky status bit, and will set upon meeting the condition regardless of the state of its corresponding interrupt enable SPIINT_EN.UCLK_EN.</p> |
| 3 | LE | RW | 0x0 | <p>Chip Select Leading Edge Detect: 1b: a chip select assertion was detected, clear by writing 1 to it 0b: no chip select assertion detected since this bit was cleared</p> <p>NOTE: This bit is cleared by writing a 1b to it. This bit is a sticky status bit, and will set upon meeting the condition regardless of the state of its corresponding interrupt enable SPIINT_EN.LE_EN.</p> |
| 2 | RDOFL | RW | 0x0 | <p>Read Buffer Overflow: set on the completion of a second incoming transfer if data hasn't been read from the SD register from the previous transfer 1b: Read Overflow detected, clear by writing 1b to it 0b: No Read Overflow since this bit was cleared</p> <p>NOTE: This bit is cleared by writing a '1' to it. This bit is a sticky status bit, and will set upon meeting the condition regardless of the state of its corresponding interrupt enable SPIINT_EN.RDOFL_EN.</p> |
| 1 | Reserved | R | 0x0 | Reserved |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|----------------|--------|-------|---|
| 0 | SPI_INT | R | 0x0 | <p>SPI Interrupt Logical OR of each raw status bit WRUFL, RDOFL, and CYC_DONE, qualified with its corresponding INT_EN enable. 1b: interrupt 0b: no interrupt</p> <p>NOTE: that if the corresponding INT_EN of those status bits is reset to '0', those status bits themselves will still assert upon meeting the condition, but will not contribute to the assertion of SPI_INT. The status bits are true "raw" status bits, and the corresponding SPIINT_EN simply allows them to cause an interrupt.</p> |

20.1.6. SPICSSTR

Register 20-5. SPICSSTR (SPI Chip Select Steering, 0x4021 0018)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-------|-----------------|--------|-------|--|
| 31:24 | Reserved | RW | 0x0 | Reserved |
| 23:20 | CKWAIT | RW | 0x0 | SPI Clock Wait (MASTER ONLY): only applies if SPICL.MTRANS=1b(multiple transfers with one chip select assertion). This value determines the minimum number of SPICLK periods to wait between back-to-back transfers. During this wait time, SPICLK does not toggle but CSx remains active. |
| 19:16 | CSWAIT | RW | 0x0 | Chip Select Wait: This value determines the minimum number of SPICLK periods to wait between the de-assertion of CSx and the re-assertion of CSx |
| 15:12 | CSHOLD | RW | 0x0 | Chip Select Hold : minimum number of SPICLK periods to wait from the last SPICLK transition to de-assertion of CSx |
| 11:8 | CSSETUP | RW | 0x0 | Chip Select Setup: minimum number of SPICLK periods to wait from the assertion of Csx to the first SPICLK transition. |
| 7:3 | Reserved | R | 0x0 | Reserved |
| 2 | CSL | RW | 0x0 | Chip Select active level select (MASTER or SLAVE mode): 1b: active HI outgoing (master) or incoming (slave) chip select 0b: active LO outgoing (master) or incoming (slave) chip select |
| 1:0 | CSNUM | RW | 0x0 | Chip Select Number: Outgoing (MASTER, GPIO modes) - select which one of the possible four chip selects are asserted (the other three are driven de-asserted). Incoming (SLAVE, GPIO modes) – select which one of the possible four chip selects are actively used. 11b: reserved 10b: SPICS2 01b: SPICS1 00b: SPICS0 |

20.1.7. SPID

Register 20-6. SPID (SPI Data, 0x4021 001C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|-------------|--------|-------|--|
| 31:0 | DATA | RW | 0x0 | SOC bus bridge data On READ: retrieve received data word from the incoming holding buffer. On WRITE: write a data word to the outgoing holding buffer. |

20.1.8. SPIINT_EN


Register 20-7. SPIINT_EN (SPI Interrupt Enable, 0x4021 0020)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|------|--------------------|--------|-------|--|
| 31:9 | Reserved | RW | 0x0 | Reserved |
| 8 | WRUFL_EN | RW | 0x0 | Write buffer underflow WRUFL interrupt enable 1b: enable SPISTAT.WRUFL interrupt 0b: disable SPISTAT.WRUFL interrupt |
| 7 | BP_DONE | RW | 0x0 | Byte-packing BP_DONE interrupt enable 1b: enable SPISTAT.BP_DONE interrupt 0b: disable SPISTAT.BP_DONE interrupt |
| 6 | TE_EN | RW | 0x0 | Trailing Edge detect TE interrupt enable 1b: enable SPISTAT.TE interrupt 0b: disable SPISTAT.TE interrupt |
| 5 | CYC_DONE_EN | RW | 0x0 | Cycle done CYC_DONE interrupt enable 1b: enable SPISTAT.CYC_DONE interrupt 0b: disable SPISTAT.CYC_DONE interrupt |
| 4 | UCLK_EN | RW | 0x1 | Underclock condition detect UCLK interrupt enable 1b: enable SPISTAT.UCLK interrupt 0b: disable SPISTAT.UCLK interrupt |
| 3 | LE_EN | RW | 0x0 | Leading Edge detect LE interrupt enable 1b: enable SPISTAT.LE interrupt 0b: disable SPISTAT.LE interrupt |
| 2 | RDOFL_EN | RW | 0x1 | Read buffer overflow RDOFL interrupt enable 1b: enable SPISTAT.RDOFL interrupt 0b: disable SPISTAT.RDOFL interrupt |
| 1:0 | Reserved | RW | 0x0 | Reserved |

20.2. Details of Operation

20.2.1. Block Diagram

Figure 20-1. SPI



20.2.2. Configuration

Following blocks need to be configured for correct use of the SPI:

- Clock Control System (CCS)
- Nested Vectored Interrupt Controller (NVIC)
- IO Controller

20.2.3. SPI

The SPI engine has selectable data byte ordering LSB or MSB first, 4 different data / clock modes, can send / receive packets 8, 16, 32, 64 boundaries, selectable CS polarity, soft reset, and auto-retransmit.

In master mode it supports up to 3 different slaves using chip select. The master mode also allows sending multiple packets per CS.

20.2.4. SPI Clock Rate Setting

The SPI Module SPICLK is derived from HCLK to drive the SPI logic, generate setup, hold and wait timings for CSx signals, and SPICLK.

The SPICLK clock is derived from HCLK using a clock divider configurable with **SPICLKDIV**. The lowest clock allowable divider in SPI slave mode is HCLK/8. In SPI Master mode the lowest allowable clock divider is HCLK/2 if **SPICFG.MTURBO** is 1b, HCLK/8 if **SPICFG.MTURBO** is 0b. **SPICFG.MTURBO** works only in Master mode.

To calculate SCLK use

$$SCLK = \frac{HCLK}{(SPICLKDIV + 1) * 2} \quad (11)$$

Where:

SCLK: SCLK in Hz

HCLK: HLCK in Hz

SPICLKDIV: **SPICLKDIV** setting

20.2.5. Master Slave Mode

The master mode is selected with **SPICTL.SE= 0b**. In master mode a write to **SPID** will initiate SPI data transfer.

When **SPICFG.TXDBUF** is set to 1b, the **SPID** is double buffering is enabled, allowing queuing of the next data word while the current one is transferred.


20.2.6. Clock Phase, Polarity

The clock and phase can be programmed independently for master and slave.

The master mode clock polarity is configured with **SPICFG.CP** and the phase is configured with **SPCFG.CPH**.

The slave mode clock polarity is configured with **SPICFG.RCVCP** and the phase is configured with **SPICFG.RCVCPH**.

Figure 20-2. SPI clock polarity and phase



20.2.7. SPI Early Data Transmit

For cases when the SPI is running at high speed the transmitted data can be transmitted 1/2 a SPICLK early to compensate for delays on the receiver side. When **SPICFG.TXDATPH** is 1b, SPI MOSI is transmitted 1/2 SPICLK early in master mode. In slave mode SPI MISO is transmitted 1/2 SPICLK early.

Figure 20-3. SPIMOSI early transmit in master mode





Figure 20-4. SPIMISO early transmit in slave mode



20.2.8. Data Format

The **SPICFG.WL** sets the word length from 8bit to 32bit in 8bit steps.

The **SPICFG.LB1ST** configures the data format to transmit, LSB or MSB first.

20.2.9. Chip Select Settings


The SPI engine supports up to 3 chip select signals SPICS0, SPICS1 and SPICS2, selectable with **SPICSSTR.CSNUM**.

The CS polarity can be set with **SPICSSTR.CSL**, 0b for active low, 1b for active high.

In SPI engine can automatically assert and deassert SPICSx with each data transaction with **SPICTL.MTRANS** = 0b. To allow multiple data words within a SPICSx assertion set **SPICTL.MTRANS** to 1b. The first data word will assert SPICSx. SPICSx will remain low until it is deasserted with writing **SPICTL.MTARM** to 1b.

Timings for CS behavior can be programmed with granularity of SPICLK. The period between assertion of SPICSx and SPICLK transition can be set with **SPICSSTR.CSSETUP**. The period between last SPICLK transition and deassertion of SPICSx can be set with **SPICSSTR.CSHOLD**. The period between deassertion and assertion of SPICSx can be set with **SPICSSTR.CSWAIT**. The period between SPICLK transitions between multi word packages can be set with **SPICSSTR.CKWAIT**.

Figure 20-5. SPICSx



20.2.10. Auto Retransmit Data Word

Upon detection of an undercount **SPISTAT.UCLK** error, the default behavior of the SPI module is to reset the SERDES bit counters and the transmit side holding buffers, assuming that software must re-load the word that did not complete transmission because of the UCLK error.

Note that the receive side holding buffers are *not* reset, and contain the data word received from the last *good* transfer.

An optional mode is provided by setting the RTRANS bit in the **SPICTL.RTRANS**. When set, the reset of the transmit side holding buffers because of UCLK error is disabled, and the word that did not complete transmission remains queued for transmit.

20.2.11. Loop Back Mode

The SPI engine has a loop back mode for test purposes, enabled with **SPICTL.LPBK**. The loop back mode is only available in master mode. In loop back mode, SPIMOSI and SPIMISO are connected together internally

and SPICLK, SPIMOSI, SPCSw can be still observed on pins.

20.2.12. SPI Interrupt

The SPI engine interrupt is enabled with **SPICTL.SIE**. Then any sub interrupts are enabled in **SPIINT_EN**.

20.2.13. SPI Enable

The SPI engine is enabled with **SPICTL.SSEN**. To soft reset the state machine and clear all status bits use **SPICFG.MRST**.

21. MULTI-MODE POWER MANAGER

21.1. Register

21.1.1. Register Map

Table 21-1. Multi-Mode Power Manager Register Map

| SOC ADDRESS | NAME | DESCRIPTION | RESET VALUE |
|---------------------------------|-----------------------|--|-------------|
| Multi-Mode Power Manager | | | |
| 0x00 | SOC.SYSSTAT | System Status | 0x00 |
| 0x01 – 0x0F | Reserved | Reserved | N/A |
| 0x10 | SOC.PWRCTL | Power Manager Control | 0x00 |
| 0x11 | SOC.PWRSTAT | Power Manager Status | 0x00 |
| 0x12 | SOC.PWRSTATCFG | Power Manager Status Configuration | 0x00 |
| 0x13 | Reserved | Reserved | 0xFF |
| 0x14 | SOC.SCFG | Power Manager DC-DC Switcher configuration | 0x00 |
| 0x15 | SOC.PWRCFG | Power Manager Configuration | N/A |
| 0x16 – 0x1F | Reserved | Reserved | N/A |

21.1.2. SOC.SYSSTAT

Register 21-1. SOC.SYSSTAT (Analog System Status, SOC 0x00)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|---|
| 7 | PBINT | R/W | 0x0 | Push button status. If PWRSTATCFG.PBEN = 1b and SYSSTAT.PBINTEN = 1b, show push button status of AIO6. 1b: AIO6 toggled, write 1b to clear. 0b: no AIO6 push button event detected or disabled or masked |
| 6 | OTWINT | R/W | 0x0 | Over temperature warning to indicate the temperature is over 140°C. When SYSSTAT.OTWINTEN = 1b, this interrupt is enabled 1b: Over temperature > 140°C detected. Write 1b to clear 0b: No over temperature detected. |
| 5:4 | VTHREF | R/W | 0x0 | Programmable threshold voltage. Used for AMP6 through AMP9 in comparator mode. 11b: 1.25V 10b: 0.5V 01b: 0.2V 00b: 0.1V |
| 3 | Reserved | R/W | 0x0 | Reserved, write to 0b |
| 2 | PBINTEN | R/W | 0x0 | Push button interrupt enable. 1b: enable SYSSTAT.PBINT 0b: mask SYSSTAT.PBINT |
| 1 | OTSD | R/W | 0x0 | Over temperature shutdown. 1b: if over temperature shutdown reached, do not shutdown device 0b: if over temperature shutdown reached, shutdown device |
| 0 | OTWINTEN | R/W | 0x0 | Over temperature Warning Interrupt enable 1b: SYSSTAT.OTWINT enabled 0b: SYSSTAT.OTWINT disabled |

21.1.3. SOC.PWRCTL

Register 21-2. SOC.PWRCTL (Power Control, SOC 0x10)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|--|
| 7 | HIB | R/W | 0x0 | <p>Hibernate Mode. 1b: Hibernate mode. Bit is cleared after wake from Wake Up timer or push button event or power up event 0b: Normal mode</p> <p>NOTE: Setting SOC.PWRCTL.HIB =1b without SOC.PWRSTATCFG.PBEN or SOC.PWRCTL.WUTIMER enabled will not allow device exit hibernate mode. Only way to exit is power cycle device.</p> |
| 6 | MCUALIVE | R/W | 0x0 | <p>Indicator for MCU that power manager is alive and released all pull down resistors on internal databus. 1b: Power manager alive 0b: Power manager in hibernate mode</p> |
| 5:3 | PWRMUX | R/W | 0x0 | <p>Power rail monitoring MUX for AB11 111b: VCOMP 110b: VHM * 1/30 101b: VP * 1/10 100b: REGI * 1/10 011b: VSYS * 4/10 010b: VCCIO * 4/10 001b: VCC33 * 4/10 000b: VCC18</p> |
| 2:0 | WUTIMER | R/W | 0x0 | <p>Wake up from hibernate mode timer setting 111b: 8s 110b: 4s 101b: 2s 100b: 1s 011b: 500ms 010b: 250ms 001b: 125ms 000b: disabled</p> |

21.1.4. SOC.PWRSTAT

Register 21-3. SOC.PWRSTAT (Power Manager Status, Persistent In Hibernate mode, SOC 0x11)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|---|
| 7 | HWRESET | R/W | 0x0 | <p>HW reset status 1b: HW reset occurred, clear by writing to 1b 0b: Normal</p> |
| 6 | WDTRESET | R/W | 0x0 | <p>Watchdog timer status 1b: Watchdog timer reset occurred, clear by writing to 1b 0b: Normal</p> |
| 5 | DCDC | R/W | 0x0 | <p>DC-DC fault 1b: DC-DC fault, clear by writing to 1b 0b: no fault</p> |
| 4 | TMP | R/W | 0x0 | <p>Over Temperature fault 1b: Over temperature fault, clear by writing to 1b 0b: no fault</p> |
| 3 | VSYS | R/W | 0x0 | <p>VSYS under voltage fault 1b: VSYS under voltage fault, clear by writing to 1b 0b: no fault</p> <p>Note: VSYS will be 1b at initial power up. Check with SOC.PWRSTATCFG.SU to determine fail or power up condition.</p> |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|--------------|--------|-------|---|
| 2 | VCCIO | R/W | 0x0 | VCCIO under voltage fault 1b: VCCIO under voltage fault, clear by writing to 1b 0b: no fault <u>Note:</u> VCCIO will be 1b at initial power up. Check with SOC.PWRSTATCFG.SU to determine fail or power up condition. |
| 1 | VCC33 | R/W | 0x0 | VCC33 under voltage fault 1b: VCC33 under voltage fault, clear by writing to 1b 0b: no fault <u>Note:</u> VCC33 will be 1b at initial power up. Check with SOC.PWRSTATCFG.SU to determine fail or power up condition. |
| 0 | VCC18 | R/W | 0x0 | VCC18 under voltage fault 1b: VCC18 under voltage fault, clear by writing to 1b 0b: no fault <u>Note:</u> VCC18 will be 1b at initial power up. Check with SOC.PWRSTATCFG.SU to determine fail or power up condition. |

21.1.5. SOC.PWRSTATCFG

Register 21-4. SOC.PWRSTATCFG (Power Status Configuration, SOC 0x12)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|------------------|--------|-------|---|
| 7 | PWRUNLOCK | R/W | 0x0 | Unlock for SOC.SCFG and SOC.PWRCFG 1b: Unlock, enable write access to SOC.SCFG and SOC.PWRCFG 0b: no write access to SOC.SCFG and SOC.PWRCFG |
| 6 | SU | R/W | 0x0 | Start up status, bit is cleared at power up, write to 1b to indicate start up from power up is recognized. As long as VHM has power this bit condition is retained. 1b: write to 1b to store power up condition 0b: power up detected |
| 5 | VPUVINT | R/W | 0x0 | vp UV Interrupt 1b: Interrupt, clear by writing to 1b 0b: no interrupt |
| 4 | Reserved | R/W | 0x0 | Reserved, write to 0b |
| 3 | VPUVINTEN | R/W | 0x0 | VP under voltage interrupt enable 1b: enabled 0b: disabled |
| 2 | WDTCFG | R/W | 0x0 | Watchdog timer setting 1b: 8s 0b: 4s |
| 1 | WDTEN | R/W | 0x0 | Watchdog timer enable 1b: enabled 0b: disabled |
| 0 | PBEN | R/W | 0x0 | AIO6 Push button enable 1b: Push button enabled 0b: Push button disabled |

21.1.6. SOC.SCFG

Register 21-5. SOC.SCFG (Power Switcher Configuration, SOC 0x14)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|--|
| 7 | SRESET | R/W | 0x0 | Soft reset 1b: Write to 1b to assert nRST to reset CPU 0b: normal |
| 6 | Reserved | R/W | 0x0 | Reserved, write to 0b |
| 5 | VHMCLAMP | R/W | 0x0 | VHM voltage clamp 1b: Clamp disabled 0b: Clamp VHM to 20V |
| 4 | FMODE | R/W | 0x0 | DC-DC Switching frequency range for SOC.SCFG.FSWM 1b: 181kHz to 500kHz 0b: 45kHz to 125kHz |
| 3:1 | FSWM | R/W | 0x0 | DC-DC frequency configuration 111b: FMODE = 0b: 125kHz, FMODE = 1b: 500kHz 110b: FMODE = 0b: 100kHz, FMODE = 1b: 400kHz 101b: FMODE = 0b: 82.5kHz, FMODE = 1b: 330kHz 100b: FMODE = 0b: 72.25kHz, FMODE = 1b: 289kHz 011b: FMODE = 0b: 62.5kHz, FMODE = 1b: 250kHz 010b: FMODE = 0b: 55kHz, FMODE = 1b: 220kHz 001b: FMODE = 0b: 50kHz, FMODE = 1b: 200kHz 000b: FMODE = 0b: 45kHz, FMODE = 1b: 181kHz |
| 0 | MAXDUTY | R/W | 0x0 | Maximum DC-DC duty 1b: Min off time 820ns 0b: FMODE = 0b: Min. off time 25% duty, FMODE = 1b: Min off time 440ns |

21.1.7. SOC.PWRCFG

Register 21-6. SOC.PWRCFG (Power Status Configuration, SOC 0x15)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|---------------------|--|
| 7:6 | VP | R/W | Varies ¹ | VP voltage setting 11b: 15V 10b: 12V 01b: 9V 00b: 5V |
| 5 | SMPSOFF | R/W | 0x0 | DC-DC disable 1b: disabled 0b: enabled |
| 4 | VSYSLIM | R/W | 0x0 | VSYS current limit 1b: 450mA 0b: 300mA |
| 3 | TRESET | R/W | 0x0 | nRESET low time 1b: 32ms 0b: 1ms |
| 2 | TON | R/W | 0x0 | Pre-startup DC-DC on time 1b: 1.2μs 0b: 0.8μs |
| 1 | VCC18 | R/W | 0x0 | VCC18 Voltage 1b: 1.8V 0b: 1.9V |
| 0 | Reserved | R/W | 0x0 | Reserved, write to 0b |

¹ See the data sheet for the reset value for this parameter

22. CONFIGURABLE ANALOG FRONT END

22.1. Register

22.1.1. Register Map

Table 22-1. Configurable Analog Front End Register Map

| SOC ADDRESS | NAME | DESCRIPTION | RESET VALUE |
|--------------------------------------|-----------------------|---|-------------|
| Configurable Analog Front End | | | |
| 0x20 | SOC.AIO0CFG | AIO0 Configuration | 0x00 |
| 0x21 | SOC.AIO1CFG | AIO1 Configuration | 0x00 |
| 0x22 | SOC.AIO2CFG | AIO2 Configuration | 0x00 |
| 0x23 | SOC.AIO3CFG | AIO3 Configuration | 0x00 |
| 0x24 | SOC.AIO4CFG | AIO4 Configuration | 0x00 |
| 0x25 | SOC.AIO5CFG | AIO5 Configuration | 0x00 |
| 0x26 | SOC.AIO6CFG | AIO6 Configuration | 0x00 |
| 0x27 | SOC.AIO7CFG | AIO7 Configuration | 0x00 |
| 0x28 | SOC.AIO8CFG | AIO8 Configuration | 0x00 |
| 0x29 | SOC.AIO9CFG | AIO9 Configuration | 0x00 |
| 0x2A | SOC.SMCFG | Signal manager Configuration | 0x00 |
| 0x2B | SOC.HPDAC | High Protection Threshold | 0x00 |
| 0x2C | SOC.LPDAC0 | Low Protection Threshold | 0x00 |
| 0x2D | SOC.LPDAC1 | Low Protection Threshold | 0x00 |
| 0x2E | SOC.ADCSCANCFG | ADC Scan Control | 0x00 |
| 0x2F | SOC.ADMUX | ADC MUX Select | 0x00 |
| 0x30 | SOC.PROTINTEN | Protection Interrupt Enable | 0x00 |
| 0x31 | SOC.PROTINT | Protection Status | 0x00 |
| 0x32 | SOC.AIOOUT0 | AIO0, AIO1, AIO2, AIO3, AIO4, AIO5 digital output control | 0x00 |
| 0x33 | SOC.AIOOUT1 | AIO6, AIO7, AIO8, AIO9 digital output control | 0x00 |
| 0x34 | SOC.AIOIN0 | AIO0, AIO1, AIO2, AIO3, AIO4, AIO5 digital input status | 0x00 |
| 0x35 | SOC.AIOIN1 | AIO6, AIO7, AIO8, AIO9 digital input status | 0x00 |
| 0x36 | SOC.AIOINTEN | AIO6, AIO7, AIO8, AIO9 Interrupt enable | 0x00 |
| 0x37 | SOC.AIOINT | AIO6, AIO7, AIO8, AIO9 Interrupt flag | 0x00 |
| 0x38 | SOC.SMCTL | Signal Manager Control | 0x00 |
| 0x39 – 0x5F | Reserved | Reserved | N/A |

22.1.2. SOC.AIO0CFG

Register 22-1. SOC.AIO0CFG (AIO0 Configuration, SOC 0x20)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|--|
| 7:6 | MODE10 | R/W | 0x0 | AIO1, AIO0 Mode 11b: reserved 10b: reserved 01b: Differential amplifier mode mode, AIO1 and AIO0 build a differential amplifier input 00b: IO Mode, AIO1 and AIO0 work in I/O mode |
| 5:4 | OPT0 | R/W | 0x0 | If AIO0CFG.MODE10 = 00b, AIO0 IO Setting 11b: Reserved 10b: Open-drain output 01b: Reserved 00b: Input, input state available at SOC.AIOIN0.AIO0DIN |
| 3 | POL0 | R/W | 0x0 | If AIO0CFG.MODE10 = 00b and CFGAIO0.OPT0 = 00b, AIO0 Input polarity setting. If AIO0CFG.MODE10 = 00b and CFGAIO0.OPT0 = 10b, AIO0 Output polarity setting. 1b: active-low 0b: active-high |
| 2:0 | MUX0 | R/W | 0x0 | If AIO0CFG.MODE10 = 00b and CFGAIO0.OPT0 = 00b, Reserved If AIO0CFG.MODE10 = 00b and CFGAIO0.OPT0 = 10b, Output polarity, set AIO0 state according to MUX0 11b: DB7 110b: DB6 101b: DB5 100b: DB4 011b: DB3 010b: DB2 001b: DB1 000b: DOUT0 |
| 5:3 | GAIN10 | R/W | 0x0 | If AIO0CFG.MODE10 = 01b, Differential amplifier gain setting 11b: 48x 110b: 32x 101b: 16x 100b: 8x 011b: 4x 010b: 2x 001b: 1x 000b: 1x |
| 2 | Reserved | R/W | 0x0 | If AIO0CFG.MODE10 = 01b, Reserved, Write to 0b |
| 1:0 | LP10EN | R/W | 0x0 | If AIO0CFG.MODE10 = 01b, LP10 comparator setting 11b: LP10 comparator enabled with 4µs blanking time 10b: LP10 comparator enabled with 2µs blanking time 01b: LP10 comparator enabled with 1µs blanking time 00b: LP10 comparator disabled |

22.1.3. SOC.AIO1CFG

Register 22-2. SOC.AIO1CFG (AIO1 Configuration, SOC 0x21)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|---|
| 7:6 | Reserved | R/W | 0x0 | If AIO0CFG.MODE10 = 00b, Reserved, write to 00b |
| 5:4 | OPT1 | R/W | 0x0 | If AIO0CFG.MODE10 = 00b, AIO1 IO Setting 11b: Reserved 10b: Open-drain output 01b: Reserved 00b: Input, input state available at SOC.AIOIN0.AIO1DIN |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|------------------|--------|-------|--|
| 3 | POL1 | R/W | 0x0 | If AIO0CFG.MODE10 = 00b and AIO0CFG.OPT0 = 00b, AIO1 Input polarity setting. If AIO0CFG.MODE10 = 00b and AIO0CFG.OPT0 = 10b, AIO1 Output polarity setting. 1b: active-low 0b: active-high |
| 2:0 | MUX1 | R/W | 0x0 | If AIO0CFG.MODE10 = 00b and AIO0CFG.OPT0 = 00b, Reserved If AIO0CFG.MODE10 = 00b and AIO0CFG.OPT0 = 10b, set AIO1 state according to MUX1 111b: DB7 110b: DB6 101b: DB5 100b: DB4 011b: DB3 010b: DB2 001b: DB1 000b: DOUT1 |
| 7 | HP10PR1EN | R/W | 0x0 | If AIO0CFG.MODE10 = 01b, HPROT10 PR1 Protection enable 1b: HP10 output to PR1 enabled 0b: HP10 output to PR1 disabled |
| 6 | HP10PR2EN | R/W | 0x0 | If AIO0CFG.MODE10 = 01b, HPROT10 PR2 Protection enable 1b: HP10 output to PR2 enabled 0b: HP10 output to PR2 disabled |
| 5 | LP10PR1EN | R/W | 0x0 | If AIO0CFG.MODE10 = 01b, LPROT10 PR1 Protection enable 1b: LP10 output to PR1 enabled 0b: LP10 output to PR1 disabled |
| 4 | LP10PR2EN | R/W | 0x0 | If AIO0CFG.MODE10 = 01b, LPROT10 PR2 Protection enable 1b: LP10 output to PR2 enabled 0b: LP10 output to PR2 disabled |
| 3 | OS10EN | R/W | 0x0 | If AIO0CFG.MODE10 = 01b, Differential Amplifier Offset 1b: Offset enabled, input signal shifted by VREF/2 0b: Offset disabled |
| 2 | CAL10EN | R/W | 0x0 | If AIO0CFG.MODE10 = 01b, Differential Amplifier Offset Calibration 1b: enabled 0b: disabled |
| 1:0 | HP10EN | R/W | 0x0 | If AIO0CFG.MODE10 = 01b, HP10 comparator setting 11b: HP10 comparator enabled with 4μs blanking time 10b: HP10 comparator enabled with 2μs blanking time 01b: HP10 comparator enabled with 1μs blanking time 00b: HP10 comparator disabled |

22.1.4. SOC.AIO2CFG

Register 22-3. SOC.AIO2CFG (AIO2 Configuration, SOC 0x22)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|---------------|--------|-------|--|
| 7:6 | MODE32 | R/W | 0x0 | AIO3, AIO2 Mode 11b: reserved 10b: reserved 01b: Differential amplifier mode mode, AIO3 and AIO2 build a differential amplifier input 00b: IO Mode, AIO3 and AIO2 work in I/O mode |
| 5:4 | OPT2 | R/W | 0x0 | If AIO2CFG.MODE32 = 00b, AIO2 IO Setting 11b: Reserved 10b: Open-drain output 01b: Reserved 00b: Input, input state available at SOC.AIOIN0.AIO2DIN |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|--|
| 3 | POL2 | R/W | 0x0 | If AIO2CFG.MODE32 = 00b and CFGAIO2.OPT2 = 00b, AIO2 Input polarity setting. If AIO2CFG.MODE32 = 00b and CFGAIO2.OPT2 = 10b, AIO2 Output polarity setting. 1b: active-low 0b: active-high |
| 2:0 | MUX2 | R/W | 0x0 | If AIO2CFG.MODE32 = 00b and CFGAIO2.OPT2 = 00b, Reserved If AIO2CFG.MODE32 = 00b and CFGAIO2.OPT2 = 10b, set AIO2 state according to MUX2 111b: DB7 110b: DB6 101b: DB5 100b: DB4 011b: DB3 010b: DB2 001b: DB1 000b: DOUT2 |
| 5:3 | GAIN32 | R/W | 0x0 | If AIO2CFG.MODE32 = 01b, Differential amplifier gain setting 111b: 48x 110b: 32x 101b: 16x 100b: 8x 011b: 4x 010b: 2x 001b: 1x 000b: 1x |
| 2 | Reserved | R/W | 0x0 | If AIO2CFG.MODE32 = 01b, Reserved, Write to 0b |
| 1:0 | LP32EN | R/W | 0x0 | If AIO2CFG.MODE32 = 01b, LP32 comparator setting 11b: LP32 comparator enabled with 4µs blanking time 10b: LP32 comparator enabled with 2µs blanking time 01b: LP32 comparator enabled with 1µs blanking time 00b: LP32 comparator disabled |

22.1.5. SOC.AIO3CFG

Register 22-4. SOC.AIO3CFG (AIO3 Configuration, SOC 0x23)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|--|
| 7:6 | Reserved | R/W | 0x0 | If AIO2CFG.MODE32 = 00b, Reserved, write to 00b |
| 5:4 | OPT3 | R/W | 0x0 | If AIO2CFG.MODE32 = 00b, AIO3 IO Setting 11b: Reserved 10b: Open-drain output 01b: Reserved 00b: Input, input state available at SOC.AIOIN0.AIO3DIN |
| 3 | POL3 | R/W | 0x0 | If AIO2CFG.MODE32 = 00b and AIO2CFG.OPT2 = 00b, AIO3 Input polarity setting. If AIO2CFG.MODE32 = 00b and AIO2CFG.OPT2 = 10b, AIO3 Output polarity setting. 1b: active-low 0b: active-high |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|------------------|--------|-------|--|
| 2:0 | MUX3 | R/W | 0x0 | If AIO2CFG.MODE32 = 00b and AIO2CFG.OPT2 = 00b, Reserved If AIO2CFG.MODE32 = 00b and AIO2CFG.OPT2 = 10b, set AIO3 state according to MUX3 111b: DB7 110b: DB6 101b: DB5 100b: DB4 011b: DB3 010b: DB2 001b: DB1 000b: DOUT3 |
| 7 | HP32PR1EN | R/W | 0x0 | If AIO2CFG.MODE32 = 01b, HPROT32 PR1 Protection enable 1b: HP32 output to PR1 enabled 0b: HP32 output to PR1 disabled |
| 6 | HP32PR2EN | R/W | 0x0 | If AIO2CFG.MODE32 = 01b, HPROT32 PR2 Protection enable 1b: HP32 output to PR2 enabled 0b: HP32 output to PR2 disabled |
| 5 | LP32PR1EN | R/W | 0x0 | If AIO2CFG.MODE32 = 01b, LPROT32 PR1 Protection enable 1b: LP32 output to PR1 enabled 0b: LP32 output to PR1 disabled |
| 4 | LP32PR2EN | R/W | 0x0 | If AIO2CFG.MODE32 = 01b, LPROT32 PR2 Protection enable 1b: LP32 output to PR2 enabled 0b: LP32 output to PR2 disabled |
| 3 | OS32EN | R/W | 0x0 | If AIO2CFG.MODE32 = 01b, Differential Amplifier Offset 1b: Offset enabled, input signal shifted by VREF/2 0b: Offset disabled |
| 2 | CAL32EN | R/W | 0x0 | If AIO2CFG.MODE32 = 01b, Differential Amplifier Offset Calibration 1b: enabled 0b: disabled |
| 1:0 | HP32EN | R/W | 0x0 | If AIO2CFG.MODE32 = 01b, HP32 comparator setting 11b: HP32 comparator enabled with 4µs blanking time 10b: HP32 comparator enabled with 2µs blanking time 01b: HP32 comparator enabled with 1µs blanking time 00b: HP32 comparator disabled |

22.1.6. SOC.AIO4CFG

Register 22-5. SOC.AIO4CFG (AIO4 Configuration, SOC 0x24)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|---------------|--------|-------|--|
| 7:6 | MODE54 | R/W | 0x0 | AIO5, AIO4 Mode 11b: reserved 10b: reserved 01b: Differential amplifier mode mode, AIO5 and AIO4 build a differential amplifier input 00b: IO Mode, AIO5 and AIO4 work in I/O mode |
| 5:4 | OPT4 | R/W | 0x0 | If AIO4CFG.MODE54 = 00b, AIO4 IO Setting 11b: Reserved 10b: Open-drain output 01b: Reserved 00b: Input, input state available at SOC.AIOIN0.AIO4DIN |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|--|
| 3 | POL4 | R/W | 0x0 | If AIO4CFG.MODE54 = 00b and CFGAIO4.OPT4 = 00b, AIO4 Input polarity setting. If AIO4CFG.MODE54 = 00b and CFGAIO4.OPT4 = 10b, AIO4 Output polarity setting. 1b: active-low 0b: active-high |
| 2:0 | MUX4 | R/W | 0x0 | If AIO4CFG.MODE54 = 00b and CFGAIO4.OPT4 = 00b, Reserved If AIO4CFG.MODE54 = 00b and CFGAIO4.OPT4 = 10b, set AIO4 state according to MUX4 111b: DB7 110b: DB6 101b: DB5 100b: DB4 011b: DB3 010b: DB2 001b: DB1 000b: DOUT4 |
| 5:3 | GAIN54 | R/W | 0x0 | If AIO4CFG.MODE54 = 01b, Differential amplifier gain setting 111b: 48x 110b: 32x 101b: 16x 100b: 8x 011b: 4x 010b: 2x 001b: 1x 000b: 1x |
| 2 | Reserved | R/W | 0x0 | If AIO4CFG.MODE54 = 01b, Reserved, Write to 0b |
| 1:0 | LP54EN | R/W | 0x0 | If AIO4CFG.MODE54 = 01b, LP54 comparator setting 11b: LP54 comparator enabled with 4µs blanking time 10b: LP54 comparator enabled with 2µs blanking time 01b: LP54 comparator enabled with 1µs blanking time 00b: LP54 comparator disabled |

22.1.7. SOC.AIO5CFG

Register 22-6. SOC.AIO5CFG (AIO5 Configuration, SOC 0x25)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|--|
| 7:6 | Reserved | R/W | 0x0 | If AIO4CFG.MODE54 = 00b, Reserved, write to 00b |
| 5:4 | OPT5 | R/W | 0x0 | If AIO4CFG.MODE54 = 00b, AIO5 IO Setting 11b: Reserved 10b: Open-drain output 01b: Reserved 00b: Input, input state available at SOC.AIOIN0.AIO5DIN |
| 3 | POL5 | R/W | 0x0 | If AIO4CFG.MODE54 = 00b and AIO4CFG.OPT4 = 00b, AIO5 Input polarity setting. If AIO4CFG.MODE54 = 00b and AIO4CFG.OPT4 = 10b, AIO5 Output polarity setting. 1b: active-low 0b: active-high |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|------------------|--------|-------|---|
| 2:0 | MUX5 | R/W | 0x0 | If AIO4CFG.MODE54 = 00b and AIO4CFG.OPT4 = 00b, Reserved If AIO4CFG.MODE32 = 00b and AIO4CFG.OPT4 = 10b, Output polarity, set AIO3 state according to MUX3 111b: DB7 110b: DB6 101b: DB5 100b: DB4 011b: DB3 010b: DB2 001b: DB1 000b: DOUT5 |
| 7 | HP54PR1EN | R/W | 0x0 | If AIO4CFG.MODE54 = 01b, HPROT54 PR1 Protection enable 1b: HP54 output to PR1 enabled 0b: HP54 output to PR1 disabled |
| 6 | HP54PR2EN | R/W | 0x0 | If AIO4CFG.MODE54 = 01b, HPROT32 PR2 Protection enable 1b: HP32 output to PR2 enabled 0b: HP32 output to PR2 disabled |
| 5 | LP54PR1EN | R/W | 0x0 | If AIO4CFG.MODE54 = 01b, LPROT54 PR1 Protection enable 1b: LP32 output to PR1 enabled 0b: LP32 output to PR1 disabled |
| 4 | LP54PR2EN | R/W | 0x0 | If AIO4CFG.MODE54 = 01b, LPROT54 PR2 Protection enable 1b: LP32 output to PR2 enabled 0b: LP32 output to PR2 disabled |
| 3 | OS54EN | R/W | 0x0 | If AIO4CFG.MODE54 = 01b, Differential Amplifier Offset 1b: Offset enabled, input signal shifted by VREF/2 0b: Offset disabled |
| 2 | CAL54EN | R/W | 0x0 | If AIO4CFG.MODE54 = 01b, Differential Amplifier Offset Calibration 1b: enabled 0b: disabled |
| 1:0 | HP54EN | R/W | 0x0 | If AIO4CFG.MODE54 = 01b, HP54 comparator setting 11b: HP54 comparator enabled with 4µs blanking time 10b: HP54 comparator enabled with 2µs blanking time 01b: HP54 comparator enabled with 1µs blanking time 00b: HP54 comparator disabled |

22.1.8. SOC.AIO6CFG

Register 22-7. SOC.AIO6CFG (AIO6 Configuration, SOC 0x26)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|--------------|--------|-------|--|
| 7:6 | MODE6 | R/W | 0x0 | AIO6 Mode 11b: Special mode 10b: Comparator mode 01b: Gain Amplifier mode 00b: IO Mode |
| 5:4 | OPT6 | R/W | 0x0 | If AIO6CFG.MODE6 = 00b, AIO6 IO Setting 11b: Reserved 10b: Open-drain output 01b: Reserved 00b: Input, input state available at SOC.AIOIN1.AIO6DIN |
| 3 | POL6 | R/W | 0x0 | If AIO6CFG.MODE6 = 00b and CFGAIO6.OPT6 = 00b, AIO6 Input polarity setting. If AIO6CFG.MODE6 = 00b and CFGAIO6.OPT6 = 10b, AIO6 Output polarity setting. 1b: active-low 0b: active-high |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|---|
| 2:0 | MUX6 | R/W | 0x0 | If AIO6CFG.MODE6 = 00b and CFGAI06.OPT6 = 00b, Reserved If AIO6CFG.MODE6 = 00b and CFGAI06.OPT6 = 10b, Output polarity, set AIO6 state according to MUX6 111b: DB7 110b: DB6 101b: DB5 100b: DB4 011b: DB3 010b: DB2 001b: DB1 000b: DOUT6 |
| 5:3 | GAIN6 | R/W | 0x0 | If AIO6CFG.MODE6 = 01b, amplifier gain setting 111b: 48x 110b: 32x 101b: 16x 100b: 8x 011b: 4x 010b: 2x 001b: 1x 000b: Gain Amplifier Bypass, Direct mode |
| 2:0 | MUX6 | R/W | 0x0 | If AIO6CFG.MODE6 = 01b, Analog MUX Setting 111b: AB7 110b: AB6 101b: AB5 100b: AB4 011b: AB3 010b: AB2 001b: AB1 000b: AB6 |
| 5:4 | OPT6 | R/W | 0x0 | If AIO6CFG.MODE6 = 10b, AIO6 Comparator Reference select 11b: AB3 10b: AB2 01b: AB1 00b: VTHREF |
| 3 | POL6 | R/W | 0x0 | If AIO6CFG.MODE6 = 10b, AIO6 Comparator output polarity setting. 1b: active-low 0b: active-high |
| 2:0 | MUX6 | R/W | 0x0 | If AIO6CFG.MODE6 = 10b ,send AIO6 comparator output state to internal digital bus and SOC.AIOIN1.AIO6DIN 111b: DB7 110b: DB6 101b: DB5 100b: DB4 011b: DB3 010b: DB2 001b: DB1 000b: Reserved |
| 5 | ADMUX | R/W | 0x0 | If AIO6CFG.MODE6 = 11b 1b: MUX ADMUX output to AB7 0b: do not MUX ADMUX output to AB7 |
| 4 | SWAP | R/W | 0x0 | If AIO6CFG.MODE6 = 11b 1b: Swap buffer offset 0b: do not swap buffer offset |
| 3 | Reserved | R/W | 0x0 | If AIO6CFG.MODE6 = 11b, Reserved, write to 0b |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-------------|--------|-------|---|
| 2:0 | MUX6 | R/W | 0x0 | If AIO6CFG.MODE6 = 11b, send AIO6 comparator output state to internal digital bus and SOC.AIOIN1.AIO6DIN 111b: DB7 110b: DB6 101b: DB5 100b: DB4 011b: DB3 010b: DB2 001b: DB1 000b: Reserved |

22.1.9. SOC.AIO7CFG

Register 22-8. SOC.AIO7CFG (AIO7 Configuration, SOC 0x27)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|--------------|--------|-------|---|
| 7:6 | MODE7 | R/W | 0x0 | AIO7 Mode 11b: Special mode 10b: Comparator mode 01b: Gain Amplifier mode 00b: IO Mode |
| 5:4 | OPT7 | R/W | 0x0 | If AIO7CFG.MODE7 = 00b, AIO7 IO Setting 11b: Reserved 10b: Open-drain output 01b: Reserved 00b: Input, input state available at SOC.AIOIN1.AIO7DIN |
| 3 | POL7 | R/W | 0x0 | If AIO7CFG.MODE7 = 00b and CFGAI07.OPT7 = 00b, AIO7 Input polarity setting. If AIO7CFG.MODE7 = 00b and CFGAI07.OPT7 = 10b, AIO7 Output polarity setting. 1b: active-low 0b: active-high |
| 2:0 | MUX7 | R/W | 0x0 | If AIO7CFG.MODE7 = 00b and CFGAI07.OPT7 = 00b, Reserved If AIO7CFG.MODE7 = 00b and CFGAI07.OPT7 = 10b, Output polarity, set AIO7 state according to MUX7 111b: DB7 110b: DB6 101b: DB5 100b: DB4 011b: DB3 010b: DB2 001b: DB1 000b: DOUT7 |
| 5:3 | GAIN7 | R/W | 0x0 | If AIO7CFG.MODE7 = 01b, amplifier gain setting 111b: 48x 110b: 32x 101b: 16x 100b: 8x 011b: 4x 010b: 2x 001b: 1x 000b: Gain Amplifier Bypass, Direct mod |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-------------|--------|-------|--|
| 2:0 | MUX7 | R/W | 0x0 | If AIO7CFG.MODE7 = 01b, Analog Mux Setting 111b: AB7 110b: AB6 101b: AB5 100b: AB4 011b: AB3 010b: AB2 001b: AB1 000b: AB7 |
| 5:4 | OPT7 | R/W | 0x0 | If AIO7CFG.MODE7 = 10b, AIO7 Comparator Reference select 11b: AB3 10b: AB2 01b: AB1 00b: VTHREF |
| 3 | POL7 | R/W | 0x0 | If AIO7CFG.MODE7 = 10b, AIO7 Comparator output polarity setting. 1b: active-low 0b: active-high |
| 2:0 | MUX7 | R/W | 0x0 | If AIO7CFG.MODE7 = 10b , send AIO7 comparator output state to internal digital bus and SOC.AIOIN1.AIO7DIN 111b: DB7 110b: DB6 101b: DB5 100b: DB4 011b: DB3 010b: DB2 001b: DB1 000b: Reserved |
| 5:4 | OPT7 | R/W | 0x0 | If AIO7CFG.MODE7 = 11b, Select reference for AIO7, AIO8, AIO9 comparator in special mode. 11b: AB3 10b: AB2 01b: AB1 00b: Reserved |
| 3 | POL7 | R/W | 0x0 | If AIO7CFG.MODE7 = 11b, AIO7 comparator output polarity setting. 1b: active-low 0b: active-high |
| 2:0 | MUX7 | R/W | 0x0 | If AIO7CFG.MODE7 = 11b Reserved |

22.1.10. SOC.AIO8CFG

Register 22-9. SOC.AIO8CFG (AIO8 Configuration, SOC 0x28)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|--------------|--------|-------|--|
| 7:6 | MODE8 | R/W | 0x0 | If AIO7CFG.MODE7 not 11b, AIO8 Mode 11b: Reserved 10b: Comparator mode 01b: Gain Amplifier mode 00b: IO Mode |
| 5:4 | OPT8 | R/W | 0x0 | If AIO8CFG.MODE8 = 00b, AIO8 IO Setting 11b: Reserved 10b: Open-drain output 01b: Reserved 00b: Input, input state available at SOC.AIOIN1.AIO8DIN |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|----------------|--------|-------|---|
| 3 | POL8 | R/W | 0x0 | If AIO8CFG.MODE8 = 00b and CFGAIO8.OPT8 = 00b, AIO8 Input polarity setting. If AIO8CFG.MODE8 = 00b and CFGAIO8.OPT8 = 10b, AIO8 Output polarity setting. 1b: active-low 0b: active-high |
| 2:0 | MUX8 | R/W | 0x0 | If AIO8CFG.MODE8 = 00b and CFGAIO8.OPT8 = 00b, Reserved If AIO8CFG.MODE8 = 00b and CFGAIO8.OPT8 = 10b, Output polarity, set AIO8 state according to MUX8 111b: DB7 110b: DB6 101b: DB5 100b: DB4 011b: DB3 010b: DB2 001b: DB1 000b: DOUT8 |
| 5:3 | GAIN8 | R/W | 0x0 | If AIO8CFG.MODE8 = 01b, amplifier gain setting 111b: 48x 110b: 32x 101b: 16x 100b: 8x 011b: 4x 010b: 2x 001b: 1x 000b: Gain Amplifier Bypass, Direct mod |
| 2:0 | MUX8 | R/W | 0x0 | If AIO8CFG.MODE8 = 01b, Analog Mux Setting 111b: AB7 110b: AB6 101b: AB5 100b: AB4 011b: AB3 010b: AB2 001b: AB1 000b: AB8 |
| 5:4 | OPT8 | R/W | 0x0 | If AIO8CFG.MODE8 = 10b, AIO8 Comparator Reference select 11b: AB3 10b: AB2 01b: AB1 00b: VTHREF |
| 3 | POL8 | R/W | 0x0 | If AIO8CFG.MODE8 = 10b, AIO8 Comparator output polarity setting. 1b: active-low 0b: active-high |
| 2:0 | MUX8 | R/W | 0x0 | If AIO8CFG.MODE8 = 10b, send AIO8 comparator output state to internal digital bus 111b: DB7 110b: DB6 101b: DB5 100b: DB4 011b: DB3 010b: DB2 001b: DB1 000b: Reserved |
| 5 | OPT8[1] | R/W | 0x0 | If AIO7CFG.MODE7 = 11b 1b: do not bypass S/H for POS signal 0b: bypass S/H for POS signal |
| 4 | OPT8[0] | R/W | 0x0 | If AIO7CFG.MODE7 = 11b, 1b: select nIRQ2/POS output to output POS 0b: select nIRQ2/POS output nIRQ2 |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-------------|--------|-------|--|
| 3 | POL8 | R/W | 0x0 | If AIO7CFG.MODE7 = 11b, AIO8 comparator output polarity setting. 1b: active-low 0b: active-high |
| 2:0 | MUX8 | R/W | 0x0 | If AIO7CFG.MODE7 = 11b Reserved |

22.1.11. SOC.AIO9CFG

Register 22-10. SOC.AIO9CFG (AIO9 Configuration, SOC 0x29)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|--------------|--------|-------|---|
| 7:6 | MODE9 | R/W | 0x0 | If AIO7CFG.MODE7 not 11b, AIO9 Mode 11b: Reserved 10b: Comparator mode 01b: Gain Amplifier mode 00b: IO Mode |
| 5:4 | OPT9 | R/W | 0x0 | If AIO9CFG.MODE9 = 00b, AIO9 IO Setting 11b: Reserved 10b: Open-drain output 01b: Reserved 00b: Input, input state available at SOC.AIOIN1.AIO9DIN |
| 3 | POL9 | R/W | 0x0 | If AIO9CFG.MODE9 = 00b and CFGAI9.OPT9 = 00b, AIO9 Input polarity setting. If AIO9CFG.MODE9 = 00b and CFGAI9.OPT9 = 10b, AIO9 Output polarity setting. 1b: active-low 0b: active-high |
| 2:0 | MUX9 | R/W | 0x0 | If AIO9CFG.MODE9 = 00b and CFGAI9.OPT9 = 00b, Reserved If AIO9CFG.MODE9 = 00b and CFGAI9.OPT9 = 10b, Output polarity, set AIO9 state according to MUX9 111b: DB7 110b: DB6 101b: DB5 100b: DB4 011b: DB3 010b: DB2 001b: DB1 000b: DOUT9 |
| 5:3 | GAIN9 | R/W | 0x0 | If AIO9CFG.MODE9 = 01b, amplifier gain setting 111b: 48x 110b: 32x 101b: 16x 100b: 8x 011b: 4x 010b: 2x 001b: 1x 000b: Gain Amplifier Bypass, Direct mod |
| 2:0 | MUX9 | R/W | 0x0 | If AIO9CFG.MODE9 = 01b, Analog Mux Setting 111b: AB7 110b: AB6 101b: AB5 100b: AB4 011b: AB3 010b: AB2 001b: AB1 000b: AB9 |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|---|
| 5:4 | OPT9 | R/W | 0x0 | If AIO9CFG.MODE9 = 10b, AIO9 Comparator Reference select 11b: AB3 10b: AB2 01b: AB1 00b: VTHREF |
| 3 | POL9 | R/W | 0x0 | If AIO9CFG.MODE9 = 10b, AIO9 Comparator output polarity setting. 1b: active-low 0b: active-high |
| 2:0 | MUX9 | R/W | 0x0 | If AIO9CFG.MODE9 = 10b and CFGAI9.OPT9 = 00b, send AIO9 comparator output state to internal digital bus and input state available at SOC.AIOIN1.AIO9DIN 111b: DB7 110b: DB6 101b: DB5 100b: DB4 011b: DB3 010b: DB2 001b: DB1 000b: Reserved |
| 7 | MODE9[1] | R/W | 0x0 | If AIO7CFG.MODE7 = 11b 1b: Connect AIO7 to AB7, AIO8 to AB8, AIO9 to AB9 with 40% attenuation 0b: do not MUX AIO7, AIO8, AIO9 inputs to ABUS |
| 6 | MODE9[0] | R/W | 0x0 | If AIO7CFG.MODE7 = 11b 1b: connect AIO7, AIO8, AIO9 to AB1 using matched 100Ω resistors 0b: keep positive comparator input of AIO7, AIO8, AIO9 separate |
| 5:4 | OPT9 | R/W | 0x0 | If AIO7CFG.MODE7 = 11b 11b: MUX AIO9 comparator output to POS 10b: MUX AIO8 comparator output to POS 01b: MUX AIO7 comparator output to POS 00b: not connected |
| 3 | POL9 | R/W | 0x0 | If AIO7CFG.MODE7 = 11b and if AIO9CFG.MODE9 = 11b, AIO9 comparator output polarity setting. 1b: active-low 0b: active-high |
| 2:0 | MUX9 | R/W | 0x0 | If AIO7CFG.MODE7 = 11b Reserved |

22.1.12. SOC.SMCFG

Register 22-11. SOC.SMCFG (Signal Manager Configuration, SOC 0x2A)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|----------------|--------|-------|---|
| 7 | AIO9HYS | R/W | 0x0 | AIO9 Comparator Hysteresis 1b: Comparator Hysteresis enabled 0b: Comparator Hysteresis disabled |
| 6 | AIO8HYS | R/W | 0x0 | AIO8 Comparator Hysteresis 1b: Comparator Hysteresis enabled 0b: Comparator Hysteresis disabled |
| 5 | AIO7HYS | R/W | 0x0 | AIO7 Comparator Hysteresis 1b: Comparator Hysteresis enabled 0b: Comparator Hysteresis disabled |
| 4 | AIO6HYS | R/W | 0x0 | AIO6 Comparator Hysteresis 1b: Comparator Hysteresis enabled 0b: Comparator Hysteresis disabled |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|---|
| 3 | HPROTHYS | R/W | 0x0 | HPx Hysteresis 1b: Comparator Hysteresis enabled 0b: Comparator Hysteresis disabled |
| 2 | LPROTHYS | R/W | 0x0 | LPx Hysteresis 1b: Comparator Hysteresis enabled 0b: Comparator Hysteresis disabled |
| 1 | LPDACAB3 | R/W | 0x0 | Connect LPDAC output to AB3 1b: LPDAC output connected to AB3 0b: LPDAC output not connected to AB3 |
| 0 | HPDACAB2 | R/W | 0x0 | Connect HPDAC output to AB2 1b: HPDAC output connected to AB2 0b: HPDAC output not connected to AB2 |

22.1.13. SOC.HPDAC

Register 22-12. SOC.HPDAC (HPDAC Setting, SOC 0x2B)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|--------------|--------|-------|---|
| 7:0 | HPDAC | R/W | 0x0 | HPDAC Setting 0xFF: 255/256*VREF .. 0x00: 0/256*VREF |

22.1.14. SOC.LPDAC0

Register 22-13. SOC.LPDAC0 (LPDAC Setting [9:2], SOC 0x2C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-------------------|--------|-------|------------------------------|
| 7:0 | LPDAC[9:2] | R/W | 0x0 | LPDAC Setting bit 9 to bit 2 |

22.1.15. SOC.LPDAC1

Register 22-14. SOC.LPDAC1 (LPDAC Setting [1:0], SOC 0x2C)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-------------------|--------|-------|------------------------------|
| 7:2 | Reserved | R/W | 0x0 | Reserved, write to 0x0 |
| 1:0 | LPDAC[1:0] | R/W | 0x0 | LPDAC Setting bit 1 to bit 0 |

22.1.16. SOC.ADCSCANCFG

Register 22-15. SOC.ADCSCANCFG (ADCSCAN Configuration, SOC 0x2E)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|--|
| 7:5 | Reserved | R/W | 0x0 | Reserved, write to 0x0 |
| 4 | SCANEN | R/W | 0x0 | ADC Scan Control Enable 1b: enabled 0b: disabled |
| 3 | ADCBUFEN | R/W | 0x0 | ADC Buffer Enable 1b: enabled 0b: disabled |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|----------------|--------|-------|---|
| 2 | DAO10SH | R/W | 0x0 | DAO10 Sample and Hold buffer enable 1b: enable S/H 0b: disable and bypass S/H |
| 1 | DAO32SH | R/W | 0x0 | DAO32 Sample and Hold buffer enable 1b: enable S/H 0b: disable and bypass S/H |
| 0 | DAO54SH | R/W | 0x0 | DAO54 Sample and Hold buffer enable 1b: enable S/H 0b: disable and bypass S/H |

22.1.17. SOC.ADMUX

Register 22-16. SOC.ADMUX (AD Mux Selector, SOC 0x2F)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|---|
| 7:4 | Reserved | R/W | 0x0 | Reserved, write to 0x0 |
| 3:0 | MUXA | R/W | 0x0 | AD Mux Channel Selector 1111b: VREF / 2 1110b: AB12 1101b: AB11 1100b: AB10 1011b: AB9 1010b: AB8 1001b: AB7 1000b: AB6 0111b: AB5 0110b: AB4 0101b: AB3 0100b: AB2 0011b: AB1 0010b: DAO54 0001b: DAO32 0000b: DAO10 |

22.1.18. SOC.PROTINTEN

Register 22-17. SOC.PROTINTEN (Protection Interrupt Enable, SOC 0x30)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|------------------|--------|-------|---|
| 7 | Reserved | R/W | 0x0 | Reserved, write to 0x0 |
| 6 | HP54INTEN | R/W | 0x0 | H PROT54 Interrupt enable 1b: enable 0b: disabled |
| 5 | HP32INTEN | R/W | 0x0 | H PROT32 Interrupt enable 1b: enable 0b: disabled |
| 4 | HP10INTEN | R/W | 0x0 | H PROT10 Interrupt enable 1b: enable 0b: disabled |
| 3 | Reserved | R/W | 0x0 | Reserved, write to 0x0 |
| 2 | LP54INTEN | R/W | 0x0 | L PROT54 Interrupt enable 1b: enable 0b: disabled |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|------------------|--------|-------|--|
| 1 | LP32INTEN | R/W | 0x0 | LPROT32 Interrupt enable 1b: enable 0b: disabled |
| 0 | LP10INTEN | R/W | 0x0 | LPROT10 Interrupt enable 1b: enable 0b: disabled |

22.1.19. SOC.PROTINT

Register 22-18. SOC.PROTINT (Protection Interrupt, SOC 0x31)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|--|
| 7 | Reserved | R/W | 0x0 | Reserved, write to 0x0 |
| 6 | HP54INT | R/W | 0x0 | HPROT54 Interrupt 1b: Interrupt, write 1 to clear 0b: No interrupt |
| 5 | HP32INT | R/W | 0x0 | HPROT32 Interrupt 1b: Interrupt, write 1 to clear 0b: No interrupt |
| 4 | HP10INT | R/W | 0x0 | HPROT10 Interrupt 1b: Interrupt, write 1 to clear 0b: No interrupt |
| 3 | Reserved | R/W | 0x0 | Reserved, write to 0x0 |
| 2 | LP54INT | R/W | 0x0 | LPROT54 Interrupt 1b: Interrupt, write 1 to clear 0b: No interrupt |
| 1 | LP32INT | R/W | 0x0 | LPROT32 Interrupt 1b: Interrupt, write 1 to clear 0b: No interrupt |
| 0 | LP10INT | R/W | 0x0 | LPROT10 Interrupt 1b: Interrupt, write 1 to clear 0b: No interrupt |

22.1.20. SOC.AIOOUT0

Register 22-19. SOC.AIOOUT0 (AIO Digital Output, SOC 0x32)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|--|
| 7:6 | Reserved | R/W | 0x0 | Reserved, write to 0x0 |
| 5 | AIO5DOUT | R/W | 0x0 | AIO5 digital out 1b: Output High Z 0b: Output VSSA |
| 4 | AIO4DOUT | R/W | 0x0 | AIO4 digital out 1b: Output High Z 0b: Output VSSA |
| 3 | AIO3DOUT | R/W | 0x0 | AIO3 digital out 1b: Output High Z 0b: Output VSSA |
| 2 | AIO2DOUT | R/W | 0x0 | AIO2 digital out 1b: Output High Z 0b: Output VSSA |

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|--|
| 1 | AIO1DOUT | R/W | 0x0 | AIO1 digital out 1b: Output High Z 0b: Output VSSA |
| 0 | AIO0DOUT | R/W | 0x0 | AIO0 digital out 1b: Output High Z 0b: Output VSSA |

22.1.21. SOC.AIOOUT1

Register 22-20. SOC.AIOOUT0 (AIO Digital Output, SOC 0x33)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|--|
| 7:4 | Reserved | R/W | 0x0 | Reserved, write to 0x0 |
| 3 | AIO9DOUT | R/W | 0x0 | AIO9 digital out 1b: Output High Z 0b: Output VSSA |
| 2 | AIO8DOUT | R/W | 0x0 | AIO8 digital out 1b: Output High Z 0b: Output VSSA |
| 1 | AIO7DOUT | R/W | 0x0 | AIO7 digital out 1b: Output High Z 0b: Output VSSA |
| 0 | AIO6DOUT | R/W | 0x0 | AIO6 digital out 1b: Output High Z 0b: Output VSSA |

22.1.22. SOC.AIOIN0

Register 22-21. SOC.AIOIN0 (AIO Digital Input, SOC 0x34)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|---|
| 7:6 | Reserved | R/W | 0x0 | Reserved, write to 0x0 |
| 5 | AIO5DIN | R | 0x0 | AIO5 digital input 1b: Input high 0b: Input low |
| 4 | AIO4DIN | R | 0x0 | AIO4 digital input 1b: Input high 0b: Input low |
| 3 | AIO3DIN | R | 0x0 | AIO3 digital input 1b: Input high 0b: Input low |
| 2 | AIO2DIN | R | 0x0 | AIO2 digital input 1b: Input high 0b: Input low |
| 1 | AIO1DIN | R | 0x0 | AIO1 digital input 1b: Input high 0b: Input low |
| 0 | AIO0DIN | R | 0x0 | AIO0 digital input 1b: Input high 0b: Input low |

22.1.23. SOC.AIOIN1

Register 22-22. SOC.AIOIN1 (AIO Digital Input 1, SOC 0x35)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|---|
| 7:4 | Reserved | R/W | 0x0 | Reserved, write to 0x0 |
| 3 | AIO9DIN | R | 0x0 | AIO9 digital input 1b: Input high 0b: Input low |
| 2 | AIO8DIN | R | 0x0 | AIO9 digital input 1b: Input high 0b: Input low |
| 1 | AIO7DIN | R | 0x0 | AIO0 digital input 1b: Input high 0b: Input low |
| 0 | AIO6DIN | R | 0x0 | AIO0 digital input 1b: Input high 0b: Input low |

22.1.24. SOC.AIOINTEN

Register 22-23. SOC.AIOINTEN (AIO6,7,8,9 Interrupt Enable, SOC 0x36)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|--------------------|--------|-------|---|
| 7 | AIO9REINTEN | R/W | 0x0 | AIO9 digital input rising edge interrupt enable 1b: enabled 0b: disabled |
| 6 | AIO8REINTEN | R/W | 0x0 | AIO8 digital input rising edge interrupt enable 1b: enabled 0b: disabled |
| 5 | AIO7REINTEN | R/W | 0x0 | AIO7 digital input rising edge interrupt enable 1b: enabled 0b: disabled |
| 4 | AIO6REINTEN | R/W | 0x0 | AIO6 digital input rising edge interrupt enable 1b: enabled 0b: disabled |
| 3 | AIO9FEINTEN | R/W | 0x0 | AIO9 digital input falling edge interrupt enable 1b: enabled 0b: disabled |
| 2 | AIO8FEINTEN | R/W | 0x0 | AIO8 digital input falling edge interrupt enable 1b: enabled 0b: disabled |
| 1 | AIO7FEINTEN | R/W | 0x0 | AIO7 digital input falling edge interrupt enable 1b: enabled 0b: disabled |
| 0 | AIO6FEINTEN | R/W | 0x0 | AIO6 digital input falling edge interrupt enable 1b: enabled 0b: disabled |

22.1.25. SOC.AIOINT

Register 22-24. SOC.AIOINT (AIO6,7,8,9 Interrupt, SOC 0x37)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|--|
| 7:4 | Reserved | R/W | 0x0 | Reserved, write to 0x0 |
| 3 | AIO9INT | R/W | 0x0 | AIO9 Interrupt 1b: Interrupt, clear by writing 1b 0b: No Interrupt |
| 2 | AIO8INT | R/W | 0x0 | AIO8 Interrupt 1b: Interrupt, clear by writing 1b 0b: No Interrupt |
| 1 | AIO7INT | R/W | 0x0 | AIO7 Interrupt 1b: Interrupt, clear by writing 1b 0b: No Interrupt |
| 0 | AIO6INT | R/W | 0x0 | AIO6 Interrupt 1b: Interrupt, clear by writing 1b 0b: No Interrupt |

22.1.26. SOC.SMCTL


Register 22-25. SOC.SMCTL (Signal Manager Control SOC 0x38)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|--|
| 7:1 | Reserved | R/W | 0x0 | Reserved, write to 0x0 |
| 0 | SMEN | R/W | 0x0 | Signal Manager Enable 1b: Enabled 0b: Disabled |

22.2. Details of Operation

22.2.1. Block Diagram

Figure 22-1. Configurable Analog Front End



22.2.2. Configuration

Following blocks need to be configured for correct use of the Configurable analog frontend.

- Clock Control System (CCS)
- Nested Vectored Interrupt Controller (NVIC)
- IO Controller
- SOC Bridge

22.2.3. Configurable Analog Front End

The configurable analog front end registers are accessible through the SOC Bridge. AIoX can be configured as digital open drain I/Os or analog inputs.

Programmable comparators and protection circuits can be connected to the analog signals.

The analog signals can be conditioned with programmable gain single ended amplifiers or programmable gain differential amplifiers before muxed to the ADC.


22.2.3.1. Configurable Analog Front End Enable

Use **SOC.SMCTL.SMEN** to enable the configurable analog front end.

22.3. AIO1, AIO0

22.3.1. Block Diagram

Figure 22-2. AIO1, AIO0



22.3.2. AIO1, AIO0

AIO1 and AIO0 can be configured as digital inputs or as differential amplifier pair with additional protection.

22.3.3. AIO1, AIO0 digital I/O Mode

Set **SOC.AIO0CFG.MODE10** = 00b to use AIO1 and AIO0 as digital inputs.

22.3.3.1. AIO0 IO

Set **SOC.AIO0CFG.OPT0** = 00b to use AIO0 as input. The input state can be read at **SOC.AIOIN0.AIO0DIN**.

Set **SOC.AIO0CFG.OPT0** = 10b to use AIO0 as open drain output. Set **SOC.AIO0CFG.MUX0** = 00b to mux the output state from **SOC.AIOOUT0.AIO0DOUT**. Use **SOC.AIO0CFG.MUX0** to mux the output signal from the internal digital bus DBUS DB1 to DB7.

22.3.3.2. AIO1 IO

Set **SOC.AIO1CFG.OPT1** = 00b to use AIO1 as input. The input state can be read at **SOC.AIOIN0.AIO1DIN**.

Set **SOC.AIO1CFG.OPT1** = 10b to use AIO1 as open drain output. Set **SOC.AIO1CFG.MUX1** = 00b to MUX the output state from **SOC.AIOOUT0.AIO1DOUT**. Use **SOC.AIO1CFG.MUX1** to MUX the output signal from the internal digital bus DBUS DB1 to DB7.

22.3.3.3. AIO0 Polarity

Use **SOC.AIO0CFG.POL0** to set logic polarity of the signal between AIO0 input/output and MUX0.

22.3.3.4. AIO1 Polarity

Use **SOC.AIO0CFG.POL1** to set logic polarity of the signal between AIO1 input/output and MUX1.

22.3.4. AIO1, AIO0 differential Amplifier Mode

Set **SOC.AIO0CFG.MODE10** = 01b to use AIO1 and AIO0 as input to a differential amplifier.

22.3.4.1. AIO1, AIO0 Differential Amplifier Gain

Use **SOC.AIO0CFG.GAIN10** to set to gain between 1x to 48x.

22.3.4.2. AIO1, AIO0 Differential Amplifier Reference

Use **SOC.AIO1CFG.OS10EN** to set the amplifier reference either VSSA or VREF/2.

22.3.4.3. AIO1, AIO0 Differential Amplifier Calibration

Use **SOC.AIO1CFG.CAL10EN** to short the input of the differential amplifier to allow reading of the amplifier offset.

22.3.5. AIO1, AIO0 Protection

In **SOC.AIO0CFG.MODE10** = 01b differential amplifier mode, a high side comparator protector HP10 and a low

side comparator protector LP10 are also active that can be configured to disabled high-side or low-side drivers in the application specific power driver section.

22.3.5.1. HP10 Comparator

The HP10 comparator takes the AIO1 voltage referenced to VSSA and compares it against the HP-DAC voltage. The 8-bit HP-DAC is programmable with **SOC.HPDAC0**.

Use **SOC.AIO1CFG.HP10EN** to enable HP10 comparator with different blanking times.

Use **SOC.SMCFGHPPROTHYS** to enable HP10 comparator hysteresis.

The output of HP10 comparator can be configured to trigger protection signal PR1 using **SOC.AIO1CFG.HP10PR1EN** or protection signal PR2 using **SOC.AIO1CFG.HP10PR2EN**.

The output of HP10 can also trigger the nIRQ1 interrupt using **SOC.PROTINTEN.HP10INTEN**. The interrupt status can be observed with **SOC.PROTINT.HP10INT**.

22.3.5.2. LP10 Comparator

The LP10 comparator takes the output of the differential amplifier and compares it against the LP-DAC voltage. The 10-bit LP-DAC is programmable with **SOC.LPDAC0** and **SOC.LPDAC1**.

Use **SOC.AIO0CFG.LP10EN** to enable LP10 comparator with different blanking times.

Use **SOC.SMCFGGLPPROTHYS** to enable LP10 comparator hysteresis.


The output of LP10 comparator can be configured to trigger protection signal PR1 using **SOC.AIO1CFG.LP10PR1EN** or protection signal PR2 using **SOC.AIO1CFG.LP10PR2EN**.

The output of LP10 can also trigger the nIRQ1 interrupt using **SOC.PROTINTEN.LP10INTEN**. The interrupt status can be observed with **SOC.PROTINT.LP10INT**.

22.4. AIO3, AIO2

22.4.1. Block Diagram

Figure 22-3. AIO3, AIO2



22.4.2. AIO3, AIO2

AIO3 and AIO2 can be configured as digital inputs or as differential amplifier pair with additional protection.

22.4.3. AIO3, AIO2 digital I/O Mode

Set **SOC.AIO2CFG.MODE32** = 00b to use AIO3 and AIO2 as digital inputs.

22.4.3.1. AIO2 IO

Set **SOC.AIO2CFG.OPT2** = 00b to use AIO2 as input. The input state can be read at **SOC.AIOIN0.AIO2DIN**.

Set **SOC.AIO2CFG.OPT2** = 10b to use AIO2 as open drain output. Set **SOC.AIO2CFG.MUX2** = 00b to MUX the output state from **SOC.AIOOUT0.AIO2DOUT**. Use **SOC.AIO2CFG.MUX2** to MUX the output signal from the internal digital bus DBUS DB1 to DB7.

22.4.3.2. AIO3 IO

Set **SOC.AIO3CFG.OPT3** = 00b to use AIO3 as input. The input state can be read at **SOC.AIOIN0.AIO3DIN**.

Set **SOC.AIO3CFG.OPT3** = 10b to use AIO3 as open drain output. Set **SOC.AIO3CFG.MUX3** = 00b to MUX the output state from **SOC.AIOOUT0.AIO3DOUT**. Use **SOC.AIO3CFG.MUX3** to MUX the output signal from the internal digital bus DBUS DB1 to DB7.

22.4.3.3. AIO2 Polarity

Use **SOC.AIO2CFG.POL2** to set logic polarity of the signal between AIO2 input/output and MUX2.

22.4.3.4. AIO3 Polarity

Use **SOC.AIO3CFG.POL3** to set logic polarity of the signal between AIO3 input/output and MUX3.

22.4.4. AIO3, AIO2 differential Amplifier Mode DAO32

Set **SOC.AIO2CFG.MODE32** = 01b to use AIO3 and AIO2 as input to a differential amplifier DAO32.

22.4.4.1. DAO32 Differential Amplifier Gain

Use **SOC.AIO2CFG.GAIN32** to set to gain between 1x to 48x.

22.4.4.2. DAO32 Differential Amplifier Reference

Use **SOC.AIO3CFG.OS32EN** to set the amplifier reference either VSSA or VREF/2.

22.4.4.3. DAO32 Differential Amplifier Calibration

Use **SOC.AIO3CFG.CAL32EN** to short the input of the differential amplifier to allow reading of the amplifier offset.

22.4.5. AIO3, AIO2 Protection

In **SOC.AIO2CFG.MODE32** = 01b differential amplifier mode, a high side comparator protector HP10 and a low

side comparator protector LP10 are also active that can be configured to disabled high-side or low-side drivers in the application specific power driver section.

22.4.5.1. HP32 Comparator

The HP32 comparator takes the AIO3 voltage referenced to VSSA and compares it against the HP-DAC voltage. The 8-bit HP-DAC is programmable with **SOC.HPDAC0**.

Use **SOC.AIO3CFG.HP32EN** to enable HP32 comparator with different blanking times.

Use **SOC.SMCFGHPPROTHYS** to enable HP32 comparator hysteresis.

The output of HP32 comparator can be configured to trigger protection signal PR1 using **SOC.AIO3CFG.HP32PR1EN** or protection signal PR2 using **SOC.AIO3CFG.HP32PR2EN**.

The output of HP32 can also trigger the nIRQ1 interrupt using **SOC.PROTINTEN.HP32INTEN**. The interrupt status can be observed with **SOC.PROTINT.HP32INT**.

22.4.5.2. LP32 Comparator

The LP32 comparator takes the output of the differential amplifier and compares it against the LP-DAC voltage. The 10-bit LP-DAC is programmable with **SOC.LPDAC0** and **SOC.LPDAC1**.

Use **SOC.AIO2CFG.LP32EN** to enable LP32 comparator with different blanking times.

Use **SOC.SMCFGGLPPROTHYS** to enable LP32 comparator hysteresis.


The output of LP32 comparator can be configured to trigger protection signal PR1 using **SOC.AIO3CFG.LP32PR1EN** or protection signal PR2 using **SOC.AIO3CFG.LP32PR2EN**.

The output of LP32 can also trigger the nIRQ1 interrupt using **SOC.PROTINTEN.LP32INTEN**. The interrupt status can be observed with **SOC.PROTINT.LP32INT**.

22.5. AIO5, AIO4

22.5.1. Block Diagram

Figure 22-4. AIO5, AIO4



* common DAC for AIO0, AIO1, AIO2, AIO3, AIO4, AIO5

22.5.2. AIO5, AIO4

AIO5 and AIO4 can be configured as digital inputs or as differential amplifier pair with additional protection.

22.5.3. AIO5, AIO4 digital I/O Mode

Set **SOC.AIO4CFG.MODE54** = 00b to use AIO5 and AIO4 as digital inputs.

22.5.3.1. AIO4 IO

Set **SOC.AIO4CFG.OPT4** = 00b to use AIO4 as input. The input state can be read at **SOC.AIOIN0.AIO4DIN**.

Set **SOC.AIO4CFG.OPT4** = 10b to use AIO4 as open drain output. Set **SOC.AIO4CFG.MUX4** = 00b to MUX the output state from **SOC.AIOOUT0.AIO4DOUT**. Use **SOC.AIO4CFG.MUX4** to MUX the output signal from the internal digital bus DBUS DB1 to DB7.

22.5.3.2. AIO5 IO

Set **SOC.AIO5CFG.OPT5** = 00b to use AIO5 as input. The input state can be read at **SOC.AIOIN0.AIO5DIN**.

Set **SOC.AIO5CFG.OPT5** = 10b to use AIO5 as open drain output. Set **SOC.AIO5CFG.MUX5** = 00b to MUX the output state from **SOC.AIOOUT0.AIO5DOUT**. Use **SOC.AIO5CFG.MUX5** to MUX the output signal from the internal digital bus DBUS DB1 to DB7.

22.5.3.3. AIO4 Polarity

Use **SOC.AIO4CFG.POL4** to set logic polarity of the signal between AIO4 input/output and MUX4.

22.5.3.4. AIO5 Polarity

Use **SOC.AIO5CFG.POL5** to set logic polarity of the signal between AIO5 input/output and MUX5.

22.5.4. AIO5, AIO4 differential Amplifier Mode DAO54

Set **SOC.AIO4CFG.MODE54** = 01b to use AIO5 and AIO4 as input to a differential amplifier DAO54.

22.5.4.1. DAO54 Differential Amplifier Gain

Use **SOC.AIO4CFG.GAIN54** to set to gain between 1x to 48x.

22.5.4.2. DAO54 Differential Amplifier Reference

Use **SOC.AIO5CFG.OS54EN** to set the amplifier reference either VSSA or VREF/2.

22.5.4.3. DAO54 Differential Amplifier Calibration

Use **SOC.AIO5CFG.CAL54EN** to short the input of the differential amplifier to allow reading of the amplifier offset.

22.5.5. AIO5, AIO4 Protection

In **SOC.AIO4CFG.MODE54** = 01b differential amplifier mode, a high side comparator protector HP54 and a low

side comparator protector LP54 are also active that can be configured to disabled high-side or low-side drivers in the application specific power driver section.

22.5.5.1. HP54 Comparator

The HP54 comparator takes the AIO5 voltage referenced to VSSA and compares it against the HP-DAC voltage. The 8-bit HP-DAC is programmable with **SOC.HPDAC0**.

Use **SOC.AIO5CFG.HP54EN** to enable HP54 comparator with different blanking times.

Use **SOC.SMCFGHPPROTHYS** to enable HP54 comparator hysteresis.

The output of HP54 comparator can be configured to trigger protection signal PR1 using **SOC.AIO5CFG.HP54PR1EN** or protection signal PR2 using **SOC.AIO5CFG.HP54PR2EN**.

The output of HP54 can also trigger the nIRQ1 interrupt using **SOC.PROTINTEN.HP54INTEN**. The interrupt status can be observed with **SOC.PROTINT.HP54INT**.

22.5.5.2. LP54 Comparator

The LP54 comparator takes the output of the differential amplifier and compares it against the LP-DAC voltage. The 10-bit LP-DAC is programmable with **SOC.LPDAC0** and **SOC.LPDAC1**.

Use **SOC.AIO4CFG.LP54EN** to enable LP54 comparator with different blanking times.

Use **SOC.SMCFGGLPPROTHYS** to enable LP54 comparator hysteresis.


The output of LP54 comparator can be configured to trigger protection signal PR1 using **SOC.AIO5CFG.LP54PR1EN** or protection signal PR2 using **SOC.AIO5CFG.LP54PR2EN**.

The output of LP54 can also trigger the nIRQ1 interrupt using **SOC.PROTINTEN.LP54INTEN**. The interrupt status can be observed with **SOC.PROTINT.LP54INT**.

22.6. AIO6

22.6.1. Block Diagram

Figure 22-5. AIO6



22.6.2. AIO6

AIO6 can be configured as digital input, as singled ended programmable gain amplifier, as comparator, as output from the analog ABUS or as push button input to wake up the device from low power hibernate mode.

22.6.3. AIO6 digital I/O Mode

Set **SOC.PWRSTAT.PBEN** = 0b and **SOC.AIO6CFG.MODE6** = 00b to use AIO6 as digital IO.

22.6.3.1. AIO6 IO

Set **SOC.AIO6CFG.OPT6** = 00b to use AIO6 as input. The input state can be read at **SOC.AIOIN1.AIO6DIN**.

Set **SOC.AIO6CFG.OPT6** = 10b to use AIO6 as open drain output. Set **SOC.AIO6CFG.MUX6** = 00b to MUX the output state from **SOC.AIOOUT1.AIO6DOUT**. Use **SOC.AIO6CFG.MUX6** to MUX the output signal from the internal digital bus DBUS DB1 to DB7.

22.6.3.2. AIO6 IO Interrupt

Set **SOC.AIOINTEN.AIO6REINTEN** to allow nIRQ2 interrupt on AIO6 low high transition.

Set **SOC.AIOINTEN.AIO6FEINTEN** to allow nIRQ2 interrupt on AIO6 high low transition.

The interrupt status can be monitored with **SOC.AIOINT.AIO6INT** and cleared by writing **SOC.AIOINT.AIO6INT** to 1b.

22.6.3.3. AIO6 Polarity

Use **SOC.AIO6CFG.POL6** to set logic polarity of the signal between AIO6 input/output and MUX6.

22.6.4. AIO6 Single Ended Amplifier Mode

Set **SOC.PWRSTAT.PBEN** = 0b and **SOC.AIO6CFG.MODE6** = 01b to use AIO6 as input to a programmable gain amplifier.

22.6.4.1. AIO6 Amplifier Gain

Use **SOC.AIO6CFG.GAIN6** to set to gain between 1x to 48x or bidirectional amplifier bypassmode.

22.6.4.2. AIO6 Analog MUX

Use **SOC.AIO6CFG.MUX6** to switch the output of the amplifier to analog channel AB1 to AB7 on the analog bus ABUS.

22.6.5. AIO6 Comparator Mode

Set **SOC.PWRSTAT.PBEN** = 0b and **SOC.AIO6CFG.MODE6** = 10b to use AIO6 in comparator mode.

22.6.5.1. AIO6 Comparator Hysteresis

Use **SOC.SMCFG.AIO6HYS** to enable AIO6 comparator hysteresis.

22.6.5.2. AIO6 Comparator setting

Use **SOC.AIO6CFG.OPT6** to set the compare value of the comparator to AB1, AB2, AB3 or VTHREF, setable with **SOC.SYSSTAT.VTHREF**.

22.6.5.3. AIO6 Comparator Polarity

Use **SOC.AIO6CFG.POL6** to set the output polarity of the comparator.

22.6.5.4. AIO6 Comparator Output MUX

Use **SOC.AIO6CFG.MUX6** to set the output of the comparator to the digital bus DB1 to DB7 or **SOC.AIOIN1.AIO6DIN**.

22.6.6. AIO6 Special Mode

Set **SOC.PWRSTAT.PBEN** = 0b and **SOC.AIO6CFG.MODE6** = 11b to use AIO6 in special mode. In special mode the AIO6 can output a buffered signal from the internal ABUS, AB1 to AB7.

22.6.6.1. AIO6 Special Mode MUX

Use **SOC.AIO6CFG.MUX6** to set the ABx channel output to AIO6.

22.6.6.2. AIO6 Special Mode ADMUX

Use **SOC.AIO6CFG.ADMUX** set the MUX the ADMUX output to AB7.

22.6.6.3. AIO6 Special Mode OFFSET SWAP

Use **SOC.AIO6CFG.SWAP** to swap the random offset of the buffer for calibration reasons.

22.6.7. AIO6 Push Button Mode

Set **SOC.PWRSTAT.PBEN** = 1b to enable AIO6 Hibernate push button mode, where AIO6 has an internal weak pull up also active in hibernate mode. Set **SOC.PWRSTAT.PBINTEN** = 1b to enable nIRQ1 interrupt. Use **SOC.PWRSTAT.PBINT** to monitor interrupt status and write 1b to clear interrupt.

22.6.7.1. AIO6 Push Button Wake Up

In Hibernate Wake Mode and enabled push button mode, if AIO6 is pulled low for the de-bouncing time period, the **SOC.PWRCTL.HIB** is cleared and the device powers up.

22.6.7.2. AIO6 Push Button Power Down

In normal mode the **SOC.PWRSTAT.PBINT** is set when AIO6 is pulled low for the de-bouncing time period. The system then can be put into hibernate mode by setting **SOC.PWRCTL.HIB = 1b**.


22.6.7.3. AIO6 Push Button Hard Reset

In normal operation if the AIO6 is pulled low for more than 8s, the nRST signal will be asserted and the MCU is reset. **SOC.PWRSTAT.HWRESET** is set to indicate this condition.

22.7. AIO7

22.7.1. Block Diagram

Figure 22-6. AIO7



22.7.2. AIO7

AIO7 can be configured as digital input, as singled ended programmable gain amplifier, as comparator, as output from the analog ABUS or as push button input to wake up the device from low power hibernate mode.

22.7.3. AIO7 digital I/O Mode

Set **SOC.AIO7CFG.MODE7 = 00b** to use AIO7 as digital IO.

22.7.3.1. AIO7 IO

Set **SOC.AIO7CFG.OPT7** = 00b to use AIO7 as input. The input state can be read at **SOC.AIOIN1.AIO7DIN**.

Set **SOC.AIO7CFG.OPT7** = 10b to use AIO7 as open drain output. Set **SOC.AIO7CFG.MUX7** = 00b to MUX the output state from **SOC.AIOOUT1.AIO7DOUT**. Use **SOC.AIO7CFG.MUX7** to MUX the output signal from the internal digital bus DBUS DB1 to DB7.

22.7.3.2. AIO7 IO Interrupt

Set **SOC.AIOINTEN.AIO7REINTEN** to allow nIRQ2 interrupt on AIO7 low high transition.

Set **SOC.AIOINTEN.AIO7FEINTEN** to allow nIRQ2 interrupt on AIO7 high low transition.

The interrupt status can be monitored with **SOC.AIOINT.AIO7INT** and cleared by writing **SOC.AIOINT.AIO7INT** to 1b.

22.7.3.3. AIO7 Polarity

Use **SOC.AIO7CFG.POL7** to set logic polarity of the signal between AIO7 input/output and MUX7.

22.7.4. AIO7 Single Ended Amplifier Mode

Set **SOC.AIO7CFG.MODE7** = 01b to use AIO7 as input to a programmable gain amplifier.

22.7.4.1. AIO7 Amplifier Gain

Use **SOC.AIO7CFG.GAIN7** to set to gain between 1x to 48x or bidirectional amplifier bypassmode.

22.7.4.2. AIO7 Analog MUX

Use **SOC.AIO7CFG.MUX7** to switch the output of the amplifier to analog channel AB1 to AB7 on the analog bus ABUS.

22.7.5. AIO7 Comparator Mode

Set **SOC.AIO7CFG.MODE7** = 10b to use AIO7 in comparator mode.

22.7.5.1. AIO7 Comparator Hysteresis

Use **SOC.SMCFG.AIO7HYS** to enable AIO7 comparator hysteresis.

22.7.5.2. AIO7 Comparator Reference

Use **SOC.AIO7CFG.OPT7** to set the compare value of the comparator to AB1, AB2, AB3 or VTHREF, setable with **SOC.SYSSTAT.VTHREF**.

22.7.5.3. AIO7 Comparator Polarity

Use **SOC.AIO7CFG.POL7** to set the output polarity of the comparator.

22.7.5.4. AIO7 Comparator Output

The comparator output can be observed with **SOC.AIOIN1.AIO7DIN**.

22.7.6. AIO7 Special Mode

Set **SOC.AIO7CFG.MODE7** = 11b to use AIO7 in special mode. In special mode the AIO7 comparator is enabled.

22.7.6.1. AIO7 Comparator Hysteresis

Use **SOC.SMCFG.AIO7HYS** to enable AIO7 comparator hysteresis.

22.7.6.2. AIO7 Comparator Reference

Use **SOC.AIO7CFG.OPT7** to set the compare value of the comparator to AB1, AB2 or AB3.

22.7.6.3. AIO7 Comparator Reference Star Point

Use **SOC.AIO9CFG.MODE9[0]** =1b to connect AIO7, AIO8 and AIO9 to AB1 with a 100kOhm resistor to create a star point reference for the comparator.

With **SOC.AIO9CFG.MODE9[0]** =0b, the AB1 reference could for example come from AIO6 in amplifier mode **SOC.AIO6CFG.MODE6** = 01b and **SOC.AIO6CFG.GAIN6** = 000b direct mode and **SOC.AIO6CFG.MUX6** = 1b.

22.7.6.4. AIO7 Voltage Reading

Use **SOC.AIO9CFG.MODE9[1]** =1b to MUX AIO7 to AB7 with 40% attenuation, so ADC can read out AIO7 voltage.

22.7.6.5. AIO7 Comparator Output

Use **SOC.AIO9CFG.OPT9** to select AIO7, AIO8 or AIO9 comparator output signal for POS.

22.7.6.6. A/I07 POS S/H Bypass

Set **SOC.AIO8CFG.OPT8[1]** =0b bypass the POS S/H.

Set **SOC.AIO8CFG.OPT8[1]** =1b use POS S/H for use with EMUX.


22.7.6.7. A/I07 nIRQ2/POS Selector

Use **SOC.AIO8CFG.OPT8[0]** to select POS or nIRQ2 output.

22.8. AIO8

22.8.1. Block Diagram

Figure 22-7. AIO8



22.8.2. AIO8

AIO8 can be configured as digital input, as singled ended programmable gain amplifier, as comparator, as output from the analog ABUS or as push button input to wake up the device from low power hibernate mode.

22.8.3. AIO8 digital I/O Mode

Set **SOC.AIO8CFG.MODE8** = 00b to use AIO8 as digital IO.

22.8.3.1. AIO8 IO

Set **SOC.AIO8CFG.OPT8** = 00b to use AIO8 as input. The input state can be read at **SOC.AIOIN1.AIO8DIN**.

Set **SOC.AIO8CFG.OPT8** = 10b to use AIO8 as open drain output. Set **SOC.AIO8CFG.MUX8** = 00b to MUX the output state from **SOC.AIOOUT1.AIO8DOUT**. Use **SOC.AIO8CFG.MUX8** to MUX the output signal from the internal digital bus DBUS DB1 to DB7.

22.8.3.2. AIO8 IO Interrupt

Set **SOC.AIOINTEN.AIO8REINTEN** to allow nIRQ2 interrupt on AIO8 low high transition.

Set **SOC.AIOINTEN.AIO8FEINTEN** to allow nIRQ2 interrupt on AIO8 high low transition.

The interrupt status can be monitored with **SOC.AIOINT.AIO8INT** and cleared by writing **SOC.AIOINT.AIO8INT** to 1b.

22.8.3.3. AIO8 Polarity

Use **SOC.AIO8CFG.POL8** to set logic polarity of the signal between AIO8 input/output and MUX8.

22.8.4. AIO8 Single Ended Amplifier Mode

Set **SOC.AIO8CFG.MODE8** = 01b to use AIO8 as input to a programmable gain amplifier.

22.8.4.1. AIO8 Amplifier Gain

Use **SOC.AIO8CFG.GAIN8** to set to gain between 1x to 48x or bidirectional amplifier bypassmode.

22.8.4.2. AIO8 Analog MUX

Use **SOC.AIO8CFG.MUX8** to switch the output of the amplifier to analog channel AB1 to AB7 on the analog bus ABUS.

22.8.5. AIO8 Comparator Mode

Set **SOC.AIO8CFG.MODE8** = 10b to use AIO8 in comparator mode.

22.8.5.1. AIO8 Comparator Hysteresis

Use **SOC.SMCFG.AIO8HYS** to enable AIO8 comparator hysteresis.

22.8.5.2. AIO8 Comparator Reference

Use **SOC.AIO8CFG.OPT8** to set the compare value of the comparator to AB1, AB2, AB3 or VTHREF, setable with **SOC.SYSSTAT.VTHREF**.

22.8.5.3. AIO8 Comparator Polarity

Use **SOC.AIO8CFG.POL8** to set the output polarity of the comparator.

22.8.5.4. AIO8 Comparator Output

The comparator output can be observed with **SOC.AIOIN1.AIO8DIN**.

22.8.6. AIO8 Special Mode

Set **SOC.AIO7CFG.MODE7** = 11b to use AIO8 in special mode. In special mode the AIO8 comparator is enabled.

22.8.6.1. AIO8 Comparator Hysteresis

Use **SOC.SMCFG.AIO8HYS** to enable AIO8 comparator hysteresis.

22.8.6.2. AIO8 Comparator Reference

Use **SOC.AIO7CFG.OPT7** to set the compare value of the comparator to AB1, AB2 or AB3.

22.8.6.3. AIO8 Comparator Reference Star Point

Use **SOC.AIO9CFG.MODE9[0]** =1b to connect AIO7, AIO8 and AIO9 to AB1 with a 100kOhm resistor to create a star point reference for the comparator.

With **SOC.AIO9CFG.MODE9[0]** =0b, the AB1 reference could for example come from AIO6 in amplifier mode **SOC.AIO6CFG.MODE6** = 01b and **SOC.AIO6CFG.GAIN6** = 000b direct mode and **SOC.AIO6CFG.MUX6** = 1b.

22.8.6.4. AIO8 Voltage Reading

Use **SOC.AIO9CFG.MODE9[1]** =1b to MUX AIO8 to AB8 with 40% attenuation, so ADC can read out AIO8 voltage.

22.8.6.5. AIO8 Comparator Output

Use **SOC.AIO9CFG.OPT9** to select AIO7, AIO8 or AIO9 comparator output signal for POS.

22.8.6.6. AIO8 POS S/H Bypass

Set **SOC.AIO8CFG.OPT8[1]** =0b bypass the POS S/H.

Set **SOC.AIO8CFG.OPT8[1]** =1b use POS S/H for use with EMUX.


22.8.6.7. AIO8 nIRQ2/POS Selector

Use **SOC.AIO8CFG.OPT8[0]** to select POS or nIRQ2 output.

22.9. AIO9

22.9.1. Block Diagram

Figure 22-8. AIO9



22.9.2. AIO9

AIO9 can be configured as digital input, as singled ended programmable gain amplifier, as comparator, as output from the analog ABUS or as push button input to wake up the device from low power hibernate mode.

22.9.3. AIO9 digital I/O Mode

Set **SOC.AIO9CFG.MODE9** = 00b to use AIO9 as digital IO.

22.9.3.1. AIO9 IO

Set **SOC.AIO9CFG.OPT9** = 00b to use AIO9 as input. The input state can be read at **SOC.AIOIN1.AIO9DIN**.

Set **SOC.AIO9CFG.OPT9** = 10b to use AIO9 as open drain output. Set **SOC.AIO9CFG.MUX9** = 00b to MUX the output state from **SOC.AIOOUT1.AIO9DOUT**. Use **SOC.AIO9CFG.MUX9** to MUX the output signal from the internal digital bus DBUS DB1 to DB7.

22.9.3.2. AIO9 IO Interrupt

Set **SOC.AIOINTEN.AIO9REINTEN** to allow nIRQ2 interrupt on AIO8 low high transition.

Set **SOC.AIOINTEN.AIO9FEINTEN** to allow nIRQ2 interrupt on AIO8 high low transition.

The interrupt status can be monitored with **SOC.AIOINT.AIO9INT** and cleared by writing **SOC.AIOINT.AIO9INT** to 1b.

22.9.3.3. AIO9 Polarity

Use **SOC.AIO9CFG.POL9** to set logic polarity of the signal between AIO9 input/output and MUX9.

22.9.4. AIO9 Single Ended Amplifier Mode

Set **SOC.AIO9CFG.MODE9** = 01b to use AIO9 as input to a programmable gain amplifier.

22.9.4.1. AIO9 Amplifier Gain

Use **SOC.AIO9CFG.GAIN9** to set to gain between 1x to 48x or bidirectional amplifier bypass mode.

22.9.4.2. AIO9 Analog MUX

Use **SOC.AIO9CFG.MUX9** to switch the output of the amplifier to analog channel AB1 to AB7 on the analog bus ABUS.

22.9.5. AIO9 Comparator Mode

Set **SOC.AIO9CFG.MODE9** = 10b to use AIO9 in comparator mode.

22.9.5.1. AIO9 Comparator Hysteresis

Use **SOC.SMCFG.AIO9HYS** to enable AIO9 comparator hysteresis.

22.9.5.2. AIO9 Comparator Reference

Use **SOC.AIO9CFG.OPT9** to set the compare value of the comparator to AB1, AB2, AB3 or VTHREF, setable with **SOC.SYSSTAT.VTHREF**.

22.9.5.3. AIO9 Comparator Polarity

Use **SOC.AIO9CFG.POL9** to set the output polarity of the comparator.

22.9.5.4. AIO9 Comparator Output

The comparator output can be observed with **SOC.AIOIN1.AIO9DIN**.

22.9.6. AIO9 Special Mode

Set **SOC.AIO7CFG.MODE7** = 11b to use AIO9 in special mode. In special mode the AIO9 comparator is enabled.

22.9.6.1. AIO9 Comparator Hysteresis

Use **SOC.SMCFG.AIO9HYS** to enable AIO9 comparator hysteresis.

22.9.6.2. AIO9 Comparator Reference

Use **SOC.AIO7CFG.OPT7** to set the compare value of the comparator to AB1, AB2 or AB3.

22.9.6.3. AIO9 Comparator Reference Star Point

Use **SOC.AIO9CFG.MODE9[0]** =1b to connect AIO7, AIO8 and AIO9 to AB1 with a 100kOhm resistor to create a star point reference for the comparator.

With **SOC.AIO9CFG.MODE9[0]** =0b, the AB1 reference could for example come from AIO6 in amplifier mode **SOC.AIO6CFG.MODE6** = 01b and **SOC.AIO6CFG.GAIN6** = 000b direct mode and **SOC.AIO6CFG.MUX6** = 1b.

22.9.6.4. AIO9 Voltage Reading

Use **SOC.AIO9CFG.MODE9[1]** =1b to MUX AIO9 to AB9 with 40% attenuation, so ADC can read out AIO9 voltage.

22.9.6.5. AIO9 Comparator Output

Use **SOC.AIO9CFG.OPT9** to select AIO7, AIO8 or AIO9 comparator output signal for POS.

22.9.6.6. AIO9 POS S/H Bypass

Set **SOC.AIO8CFG.OPT8[1]** =0b bypass the POS S/H.

Set **SOC.AIO8CFG.OPT8[1]** =1b use POS S/H for use with EMUX.


22.9.6.7. AIO9 nIRQ2/POS Selector

Use **SOC.AIO8CFG.OPT8[0]** to select POS or nIRQ2 output.

22.10. EMUX and ADMUX

22.10.1. Block Diagram

Figure 22-9. EMUX



22.10.2. EMUX

The EMUX is a dedicated high speed low latency serial interface to control the ADMUX, the AIO7, AIO8, AIO9 POS S/H and the DAOxy S/H using the ASC0, ASC1 sequencer.

22.10.2.1. EMUX Enable

Set **SOC.ADCSCANCFG.SCANEEN** = 01b enable the EMUX control of the **SOC.ADMUX** and the DAOxy S/H.

22.10.2.2. EMUXD Packet Structure

The EMUXD packet is transmitted MSB first.

Register 22-26. SOC.AIOIN0 (AIO Digital Input, SOC 0x34)

| BIT | NAME | DESCRIPTION |
|-----|------|---|
| 7:6 | C | Header, write to 01b |
| 5 | CMP | Comparator toggle 1b: Hold POS value 0b: Sample POS value |
| 4 | DASH | DAxy SH toggle 1b: Hold DAOxy value 0b: Sample DAOxy |

| BIT | NAME | DESCRIPTION |
|-----|------------|---|
| 3:0 | MUX | AD MUX Channel Selector 1111b: VREF / 2 1110b: AB12 1101b: AB11 1100b: AB10 1011b: AB9 1010b: AB8 1001b: AB7 1000b: AB6 0111b: AB5 0110b: AB4 0101b: AB3 0100b: AB2 0011b: AB1 0010b: DAO54 0001b: DAO32 0000b: DAO10 |

22.10.2.3. EMUX Timing

The EMUXD packet is transmitted MSB first.


The header C1, C2 is fixed and need to be written to 01b.

The POS S/H is toggled based on the CMP bit in the EMUXD packet with the falling edge of the 3rd clock cycle.

The DAOxy S/H is toggled based on the DASH bit in the EMUXD packet with the falling edge of the 4th clock cycle.

The ADMUX is switched with the falling edge of the 8th clock based on the data of bits 3:1 of the EMUXD packet.

Figure 22-10. EMUX Timing



22.10.3. ADMUX

The ADMUX is a dedicated analog MUX in the configurable analog front-end.

22.10.3.1. ADMUX Control

Use **SOC.ADMUX** to set the channel for the ADMUX.

When EMUX is enabled, the SOC.ADMUX can be controlled directly from the ASC0, ASC1 sequencers using EMUXD.

22.10.3.2. ADMUX Buffer

Use **SOC.ADCSCANCFG.ADCBUFEN** to enable the ADMUX buffer.

22.10.3.3. ADMUX

Use **SOC.AIO6CFG.ADMUX** to route the output of the ADMUX to AB7 for debug purposes.

23. APPLICATION SPECIFIC POWER DRIVER

23.1. Register

23.1.1. Register Map

Table 23-1. Application Specific Power Driver Register Map

| SOC ADDRESS | NAME | DESCRIPTION | RESET VALUE |
|--|--------------------|------------------------|-------------|
| Application Specific Power Driver | | | |
| 0x60 | Reserved | Reserved | 0x00 |
| 0x61 | SOC.PRCTL | PR1, PR2 Control | 0x00 |
| 0x62 | Reserved | Reserved | 0x00 |
| 0x63 | Reserved | Reserved | 0x00 |
| 0x64 | SOC.OMOUT | OM0/2/4 output control | 0x00 |
| 0x65 | Reserved | Reserved | 0x00 |
| 0x66 | SOC.DRVCTL | Gate Driver Control | 0x00 |
| 0x67 | SOC.PROTCTL | PROT Control | 0x00 |
| 0x68 | Reserved | Reserved | 0x00 |
| 0x69 – 0x7F | Reserved | Reserved | N/A |

23.1.2. SOC.PRCTL

Register 23-1. SOC.PRCTL (PR1, PR2 Control, SOC 0x61)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|--|
| 7 | HSPR1EN | R/W | 0x0 | High side PR1 protection enable 1b: PR1 enabled 0b: PR1 disabled |
| 6 | HSPR2EN | R/W | 0x0 | High side PR2 protection enable 1b: PR2 enabled 0b: PR2 disabled |
| 5:0 | Reserved | R/W | 0x0 | Reserved, write to 0x0 |

23.1.3. SOC.OMOUT

Register 23-2. SOC.OMOUT (OM0/2/4 Output, SOC 0x64)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|------------------|--------|-------|---|
| 7:6 | Reserved | R/W | 0x0 | Reserved, write to 0x0 |
| 5 | PROTDB7EN | R/W | 0x0 | DB7 signal enable for PROT 1b: enable DB7 0b: disable DB7 |
| 4 | OM4DOUT | R/W | 0x0 | OM4 output in open drain mode 1b: High-Z 0b: VSS |
| 3 | PROTDB6EN | R/W | 0x0 | DB6 signal enable for PROT 1b: enable DB6 0b: disable DB6 |
| 2 | OM2DOUT | R/W | 0x0 | OM2 output in open drain mode 1b: High-Z 0b: VSS |
| 1 | PROTDB5EN | R/W | 0x0 | DB5 signal enable for PROT 1b: enable DB5 0b: disable DB5 |
| 0 | OM0DOUT | R/W | 0x0 | OM0 output in open drain mode 1b: High-Z 0b: VSS |

23.1.4. SOC.DRVCTL

Register 23-3. SOC.DRVCTL (Application Specific Power Driver Control, SOC 0x66)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|---|
| 7:1 | Reserved | R/W | 0x0 | Reserved, write to 0x0 |
| 0 | DRVEN | R/W | 0x0 | Application Specific Power Driver Enable 1b: enabled 0b: disabled |

23.1.5. SOC.PROTCTL


Register 23-4. SOC.PROTCTL (PROT Control, SOC 0x67)

| BIT | NAME | ACCESS | RESET | DESCRIPTION |
|-----|-----------------|--------|-------|---|
| 7:1 | Reserved | R/W | 0x0 | Reserved, write to 0x0 |
| 0 | PROTSEL | R/W | 0x0 | Select input signal for PROT 1b: nIRQ2, DB5, DB6 or DB7 0b: PR1 |

23.2. Details of Operation

23.2.1. Block Diagram

Figure 23-1. Application Specific Power Driver



23.2.2. Configuration

Following blocks need to be configured for correct use of the Application specific power driver

- Clock Control System (CCS)
- Nested Vectored Interrupt Controller (NVIC)
- IO Controller
- SOC Bridge

23.2.3. Application Specific Power Driver

The application specific power driver registers are accessible through the SOC Bridge. The OMx open drain drivers are controlled by SOC registers. The ENHS0 and ENHS1 protection outputs can be configured to toggle based on protection from the configurable analog front end.


23.2.3.1. Application Specific Power Driver Enable

Use **SOC.DRVCTL.DRVEN** to enable the application specific power driver.

23.3. OM0

23.3.1. Block Diagram

Figure 23-2. OM0



23.3.2. OM0

OM0 is a medium voltage open drain output.


23.3.2.1. OM0 Open Drain Output

Use **SOC.OMOUT.OM0DOUT** to toggle output state of OM0.

23.4. OM2

23.4.1. Block Diagram

Figure 23-3. OM2



23.4.2. OM2

OM2 is a medium voltage open drain output.


23.4.2.1. OM2 Open Drain Output

Use **SOC.OMOUT.OMD2OUT** to toggle output state of OM2.

23.5. OM4

23.5.1. Block Diagram

Figure 23-4. OM4



23.5.2. OM4

OM4 is a medium voltage open drain output.


23.5.2.1. OM4 Open Drain Output

Use **SOC.OMOUT.OM4DOUT** to toggle output state of OM4.

23.6. ENHS1 Protection

23.6.1. Block Diagram

Figure 23-5. ENHS1 Protection



23.6.2. ENHS1 Protection

The PR1, nIRQ2, DB5, DB6, DB7 signals from the AIOx inputs in the configurable analog front-end can be used to drive the ENHS1 pin to signal external components.

23.6.2.1. Protection Enable

Use **SOC.DRV1CFG.HSPR1EN** to enable protection signal ENHS1 for ENHS1 output.

23.6.2.2. Input Signal Selection


Use **SOC.PROTCTL.PROTSEL** to select between PR1 or PROT signal as input to ENHS1 protection signal.

Use **SOC.OHIOMOUT.PROTDB5EN**, **SOC.OHIOMOUT.PROTDB6EN**, and **SOC.OHIOMOUT.PROTDB7EN** to select input signal to PROT.

23.7. ENHS2 Protection

23.7.1. Block Diagram

Figure 23-6. ENHS2 Protection



23.7.2. ENHS2 Protection

The PR2 signal from the AIoX inputs in the configurable analog front-end can be used to toggle ENHS2 output.

23.7.2.1. Protection Enable

Use **SOC.DRV1CFG.HSPR2EN** to enable protection signal PR2 to ENHS2 output.

24. ARM CORTEX-M0 REFERENCE

24.1. Introduction

24.1.1. Overview


This chapter is taken from the ARM Cortex-M0 User Guide with minimal modifications made to account for the specific Cortex-M0 implementation.

24.1.2. About the Cortex-M0 processor and core peripherals

The Cortex™-M0 processor is an entry-level 32-bit ARM Cortex processor designed for a broad range of embedded applications. It offers significant benefits to developers, including:

- a simple architecture that is easy to learn and program
- ultra-low power, energy efficient operation
- excellent code density
- deterministic, high-performance interrupt handling
- upward compatibility with Cortex-M processor family.

Figure 24-1. Cortex-M0 implementation



The Cortex-M0 processor is built on a highly area and power optimized 32-bit processor core, with a 3-stage pipeline von Neumann architecture. The processor delivers exceptional energy efficiency through a small but powerful instruction set and extensively optimized design, providing high-end processing hardware including a single-cycle multiplier.

The Cortex-M0 processor implements the ARMv6-M architecture, which is based on the 16-bit Thumb® instruction set and includes Thumb-2 technology. This provides the exceptional performance expected of a modern 32-bit architecture, with a higher code density than other 8-bit and 16-bit microcontrollers.

The Cortex-M0 processor closely integrates a configurable Nested Vectored Interrupt Controller (NVIC), to deliver industry-leading interrupt performance. The NVIC:

- includes a non-maskable interrupt (NMI)
- provides zero jitter interrupt option
- provides four interrupt priority levels.

The tight integration of the processor core and NVIC provides fast execution of interrupt service routines (ISRs), dramatically reducing the interrupt latency. This is achieved through the hardware stacking of registers, and the ability to abandon and restart load-multiple and store-multiple operations. Interrupt handlers do not require any assembler wrapper code, removing any code overhead from the ISRs. Tail-chaining optimization also significantly reduces the overhead when switching from one ISR to another.

To optimize low-power designs, the NVIC integrates with the sleep modes, that include a deep sleep function that enables the entire device to be rapidly powered down.

24.1.2.1. System-level interface

The Cortex-M0 processor provides a single system-level interface using AMBA® technology to provide high speed, low latency memory accesses.

24.1.2.2. Integrated configurable debug

The Cortex-M0 processor implements a complete hardware debug solution, with extensive hardware breakpoint and watchpoint options. This provides high system visibility of the processor, memory and peripherals through a Serial Wire Debug (SWD) port that is ideal for microcontrollers and other small package devices. The device supports 4 hardware breakpoints.

24.1.2.3. Cortex-M0 processor features summary

- high code density with 32-bit performance
- tools and binary upwards compatible with Cortex-M processor family
- integrated ultra low-power sleep modes
- efficient code execution permits slower processor clock or increases sleep mode time
- single-cycle 32-bit hardware multiplier
- zero jitter interrupt handling
- extensive debug capabilities.

24.1.2.4. Cortex-M0 core peripherals

These are:

24.1.2.4.1. NVIC

The NVIC is an embedded interrupt controller that supports low latency interrupt processing.

24.1.2.4.2. System Control Block

The System Control Block (SCB) is the programmers model interface to the processor. It provides system implementation information and system control, including configuration, control, and reporting of system exceptions.

24.1.2.4.3. System timer

The system timer, SysTick, is a 24-bit count-down timer. Use this as a Real Time Operating System (RTOS) tick timer or as a simple counter.

24.2. The Cortex-M0 Processor

24.2.1. Programmers Model

This section describes the Cortex-M0 programmers model. In addition to the individual core register descriptions, it contains information about the processor modes and stacks.

24.2.1.1. Processor modes

The processor modes are:

Thread mode

Used to execute application software. The processor enters Thread mode when it comes out of reset.

Handler mode

Used to handle exceptions. The processor returns to Thread mode when it has finished all exception processing.

24.2.1.2. Stacks

The processor uses a full descending stack. This means the stack pointer indicates the last stacked item on the stack memory. When the processor pushes a new item onto the stack, it decrements the stack pointer and then writes the item to the new memory location. The processor implements two stacks, the main stack and the process stack, with independent copies of the stack pointer, see Stack Pointer in chapter 24.2.1.3.2 on page 281.

In Thread mode, the CONTROL register controls whether the processor uses the main stack or the process stack, see CONTROL register in chapter 24.2.1.3.12 on page 284. In Handler mode, the processor always uses the main stack. The options for processor operations are:

Table 24-1. Summary of processor mode and stack use options

| PROCESSOR MODE | USED TO EXECUTE | STACK USED |
|----------------|--------------------|------------------------------|
| Thread | Applications | Main stack or process stack* |
| Handler | Exception handlers | Main stack |

* See CONTROL Register in chapter 24.2.1.3.12 on page 284

24.2.1.3. Core Registers

Figure 24-2. Core Registers




Table 24-2. Core register set summary

| NAME | TYPE* | RESET VALUE | DESCRIPTION |
|----------|-------|-----------------|---|
| R0 – R12 | RW | Unknown | General Purpose Register, see chapter 24.2.1.3.1 on page 280 |
| MSP | RW | See description | Stack pointer, see chapter 24.2.1.3.2 on page 281 |
| PSP | RW | Unknown | Stack pointer, see chapter 24.2.1.3.2 on page 281 |
| LR | RW | Unknown | Link Register, see chapter 24.2.1.3.3 on page 281 |
| PC | RW | See description | Program Counter, see chapter 28224.2.1.3.4 on page 281 |
| PSR | RW | Unknown ** | Program Status Register, see chapter 24.2.1.3.5 on page 281 |
| APSR | RW | Unknown | Application Program status register, see chapter 24.2.1.3.6 on page 282 |
| IPSR | RW | 0x0000 0000 | Interrupt Program status register, see chapter 24.2.1.3.7 on page 282 |
| ESPR | RW | Unknown ** | Execution Program status register, see chapter 24.2.1.3.8 on page 283 |
| PRIMASK | RW | 0x0000 0000 | Priority Mask Register, see chapter 24.2.1.3.11 on page 284 |
| CONTROL | RW | 0x0000 0000 | Control Register, see chapter 24.2.1.3.12 on page 284 |

*. Describes access type during program execution in thread mode and Handler mode. Debug access can differ.

**. Bit[24] is the T-bit and is loaded from bit[0] of the reset vector.

24.2.1.3.1. General-purpose registers

R0-R12 are 32-bit general-purpose registers for data operations.

24.2.1.3.2. Stack Pointer

The Stack Pointer (SP) is register R13. In Thread mode, bit[1] of the CONTROL register indicates the stack pointer to use:

- 0 = Main Stack Pointer (MSP). This is the reset value.
- 1 = Process Stack Pointer (PSP).

On reset, the processor loads the MSP with the value from address 0x0000 0000

24.2.1.3.3. Link Register

The Link Register (LR) is register R14. It stores the return information for subroutines, function calls, and exceptions. On reset, the LR value is Unknown.

24.2.1.3.4. Program Counter

The Program Counter (PC) is register R15. It contains the current program address. On reset, the processor loads the PC with the value of the reset vector, which is at address 0x0000 0004. Bit[0] of the value is loaded into the EPSR T-bit at reset and must be 1.


24.2.1.3.5. Program Status Register

The Program Status Register (PSR) combines:

- Application Program Status Register (APSR)
- Interrupt Program Status Register (IPSR)
- Execution Program Status Register (EPSR).

These registers are mutually exclusive bitfields in the 32-bit PSR. The PSR bit assignments are:

Figure 24-3. PSR



Access these registers individually or as a combination of any two or all three registers, using the register name as an argument to the `MSR` or `MRS` instructions. For example:

- read all of the registers using PSR with the `MRS` instruction

- write to the APSR using APSR with the `MSR` instruction.

The PSR combinations and attributes are:

Table 24-3. Core register set summary

| REGISTER | TYPE* | COMBINATION |
|----------|----------|----------------------|
| PSR | RW *, ** | APSR, EPSR, and IPSR |
| IEPSR | RO | EPSR and IPSR |
| IAPSR | RW,* | APSR and IPSR |
| EAPST | RW,** | APSR and EPSR |

* The processor ignores writes to the IPSR bits.

** Reads of the EPSR bits return zero, and the processor ignores writes to these bits

See the instruction descriptions `MRS` in chapter 24.3.7.6 on page 333 and `MSR` in chapter 24.3.7.7 on page 334 for more information about how to access the program status registers.

24.2.1.3.6. Application Program Status Register

The APSR contains the current state of the condition flags, from previous instruction executions. See the register summary in Table 24-2. Core register set summary on page 280 for its attributes. The bit assignments are:

Table 24-4. APSR bit assignments

| BIT | NAME | FUNCTION |
|------|----------|----------------------|
| 31 | N | Negative Flag |
| 30 | Z | Zero Flag |
| 29 | C | Carry or Borrow Flag |
| 28 | V | Overflow Flag |
| 27:0 | Reserved | Reserved |

See The condition flags in chapter 24.3.3.6.1 on page 307 for more information about the APSR negative, zero, carry or borrow, and overflow flags.

24.2.1.3.7. Interrupt Program Status Register

The IPSR contains the exception number of the current Interrupt Service Routine (ISR). See the register summary in Table 24-2. Core register set summary on page 280 for its attributes. The bit assignments are:

Table 24-5. IPSR bit assignments

| BIT | NAME | FUNCTION |
|------|----------|----------|
| 31:6 | Reserved | Reserved |

| BIT | NAME | FUNCTION |
|-----|------------------|---|
| 5:0 | Exception Number | This is the number of the current exception: 63-48: Reserved 47: IRQ31 . . . 16: IRQ0 15: SysTick 14: PendSV 13-12: Reserved 11: SVCALL 10-4: Reserved 3: HardFault 2: NMI 1: Reserved 0: Thread mode see Exception types in chapter 24.2.3.2 on page 291 |

24.2.1.3.8. Execution Program Status Register

The EPSR contains the Thumb state bit.

See the register summary in Table 24-2. Core register set summary on page 280 for ESPR attributes. The bit assignments are:

Table 24-6. EPSR bit assignments

| BIT | NAME | FUNCTION |
|-------|----------|-----------------|
| 31:25 | Reserved | Reserved |
| 24 | T | Thumb state bit |
| 23:0 | Reserved | Reserved |

Attempts by application software to read the EPSR directly using the MRS instruction always return zero. Attempts to write the EPSR using the MSR instruction are ignored. Fault handlers can examine the EPSR value in the stacked PSR to determine the cause of the fault. See Exception entry and return in chapter 24.2.3.6 on page 295. The following can clear the T bit to 0:

- instructions BLX, BX and POP { PC }
- restoration from the stacked xPSR value on an exception return
- bit[0] of the vector value on an exception entry.

Attempting to execute instructions when the T bit is 0 results in a HardFault or lockup.

See Lockup in chapter 24.2.4.1 on page 297 for more information.

24.2.1.3.9. Interruptible-restartable instructions

The interruptible-restartable instructions are LDM and STM, and the multiply instruction. When an interrupt occurs during the execution of one of these instructions, the processor abandons execution of the instruction.

After servicing the interrupt, the processor restarts execution of the instruction from the beginning.

24.2.1.3.10. Exception mask register

The exception mask register disables the handling of exceptions by the processor. Disable exceptions where they might impact on timing critical tasks or code sequences requiring atomicity.

To disable or re-enable exceptions, use the `MSR` and `MRS` instructions, or the `CPS` instruction, to change the value of PRIMASK. See `MRS` in chapter 24.3.7.6 on page 333, `MSR` in chapter 24.3.7.7 on page 334, and `CPS` in chapter 24.3.7.2 on page 330 for more information.

24.2.1.3.11. Priority Mask Register

The PRIMASK register prevents activation of all exceptions with configurable priority.

See the register summary in Table 24-2. Core register set summary on page 280 for its attributes. The bit assignments are:

Figure 24-4. PRIMASK




Table 24-7. PRIMASK register bit assignments

| BIT | NAME | FUNCTION |
|------|----------|---|
| 31:1 | Reserved | Reserved |
| 0 | PRIMASK | 1: prevents activation of all exceptions with configurable priority 0: no effect |

24.2.1.3.12. Control Register

The CONTROL register controls the stack used when the processor is in Thread mode.

See the register summary in Table 24-2. Core register set summary on page 280 for its attributes. The bit assignments are:

Figure 1-6. CONTROL




Table 24-8. CONTROL register bit assignments

| BIT | NAME | FUNCTION |
|------|-----------------------------|--|
| 31:1 | Reserved | Reserved |
| 0 | Active Stack Pointer | Defines the current stack: 1: MSP is the current stack pointer 0: PSP is the current stack pointer In Handler mode this bit reads as zero and ignores writes. |
| 0 | Reserved | Reserved |

Handler mode always uses the MSP, so the processor ignores explicit writes to the active stack pointer bit of the CONTROL register when in Handler mode. The exception entry and return mechanisms update the CONTROL register.

In an OS environment, it is recommended that threads running in Thread mode use the process stack and the kernel and exception handlers use the main stack.

By default, Thread mode uses the MSP. To switch the stack pointer used in Thread mode to the PSP, use the MSR instruction to set the Active stack pointer bit to 1, see [MSR](#) in chapter 24.3.7.7 on page 334.

Note

When changing the stack pointer, software must use an ISB instruction immediately after the MSR instruction. This ensures that instructions after the ISB execute using the new stack pointer. See [ISB](#) in chapter 24.3.7.5 on page 332.

24.2.1.4. Exceptions and interrupts

The Cortex-M0 processor supports interrupts and system exceptions. The processor and the Nested Vectored Interrupt Controller (NVIC) prioritize and handle all exceptions. An interrupt or exception changes the normal flow of software control. The processor uses handler mode to handle all exceptions except for reset. See Exception entry in chapter 24.2.3.6.5 on page 296 and Exception return in chapter 24.2.3.6.6 on page 296 for more information.

The NVIC registers control interrupt handling. See Nested Vectored Interrupt Controller in chapter 24.4.2 on page 339 for more information.

24.2.1.5. Data Types

The processor:

- supports the following data types:
 - 32-bit words
 - 16-bit halfwords
 - 8-bit bytes
- manages all data memory accesses as little-endian. Instruction memory and Private Peripheral Bus (PPB) accesses are always little-endian. See Memory regions, types and attributes in chapter 24.2.2.1 on page 287 for more information.

24.2.1.6. The Cortex Microcontroller Software Interface Standard

ARM provides the Cortex Microcontroller Software Interface Standard (CMSIS) for programming Cortex-M0 microcontrollers. The CMSIS is an integrated part of the device driver library. For a Cortex-M0 microcontroller system, CMSIS defines:

- a common way to:
 - access peripheral registers
 - define exception vectors
- the names of:
 - the registers of the core peripherals
 - the core exception vectors
- a device-independent interface for RTOS kernels.

The CMSIS includes address definitions and data structures for the core peripherals in the Cortex-M0 processor. It also includes optional interfaces for middleware components comprising a TCP/IP stack and a Flash file system.

The CMSIS simplifies software development by enabling the reuse of template code, and the combination of CMSIS-compliant software components from various middleware vendors. Software vendors can expand the CMSIS to include their peripheral definitions and access functions for those peripherals.

This document includes the register names defined by the CMSIS, and gives short descriptions of the CMSIS functions that address the processor core and the core peripherals.

Note

This document uses the register short names defined by the CMSIS. In a few cases these differ from the architectural short names that might be used in other documents.

The following sections give more information about the CMSIS:

- Power management programming hints in chapter 24.2.5.5 on page 300
- Intrinsic functions in chapter 24.3.2 onpage 302
- Accessing the Cortex-M0 NVIC registers using CMSIS in chapter 24.4.2.1 on page 340
- NVIC programming hints in chapter 24.4.2.8.1 on page 344

24.2.2. Memory model

This section describes the processor memory map and the behavior of memory accesses. The processor has a fixed memory map that provides up to 4GB of addressable memory. The memory map is:

Figure 24-6. Memory Map

| | | |
|------------------------|-------|--|
| Device | 511MB | 0xFFFFFFFF |
| Private peripheral bus | 1MB | 0xE0100000 0xE00FFFFF 0xE0000000 0xDFFFFFFF |
| External device | 1.0GB | |
| External RAM | 1.0GB | 0xA0000000 0x9FFFFFFF |
| Peripheral | 0.5GB | 0x60000000 0x5FFFFFFF |
| SRAM | 0.5GB | 0x40000000 0x3FFFFFFF |
| Code | 0.5GB | 0x20000000 0x1FFFFFFF |
| | | 0x00000000 |

The processor reserves regions of the Private peripheral bus (PPB) address range for core peripheral registers, see About the Cortex-M0 processor and core peripherals in chapter 24.1.2 on page 277

24.2.2.1. Memory regions, types and attributes

The memory map is split into regions. Each region has a defined memory type, and some regions have additional memory attributes. The memory type and attributes determine the behavior of accesses to the region.

The memory types are:

24.2.2.1.1. Normal

The processor can re-order transactions for efficiency, or perform speculative reads.

24.2.2.1.2. Device

The processor preserves transaction order relative to other transactions to Device or Strongly-ordered memory.

24.2.2.1.3. Strongly-ordered

The processor preserves transaction order relative to all other transactions.

The different ordering requirements for Device and Strongly-ordered memory mean that the memory system can buffer a write to Device memory, but must not buffer a write to Strongly-ordered memory.

The additional memory attributes include.

24.2.2.1.4. Execute Never (XN)

Means the processor prevents instruction accesses. A HardFault exception is generated on executing an instruction fetched from an XN region of memory.

24.2.2. Memory system ordering of memory accesses

For most memory accesses caused by explicit memory access instructions, the memory system does not guarantee that the order in which the accesses complete matches the program order of the instructions, providing any re-ordering does not affect the behavior of the instruction sequence. Normally, if correct program execution depends on two memory accesses completing in program order, software must insert a memory barrier instruction between the memory access instructions, see Software ordering of memory accesses in chapter 24.2.2.4 on page 289.

However, the memory system does guarantee some ordering of accesses to Device and Strongly-ordered memory. For two memory access instructions A1 and A2, if A1 occurs before A2 in program order, the ordering of the memory accesses caused by two instructions is:

Figure 24-7. Memory Ordering Restrictions

| A1 | A2 | Normal access | Device access | | Strongly-ordered access |
|------------------------------|----|---------------|---------------|-----------|-------------------------|
| | | | Non-shareable | Shareable | |
| Normal access | - | - | - | - | - |
| Device access, non-shareable | - | < | - | - | < |
| Device access, shareable | - | - | < | < | < |
| Strongly-ordered access | - | < | < | < | < |

Where:

- Means that the memory system does not guarantee the ordering of the accesses.

< Means that accesses are observed in program order, that is, A1 is always observed before A2.

24.2.2.3. Behavior of memory accesses

The behavior of accesses to each region in the memory map is:

Table 24-9. Memory Access Behavior

| ADDRESS RANGE | MEMORY REGION | MEMORY TYPE | XN* | DESCRIPTION |
|---------------------------|------------------------|------------------|-----|---|
| 0xFFFF FFFF – 0xE010 0000 | Device | Device | XN | Reserved |
| 0xE00F FFFF – 0xE000 0000 | Private Peripheral Bus | Strongly-ordered | XN | This region includes the NVIC, System timer, and System Control Block. Only word accesses can be used in this region. |
| 0xDFFF FFFF – 0xA000 0000 | External Device | Device | XN | External device memory |
| 0x9FFF FFFF – 0x6000 0000 | External RAM | Normal | - | Executable region for data |
| 0x5FFF FFFF – 0x4000 0000 | Peripheral | Device | XN | External device memory |
| 0x3FFF FFFF – 0x2000 0000 | SRAM | Normal | - | Executable region for data. You can also put code here |
| 0x1FFF FFFF – 0x0000 0000 | Code | Normal | - | Executable region for program code. You can also put data here |

* See Memory regions, types and attributes in chapter 24.2.2.1 on page 287 for more information.

The Code, SRAM, and external RAM regions can hold programs.

24.2.2.4. Software ordering of memory accesses

The order of instructions in the program flow does not always guarantee the order of the corresponding memory transactions. This is because:

- the processor can reorder some memory accesses to improve efficiency, providing this does not affect the behavior of the instruction sequence
- memory or devices in the memory map might have different wait states
- some memory accesses are buffered or speculative.

Memory system ordering of memory accesses in chapter 24.2.2.2 on page 288 describes the cases where the memory system guarantees the order of memory accesses. Otherwise, if the order of memory accesses is critical, software must include memory barrier instructions to force that ordering. The processor provides the following memory barrier instructions:

24.2.2.4.1. DMB

The Data Memory Barrier (DMB) instruction ensures that outstanding memory transactions complete before subsequent memory transactions. See [DMB](#) in chapter 24.3.7.3 on page 331.

24.2.2.4.2. DSB

The Data Synchronization Barrier (DSB) instruction ensures that outstanding memory transactions complete

before subsequent instructions execute. See `DSB` in chapter 24.3.7.4 on page 332.

24.2.2.4.3. ISB

The Instruction Synchronization Barrier (`ISB`) ensures that the effect of all completed memory transactions is recognizable by subsequent instructions. See `ISB` in chapter 24.3.7.5 on page 332.

The following are examples of using memory barrier instructions:

24.2.2.4.4. Vector table

If the program changes an entry in the vector table, and then enables the corresponding exception, use a `DMB` instruction between the operations. This ensures that if the exception is taken immediately after being enabled the processor uses the new exception vector.

24.2.2.4.5. Self-modifying code

If a program contains self-modifying code, use an `ISB` instruction immediately after the code modification in the program. This ensures subsequent instruction execution uses the updated program.

24.2.2.4.6. Memory map switching

If the system contains a memory map switching mechanism, use a `DSB` instruction after switching the memory map. This ensures subsequent instruction execution uses the updated memory map.

Memory accesses to Strongly-ordered memory, such as the System Control Block, do not require the use of `DMB` instructions.

24.2.2.5. Memory endianness

The processor views memory as a linear collection of bytes numbered in ascending order from zero. For example, bytes 0-3 hold the first stored word, and bytes 4-7 hold the second stored word. Little-endian format in chapter 24.2.2.5.1 on page 290 describes how words of data are stored in memory.

24.2.2.5.1. Little-endian format

In little-endian format, the processor stores the least significant byte (lsbyte) of a word at the lowest-numbered byte, and the most significant byte (msbyte) at the highest-numbered byte. For example:




Figure 24-8. Little Endian Format

24.2.3. Exception model

This section describes the exception model.

24.2.3.1. Exception states

Each exception is in one of the following states:

24.2.3.1.1. Inactive

The exception is not active and not pending.

24.2.3.1.2. Pending

The exception is waiting to be serviced by the processor.

An interrupt request from a peripheral or from software can change the state of the corresponding interrupt to pending.

24.2.3.1.3. Active

An exception that is being serviced by the processor but has not completed.

Note

An exception handler can interrupt the execution of another exception handler. In this case both exceptions are in the active state.

24.2.3.1.4. Active and pending

The exception is being serviced by the processor and there is a pending exception from the same source.

24.2.3.2. Exception types

The exception types are:

24.2.3.2.1. Reset

Reset is invoked on power up or a warm reset. The exception model treats reset as a special form of exception. When reset is asserted, the operation of the processor stops, potentially at any point in an instruction. When reset is deasserted, execution restarts from the address provided by the reset entry in the vector table. Execution restarts in Thread mode.

24.2.3.2.2. NMI

A NonMaskable Interrupt (NMI) can be signaled by a peripheral or triggered by software. This is the highest priority exception other than reset. It is permanently enabled and has a fixed priority of -2. NMIs cannot be:

- masked or prevented from activation by any other exception
- preempted by any exception other than Reset.

24.2.3.2.3. HardFault

A HardFault is an exception that occurs because of an error during normal or exception processing. HardFaults have a fixed priority of -1, meaning they have higher priority than any exception with configurable priority.

24.2.3.2.4. SVCALL

A supervisor call (SVC) is an exception that is triggered by the SVC instruction. In an OS environment, applications can use SVC instructions to access OS kernel functions and device drivers.

24.2.3.2.5. PendSV

PendSV is an interrupt-driven request for system-level service. In an OS environment, use PendSV for context switching when no other exception is active.

24.2.3.2.6. SysTick

A SysTick exception is an exception the system timer generates when it reaches zero. Software can also generate a SysTick exception. In an OS environment, the processor can use this exception as system tick.

24.2.3.2.7. Interrupt (IRQ)

An interrupt, or IRQ, is an exception signaled by a peripheral, or generated by a software request. All interrupts are asynchronous to instruction execution. In the system, peripherals use interrupts to communicate with the processor.

Table 24-10. Properties of the different exception types

| EXCEPTION NUMBER* | IRQ NUMBER* | EXCEPTION TYPE | PRIORITY | VECTOR ADDRESS** | ACTIVATION |
|-------------------|-------------|----------------|-----------------|------------------|--------------|
| 1 | - | Reset | -3, the highest | 0x0000 0004 | Asynchronous |
| 2 | -14 | NMI | -2 | 0x0000 0008 | Asynchronous |
| 3 | -13 | HardFault | -1 | 0x0000 000C | Synchronous |
| 4-10 | - | Reserved | - | - | - |
| 11 | -5 | SVCALL | Configurable*** | 0x0000 002C | Synchronous |

| EXCEPTION NUMBER* | IRQ NUMBER* | EXCEPTION TYPE | PRIORITY | VECTOR ADDRESS** | ACTIVATION |
|-------------------|-------------|-----------------|-----------------|---------------------------|--------------|
| 12-13 | - | Reserved | - | - | - |
| 14 | -2 | PendSV | Configurable*** | 0x0000 0038 | Asynchronous |
| 15 | -1 | SysTick | Configurable*** | 0x0000 003C | Asynchronous |
| 16 and above | 0 and above | Interrupt (IRQ) | Configurable*** | 0x0000 0040 and above**** | Asynchronous |

*To simplify the software layer, the CMSIS only uses IRQ numbers and therefore uses negative values for exceptions other than interrupts. The IPSR returns the Exception number, see Interrupt Program Status Register in chapter 24.2.1.3.5 on page 281.

**See Vector table for more information.

***See Interrupt Priority Registers in chapter 24.4.2.6 on page 342.

****Increasing in steps of 4.

For an asynchronous exception, other than reset, the processor can execute additional instructions between when the exception is triggered and when the processor enters the exception handler.

Privileged software can disable the exceptions that Table 24-10. Properties of the different exception types on page 292 shows as having configurable priority, see Interrupt Clear-enable Register in chapter 24.4.2.3 on page 341.

For more information about HardFaults, see Fault handling in chapter 24.2.4 on page 297.

24.2.3.3. *Exception handlers*

The processor handles exceptions using:

24.2.3.3.1. **Interrupt Service Routines (ISRs)**

Interrupts IRQ0 to IRQ31 are the exceptions handled by ISRs.

24.2.3.3.2. **Fault handler**

HardFault is the only exception handled by the fault handler.

24.2.3.3.3. **System handlers**

NMI, PendSV, SVCall SysTick, and HardFault are all system exceptions handled by system handlers.

24.2.3.4. *Vector table*

The vector table contains the reset value of the stack pointer, and the start addresses, also called exception vectors, for all exception handlers. Figure 24-9. Vector Table on page 294 shows the order of the exception vectors in the vector table. The least-significant bit of each vector must be 1, indicating that the exception handler is written in Thumb code.

Figure 24-9. Vector Table

| Exception number | IRQ number | Vector | Offset |
|------------------|------------|--------------------|--------|
| 47 | 31 | IRQ31 | 0xBC |
| . | . | . | . |
| . | . | . | . |
| 18 | 2 | IRQ2 | 0x48 |
| 17 | 1 | IRQ1 | 0x44 |
| 16 | 0 | IRQ0 | 0x40 |
| 15 | -1 | SysTick Reserved | 0x3C |
| 14 | -2 | PendSV | 0x38 |
| 13 | | Reserved | |
| 12 | | | |
| 11 | -5 | SVCall | 0x2C |
| 10 | | | |
| 9 | | | |
| 8 | | | |
| 7 | | Reserved | |
| 6 | | | |
| 5 | | | |
| 4 | | | |
| 3 | -13 | HardFault | 0x10 |
| 2 | -14 | NMI | 0x0C |
| 1 | | Reset | 0x08 |
| | | Initial SP value | 0x04 |
| | | | 0x00 |

The vector table is fixed at address 0x0000 0000.

24.2.3.5. Exception priorities

As Table 24-10. Properties of the different exception types on page 292 shows, all exceptions have an associated priority, with:

- a lower priority value indicating a higher priority
- configurable priorities for all exceptions except Reset, HardFault, and NMI.

If software does not configure any priorities, then all exceptions with a configurable priority have a priority of 0. For information about configuring exception priorities see

- System Handler Priority Registers in chapter 24.4.3.7 on page 350
- Interrupt Priority Registers in chapter 24.4.2.6 on page 342.

Note

Configurable priority values are in the range 0-192, in steps of 64. The Reset, HardFault, and NMI exceptions, with fixed negative priority values, always have higher priority than any other exception.

Assigning a higher priority value to IRQ[0] and a lower priority value to IRQ[1] means that IRQ[1] has higher priority than IRQ[0]. If both IRQ[1] and IRQ[0] are asserted, IRQ[1] is processed before IRQ[0].

If multiple pending exceptions have the same priority, the pending exception with the lowest exception number takes precedence. For example, if both IRQ[0] and IRQ[1] are pending and have the same priority, then IRQ[0] is processed before IRQ[1].

When the processor is executing an exception handler, the exception handler is preempted if a higher priority exception occurs. If an exception occurs with the same priority as the exception being handled, the handler is not preempted, irrespective of the exception number. However, the status of the new interrupt changes to pending.

24.2.3.6. *Exception entry and return*

Descriptions of exception handling use the following terms:

24.2.3.6.1. Preemption

When the processor is executing an exception handler, an exception can preempt the exception handler if its priority is higher than the priority of the exception being handled.

When one exception preempts another, the exceptions are called nested exceptions. See Exception entry in chapter 24.2.3.6.5 on page 296 for more information.

24.2.3.6.2. Return

This occurs when the exception handler is completed, and:

- there is no pending exception with sufficient priority to be serviced
- the completed exception handler was not handling a late-arriving exception.

The processor pops the stack and restores the processor state to the state it had before the interrupt occurred. See Exception return in chapter 24.2.3.6.6 on page 296 for more information.

24.2.3.6.3. Tail-chaining

This mechanism speeds up exception servicing. On completion of an exception handler, if there is a pending exception that meets the requirements for exception entry, the stack pop is skipped and control transfers to the new exception handler.

24.2.3.6.4. Late-arriving

This mechanism speeds up preemption. If a higher priority exception occurs during state saving for a previous exception, the processor switches to handle the higher priority exception and initiates the vector fetch for that exception. State saving is not affected by late arrival because the state saved would be the same for both exceptions. On return from the exception handler of the late-arriving exception, the normal tail-chaining rules apply.

24.2.3.6.5. Exception entry

Exception entry occurs when there is a pending exception with sufficient priority and either:


- the processor is in Thread mode
- the new exception is of higher priority than the exception being handled, in which case the new exception preempts the exception being handled.

When one exception preempts another, the exceptions are nested.

Sufficient priority means the exception has greater priority than any limit set by the mask register, see Exception mask register in chapter 24.2.1.3.10 on page 284. An exception with less priority than this is pending but is not handled by the processor.

When the processor takes an exception, unless the exception is a tail-chained or a late-arriving exception, the processor pushes information onto the current stack. This operation is referred to as stacking and the structure of eight data words is referred as a stack frame. The stack frame contains the following information:

Figure 24-10. Exception Entry Stack Contents



Immediately after stacking, the stack pointer indicates the lowest address in the stack frame. The stack frame is aligned to a double-word address.

The stack frame includes the return address. This is the address of the next instruction in the interrupted program. This value is restored to the PC at exception return so that the interrupted program resumes.

The processor performs a vector fetch that reads the exception handler start address from the vector table. When stacking is complete, the processor starts executing the exception handler. At the same time, the processor writes an EXC_RETURN value to the LR. This indicates which stack pointer corresponds to the stack frame and what operation mode the processor was in before the entry occurred.

If no higher priority exception occurs during exception entry, the processor starts executing the exception handler and automatically changes the status of the corresponding pending interrupt to active.

If another higher priority exception occurs during exception entry, the processor starts executing the exception handler for this exception and does not change the pending status of the earlier exception. This is the late arrival case.

24.2.3.6.6. Exception return

Exception return occurs when the processor is in Handler mode and execution of one of the following instructions attempts to set the PC to an EXC_RETURN value:

- a POP instruction that loads the PC
- a BX instruction using any register.

The processor saves an EXC_RETURN value to the LR on exception entry. The exception mechanism relies on this value to detect when the processor has completed an exception handler. Bits[31:4] of an EXC_RETURN value are 0xFFFF FFFF. When the processor loads a value matching this pattern to the PC it detects that the operation is not a normal branch operation and, instead, that the exception is complete. Therefore, it starts the exception return sequence. Bits[3:0] of the EXC_RETURN value indicate the required return stack and processor mode, as Table 24-11. Execution return behavior on page 297 shows.

Table 24-11. Execution return behavior

| EXEC_RETURN | DESCRIPTION |
|------------------|---|
| 0xFFFF FFF1 | Return to Handler mode. Exception return gets state from the main stack. Execution uses MSP after return. |
| 0xFFFF FFF9 | Return to Thread mode. Exception return gets state from MSP. Execution uses MSP after return. |
| 0xFFFF FFFD | Return to Thread mode. Exception return gets state from PSP. Execution uses PSP after return. |
| All other values | Reserved |

24.2.4. Fault handling

Faults are a subset of exceptions, see Exception model in chapter 24.2.3 on page 291. All faults result in the HardFault exception being taken or cause lockup if they occur in the NMI or HardFault handler. The faults are:

- execution of an SVC instruction at a priority equal or higher than SVCall
- execution of a BKPT instruction without a debugger attached
- a system-generated bus error on a load or store
- execution of an instruction from an XN memory address
- execution of an instruction from a location for which the system generates a bus fault
- a system-generated bus error on a vector fetch
- execution of an Undefined instruction
- execution of an instruction when not in Thumb-State as a result of the T-bit being previously cleared to 0
- an attempted load or store to an unaligned address.

Note

Only Reset and NMI can preempt the fixed priority HardFault handler. A HardFault can preempt any exception other than Reset, NMI, or another hard fault.

24.2.4.1. Lockup

The processor enters a lockup state if a fault occurs when executing the NMI or HardFault handlers, or if the system generates a bus error when unstacking the PSR on an exception return using the MSP. When the

processor is in lockup state it does not execute any instructions. The processor remains in lockup state until one of the following occurs:

- it is reset
- a debugger halts it
- an NMI occurs and the current lockup is in the HardFault handler.
-

Note

If lockup state occurs in the NMI handler a subsequent NMI does not cause the processor to leave lockup state.

24.2.5. Power management

The Cortex-M0 processor sleep modes reduce power consumption:

- a sleep mode, that stops the processor clock
- a deep sleep mode, that stops the system clock and switches off the PLL and flash memory.

The SLEEPDEEP bit of the SCR selects which sleep mode is used, see System Control Register in chapter 24.4.3.5 on page 349.

This section describes the mechanisms for entering sleep mode, and the conditions for waking up from sleep mode.

24.2.5.1. *Entering sleep mode*

This section describes the mechanisms software can use to put the processor into sleep mode.

The system can generate spurious wakeup events, for example a debug operation wakes up the processor. Therefore software must be able to put the processor back into sleep mode after such an event. A program might have an idle loop to put the processor back in to sleep mode.

24.2.5.1.1. Wait for interrupt

The Wait For Interrupt instruction, WFI, causes immediate entry to sleep mode. When the processor executes a WFI instruction it stops executing instructions and enters sleep mode. See [WFI](#) in chapter 24.3.7.12 on page 338 for more information.

24.2.5.1.2. Wait for event

The Wait For Event instruction, WFE, causes entry to sleep mode conditional on the value of a one-bit event register. When the processor executes a WFE instruction, it checks the value of the event register:

0: The processor stops executing instructions and enters sleep mode

1: The processor sets the register to zero and continues executing instructions without entering sleep mode.

See [WFE](#) in chapter 24.3.7.11 on page 337 for more information.

If the event register is 1b, this indicates that the processor must not enter sleep mode on execution of a WFE instruction. Typically, this is because of the assertion of an external event, or because another processor in the system has executed a SEV instruction, see SEV in chapter 24.3.7.9 on page 335. Software cannot access this register directly.

24.2.5.1.3. Sleep-on-exit

If the SLEEPONEXIT bit of the SCR is set to 1, when the processor completes the execution of an exception handler and returns to Thread mode it immediately enters sleep mode. Use this mechanism in applications that only require the processor to run when an interrupt occurs.

24.2.5.2. Wakeup from sleep mode

The conditions for the processor to wakeup depend on the mechanism that caused it to enter sleep mode.

24.2.5.2.1. Wakeup from WFI or sleep-on-exit

Normally, the processor wakes up only when it detects an exception with sufficient priority to cause exception entry.

Some embedded systems might have to execute system restore tasks after the processor wakes up, and before it executes an interrupt handler. To achieve this set the PRIMASK bit to 1. If an interrupt arrives that is enabled and has a higher priority than current exception priority, the processor wakes up but does not execute the interrupt handler until the processor sets PRIMASK to zero. For more information about PRIMASK, see Exception mask register in chapter 24.2.1.3.10 on page 284.

24.2.5.2.2. Wakeup from WFE

The processor wakes up if:

- it detects an exception with sufficient priority to cause exception entry.
- it detects an external event signal, see The external event input in chapter 24.2.5.4 on page 300.
- in a multiprocessor system, another processor in the system executes a SEV instruction.

In addition, if the SEVONPEND bit in the SCR is set to 1, any new pending interrupt triggers an event and wakes up the processor, even if the interrupt is disabled or has insufficient priority to cause exception entry. For more information about the SCR see System Control Register in chapter 24.4.3.5 on page 349.

24.2.5.3. The Wakeup Interrupt Controller

The Wakeup Interrupt Controller (WIC) is a peripheral that can detect an interrupt and wake the processor from deep sleep mode. The WIC is enabled only when the DEEPSLEEP bit in the SCR is set to 1b, see System Control Register in chapter 24.4.3.5 on page 349.

The WIC is not programmable, and does not have any registers or user interface. It operates entirely from hardware signals.

When the WIC is enabled and the processor enters deep sleep mode, the power management unit in the system can power down most of the Cortex-M0 processor. This has the side effect of stopping the SysTick timer. When the WIC receives an interrupt, it takes a number of clock cycles to wakeup the processor and restore its state, before it can process the interrupt. This means interrupt latency is increased in deep sleep mode.

24.2.5.4. The external event input

The processor provides an external event input signal. This signal is not available on this device.

24.2.5.5. Power management programming hints

ISO/IEC C cannot directly generate the WFI, WFE, and SEV instructions. The CMSIS provides the following intrinsic functions for these instructions:

```
void __WFE(void) // Wait for Event  
void __WFI(void) // Wait for Interrupt  
void __SEV(void) // Send Event
```

24.3. The Cortex-M0 Instruction Set

This chapter is the reference material for the Cortex-M0 instruction set description in a User Guide. The following sections give general information:

- Instruction set summary in chapter 24.3.1 on page 300.
- Intrinsic functions in chapter 24.3.2 on page 302.
- About the instruction descriptions in chapter 24.3.3 on page 303.

Each of the following sections describes a functional group of Cortex-M0 instructions.

Together they describe all the instructions supported by the Cortex-M0 processor:

- Memory access instructions in chapter 24.3.4 on page 308.
- General data processing instructions in chapter 24.3.5 on page 315.
- Branch and control instructions in chapter 24.3.6 on page 327.
- Miscellaneous instructions in chapter 24.3.7 on page 329.

24.3.1. Instruction set summary

The processor implements a version of the Thumb instruction set. Table 24-12. Cortex-M0 instructions lists the supported instructions.

Note

In Table 24-12. Cortex-M0 instructions:

- angle brackets, <>, enclose alternative forms of the operand
- braces, {}, enclose optional operands and mnemonic parts
- the Operands column is not exhaustive.

For more information on the instructions and operands, see the instruction descriptions.

Table 24-12. Cortex-M0 instructions

| MNEMONIC | OPERANDS | BRIEF DESCRIPTION | FLAGS | CHAPTER, PAGE |
|----------|---------------------|--|------------|----------------------------|
| ADCS | {Rd,} Rn, Rm | Add with Carry | N, Z, C, V | Chapter 24.3.5.1, page 316 |
| ADD{S} | {Rd,} Rn, <Rm #imm> | Add | N, Z, C, V | Chapter 24.3.5.1, page 316 |
| ADR | Rd, label | PC-relative Address to Register | - | Chapter 24.3.4.1, page 309 |
| ANDS | {Rd,} Rn, Rm | Bitwise AND | N, Z | Chapter 24.3.5.1, page 316 |
| ASRS | {Rd,} Rn, <Rm #imm> | Arithmetic Shift Right | N, Z, C | Chapter 24.3.5.3, page 320 |
| B{cc} | label | Branch {conditionally} | - | Chapter 24.3.6.1, page 328 |
| BICS | {Rd,} Rn, Rm | Bit Clear | N, Z | Chapter 24.3.5.2, page 318 |
| BKPT | #imm | Breakpoint | - | Chapter 24.3.7.1, page 330 |
| BL | label | Branch with Link | - | Chapter 24.3.6.1, page 328 |
| BLX | Rm | Branch indirect with Link | - | Chapter 24.3.6.1, page 328 |
| BX | Rm | Branch indirect | - | Chapter 24.3.6.1, page 328 |
| CMN | Rn, RM | Compare Negative | N, Z, C, V | Chapter 24.3.5.4, page 321 |
| CMP | Rn, <Rm #imm> | Compare | N, Z, C, V | Chapter 24.3.5.4, page 321 |
| CPSID | i | Change Processor State, Disable Interrupts | - | Chapter 24.3.7.2, page 330 |
| CPSIE | i | Change Processor State, Enable Interrupts | - | Chapter 24.3.7.2, page 330 |
| DMB | - | Data Memory Barrier | - | Chapter 24.3.7.3, page 331 |
| DSB | - | Data Synchronization Barrier | - | Chapter 24.3.7.4, page 332 |
| EORS | {Rd,} Rn, Rm | Exclusive OR | N, Z | Chapter 24.3.5.2, page 318 |
| ISB | - | Instruction Synchronization Barrier | - | Chapter 24.3.7.5, page 332 |
| LDM | Rn{!}, reglist | Load Multiple Registers, increment after | - | Chapter 24.3.4.5, page 313 |
| LDR | Rt, label | Load Register from PC-relative Address | - | Chapter 24.3.4.4, page 312 |
| LDR | Rt, [Rn, <Rm #imm>] | Load Register with Word | - | Chapter 24.3.4, page 308 |
| LDRB | Rt, [Rn, <Rm #imm>] | Load Register with Byte | - | Chapter 24.3.4, page 308 |
| LDRH | Rt, [Rn, <Rm #imm>] | Load Register with Half-Word | - | Chapter 24.3.4, page 308 |
| LDRSB | Rt, [Rn, <Rm #imm>] | Load Register with signed Byte | - | Chapter 24.3.4, page 308 |
| LDRSH | Rt, [Rn, <Rm #imm>] | Load Register with signed Half-Word | - | Chapter 24.3.4, page 308 |
| LSLS | {Rd,} Rn, <Rs #imm> | Logical Shift Left | N, Z, C | Chapter 24.3.5.3, page 320 |
| LSRS | {Rd,} Rn, <Rs #imm> | Logical Shift Right | N, Z, C | Chapter 24.3.5.3, page 320 |
| MOV{S} | Rd, Rm | Move | N, Z | Chapter 24.3.5.5, page 322 |
| MRS | Rd, spec_reg | Move to General Register from Special Register | - | Chapter 24.3.7.6, page 333 |
| MSR | spec_reg, Rm | Move to special register from General Register | N, Z, C, V | Chapter 24.3.7.7, page 334 |

| MNEMONIC | OPERANDS | BRIEF DESCRIPTION | FLAGS | CHAPTER, PAGE |
|----------|---------------------|---|------------|-----------------------------|
| MULS | Rd, Rn, Rm | Multiply, 32-bit result | N, Z | Chapter 24.3.5.6, page 323 |
| MVNS | Rd, Rm | Bitwise NOT | N, Z | Chapter 24.3.5.5, page 322 |
| NOP | - | No Operation | - | Chapter 24.3.7.8, page 335 |
| ORRS | {Rd,} Rn, Rm | Logical OR | N, Z | Chapter 24.3.5.2, page 318 |
| POP | reglist | Pop registers from stack | - | Chapter 24.3.4.6, page 314 |
| PUSH | reglist | Push registers onto stack | - | Chapter 24.3.4.6, page 314 |
| REV | Rd, Rm | Byte-Reverse word | - | Chapter 24.3.5.7, page 324 |
| REV16 | Rd, Rm | Byte-Reverse packed halfwords | - | Chapter 24.3.5.7, page 324 |
| REVSH | Rd, Rm | Byte-Reverse signed halfword | - | Chapter 24.3.5.7, page 324 |
| RORS | {Rd,} Rn, Rs | Rotate Right | N, Z, C | Chapter 24.3.5.3, page 320 |
| RSBS | {Rd,} Rn, #0 | Reverse Subtract | N, Z, C, V | Chapter 24.3.5.1, page 316 |
| SBCS | {Rd,} Rn, Rm | Subtract with Carry | N, Z, C, V | Chapter 24.3.5.1, page 316 |
| SEV | - | Send Event | - | Chapter 24.3.7.9, page 335 |
| STM | Rn!, reglist | Store Multiple Registers, Increment After | - | Chapter 24.3.4.5, page 313 |
| STR | Rt, [Rn, <Rm #imm>] | Store Register as word | - | Chapter 24.3.4, page 308 |
| STRB | Rt, [Rn, <Rm #imm>] | Store Register as byte | - | Chapter 24.3.4, page 308 |
| STRH | Rt, [Rn, <Rm #imm>] | Store Register as half word | - | Chapter 24.3.4, page 308 |
| SUB {S} | Rt, Rn, <Rm #imm> | Subtract | N,Z,C,V | Chapter 24.3.5.1, page 316 |
| SVC | #imm | Supervisor Call | - | Chapter 24.3.7.10, page 336 |
| SXTB | Rd, Rm | Sign extend byte | - | Chapter 24.3.5.8, page 325 |
| SXTH | Rd, Rm | Sign extend half word | - | Chapter 24.3.5.8, page 325 |
| TST | Rd, Rm | Logical AND based test | N, Z | Chapter 24.3.5.9, page 326 |
| UXTB | Rd, Rm | Zero extend a byte | - | Chapter 24.3.5.8, page 325 |
| UXTH | Rd, Rm | Zero extend a halfword | - | Chapter 24.3.5.8, page 325 |
| WFE | - | Wait for Event | - | Chapter 24.3.7.11, page 337 |
| WFI | - | Wait for Interrupt | - | Chapter 24.3.7.12, page 338 |

24.3.2. Intrinsic Functions

ISO/IEC C code cannot directly access some Cortex-M0 instructions. This section describes intrinsic functions that can generate these instructions, provided by the CMSIS and that might be provided by a C compiler. If a C compiler does not support an appropriate intrinsic function, you might have to use inline assembler to access the relevant instruction.

The CMSIS provides the following intrinsic functions to generate instructions that ISO/IEC C code cannot directly access:

Table 24-13. CMSIS intrinsic functions to generate some Cortex-M0 instructions

| INSTRUCTION | CMSIS INTRINSIC FUNCTION |
|-------------|---------------------------|
| CPSIE i | void __enable_irq (void) |
| CPSID i | void __disable_irq (void) |
| ISB | void __ISB(void) |
| DSB | void __DSB(void) |

| INSTRUCTION | CMSIS INTRINSIC FUNCTION |
|-------------|------------------------------------|
| DMB | void __DMB(void) |
| NOP | void __NOP(void) |
| REV | uint32_t REV(uint32_t int value) |
| REV16 | uint32_t REV16(uint32_t int value) |
| REVSH | uint32_t REVSH(uint32_t int value) |
| SEV | void __SEV(void) |
| WFE | void __WFE(void) |
| WFI | void __WFI(void) |

The CMSIS also provides a number of functions for accessing the special registers using MRS and MSR instructions:

Table 24-14. CMSIS intrinsic functions to access special registers

| SPECIAL REGISTER | ACCESS | CMSIS FUNCTION |
|------------------|--------|--|
| PRIMASK | Read | uint32_t __get_PRIMASK (void) |
| | Write | void __set_PRIMASK (uint32_t value) |
| CONTROL | Read | uint32_t __get_CONTROL (void) |
| | Write | void __set_CONTROL (uint32_t value) |
| MSP | Read | uint32_t __get_MSP (void) |
| | Write | void __set_MSP (uint32_t TopOfMainStack) |
| PSP | Read | uint32_t __get_PSP (void) |
| | Write | void __set_PSP (uint32_t TopOfMainStack) |

24.3.3. About the Instruction Descriptions

The following sections give more information about using the instructions:

- Operands in chapter 24.3.3.1 on page 303
- Restrictions when using PC or SP in chapter 24.3.3.2 on page 304
- Shift Operations in chapter 24.3.3.3 on page 304
- Address alignment in chapter 24.3.3.4 on page 306
- PC-relative expressions in chapter 24.3.3.5 on page 306
- Conditional execution in chapter 24.3.3.6 on page 307

24.3.3.1. Operands

An instruction operand can be an ARM register, a constant, or another instruction-specific parameter. Instructions act on the operands and often store the result in a destination register. When there is a destination register in the instruction, it is usually specified before the other operands.

24.3.3.2. Restrictions when using PC or SP

Many instructions are unable to use, or have restrictions on whether you can use, the Program Counter (PC) or Stack Pointer (SP) for the operands or destination register. See instruction descriptions for more information.

Note

When you update the PC with a `BX`, `BLX`, or `POP` instruction, bit[0] of any address must be 1 for correct execution. This is because this bit indicates the destination instruction set, and the Cortex-M0 processor only supports Thumb instructions. When a `BL` or `BLX` instruction writes the value of bit[0] into the LR it is automatically assigned the value 1.

24.3.3.3. Shift Operations

Register shift operations move the bits in a register left or right by a specified number of bits, the shift length. Register shift can be performed directly by the instructions `ASR`, `LSR`, `LSL`, and `ROR` and the result is written to a destination register.

The permitted shift lengths depend on the shift type and the instruction, see the individual instruction description. If the shift length is 0, no shift occurs. Register shift operations update the carry flag except when the specified shift length is 0. The following sub-sections describe the various shift operations and how they affect the carry flag. In these descriptions, Rm is the register containing the value to be shifted, and n is the shift length.

24.3.3.3.1. ASR

Arithmetic shift right by n bits moves the left-hand $32-n$ bits of the register Rm , to the right by n places, into the right-hand $32-n$ bits of the result, and it copies the original bit[31] of the register into the left-hand n bits of the result. See Figure 24-11. ASR #3 on page 304.


You can use the `ASR` operation to divide the signed value in the register Rm by 2^n , with the result being rounded towards negative-infinity.

When the instruction is `ASRS` the carry flag is updated to the last bit shifted out, bit[$n-1$], of the register Rm .

Note

- If n is 32 or more, then all the bits in the result are set to the value of bit[31] of Rm .
- If n is 32 or more and the carry flag is updated, it is updated to the value of bit[31] of Rm .

Figure 24-11. ASR #3



24.3.3.3.2. LSR

Logical shift right by n bits moves the left-hand 32-n bits of the register Rm , to the right by n places, into the right-hand 32-n bits of the result, and it sets the left-hand n bits of the result to 0. See Figure 24-12. LSR #3 on page 305.


You can use the `LSR` operation to divide the value in the register Rm by 2^n , if the value is regarded as an unsigned integer.

When the instruction is `LSRS`, the carry flag is updated to the last bit shifted out, bit[n-1], of the register Rm .

Note

- If n is 32 or more, then all the bits in the result are cleared to 0.
- If n is 33 or more and the carry flag is updated, it is updated to 0.

Figure 24-12. LSR #3



24.3.3.3.3. LSL

Logical shift left by n bits moves the right-hand 32-n bits of the register Rm , to the left by n places, into the left-hand 32-n bits of the result, and it sets the right-hand n bits of the result to 0. See Figure 24-13. LSL #3 on page 306.


You can use the `LSL` operation to multiply the value in the register Rm by 2^n , if the value is regarded as an unsigned integer or a two's complement signed integer. Overflow can occur without warning.

When the instruction is `LSLS` the carry flag is updated to the last bit shifted out, bit[32-n], of the register Rm . These instructions do not affect the carry flag when used with `LSL #0`.

Note

- If n is 32 or more, then all the bits in the result are cleared to 0.
- If n is 33 or more and the carry flag is updated, it is updated to 0.

Figure 24-13. LSL #3



24.3.3.3.4. ROR


Rotate right by n bits moves the left-hand 32-n bits of the register Rm , to the right by n places, into the right-hand 32-n bits of the result, and it moves the right-hand n bits of the register into the left-hand n bits of the result. See Figure 24-14. ROR #3 on page 306.

When the instruction is `RORS` the carry flag is updated to the last bit rotation, bit[n-1], of the register Rm .

Note

- If n is 32, then the value of the result is same as the value in Rm , and if the carry flag is updated, it is updated to bit[31] of Rm .
- ROR with shift length, n, greater than 32 is the same as ROR with shift length n-32.

Figure 24-14. ROR #3



24.3.3.4. Address alignment

An aligned access is an operation where a word-aligned address is used for a word, or multiple word access, or where a halfword-aligned address is used for a halfword access. Byte accesses are always aligned.

There is no support for unaligned accesses on the Cortex-M0 processor. Any attempt to perform an unaligned memory access operation results in a HardFault exception.

24.3.3.5. PC-relative expressions

A PC-relative expression or label is a symbol that represents the address of an instruction or literal data. It is represented in the instruction as the PC value plus or minus a numeric offset. The assembler calculates the required offset from the label and the address of the current instruction. If the offset is too big, the assembler produces an error.

Note

- For most instructions, the value of the PC is the address of the current instruction plus 4 bytes.
- Your assembler might permit other syntaxes for PC-relative expressions, such as a label plus or minus a number, or an expression of the form [PC, #imm].

24.3.3.6. Conditional execution

Most data processing instructions update the condition flags in the Application Program Status Register (APSR) according to the result of the operation, see Application Program Status Register in chapter 24.2.1.3.6 on page 282. Some instructions update all flags, and some only update a subset. If a flag is not updated, the original value is preserved. See the instruction descriptions for the flags they affect.

You can execute a conditional branch instruction, based on the condition flags set in another instruction, either:

- immediately after the instruction that updated the flags
- after any number of intervening instructions that have not updated the flags.

On the Cortex-M0 processor, conditional execution is available by using conditional branches.

This section describes:

- The condition flags in chapter 24.3.3.6.1 on page 307
- Condition code suffixes in chapter 24.3.3.6.2 on page 308

24.3.3.6.1. The condition flags

The APSR contains the following condition flags:

- | | |
|---|---|
| N | Set to 1 when the result of the operation was negative, cleared to 0 otherwise. |
| Z | Set to 1 when the result of the operation was zero, cleared to 0 otherwise. |
| C | Set to 1 when the operation resulted in a carry, cleared to 0 otherwise. |
| V | Set to 1 when the operation caused overflow, cleared to 0 otherwise. |

For more information about the APSR see Program Status Register in chapter 24.2.1.3.5 on page 281

A carry occurs:

- if the result of an addition is greater than or equal to 2^{32}
- if the result of a subtraction is positive or zero
- as the result of a shift or rotate instruction.

Overflow occurs when the sign of the result, in bit[31], does not match the sign of the result had the operation been performed at infinite precision, for example:

- if adding two negative values results in a positive value
- if adding two positive values results in a negative value
- if subtracting a positive value from a negative value generates a positive value
- if subtracting a negative value from a positive value generates a negative value.

The Compare operations are identical to subtracting, for `CMP`, or adding, for `CMN`, except that the result is discarded. See the instruction descriptions for more information.

24.3.3.6.2. Condition code suffixes

Conditional branch is shown in syntax descriptions as $B\{cond\}$. A branch instruction with a condition code is only taken if the condition code flags in the APSR meet the specified condition, otherwise the branch instruction is ignored. Table 24-15. Condition code suffixes on page 308 shows the condition codes to use.

Table 24-15. Condition code suffixes on page 308 also shows the relationship between condition code suffixes and the N, Z, C, and V flags.

Table 24-15. Condition code suffixes

| SUFFIX | FLAGS | MEANING |
|----------|--------------------|---|
| EQ | Z = 1 | Equal, last flag setting result was zero |
| NE | Z = 0 | Not equal, last flag setting result was non-zero |
| CS or HS | C = 1 | Higher or same, unsigned |
| CC or LO | C = 0 | Lower, unsigned |
| MI | N = 1 | Negative |
| PL | N = 0 | Positive or zero |
| VS | V = 1 | Overflow |
| VC | V = 0 | No overflow |
| HI | C = 1 and Z = 0 | Higher, unsigned |
| LS | C = 0 or Z = 1 | Lower or same, unsigned |
| GE | N = V | Greater than or equal, signed |
| LT | N != V | Less than, signed |
| GT | Z = 0 and N = V | Greater than, signed |
| LE | Z = 1 and N != V | Less than or equal, signed |
| AL | Can have any value | Always. This is the default when no suffix is specified |

24.3.4. Memory access instructions

Table 24-16. Memory access instructions on page 308 shows the memory access instructions:

Table 24-16. Memory access instructions

| MNEMONIC | BRIEF DESCRIPTION | SEE |
|-----------|--|---|
| ADR | Generate PC-Relative Address | ADR in chapter 24.3.4.1 on page 309 |
| LDM | Load Multiple Registers | LDM and STM in chapter 24.3.4.5 on page 313 |
| LDR{type} | Load Register using Immediate Offset | LDR and STR, immediate offset in chapter 24.3.4.2 on page 310 |
| LDR{type} | Load Register Using Register Offset | LDR and STR, register offset in chapter 24.3.4.3 on page 311 |
| LDR | Load Register from PC-Relative Address | LDR, PC-relative in chapter 24.3.4.4 on page 312 |
| POP | Pop Registers From Stack | PUSH and POP in chapter 24.3.4.6 on page 314 |

| MNEMONIC | BRIEF DESCRIPTION | SEE |
|-----------|---------------------------------------|--|
| PUSH | Push Registers To Stack | PUSH and POP in chapter 24.3.4.6 on page 314 |
| STM | Store Multiple Registers | LDM and STM in chapter 24.3.4.5 on page 313 |
| STR{type} | Store Register Using Immediate Offset | LDR and STR in chapter 24.3.4.2 on page 310 |
| STR{type} | Store Register Using Register Offset | LDR and STR in chapter 24.3.4.3 on page 311 |

24.3.4.1. ADR

Generates a PC-relative address.

24.3.4.1.1. Syntax

ADR *Rd, label*

where:

Rd is the destination register.

Label is a PC-relative expression. See PC-relative expressions in chapter 24.3.3.5 on page 306.

24.3.4.1.2. Operation

ADR generates an address by adding an immediate value to the PC, and writes the result to the destination register.

ADR facilitates the generation of position-independent code, because the address is PC-relative.

If you use ADR to generate a target address for a BX or BLX instruction, you must ensure that bit[0] of the address you generate is set to 1 for correct execution.

24.3.4.1.3. Restrictions

In this instruction *Rd* must specify R0-R7. The data-value addressed must be word aligned and within 1020 bytes of the current PC.

24.3.4.1.4. Condition flags

This instruction does not change the flags.

24.3.4.1.5. Examples

```
ADR R1, TextMessage ; Write address value of a location labeled as
; TextMessage to R1
```

ADR R3, [PC, #996] ; Set R3 to value of PC + 996.

24.3.4.2. LDR and STR, immediate offset

Load and Store with immediate offset.

24.3.4.2.1. Syntax

LDR *Rt*, [<*Rn* | SP> {, #*imm*}]

LDR<B|H> *Rt*, [*Rn* {, #*imm*}]

STR *Rt*, [<*Rn* | SP>, {, #*imm*}]

STR<B|H> *Rt*, [*Rn* {, #*imm*}]

where:

Rt is the register to load or store.

Rn is the register on which the memory address is based.

imm is an offset from *Rn*. If *imm* is omitted, it is assumed to be zero.

24.3.4.2.2. Operation

LDR, LDRB and LDRH instructions load the register specified by *Rt* with either a word, byte or halfword data value from memory. Sizes less than word are zero extended to 32-bits before being written to the register specified by *Rt*.

STR, STRB and STRH instructions store the word, least-significant byte or lower halfword contained in the single register specified by *Rt* in to memory. The memory address to load from or store to is the sum of the value in the register specified by either *Rn* or SP and the immediate value *imm*.

24.3.4.2.3. Restrictions

In these instructions:

- *Rt* and *Rn* must only specify R0-R7.
- *imm* must be between:
 - 0 and 1020 and an integer multiple of four for LDR and STR using SP as the base register
 - 0 and 124 and an integer multiple of four for LDR and STR using R0-R7 as the base register
 - 0 and 62 and an integer multiple of two for LDRH and STRH
 - 0 and 31 for LDRB and STRB
- The computed address must be divisible by the number of bytes in the transaction, see Address alignment in chapter 24.3.3.4 on page 306.

24.3.4.2.4. Condition flags

These instructions do not change the flags.

24.3.4.2.5. Examples

```
LDR R4, [R7] ; Loads R4 from the address in R7.  
STR R2, [R0,#const-struc] ; const-struc is an expression evaluating  
; to a constant in the range 0-1020.
```

24.3.4.3. LDR and STR, register offset

Load and Store with register offset.

24.3.4.3.1. Syntax

```
LDR Rt, [Rn, Rm]  
LDR<B|H> Rt, [Rn, Rm]  
LDR<SB|SH> Rt, [Rn, Rm]  
STR Rt, [Rn, Rm]  
STR<B|H> Rt, [Rn, Rm]
```

where:

- Rt* is the register to load or store.
- Rn* is the register on which the memory address is based.
- Rm* is a register containing a value to be used as the offset.

24.3.4.3.2. Operation

LDR, LDRB, LDRH, LDRSB and LDRSH load the register specified by *Rt* with either a word, zero extended byte, zero extended halfword, sign extended byte or sign extended halfword value from memory.

STR, STRB and STRH store the word, least-significant byte or lower halfword contained in the single register specified by *Rt* into memory.

The memory address to load from or store to is the sum of the values in the registers specified by *Rn* and *Rm*.

24.3.4.3.3. Restrictions

In these instructions:

- *Rt*, *Rn*, and *Rm* must only specify R0-R7.

- the computed memory address must be divisible by the number of bytes in the load or store, see Address alignment in chapter 24.3.3.4 on page 306.

24.3.4.3.4. Condition flags

These instructions do not change the flags.

24.3.4.3.5. Examples

```
STR R0, [R5, R1]          ; Store value of R0 into an address equal to
                           ; sum of R5 and R1
LDRSH R1, [R2, R3]         ; Load a halfword from the memory address
                           ; specified by (R2 + R3), sign extend to 32-bits
                           ; and write to R1.
```

24.3.4.4. LDR, PC-relative

Load register (literal) from memory.

24.3.4.4.1. Syntax

LDR *Rt, label*

where:

Rt is the register to load.

label is a PC-relative expression. See PC-relative expressions in chapter 24.3.3.5 on page 306.

24.3.4.4.2. Operation

Loads the register specified by *Rt* from the word in memory specified by label.

24.3.4.4.3. Restrictions

In these instructions, label must be within 1020 bytes of the current PC and word aligned.

24.3.4.4.4. Condition flags

These instructions do not change the flags.

24.3.4.4.5. Examples

| | |
|---------------------|--|
| LDR R0, LookUpTable | ; Load R0 with a word of data from an address ; labeled as LookUpTable. |
| LDR R3, [PC, #100] | ; Load R3 with memory word at (PC + 100). |

24.3.4.5. LDM and STM

Load and Store Multiple registers.

24.3.4.5.1. Syntax

LDM *Rn{!}, reglist*

STM *Rn!, reglist*

where:

Rn is the register on which the memory addresses are based.

! writeback suffix.

reglist is a list of one or more registers to be loaded or stored, enclosed in braces.

It can contain register ranges. It must be comma separated if it contains more than one register or register range, see Examples in chapter 24.3.4.5.5 on page 314.

LDMIA and LDMFD are synonyms for LDM. LDMIA refers to the base register being Incremented After each access. LDMFD refers to its use for popping data from Full Descending stacks.

STMIA and STMEA are synonyms for STM. STMIA refers to the base register being Incremented After each access. STMEA refers to its use for pushing data onto Empty Ascending stacks.

24.3.4.5.2. Operation

LDM instructions load the registers in reglist with word values from memory addresses based on *Rn*.

STM instructions store the word values in the registers in reglist to memory addresses based on *Rn*.

The memory addresses used for the accesses are at 4-byte intervals ranging from the value in the register specified by *Rn* to the value in the register specified by *Rn + 4 * (n-1)*, where *n* is the number of registers in *reglist*. The accesses happens in order of increasing register numbers, with the lowest numbered register using the lowest memory address and the highest number register using the highest memory address. If the writeback suffix is specified, the value in the register specified by *Rn + 4 * n* is written back to the register specified by *Rn*.

24.3.4.5.3. Restrictions

In these instructions:

- *reglist* and *Rn* are limited to R0-R7.
- the writeback suffix must always be used unless the instruction is an LDM where *reglist* also contains *Rn*, in which case the writeback suffix must not be used.
- the value in the register specified by *Rn* must be word aligned. See Address alignment in chapter 24.3.3.4 on page 306.
- for STM, if *Rn* appears in *reglist*, then it must be the first register in the list.

24.3.4.5.4. Condition flags

These instructions do not change the flags.

24.3.4.5.5. Examples

```
LDM R0, {R0,R3,R4} ; LDMIA is a synonym for LDM
STMIA R1!, {R2-R4,R6}
```

24.3.4.5.6. Incorrect examples

```
STM R5!, {R4,R5,R6} ; Value stored for R5 is unpredictable
LDM R2, {} ; There must be at least one register in the list
```

24.3.4.6. PUSH and POP

Push registers onto, and pop registers off a full-descending stack.

24.3.4.6.1. Syntax

PUSH *reglist*

POP *reglist*

where:

reglist is a non-empty list of registers, enclosed in braces. It can contain register ranges. It must be comma separated if it contains more than one register or register range.

24.3.4.6.2. Operation

PUSH stores registers on the stack, with the lowest numbered register using the lowest memory address and the

highest numbered register using the highest memory address.

`POP` loads registers from the stack, with the lowest numbered register using the lowest memory address and the highest numbered register using the highest memory address.

`PUSH` uses the value in the SP register minus four as the highest memory address, `POP` uses the value in the SP register as the lowest memory address, implementing a full-descending stack. On completion, `PUSH` updates the SP register to point to the location of the lowest store value, `POP` updates the SP register to point to the location above the highest location loaded.

If a `POP` instruction includes PC in its *reglist*, a branch to this location is performed when the `POP` instruction has completed. Bit[0] of the value read for the PC is used to update the APSR T-bit. This bit must be 1 to ensure correct operation.

24.3.4.6.3. Restrictions

In these instructions:

- *reglist* must use only R0-R7.
- The exception is LR for a `PUSH` and PC for a `POP`.

24.3.4.6.4. Condition flags

These instructions do not change the flags.

24.3.4.6.5. Examples

```

PUSH {R0,R4-R7} ; Push R0,R4,R5,R6,R7 onto the stack
PUSH {R2,LR}      ; Push R2 and the link-register onto the stack
POP {R0,R6,PC}    ; Pop r0,r6 and PC from the stack, then branch to
                  ; the new PC.
  
```

24.3.5. General data processing instructions

Table 24-17. Data processing instructions on page 315 shows the data access instructions:

Table 24-17. Data processing instructions

| MNEMONIC | BRIEF DESCRIPTION | SEE |
|----------|------------------------|--|
| ADCS | Add with Carry | ADC, ADD, RSB, SBC, and SUB in chapter 24.3.5.1on page 316 |
| ADD{S} | Add | ADC, ADD, RSB, SBC, and SUB in chapter 24.3.5.1on page 316 |
| ANDS | Logical AND | AND, ORR, EOR, and BIC on page |
| ASRS | Arithmetic Shift Right | ASR, LSL, LSR, and ROR in chapter 24.3.5.3 on page 320 |

| MNEMONIC | BRIEF DESCRIPTION | SEE |
|----------|--|---|
| BICS | Bit Clear | AND, ORR, EOR, and BIC in chapter 24.3.5.2 on page 318 |
| CMN | Compare Negative | CMP and CMN in chapter 24.3.5.4 on page 321 |
| CMP | Compare | CMP and CMN in chapter 24.3.5.4 on page 321 |
| EORS | Exclusive OR | AND, ORR, EOR, and BIC in chapter 24.3.5.2 on page 318 |
| LSLS | Logical Shift Left | ASR, LSL, LSR, and ROR in chapter 24.3.5.3 on page 320 |
| LSRS | Logical Shift Right | ASR, LSL, LSR, and ROR in chapter 24.3.5.3 on page 320 |
| MOV{S} | Move | MOV and MVN in chapter 24.3.5.5 on page 322 |
| MULS | Multiply | MULS in chapter 24.3.5.6 on page 323 |
| MVNS | Move NOT | MOV and MVN in chapter 24.3.5.5 on page 322 |
| ORRS | Logical OR | AND, ORR, EOR, and BIC in chapter 24.3.5.2 on page 318 |
| REV | Reverse Byte Order In A Word | REV, REV16, and REVSH in chapter 24.3.5.7 on page 324 |
| REV16 | Reverse Byte Order In each Half Word | REV, REV16, and REVSH in chapter 24.3.5.7 on page 324 |
| REVSH | Reverse Byte Order In Bottom Half Word and Sign Extend | REV, REV16, and REVSH in chapter 24.3.5.7 on page 324 |
| RORS | Rotate Right | ASR, LSL, LSR, and ROR in chapter 24.3.5.3 on page 320 |
| RSBS | Reverse Subtract | ADC, ADD, RSB, SBC, and SUB in chapter 24.3.5.1 on page 316 |
| SBCS | Subtract with Carry | ADC, ADD, RSB, SBC, and SUB in chapter 24.3.5.1 on page 316 |
| SUBS | Subtract | ADC, ADD, RSB, SBC, and SUB in chapter 24.3.5.1 on page 316 |
| SXTB | Sign Extend A Byte | SXT and UXT in chapter 24.3.5.8 on page 325 |
| SXTH | Sign Extend a Halfword | SXT and UXT in chapter 24.3.5.8 on page 325 |
| UXTB | Zero Extend a Byte | SXT and UXT in chapter 24.3.5.8 on page 325 |
| UXTH | Zero Extend a Halfword | SXT and UXT in chapter 24.3.5.8 on page 325 |
| TST | Test | TST in chapter 24.3.5.9 on page 326 |

24.3.5.1. ADC, ADD, RSB, SBC, and SUB

Add with carry, Add, Reverse Subtract, Subtract with carry, and Subtract.

24.3.5.1.1. Syntax

ADCS {Rd, } Rn, Rm

ADD{S} {Rd, } Rn, <Rm | #imm>

RSBS {Rd, } Rn, Rm, #0

SBCS {Rd, } Rn, Rm

SUB{S} {Rd, } Rn, <Rm | #imm>

Where:

S causes an ADD or SUB instruction to update flags

Rd specifies the result register

Rn specifies the first source register

Rm specifies the second source register

imm specifies a constant immediate value.

When the optional *Rd* register specifier is omitted, it is assumed to take the same value as *Rn*, for example

ADDS R1,R2 is identical to ADDS R1,R1,R2.

24.3.5.1.2. Operation

The ADCS instruction adds the value in *Rn* to the value in *Rm*, adding a further one if the carry flag is set, places the result in the register specified by *Rd* and updates the N, Z, C, and V flags.

The ADD instruction adds the value in *Rn* to the value in *Rm* or an immediate value specified by *imm* and places the result in the register specified by *Rd*.

The ADDS instruction performs the same operation as ADD and also updates the N, Z, C and V flags.

The RSBS instruction subtracts the value in *Rn* from zero, producing the arithmetic negative of the value, and places the result in the register specified by *Rd* and updates the N, Z, C and V flags.

The SBCS instruction subtracts the value of *Rm* from the value in *Rn*, deducts a further one if the carry flag is set. It places the result in the register specified by *Rd* and updates the N, Z, C and V flags.

The SUB instruction subtracts the value in *Rm* or the immediate specified by *imm*. It places the result in the register specified by *Rd*.

The SUBS instruction performs the same operation as SUB and also updates the N, Z, C and V flags.

Use ADC and SBC to synthesize multiword arithmetic, see Examples in chapter 24.3.5.1.4 on page 318.

See also ADR in chapter 24.3.4.1 on page 309.

24.3.5.1.3. Restrictions

Table 24-18. ADC, ADD, RSB, SBC, and SUB operand restrictions on page 317 lists the legal combinations of register specifiers and immediate values that can be used with each instruction.

Table 24-18. ADC, ADD, RSB, SBC, and SUB operand restrictions

| INSTRUCTION | RD | Rn | Rm | imm | RESTRICTIONS |
|-------------|--------|----------|-------|--------|--|
| ADCS | R0-R7 | R0-R7 | R0-R7 | - | <i>Rd</i> and <i>Rn</i> must specify the same register |
| ADD | R0-R15 | R0-R15 | R0-PC | - | <i>Rd</i> and <i>Rn</i> must specify the same register <i>Rn</i> and <i>Rm</i> must not both specify PC |
| | R0-R7 | SP or PC | - | 0-1020 | Immediate value must be an integer multiple of four |
| | SP | SP | - | 0-508 | Immediate value must be an integer multiple of four |
| ADDS | R0-R7 | R0-R7 | - | 0-7 | - |
| | R0-R7 | R0-R7 | - | 0-255 | <i>Rd</i> and <i>Rn</i> must specify the same register |
| | R0-R7 | R0-R7 | R0-R7 | - | - |
| RSBS | R0-R7 | R0-R7 | - | - | - |
| SBCS | R0-R7 | R0-R7 | R0-R7 | - | <i>Rd</i> and <i>Rn</i> must specify the same register |
| SUB | SP | SP | - | 0-508 | Immediate value must be an integer multiple of four |
| SUBS | R0-R7 | R0-R7 | - | 0-7 | - |
| | R0-R7 | R0-R7 | - | 0-255 | <i>Rd</i> and <i>Rn</i> must specify the same register |
| | R0-R7 | R0-R7 | R0-R7 | - | - |

24.3.5.1.4. Examples

Example below shows two instructions that add a 64-bit integer contained in R0 and R1 to another 64-bit integer contained in R2 and R3, and place the result in R0 and R1.

```
ADDS R0, R0, R2      ; add the least significant words
ADCS R1, R1, R3      ; add the most significant words with carry
```

Multiword values do not have to use consecutive registers. Example below shows instructions that subtract a 96-bit integer contained in R1, R2, and R3 from another contained in R4, R5, and R6. The example stores the result in R4, R5, and R6.

```
SUBS R4, R4, R1      ; subtract the least significant words
SBCS R5, R5, R2      ; subtract the middle words with carry
SBCS R6, R6, R3      ; subtract the most significant words with carry
```

Example below the RSBS instruction used to perform a 1's complement of a single register.

```
RSBS R7, R7, #0      ; subtract R7 from zero
```

24.3.5.2. AND, ORR, EOR, and BIC

Logical AND, OR, Exclusive OR, and Bit Clear.

24.3.5.2.1. Syntax

ANDS {*Rd*, } *Rn*, *Rm*

ORRS {*Rd*, } *Rn*, *Rm*

EORS {*Rd*, } *Rn*, *Rm*

BICS {*Rd*, } *Rn*, *Rm*

where:

Rd is the destination register.

Rn is the register holding the first operand and is the same as the destination register.

Rm second register.

24.3.5.2.2. Operation

The AND, EOR, and ORR instructions perform bitwise AND, exclusive OR, and inclusive OR operations on the values in *Rn* and *Rm*.

The BIC instruction performs an AND operation on the bits in *Rn* with the logical negation of the corresponding bits in the value of *Rm*.

The condition code flags are updated on the result of the operation, see Condition flags in chapter 24.3.4.6.4 on page 315.

24.3.5.2.3. Restrictions

In these instructions, *Rd*, *Rn*, and *Rm* must only specify R0-R7.

24.3.5.2.4. Condition flags

These instructions:

- update the N and Z flags according to the result
- do not affect the C or V flag.

24.3.5.2.5. Examples

ANDS R2, R2, R1

ORRS R2, R2, R5

ANDS R5, R5, R8

EORS R7, R7, R6

BICS R0, R0, R1

24.3.5.3. ASR, LSL, LSR, and ROR

Arithmetic Shift Right, Logical Shift Left, Logical Shift Right, and Rotate Right.

24.3.5.3.1. Syntax

ASRS {*Rd*, } *Rm*, *Rs*

ASRS {*Rd*, } *Rm*, #*imm*

LSLS {*Rd*, } *Rm*, *Rs*

LSLS {*Rd*, } *Rm*, #*imm*

LSRS {*Rd*, } *Rm*, *Rs*

LSRS {*Rd*, } *Rm*, #*imm*

RORS {*Rd*, } *Rm*, *Rs*

where:

Rd is the destination register. If *Rd* is omitted, it is assumed to take the same value as *Rm*.

Rm is the register holding the value to be shifted.

Rs is the register holding the shift length to apply to the value in *Rm*.

imm is the shift length. The range of shift length depends on the instruction:

ASR shift length from 1 to 32

LSL shift length from 0 to 31

LSR shift length from 1 to 32.

Note

MOVS *Rd*, *Rm* is a pseudonym for LSLS *Rd*, *Rm*, #0.

24.3.5.3.2. Operation

ASR, LSL, LSR, and ROR perform an arithmetic-shift-left, logical-shift-left, logical-shift-right or a right-rotation of the bits in the register *Rm* by the number of places specified by the immediate *imm* or the value in the least-significant byte of the register specified by *Rs*.

For details on what result is generated by the different instructions, see Shift Operations in chapter 24.3.3.3 on page 304.

24.3.5.3.3. Restrictions

In these instructions, *Rd*, *Rm*, and *Rs* must only specify R0-R7. For non-immediate instructions, *Rd* and *Rm* must specify the same register.

24.3.5.3.4. Condition flags

These instructions update the N and Z flags according to the result.

The C flag is updated to the last bit shifted out, except when the shift length is 0, see Shift Operations in chapter 24.3.3.3 on page 304. The V flag is left unmodified.

24.3.5.3.5. Examples

```
ASRS R7, R5, #9          ; Arithmetic shift right by 9 bits
LSLS R1, R2, #3          ; Logical shift left by 3 bits with flag update
LSRS R4, R5, #6          ; Logical shift right by 6 bits
RORS R4, R4, R6          ; Rotate right by the value in the bottom byte of R6.
```

24.3.5.4. CMP and CMN

Compare and Compare Negative.

24.3.5.4.1. Syntax

CMN *Rn*, *Rm*

CMP *Rn*, #*imm*

CMP *Rn*, *Rm*

where:

Rn is the register holding the first operand.

Rm is the register to compare with.

imm is the immediate value to compare with.

24.3.5.4.2. Operation

These instructions compare the value in a register with either the value in another register or an immediate value. They update the condition flags on the result, but do not write the result to a register.

The **CMP** instruction subtracts either the value in the register specified by *Rm*, or the immediate *imm* from the value in *Rn* and updates the flags. This is the same as a **SUBS** instruction, except that the result is discarded.

The **CMN** instruction adds the value of *Rm* to the value in *Rn* and updates the flags. This is the same as an **ADDS**

instruction, except that the result is discarded.

24.3.5.4.3. Restrictions

For the:

- CMN instruction Rn , and Rm must only specify R0-R7.
- CMP instruction:
 - Rn and Rm can specify R0-R14
 - immediate must be in the range 0-255.

24.3.5.4.4. Condition flags

These instructions update the N, Z, C and V flags according to the result

24.3.5.4.5. Examples

CMP R2, R9

CMN R0, R2

24.3.5.5. MOV and MVN

Move and Move NOT.

24.3.5.5.1. Syntax

MOV{S} Rd, Rm

MOVS Rd, #imm

MVNS Rd, Rm

where:

S is an optional suffix. If S is specified, the condition code flags are updated on the result of the operation, see Conditional execution in chapter 24.3.3.6 on page 307.

Rd is the destination register.

Rm is a register.

imm is any value in the range 0-255.

24.3.5.5.2. Operation

The `MOV` instruction copies the value of *Rm* into *Rd*.

The `MOVS` instruction performs the same operation as the `MOV` instruction, but also updates the N and Z flags.

The `MVNS` instruction takes the value of *Rm*, performs a bitwise logical negate operation on the value, and places the result into *Rd*.

24.3.5.5.3. Restrictions

In these instructions, *Rd*, and *Rm* must only specify R0-R7.

When *Rd* is the PC in a `MOV` instruction:

- Bit[0] of the result is discarded.
- A branch occurs to the address created by forcing bit[0] of the result to 0. The T-bit remains unmodified.
-

Note

Though it is possible to use `MOV` as a branch instruction, ARM strongly recommends the use of a `BX` or `BLX` instruction to branch for software portability.

24.3.5.5.4. Condition flags

If S is specified, these instructions:

- update the N and Z flags according to the result
- do not affect the C or V flags.

24.3.5.5.5. Example

```

MOVS R0, #0x000B      ; Write value of 0x000B to R0, flags get updated
MOVS R1, #0x0           ; Write value of zero to R1, flags are updated
MOV R10, R12            ; Write value in R12 to R10, flags are not updated
MOVS R3, #23             ; Write value of 23 to R3
MOV R8, SP              ; Write value of stack pointer to R8
MVNS R2, R0              ; Write inverse of R0 to the R2 and update flags

```

24.3.5.6. MULS

Multiply using 32-bit operands, and producing a 32-bit result.

24.3.5.6.1. Syntax

MULS *Rd*, *Rn*, *Rm*

where:

Rd is the destination register.

Rn, *Rm* are registers holding the values to be multiplied.

24.3.5.6.2. Operation

The MUL instruction multiplies the values in the registers specified by *Rn* and *Rm*, and places the least significant 32 bits of the result in *Rd*. The condition code flags are updated on the result of the operation, see Conditional execution in chapter 24.3.3.6 on page 307.

The results of this instruction does not depend on whether the operands are signed or unsigned.

24.3.5.6.3. Restrictions

In this instruction:

- *Rd*, *Rn*, and *Rm* must only specify R0-R7
- *Rd* must be the same as *Rm*.

24.3.5.6.4. Condition flags

This instruction:

- updates the N and Z flags according to the result
- does not affect the C or V flags.

24.3.5.6.5. Examples

MULS R0, R2, R0 ; Multiply with flag update, R0 = R0 × R2

24.3.5.7. REV, REV16, and REVSH

Reverse bytes.

24.3.5.7.1. Syntax

REV *Rd*, *Rn*

REV16 *Rd*, *Rn*

REVSH *Rd, Rn*

where:

Rd is the destination register.

Rn is the source register.

24.3.5.7.2. Operation

Use these instructions to change endianness of data:

REV converts 32-bit big-endian data into little-endian data or 32-bit little-endian data into big-endian data.

REV16 converts two packed 16-bit big-endian data into little-endian data or two packed 16-bit little-endian data into big-endian data.

REVSH converts 16-bit signed big-endian data into 32-bit signed little-endian data or 16-bit signed little-endian data into 32-bit signed big-endian data.

24.3.5.7.3. Restrictions

In these instructions, *Rd*, and *Rn* must only specify R0-R7.

24.3.5.7.4. Condition flags

These instructions do not change the flags.

24.3.5.7.5. Examples

| | |
|--------------|--|
| REV R3, R7 | ; Reverse byte order of value in R7 and write it to R3 |
| REV16 R0, R0 | ; Reverse byte order of each 16-bit halfword in R0 |
| REVSH R0, R5 | ; Reverse signed halfword |

24.3.5.8. SXT and UXT

Sign extend and Zero extend.

24.3.5.8.1. Syntax

SXTB *Rd, Rm*

SXTH *Rd, Rm*

UXTB *Rd, Rm*

UXTH *Rd*, *Rm*

where:

Rd is the destination register.

Rm is the register holding the value to be extended.

24.3.5.8.2. Operation

These instructions extract bits from the resulting value:

- SXTB extracts bits[7:0] and sign extends to 32 bits
- UXTB extracts bits[7:0] and zero extends to 32 bits
- SXTH extracts bits[15:0] and sign extends to 32 bits
- UXTH extracts bits[15:0] and zero extends to 32 bits.

24.3.5.8.3. Restrictions

In these instructions, *Rd* and *Rm* must only specify R0-R7.

24.3.5.8.4. Condition flags

These instructions do not affect the flags.

24.3.5.8.5. Examples

```
SXTH R4, R6          ; Obtain the lower halfword of the
                      ; value in R6 and then sign extend to
                      ; 32 bits and write the result to R4.

UXTB R3, R1          ; Extract lowest byte of the value in R10 and zero
                      ; extend it, and write the result to R3
```

24.3.5.9. TST

Test bits.

24.3.5.9.1. Syntax

TST *Rn*, *Rm*

where:

Rn is the register holding the first operand.

Rm the register to test against.

24.3.5.9.2. Operation

This instruction tests the value in a register against another register. It updates the condition flags based on the result, but does not write the result to a register.

The **TST** instruction performs a bitwise AND operation on the value in *Rn* and the value in *Rm*. This is the same as the **ANDS** instruction, except that it discards the result.

To test whether a bit of *Rn* is 0 or 1, use the **TST** instruction with a register that has that bit set to 1 and all other bits cleared to 0.

24.3.5.9.3. Restrictions

In these instructions, *Rn* and *Rm* must only specify R0-R7.

24.3.5.9.4. Condition flags

This instruction:

- updates the N and Z flags according to the result
- does not affect the C or V flags.

24.3.5.9.5. Examples

```
TST R0, R1          ; Perform bitwise AND of R0 value and R1 value,
                     ; condition code flags are updated but result is discarded
```

24.3.6. Branch and control instructions

Table 24-19. Branch and Control instructions on page 327 shows the branch and control instructions:

Table 24-19. Branch and Control instructions

| MNEMONIC | BRIEF DESCRIPTION | SEE |
|----------|---------------------------|--|
| B{CC} | Branch {conditionally} | B, BL, BX, and BLX in chapter 24.3.6.1 on page 328 |
| BL | Branch with Link | B, BL, BX, and BLX in chapter 24.3.6.1 on page 328 |
| BLX | Branch indirect with Link | B, BL, BX, and BLX in chapter 24.3.6.1 on page 328 |
| BX | Branch indirect | B, BL, BX, and BLX in chapter 24.3.6.1 on page 328 |

24.3.6.1. B, BL, BX, and BLX

Branch instructions.

24.3.6.1.1. Syntax

B {cond} *label*

BL *label*

BX *Rm*

BLX *Rm*

where:

cond is an optional condition code, see Conditional execution in chapter 24.3.3.6 on page 307.

label is a PC-relative expression. See PC-relative expressions in chapter 24.3.3.5 on page 306.

Rm is a register providing the address to branch to.

24.3.6.1.2. Operation

All these instructions cause a branch to the address indicated by *label* or contained in the register specified by *Rm*. In addition:

- The BL and BLX instructions write the address of the next instruction to LR, the link register R14.
- The BX and BLX instructions result in a HardFault exception if bit[0] of *Rm* is 0.

BL and BLX instructions also set bit[0] of the LR to 1. This ensures that the value is suitable for use by a subsequent POP {PC} or BX instruction to perform a successful return branch.

Table 24-20. Branch ranges on page 328 shows the ranges for the various branch instructions.

Table 24-20. Branch ranges

| INSTRUCTION | BRANCH RANGE |
|-------------|-------------------------|
| B label | -2KB to + 2KB |
| Bcond label | -256bytes to +254 bytes |
| BL label | -16MB to +16MB |
| BX Rm | Any value in register |
| BLX Rm | Any value in register |

24.3.6.1.3. Restrictions

In these instructions:

- Do not use SP or PC in the BX or BLX instruction.
- For BX and BLX, bit[0] of *Rm* must be 1 for correct execution. Bit[0] is used to update the EPSR T-bit

and is discarded from the target address.

•

Note

BCOND is the only conditional instruction on the Cortex-M0 processor.

Condition flags

These instructions do not change the flags.

Examples

```

B loopA          ; Branch to loopA
BL funC          ; Branch with link (Call) to function funC, return address
                  ; stored in LR
BX LR            ; Return from function call
BLX R0            ; Branch with link and exchange (Call) to an address stored
                  ; in R0
BEQ labelD       ; Conditionally branch to labelD if last flag setting
                  ; instruction set the Z flag, else do not branch.

```

24.3.7. Miscellaneous instructions

Table 24-21. Miscellaneous instructions on page 329 shows the remaining Cortex-M0 instructions:

Table 24-21. Miscellaneous instructions

| MNEMONIC | BRIEF DESCRIPTION | SEE |
|----------|---|--------------------------------------|
| BKPT | Breakpoint | BKPT in chapter 24.3.7.1 on page 330 |
| CPSID | Change Processor State, Disposable Interrupts | CPS in chapter 24.3.7.2 on page 330 |
| CPSIE | Change Processor State, Enable Interrupts | CPS in chapter 24.3.7.2 on page 330 |
| DMB | Data Memory Barrier | DMB in chapter 24.3.7.3 on page 331 |
| DSB | Data Synchronization Barrier | DSB in chapter 24.3.7.4 on page 332 |
| ISB | Instruction Synchronization Barrier | ISB in chapter 24.3.7.5 on page 332 |
| MRS | Move from special register to register | MRS in chapter 24.3.7.6 on page 333 |
| MSR | Move from register to special register | MSR in chapter 24.3.7.7 on page 334 |
| NOP | No operation | NOP in chapter 24.3.7.8 on page 335 |
| SEV | Send Event | SEV in chapter 24.3.7.9 on page 335 |
| SVC | Supervisor Call | SVC in chapter 24.3.7.10 on page 336 |
| WFE | Wait for Event | WFE in chapter 24.3.7.11 on page 337 |
| WFI | Wait for interrupt | WFI in chapter 24.3.7.12 on page 338 |

24.3.7.1. BKPT

Breakpoint.

24.3.7.1.1. Syntax

BKPT #*imm*

where:

imm is an integer in the range 0-255.

24.3.7.1.2. Operation

The BKPT instruction causes the processor to enter Debug state. Debug tools can use this to investigate system state when the instruction at a particular address is reached.

imm is ignored by the processor. If required, a debugger can use it to store additional information about the breakpoint.

The processor might also produce a HardFault or go into lockup if a debugger is not attached when a BKPT instruction is executed. See Lockup in chapter 24.2.4.1 on page 297 for more information.

24.3.7.1.3. Restrictions

There are no restrictions.

24.3.7.1.4. Condition flags

This instruction does not change the flags.

24.3.7.1.5. Examples

BKPT #0 ; Breakpoint with immediate value set to 0x0.

24.3.7.2. CPS

Change Processor State.

24.3.7.2.1. Syntax

CPSID i

CPSIE i

24.3.7.2.2. Operation

CPS changes the PRIMASK special register values. CPSID causes interrupts to be disabled by setting PRIMASK. CPSIE cause interrupts to be enabled by clearing PRIMASK. See Exception mask register in chapter 24.2.1.3.10 on page 284 for more information about these registers.

24.3.7.2.3. Restrictions

There are no restrictions.

24.3.7.2.4. Condition flags

This instruction does not change the condition flags.

24.3.7.2.5. Examples

```
CPSID i           ; Disable all interrupts except NMI (set PRIMASK)  
CPSIE i           ; Enable interrupts (clear PRIMASK)
```

24.3.7.3. DMB

Data Memory Barrier.

24.3.7.3.1. Syntax

DMB

24.3.7.3.2. Operation

DMB acts as a data memory barrier. It ensures that all explicit memory accesses that appear in program order before the DMB instruction are observed before any explicit memory accesses that appear in program order after the DMB instruction. DMB does not affect the ordering of instructions that do not access memory.

24.3.7.3.3. Restrictions

There are no restrictions.

24.3.7.3.4. Condition flags

This instruction does not change the flags.

24.3.7.3.5. Examples

```
DMB ; Data Memory Barrier
```

24.3.7.4. DSB

Data Synchronization Barrier.

24.3.7.4.1. Syntax

```
DSB
```

24.3.7.4.2. Operation

`DSB` acts as a special data synchronization memory barrier. Instructions that come after the `DSB`, in program order, do not execute until the `DSB` instruction completes. The `DSB` instruction completes when all explicit memory accesses before it complete.

24.3.7.4.3. Restrictions

There are no restrictions.

24.3.7.4.4. Condition flags

This instruction does not change the flags.

24.3.7.4.5. Examples

```
DSB ; Data Synchronisation Barrier
```

24.3.7.5. ISB

Instruction Synchronization Barrier.

24.3.7.5.1. Syntax

ISB

24.3.7.5.2. Operation

ISB acts as an instruction synchronization barrier. It flushes the pipeline of the processor, so that all instructions following the ISB are fetched from cache or memory again, after the ISB instruction has been completed.

24.3.7.5.3. Restrictions

There are no restrictions.

24.3.7.5.4. Condition flags

This instruction does not change the flags.

24.3.7.5.5. Examples

ISB ; Instruction Synchronisation Barrier

24.3.7.6. MRS

Move the contents of a special register to a general-purpose register.

24.3.7.6.1. Syntax

MRS *Rd*, *spec_reg*

where:

Rd is the general-purpose destination register.

spec_reg is one of the special-purpose registers: APSR, IPSR, EPSR, IEPSR, IAPSR, EAPSR, PSR, MSP, PSP, PRIMASK, or CONTROL.

24.3.7.6.2. Operation

MRS stores the contents of a special-purpose register to a general-purpose register. The MRS instruction can be combined with the MSR instruction to produce read-modify-write sequences, which are suitable for modifying a specific flag in the PSR.

See MSR in chapter 24.3.7.7 on page 334.

24.3.7.6.3. Restrictions

In this instruction, Rd must not be SP or PC.

24.3.7.6.4. Condition flags

This instruction does not change the flags.

24.3.7.6.5. Examples

```
MRS R0, PRIMASK ; Read PRIMASK value and write it to R0
```

24.3.7.7. MSR

Move the contents of a general-purpose register into the specified special register.

24.3.7.7.1. Syntax

MSR *spec_reg*, *Rn*

where:

Rn is the general-purpose source register.

spec_reg is the special-purpose destination register: APSR, IPSR, EPSR, IEPSR, IAPSR, EAPSR, PSR, MSP, PSP, PRIMASK, or CONTROL.

24.3.7.7.2. Operation

MSR updates one of the special registers with the value from the register specified by *Rn*.

See [MRS on 24.3.7.6](#) on page 333.

24.3.7.7.3. Restrictions

In this instruction, *Rn* must not be SP and must not be PC.

24.3.7.7.4. Condition flags

This instruction updates the flags explicitly based on the value in *Rn*.

24.3.7.7.5. Examples

MSR CONTROL, R1

; Read R1 value and write it to the CONTROL register

24.3.7.8. NOP

No Operation.

24.3.7.8.1. Syntax

NOP

24.3.7.8.2. Operation

NOP performs no operation and is not guaranteed to be time consuming. The processor might remove it from the pipeline before it reaches the execution stage. Use NOP for padding, for example to place the subsequent instructions on a 64-bit boundary.

24.3.7.8.3. Restrictions

There are no restrictions.

24.3.7.8.4. Condition flags

This instruction does not change the flags.

24.3.7.8.5. Examples

NOP ; No operation

24.3.7.9. SEV

Send Event.

24.3.7.9.1. Syntax

SEV

24.3.7.9.2. Operation

SEV causes an event to be signaled to all processors within a multiprocessor system. It also sets the local event register, see Power management in chapter 24.2.5 on page 298.

See also WFE in chapter 24.3.7.11 on page 337.

24.3.7.9.3. Restrictions

There are no restrictions.

24.3.7.9.4. Condition flags

This instruction does not change the flags.

24.3.7.9.5. Examples

```
SEV ; Send Event
```

24.3.7.10. SVC

Supervisor Call.

24.3.7.10.1. Syntax

```
SVC #imm
```

where:

imm is an integer in the range 0-255.

24.3.7.10.2. Operation

The SVC instruction causes the SVC exception.

imm is ignored by the processor. If required, it can be retrieved by the exception handler to determine what service is being requested.

24.3.7.10.3. Restrictions

There are no restrictions.

24.3.7.10.4. Condition flags

This instruction does not change the flags.

24.3.7.10.5. Examples

```
SVC #0x32          ; Supervisor Call (SVC handler can extract the immediate value  
                  ; by locating it via the stacked PC)
```

24.3.7.11. WFE

Wait For Event.

24.3.7.11.1. Syntax

WFE

24.3.7.11.2. Operation

If the event register is 0, WFE suspends execution until one of the following events occurs:

- an exception, unless masked by the exception mask registers or the current priority level
- an exception enters the Pending state, if SEVONPEND in the System Control Register is set
- a Debug Entry request, if debug is enabled
- an event signaled by a peripheral or another processor in a multiprocessor system using the SEV instruction.

If the event register is 1, WFE clears it to 0 and completes immediately.

For more information see see Power management in chapter 24.2.5 on page 298.

Note

WFE is intended for power saving only. When writing software assume that WFE might behave as NOP.

24.3.7.11.3. Restrictions

There are no restrictions.

24.3.7.11.4. Condition flags

This instruction does not change the flags.

24.3.7.11.5. Examples

```
WFE ; Wait for event
```

24.3.7.12. WFI

Wait for Interrupt.

24.3.7.12.1. Syntax

```
WFI
```

24.3.7.12.2. Operation

WFI suspends execution until one of the following events occurs:

- an exception
- an interrupt becomes pending which would preempt if PRIMASK was clear
- a Debug Entry request, regardless of whether debug is enabled.
-

Note

WFI is intended for power saving only. When writing software assume that WFI might behave as a NOP operation.

24.3.7.12.3. Restrictions

There are no restrictions.

24.3.7.12.4. Condition flags

This instruction does not change the flags.

24.3.7.12.5. Examples

```
WFI ; Wait for interrupt
```

24.4. Cortex-M0 Peripherals

The following sections are the reference material for the ARM Cortex-M0 core peripherals descriptions in a User Guide:

- About the Cortex-M0 peripherals in chapter 24.4.1 on page 339
- Nested Vectored Interrupt Controller in chapter 24.4.2 on page 339
- System Control Block in chapter 24.4.3 on page 345
- System timer, SysTick in chapter 24.4.4 on page 352

24.4.1. About the Cortex-M0 peripherals

The address map of the Private peripheral bus (PPB) is:

Table 24-22. Core peripheral register regions

| ADDRESS | CORE PERIPHERAL | DESCRIPTION |
|---------------------------|--------------------------------------|--|
| 0xE000 E008 – 0xE000 E00F | System Control Block | Table 24-31. Summary of the SCB register on page 345 |
| 0xE000 E010 – 0xE000 E01F | System Timer | Table 24-40. System timer register summary on page 352 |
| 0xE000 E100 – 0xE000 E4EF | Nested Vectored Interrupt Controller | Table 24-23. NVIC register summary on page 339 |
| 0xE000 ED00 – 0xE000 ED3F | System Control Block | Table 24-31. Summary of the SCB register on page 345 |
| 0xE000 EF00 – 0xE000 EF03 | Nested Vectored Interrupt Controller | Table 24-23. NVIC register summary on page 339 |

In register descriptions, the register type is described as follows:

RW Read and write.

RO Read-only.

WO Write-only.

24.4.2. Nested Vectored Interrupt Controller

This section describes the Nested Vectored Interrupt Controller (NVIC) and the registers it uses. The NVIC supports:

- 1 to 32 interrupts.
- A programmable priority level of 0-192 in steps of 64 for each interrupt. A higher level corresponds to a lower priority, so level 0 is the highest interrupt priority.
- Level and pulse detection of interrupt signals.
- Interrupt tail-chaining.
- An external Non-maskable interrupt (NMI).

The processor automatically stacks its state on exception entry and unstacks this state on exception exit, with no instruction overhead. This provides low latency exception handling. The hardware implementation of the NVIC registers is:

Table 24-23. NVIC register summary

| ADDRESS | NAME | TYPE | RESET VALUE | DESCRIPTION |
|---------------------------|--------|------|-------------|--|
| 0xE000 E100 | ISER | RW | 0x0000 0000 | Interrupt Set-enable Register in chapter 24.4.2.2 on page 340 |
| 0xE000 E180 | ICER | RW | 0x0000 0000 | Interrupt Clear-enable Register in chapter 24.4.2.3 on page 341 |
| 0xE000 E200 | ISPR | RW | 0x0000 0000 | Interrupt Set-pending Register in chapter 24.4.2.4 on page 341 |
| 0xE000 E280 | ICPR | RW | 0x0000 0000 | Interrupt Clear-pending Register in chapter 24.4.2.5 on page 342 |
| 0xE000 E400 – 0xE000 E41C | IPR0-7 | RW | 0x0000 0000 | Interrupt Priority Registers in chapter 24.4.2.6 on page 342 |

24.4.2.1. Accessing the Cortex-M0 NVIC registers using CMSIS

CMSIS functions enable software portability between different Cortex-M profile processors.

To access the NVIC registers when using CMSIS, use the following functions:

Table 24-24. CMSIS access NVIC functions

| CMSIS FUNCTION | DESCRIPTION |
|--|--|
| void NVIC_EnableIRQ(IRQn_Type IRQn) * | Enables an interrupt or exception |
| void NVIC_DisableIRQ(IRQn_Type IRQn) * | Disables an interrupt or exception |
| void NVIC_SetPendingIRQ(IRQn_Type IRQn) * | Set the pending status of interrupt or exception to 1 |
| void NVIC_ClearPendingIRQ(IRQn_Type IRQn) * | Clears the pending status of interrupt or exception to 0 |
| uint32_t NVIC_GetPendingIRQ(IRQn_Type IRQn) * | Reads the pending status of interrupt or exception. This function returns non-zero value if the pending status is set to 1. |
| void NVIC_SetPriority(IRQn_Type IRQn, uint32_t priority) * | Sets the priority of an interrupt or exception with configurable priority level to 1 |
| uint32_t NVIC_GetPriority(IRQn_Type IRQn) * | Reads the priority of an interrupt or exception with configurable priority level. This function returns the current priority level |

* The input parameter IRQn is the IRQ number see Table 24-10. Properties of the different exception types on page 292 for more information

24.4.2.2. Interrupt Set-enable Register

The ISER enables interrupts, and shows which interrupts are enabled. See the register summary in Table 24-23. NVIC register summary on page 339 for the register attributes.

The bit assignments are:

Figure 24-15. ISER




Table 24-25. ISER bit assignments

| BIT | NAME | FUNCTION |
|------|---------------|---|
| 31:0 | SETENA | Interrupt set-enable bits. Write: 1: enable interrupt 0: no effect Read: 1: interrupt enabled 0: interrupt disabled |

If a pending interrupt is enabled, the NVIC activates the interrupt based on its priority.

If an interrupt is not enabled, asserting its interrupt signal changes the interrupt state to pending, but the NVIC never activates the interrupt, regardless of its priority.

24.4.2.3. Interrupt Clear-enable Register

The ICER disables interrupts, and shows which interrupts are enabled. See the register summary in Table 24-23. NVIC register summary on page 339 for the register attributes.

The bit assignments are:

Figure 24-16. ICER



Table 24-26. ICER bit assignments

| BIT | NAME | FUNCTION |
|------|-----------------|--|
| 31:0 | CLEARENA | Interrupt clear-enable bits. Write: 1: disable interrupt 0: no effect Read: 1: interrupt enabled 0: interrupt disabled |

24.4.2.4. Interrupt Set-pending Register

The ISPR forces interrupts into the pending state, and shows which interrupts are pending. See the register summary in Table 24-23. NVIC register summary on page 339 for the register attributes.

The bit assignments are:

Figure 24-17. ISPR



Table 24-27. ISPR bit assignments

| BIT | NAME | FUNCTION |
|------|----------------|--|
| 31:0 | SETPEND | Interrupt set-pending bits. Write: 1: changes interrupt state to pending 0: no effect Read: 1: changes interrupt state to pending 0: interrupt not pending |

Note

Writing 1 to the ISPR bit corresponding to:

- an interrupt that is pending has no effect
- a disabled interrupt sets the state of that interrupt to pending.

24.4.2.5. Interrupt Clear-pending Register

The ICPR removes the pending state from interrupts, and shows which interrupts are pending. See the register summary in Table 24-23. NVIC register summary on page 339 for the register attributes.

The bit assignments are:

Figure 24-18. ICPR

Table 24-28. ICPR bit assignments


| BIT | NAME | FUNCTION |
|------|----------------|--|
| 31:0 | CLRPEND | Interrupt clear-pending bits. Write: 1: removes pending state an interrupt 0: no effect Read: 1: interrupt is pending 0: interrupt not pending |

Note

Writing 1 to an ICPR bit does not affect the active state of the corresponding interrupt

24.4.2.6. Interrupt Priority Registers

The IPR0-IPR7 registers provide an 8-bit priority field for each interrupt. These registers are only word-accessible. See the register summary in Table 24-23. NVIC register summary on page 339 for their attributes. Each register holds four priority fields as shown:

Figure 24-19. IPR

Table 24-29. IPR bit assignments

| BIT | NAME | FUNCTION |
|-------|-------------------------|--|
| 31:24 | Priority, byte offset 3 | Each priority field holds a priority value, 0-192. The lower the value, the greater the priority of the corresponding interrupt. The processor implements only bits[7:6] of each field, bits [5:0] read as zero and ignore writes. This means writing 255 to a priority register saves value 192 to the register |
| 23:16 | Priority, byte offset 2 | |
| 15:8 | Priority, byte offset 1 | |
| 7:0 | Priority, byte offset 3 | |

See Accessing the Cortex-M0 NVIC registers using CMSIS in chapter 24.4.2.1 on page 340 for more information about the access to the interrupt priority array, which provides the software view of the interrupt priorities.

Find the IPR number and byte offset for interrupt M as follows:

- the corresponding IPR number, N, is given by $N = N \text{ DIV } 4$
- the byte offset of the required Priority field in this register is $M \text{ MOD } 4$, where:
 - byte offset 0 refers to register bits[7:0]
 - byte offset 1 refers to register bits[15:8]
 - byte offset 2 refers to register bits[23:16]
 - byte offset 3 refers to register bits[31:24]

24.4.2.7. Level-sensitive and pulse interrupts

The processor supports both level-sensitive and pulse interrupts. Pulse interrupts are also described as edge-triggered interrupts.

A level-sensitive interrupt is held asserted until the peripheral deasserts the interrupt signal. Typically this happens because the ISR accesses the peripheral, causing it to clear the interrupt request. A pulse interrupt is an interrupt signal sampled synchronously on the rising edge of the processor clock. To ensure the NVIC detects the interrupt, the peripheral must assert the interrupt signal for at least one clock cycle, during which the NVIC

detects the pulse and latches the interrupt.

When the processor enters the ISR, it automatically removes the pending state from the interrupt, see Hardware and software control of interrupts in chapter 24.4.2.7.1 on page 344. For a level-sensitive interrupt, if the signal is not deasserted before the processor returns from the ISR, the interrupt becomes pending again, and the processor must execute its ISR again. This means that the peripheral can hold the interrupt signal asserted until it no longer needs servicing.

24.4.2.7.1. Hardware and software control of interrupts

The Cortex-M0 latches all interrupts. A peripheral interrupt becomes pending for one of the following reasons:

- the NVIC detects that the interrupt signal is active and the corresponding interrupt is not active
- the NVIC detects a rising edge on the interrupt signal
- software writes to the corresponding interrupt set-pending register bit, see Interrupt Set-pending Register in chapter 24.4.2.4 on page 341

A pending interrupt remains pending until one of the following:

- The processor enters the ISR for the interrupt. This changes the state of the interrupt from pending to active. Then:
 - For a level-sensitive interrupt, when the processor returns from the ISR, the NVIC samples the interrupt signal. If the signal is asserted, the state of the interrupt changes to pending, which might cause the processor to immediately re-enter the ISR. Otherwise, the state of the interrupt changes to inactive.
 - For a pulse interrupt, the NVIC continues to monitor the interrupt signal, and if this is pulsed the state of the interrupt changes to pending and active. In this case, when the processor returns from the ISR the state of the interrupt changes to pending, which might cause the processor to immediately re-enter the ISR. If the interrupt signal is not pulsed while the processor is in the ISR, when the processor returns from the ISR the state of the interrupt changes to inactive.
- Software writes to the corresponding interrupt clear-pending register bit. For a level-sensitive interrupt, if the interrupt signal is still asserted, the state of the interrupt does not change. Otherwise, the state of the interrupt changes to inactive. For a pulse interrupt, state of the interrupt changes to:
 - inactive, if the state was pending
 - active, if the state was active and pending.

24.4.2.8. NVIC usage hints and tips

Ensure software uses correctly aligned register accesses. The processor does not support unaligned accesses to NVIC registers.

An interrupt can enter pending state even if it is disabled. Disabling an interrupt only prevents the processor from taking that interrupt.

24.4.2.8.1. NVIC programming hints

Software uses the CPSIE i and CPSID i instructions to enable and disable interrupts. The CMSIS provides the following intrinsic functions for these instructions:

```
void __disable_irq(void) // Disable Interrupts
void __enable_irq(void) // Enable Interrupts
```

In addition, the CMSIS provides a number of functions for NVIC control, including:

Table 24-30. CMSIS access NVIC functions

| CMSIS FUNCTION | DESCRIPTION |
|--|------------------------------------|
| void NVIC_EnableIRQ(IRQn_Type IRQn) | Enable IRQn |
| void NVIC_DisableIRQ(IRQn_Type IRQn) | Disable IRQn |
| uint32_t NVIC_GetPendingIRQ(IRQn_Type IRQn) | Return true (1) if IRQn is pending |
| void NVIC_SetPendingIRQ(IRQn_Type IRQn) | Set IRQn pending |
| void NVIC_ClearPendingIRQ(IRQn_Type IRQn) | Clear IRQn pending state |
| void NVIC_SetPriority(IRQn_Type IRQn, uint32_t priority) | Set priority for IRQn |
| uint32_t NVIC_GetPriority(IRQn_Type IRQn) | Read priority of IRQn |
| void NVIC_SystemReset (void) | Reset the system |

The input parameter IRQn is the IRQ number, see Table 24-10. Properties of the different exception types on page 292 more information. For more information about these functions, see the CMSIS documentation.

24.4.3. System Control Block

The System Control Block (SCB) provides system implementation information, and system control. This includes configuration, control, and reporting of the system exceptions. The SCB registers are:

Table 24-31. Summary of the SCB register

| ADDRESS | NAME | TYPE | RESET VALUE | DESCRIPTION |
|-------------|-------|------|-------------|--|
| 0xE000 ED00 | CPUID | RO | 0x410C C200 | CPUID Register in chapter 24.4.3.2 on page 346 |
| 0xE000 ED04 | ICSR | RW* | 0x0000 0000 | Interrupt Control and State Register in chapter 24.4.3.3 on page 346 |
| 0xE000 ED0C | AIRCR | RW* | 0xFA05 0000 | Application Interrupt and Reset Control Register in chapter 24.4.3.4 on page 348 |
| 0xE000 ED10 | SCR | RW | 0x0000 0000 | System Control Register in chapter 24.4.3.5 on page 349 |
| 0xE000 ED14 | CCR | RW | 0x0000 0204 | Configuration and Control register in chapter 24.4.3.6 on page 350 |
| 0xE000 ED1C | SHPR2 | RW | 0x0000 0000 | System Handler Priority register in chapter 24.4.3.7 on page 350 |
| 0xE000 ED20 | SHPR3 | RW | 0x0000 0000 | System Handler Priority register in chapter 24.4.3.7 on page 350 |

* See the register description for more information

24.4.3.1. The CMSIS mapping of the Cortex-M0 SCB registers

To improve software efficiency, the CMSIS simplifies the SCB register presentation. In the CMSIS, the array SHP[1] corresponds to the registers SHPR2-SHPR3

24.4.3.2. CPUID Register

The CPUID register contains the processor part number, version, and implementation information. See the register summary in Table 24-32. CPUID register bit assignments on page 346 for its attributes. The bit assignments are:

Figure 24-20. CPUID




Table 24-32. CPUID register bit assignments


| BIT | NAME | FUNCTION |
|-------|--------------------|--|
| 31:24 | Implementer | Implementer code: 0x41 = ARM |
| 23:20 | Variant | Variant number, the r value in the rnnp product revision identifier: 0x0 = Revision 0 |
| 19:16 | Constant | Constant that defines the architecture of the processor:, reads as 0xC = ARMv6-M architecture |
| 15:4 | Partno | Part number of the processor: 0xC20 = Cortex-M0 |
| 3:0 | Revision | Revision number, the p value in the rnnp product revision identifier: 0x0 = Patch 0 |

24.4.3.3. Interrupt Control and State Register

The ICSR:

- provides:
 - a set-pending bit for the Non-Maskable Interrupt (NMI) exception
 - set-pending and clear-pending bits for the PendSV and SysTick exceptions
- indicates:
 - the exception number of the exception being processed
 - whether there are preempted active exceptions
 - the exception number of the highest priority pending exception
 - whether any interrupts are pending.

See the register summary in Table 24-33. ICSR register bit assignments on page 347 for the ICSR attributes. The bit assignments are:

Figure 24-21. ICSR

Table 24-33. ICSR register bit assignments

| BIT | NAME | TYPE | FUNCTION |
|-------|-------------------|------|---|
| 31 | NMIPENDSET | RW | <p>NMI set-pending bit Write: 1: changes NMI exception state to pending 0: no effect Read: 1: NMI exception is pending 0: NMI exception is not pending Because NMI is the highest-priority exception, normally the processor enters the NMI exception handler as soon as it detects a write of 1 to this bit. Entering the handler then clears this bit to 0. This means a read of this bit by the NMI exception handler returns 1 only if the NMI signal is reasserted while the processor is executing that handler.</p> |
| 30:29 | Reserved | RW | Reserved |
| 28 | PENDSVSET | RW | <p>PendSV set-pending bit Write: 1: changes PendSV exception state to pending 0: no effect Read: 1: PendSV exception is pending 0: PendSV exception is not pending Writing 1 to this bit is the only way to set the PendSV state to pending</p> |
| 27 | PENDSVCLR | WO | <p>PendSV clear-pending bit Write: 1: removes the pending state from the PendSV exception 0: no effect</p> |
| 26 | PENDSTSET | RW | <p>SysTick exception set-pending bit. Write: 1: changes SysTick exception state to pending 0: no effect Read: 1: SysTick exception is pending 0: SysTick exception is not pending</p> |
| 25 | PENDSTCLR | WO | <p>SysTick exception clear-pending bit. Write: 1: removes the pending state from the SysTick exception This bit is WO. On a register read it's value is unknown</p> |
| 24:23 | Reserved | RW | Reserved |
| 22 | ISRPENDING | RO | <p>Interrupt pending flag, excluding NMI and Faults: 1: Interrupt pending 0: Interrupt not pending</p> |

| BIT | NAME | TYPE | FUNCTION |
|-------|--------------------|------|--|
| 21:18 | Reserved | RW | Reserved |
| 17:12 | VECTPENDING | RO | Indicates the exception number of the highest priority pending enabled exception: Nonzero: the exception number of the highest priority pending enabled exception 0: no pending exceptions |
| 11:6 | Reserved | RW | Reserved |
| 5:0 | VECTACTIVE* | RO | Contains the active exception number: Nonzero: The exception number* of the currently active exception 0: Thread mode Note: Subtract 16 from this value to obtain the CMSIS IRQ number that identifies the corresponding bit in the Interrupt Clear-Enable, Set-Enable, Clear-Pending, Set-pending, and Priority Register, see Table 24-5. IPSR bit assignments on page 282 |

* This is the same value as IPSR bits[5:0], see Table 24-5. IPSR bit assignments on page 282

When you write to the ICSR, the effect is Unpredictable if you:

- write 1 to the PENDSVSET bit and write 1 to the PENDSVCLR bit
- write 1 to the PENDSTSET bit and write 1 to the PENDSTCLR bit.

24.4.3.4. Application Interrupt and Reset Control Register

The AIRCR provides endian status for data accesses and reset control of the system. See the register summary in Table 24-31. Summary of the SCB register on page 345 and Table 24-34. AIRCR register bit assignments on page 348 for its attributes.

To write to this register, you must write 0x05FA to the VECTKEY field, otherwise the processor ignores the write.

The bit assignments are:

Figure 24-22. AIRCR




Table 24-34. AIRCR register bit assignments

| BIT | NAME | TYPE | FUNCTION |
|-------|------------------|------|---|
| 31:16 | VECTKEY | RW | Register key Read: unknown Write: write 0x05FA to VECTKEY, otherwise the write is ignored |
| 15 | ENDIANESS | RO | Data endianess implemented 0x0: Little Endian |

| BIT | NAME | TYPE | FUNCTION |
|------|----------------------|------|--|
| 14:3 | Reserved | RW | Reserved |
| 2 | SYSRESETREQ | WO | System reset request: Read: This bit reads as 0. Write: 1: requests a system level reset. 0: no effect |
| 1 | VECTCLRACTIVE | WO | Reserved for debug use. This bit reads as 0. When writing to the register you must write 0 to this bit, otherwise behavior is Unpredictable. |
| 0 | Reserved | RW | Reserved |

24.4.3.5. System Control Register

The SCR controls features of entry to and exit from low power state. See the register summary in Table 24-35. SCR register bit assignments on page 349 for its attributes. The bit assignments are:

Figure 24-23. SCR




Table 24-35. SCR register bit assignments

| BIT | NAME | TYPE | FUNCTION |
|------|------------------|------|--|
| 31:5 | Reserved | R | Reserved |
| 4 | SEVONPEND | RW | Send Event on Pending bit: 1: enabled events and all interrupts, including disabled interrupts, can wakeup the processor 0: only enabled interrupts or events can wakeup the processor ,disabled interrupts are excluded When an event or interrupt enters pending state, the event signal wakes up the processor from WFE. If the processor is not waiting for an event ,the event is registered and affects the next WFE. The processor also wakes up on execution of an SEV instruction or external event |
| 3 | Reserved | R | Reserved |
| 2 | SLEEPDEEP | RW | Controls whether the processor uses sleep or deep sleep as its low power mode: 1: deep sleep 0: sleep |

| BIT | NAME | TYPE | FUNCTION |
|-----|-------------|------|---|
| 1 | SLEEPONEXIT | RW | Indicates sleep-on-exit when returning from Handler mode to Thread mode: 1: enter sleep, or deep sleep, on return from an ISR to Thread mode. 0: do not sleep when returning to Thread mode. Setting this bit to 1 enables an interrupt driven application to avoid returning to an empty main application |
| 0 | Reserved | R | Reserved |

24.4.3.6. Configuration and Control Register

The CCR is a read-only register and indicates some aspects of the behavior of the Cortex-M0 processor. See the register summary in Table 24-36. CCR register bit assignments in page 350 for the CCR attributes. The bit assignments are:

Figure 24-24. CCR




Table 24-36. CCR register bit assignments

| BIT | NAME | TYPE | FUNCTION |
|-------|-------------|------|---|
| 31:10 | Reserved | R | Reserved |
| 9 | STKALIGN | RW | Always reads as one, indicates 8-byte stack alignment on exception entry. On exception entry, the processor uses bit[9] of the stacked PSR to indicate the stack alignment. On return from the exception it uses this stacked bit to restore the correct stack alignment. |
| 8:4 | Reserved | R | Reserved |
| 3 | UNALIGN_TRP | RW | Always reads as one, indicates that all unaligned accesses generate a HardFault. |
| 0 | Reserved | R | Reserved |

24.4.3.7. System Handler Priority Registers

The SHPR2-SHPR3 registers set the priority level, 0 to 192, of the exception handlers that have configurable priority.

SHPR2-SHPR3 are word accessible. See the register summary in Table 24-31. Summary of the SCB register on page 345 for their attributes.

To access to the system exception priority level using CMSIS, use the following CMSIS functions:

- `uint32_t NVIC_GetPriority(IRQn_Type IRQn)`
- `void NVIC_SetPriority(IRQn_Type IRQn, uint32_t priority)`

The input parameter IRQn is the IRQ number, see Table 24-10. Properties of the different exception types on

page 292 for more information.

The system fault handlers, and the priority field and register for each handler are:

Table 24-37. System fault handler priority fields

| HANDLER | FIELD | REGISTER DESCRIPTION |
|---------|---------------|--|
| SVCall | PRI_11 | System handler Priority Register 2 on page |
| PendSV | PRI_14 | System Handler Priority register 3 on page |
| SysTick | PRI_15 | System Handler Priority register 3 on page |

Each PRI_N field is 8 bits wide, but the processor implements only bits[7:6] of each field, and bits[5:0] read as zero and ignore writes.

24.4.3.7.1. System Handler Priority Register 2

The bit assignments are:

Figure 24-25. SHPR2




Table 24-38. SHPR2 register bit assignments

| BIT | NAME | TYPE | FUNCTION |
|-------|-----------------|------|---------------------------------------|
| 31:24 | PRI_11 | RW | Priority of system Handler 11, SVCall |
| 23:0 | Reserved | R | Reserved |

24.4.3.7.2. System Handler Priority Register 3

The bit assignments are:

Figure 24-26. SHPR3




Table 24-39. SHPR3 register bit assignments

| BIT | NAME | TYPE | FUNCTION |
|-------|---------------|------|--|
| 31:24 | PRI_15 | RW | Priority of system Handler 15, SysTick exception |

| BIT | NAME | TYPE | FUNCTION |
|-------|-----------------|------|---------------------------------------|
| 23:16 | PRI_14 | RW | Priority of system Handler 14, PendSV |
| 15:0 | Reserved | R | Reserved |

24.4.3.8. SCB usage hints and tips

Ensure software uses aligned 32-bit word size transactions to access all the SCB registers.

24.4.4. System timer, SysTick

When enabled, the timer counts down from the reload value to zero, reloads (wraps to) the value in the SYST_RVR on the next clock cycle, then decrements on subsequent clock cycles. Writing a value of zero to the SYST_RVR disables the counter on the next wrap. When the counter transitions to zero, the COUNTFLAG status bit is set to 1. Reading SYST_CSR clears the COUNTFLAG bit to 0.

Writing to the SYST_CVR clears the register and the COUNTFLAG status bit to 0. The write does not trigger the SysTick exception logic. Reading the register returns its value at the time it is accessed.

Note


When the processor is halted for debugging the counter does not decrement. The system timer registers are:

Table 24-40. System timer register summary

| ADDRESS | NAME | TYPE | RESET VALUE | DESCRIPTION |
|-------------|------------|------|-------------|---|
| 0xE000 E010 | SYST_CSR | RW | 0x0000 0000 | Systick Control and Status Register in chapter 24.4.4.1 on page 352 |
| 0xE000 E014 | SYST_RVR | RW | Unknown | Systick Reload Value Register in chapter 24.4.4.2 on page 353 |
| 0xE000 E018 | SYST_CVR | RW | Unknown | Systick Current Register in chapter 24.4.4.3 on page 354 |
| 0xE000 E01C | SYST_CALIB | RO | 0x0000 0000 | Systick Calibration value Register in chapter 24.4.4.4 on page 354 |

24.4.4.1. SysTick Control and Status Register

The SYST_CSR enables the SysTick features. See the register summary in Table 24-41. SYST_CSR register bit assignments on page 353 for its attributes. The bit assignments are:

Figure 24-27. SYST_CSR

Table 24-41. SYST_CSR register bit assignments

| BIT | NAME | TYPE | FUNCTION |
|-------|-----------|------|---|
| 31:17 | Reserved | R | Reserved |
| 16 | COUNTFLAG | RW | Returns 1 if timer counted to 0 since the last read of this register |
| 15:3 | Reserved | R | Reserved |
| 2 | CLKSOURCE | RW | Selects the SysTick timer clock source 1: HCLK 0: FCLK / 3 |
| 1 | TICKINT | RW | Enables SysTick exception request 1: counting down to zero to assert the SysTick exception request 0: counting down to zero does not assert the SysTick exception request |
| 0 | ENABLE | RW | Enables the counter 1: counter enabled 0: counter disabled |

24.4.4.2. SysTick Reload Value Register

The SYST_RVR specifies the start value to load into the SYST_CVR. See the register summary in Table 24-42. SYST_RVR register bit assignments on page 353 for its attributes. The bit assignments are:

Figure 24-28. SYST_RVR

Table 24-42. SYST_RVR register bit assignments

| BIT | NAME | TYPE | FUNCTION |
|-------|----------|------|--|
| 31:24 | Reserved | R | Reserved |
| 23:0 | RELOAD | RW | Value to load into the SYST_CVR when the counter is enabled and when it reaches 0, see Calculating the RELOAD value. |

24.4.4.2.1. Calculating the RELOAD value

The RELOAD value can be any value in the range 0x0000 00001 – 0x00FF FFFF. You can program a value of 0,

but this has no effect because the SysTick exception request and COUNTFLAG are activated when counting from 1 to 0.

To generate a multi-shot timer with a period of N processor clock cycles, use a RELOAD value of N-1. For example, if the SysTick interrupt is required every 100 clock pulses, set RELOAD to 99.

24.4.4.3. SysTick Current Value Register

The SYST_CVR contains the current value of the SysTick counter. See the register summary in Table 24-43. SYST_CVR register bit assignments on page 354 for its attributes. The bit assignments are:

Figure 24-29. SYST_CVR



Table 24-43. SYST_CVR register bit assignments

| BIT | NAME | TYPE | FUNCTION |
|-------|-----------------|------|--|
| 31:24 | Reserved | R | Reserved |
| 23:0 | CURRENT | RW | Reads return the current value of the SysTick counter. A write of any value clears the field to 0, and also clears the SYST_CSR.COUNTFLAG bit to 0. |

24.4.4.4. SysTick Calibration Value Register

The SYST_CALIB register indicates the SysTick calibration properties. See the register summary in Table 24-44. SYST_CALIB register bit assignments on page 354 for its attributes. The bit assignments are:

Figure 24-30. SYST_CALIB




Table 24-44. SYST_CALIB register bit assignments

| BIT | NAME | TYPE | FUNCTION |
|-----|--------------|------|--|
| 31 | NOREF | R | Reads as one. Indicates no separate reference clock is provided |
| 30 | SKEW | R | Reads as one. Calibration value for the 10ms inexact timing is not known because TENMS is not known. This can affect the suitability of SysTick as a software real time clock. |

| BIT | NAME | TYPE | FUNCTION |
|-------|-----------------|------|---|
| 29:24 | Reserved | R | Reserved |
| 23:0 | TENMS | RW | Reads as zero. Indicates calibration value is not known |

If calibration information is not known, calculate the calibration value required from the frequency of the processor clock or external clock.

24.4.4.5. SysTick usage hints and tips

The interrupt controller clock updates the SysTick counter.

Ensure software uses word accesses to access the SysTick registers.

If the SysTick counter reload and current value are undefined at reset, the correct initialization sequence for the SysTick counter is:

1. Program reload value.
2. Clear current value.
3. Program Control and Status register.

25. LEGAL INFORMATION

Copyright © 2013 Active-Semi, Inc. All rights reserved.

All information provided in this document is subject to legal disclaimers.

Active-Semi reserves the right to modify its products, circuitry or product specifications without notice. Active-Semi products are not intended, designed, warranted or authorized for use as critical components in life-support, life-critical or safety-critical devices, systems, or equipment, nor in applications where failure or malfunction of any Active-Semi product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Active-Semi accepts no liability for inclusion and/or use of its products in such equipment or applications. Active-Semi does not assume any liability arising out of the use of any product, circuit, or any information described in this document. No license, express, implied or otherwise, is granted under any patents, copyrights or other intellectual property rights of Active-Semi or others. Active-Semi assumes no liability for any infringement of the intellectual property rights or other rights of third parties which would result from the use of information contained herein. Customers should evaluate each product to make sure that it is suitable for their applications. Customers are responsible for the design, testing, and operation of their applications and products using Active-Semi products. Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products. All products are sold subject to Active-Semi's terms and conditions of sale supplied at the time of order acknowledgment. Exportation of any Active-Semi product may be subject to export control laws.

Active-Semi™, Active-Semi logo, Solutions for Sustainability™, Power Application Controller™, Micro Application Controller™, Multi-Mode Power Manager™, Configurable Analog Front End™, and Application Specific Power Drivers™ are trademarks of Active-Semi, Inc.

ARM® is a registered trademark and Cortex™ is a trademark of ARM Limited. All referenced brands and trademarks are the property of their respective owners.

For more information on this and other products, contact sales@active-semi.com or visit www.active-semi.com.