

Product Overview

The QPD1003 is a 500W (P_{3dB}) internally matched discrete GaN on SiC HEMT which operates from 1.2 to 1.4 GHz and a 50V supply rail. The device is GaN IMFET fully matched to 50 Ω in an industry standard air cavity package and is ideally suited for military and civilian Radar. The device can support pulsed and linear operations.

ROHS compliant.

Evaluation boards are available upon request.



17.40 x 24.0 x 4.31 mm

QPD1003PC4B01 Pulsed Performance

Freq.(GHz)	P_{3dB} (W)	G_{3dB} (dB)	DE_{3dB} (%)
1.2	517.5	15.6	59.4
1.3	458.7	16.8	63.3
1.4	440.0	15.5	60.9

Pulse CW: Pulse Width = 1 ms, Duty Cycle = 10%

$V_D = +50$ V, $I_{DQ} = 750$ mA, Baseplate Temperature of 25°C


Key Features

- Frequency: 1.2 to 1.4 GHz
- Linear Gain¹: 18.6 dB
- Output Power (P_{3dB})¹: 517.5 W
- Gain (P_{3dB})¹: 15.6 dB
- DE (P_{3dB})¹: 59.4%
- Operating Voltage: 50 V
- Low thermal resistance package
- Pulse capable

Notes:

1. Typical EVB Performance at 1.2 GHz

Functional Block Diagram



Applications

- Military Radar
- Civilian Radar

Ordering Information

Part Number	Description
1131389	1.2 – 1.4 GHz RF IMFET
1131532 (QPD1003PC4B01)	1.2 – 1.4 GHz EVB

Absolute Maximum Ratings¹

Parameter	Rating	Units
Breakdown Voltage (V_{D0})	+145	V
Gate Voltage (V_G)	-7 to +2	V
Drain Current (I_D)	20	A
Power Dissipation (P_D) ²	410	W
RF Input Power (RF_{IN}) ^{2,3}	+42	dBm
Mounting Temperature (30 seconds)	320	°C
Storage Temperature	-65 to +150	°C

Notes:

1. Operation of this device outside the parameter ranges given above may cause permanent damage.
2. Pulsed CW: Duty Cycle = 10%, Pulse Width = 1 ms
3. Frequency at 1.3 GHz, T = 25 °C

Recommended Operating Conditions¹

Parameter	Min	TYP	Max	Units
Operating Temperature	-40	+25	+85	°C
Drain Voltage (V_D)	+28	+50	+55	V
Drain Bias Current (I_{DQ})	-	750	-	mA
Drain Current (I_D)	-	15	-	A
Gate Voltage (V_G) ³	-	-2.8	-	V
Power Dissipation (P_D) ²	-	-	370	W

Notes:

1. Electrical performance is measured under conditions noted in the electrical specifications table. Specifications are not guaranteed over all recommended operating conditions.
2. Pulsed CW: Pulse Width = 1 ms, Duty Cycle = 10
Package base at 85°C
3. To be adjusted to desired I_{DQ}

Pulsed Characterization – Load Pull Performance – Power Tuned¹

Parameters	Typical Values			Units
	1.2	1.3	1.4	
Frequency	1.2	1.3	1.4	GHz
Linear Gain (G_{LIN})	19	19.9	18.6	dB
Output Power at 3dB Compression (P_{3dB})	57.3	57.3	57	dBm
Power-Added-Efficiency at 3dB Compression (PAE_{3dB})	55.1	57.6	56.9	%
Gain at 3dB Compression (G_{3dB})	16	16.9	15.6	dB

Notes:

1. Test conditions unless otherwise noted: $V_D = +50$ V, $I_{DQ} = 750$ mA, $T_A = +25$ °C, Pulse Width = 1 ms, Duty Cycle = 10%

Pulsed Characterization – Load Pull Performance – Efficiency Tuned¹

Parameters	Typical Values			Units
	1.2	1.3	1.4	
Frequency	1.2	1.3	1.4	GHz
Linear Gain (G_{LIN})	20.3	20.6	19.4	dB
Output Power at 3dB Compression (P_{3dB})	55.4	55.6	55.3	dBm
Power-Added-Efficiency at 3dB Compression (PAE_{3dB})	70.3	66.7	67.4	%
Gain at 3dB Compression (G_{3dB})	17.3	17.6	16.4	dB

Notes:

1. Test conditions unless otherwise noted: $V_D = +50$ V, $I_{DQ} = 750$ mA, $T_A = +25$ °C, Pulse Width = 1 ms, Duty Cycle = 10%

RF Characterization – 1.2 – 1.4 GHz EVB Performance at 1.2 GHz¹

Parameters	Typical Values			Units
Linear Gain (G_{LIN})	-	18.6	-	dB
Output Power at 3dB Compression (P_{3dB})	-	57.1	-	dBm
Drain Efficiency at 3dB Compression (DE_{3dB})	-	59.4	-	%
Gain at 3dB Compression (G_{3dB})	-	15.6	-	dB

Notes:

1. Test conditions: Pulse Width = 1 ms, Duty Cycle = 10%, $V_D = +50$ V, $I_{DQ} = 750$ mA, $T_A = +25$ °C

RF Characterization – 1.2 – 1.4 GHz EVB Performance at 1.3 GHz¹

Parameters	Typical Values			Units
Linear Gain (G_{LIN})	-	19.8	-	dB
Output Power at 3dB Compression (P_{3dB})	-	56.6	-	dBm
Drain Efficiency at 3dB Compression (DE_{3dB})	-	63.3	-	%
Gain at 3dB Compression (G_{3dB})	-	16.8	-	dB

Notes:

1. Test conditions: Pulse Width = 1 ms, Duty Cycle = 10%, $V_D = +50$ V, $I_{DQ} = 750$ mA, $T_A = +25$ °C

RF Characterization – 1.2 – 1.4 GHz EVB Performance at 1.4 GHz¹

Parameters	Typical Values			Units
Linear Gain (G_{LIN})	-	18.5	-	dB
Output Power at 3dB Compression (P_{3dB})	-	56.4	-	dBm
Drain Efficiency at 3dB Compression (DE_{3dB})	-	60.9	-	%
Gain at 3dB Compression (G_{3dB})	-	15.5	-	dB

Notes:

1. Test conditions: Pulse Width = 1 ms, Duty Cycle = 10%, $V_D = +50$ V, $I_{DQ} = 750$ mA, $T_A = +25$ °C

RF Characterization – Mismatch Ruggedness at 1.3 GHz¹

Symbol	Parameter	dB Compression	Typical
VSWR	Impedance Mismatch Ruggedness	3	5:1


Notes:

1. Test conditions unless otherwise noted: $V_D = +50$ V, $I_{DQ} = 750$ mA, $T_A = +25$ °C, Pulse Width = 1 ms, Duty Cycle = 10%
2. Driving input power is determined at pulsed compression under matched condition at EVB output connector.

Thermal and Reliability Information – Pulsed

Peak IR Surface Temperature vs. Pulse Width

$P_{diss} = 346 \text{ W}$, Base Temperature @ $85 \text{ }^\circ\text{C}$



Parameter	Conditions	Values	Units
Thermal Resistance, IR^1 (θ_{JC})	85 °C back side temperature	0.3	°C/W
Peak IR Surface Temperature ¹ (T_{CH})	346 W P_D , Pulse Width = 1 ms, Duty Cycle = 10%	189	°C

Notes:


1. Refer to the following document [GaN Device Channel Temperature, Thermal Resistance, and Reliability Estimates](#)

Load Pull Contours^{1, 2}

Notes:

1. $V_D = 50\text{ V}$, $I_{DQ} = 750\text{ mA}$, Pulse Width = 1 ms. Duty Cycle = 10%. Performance is at 3dB gain compression referenced to peak gain.
2. See page 11 for load-pull and source-pull reference planes. 50 Ω load-pull TRL fixtures are built with 20 mils RO4350B material.

1.2GHz, Load-pull




Load Pull Contours^{1, 2}

Notes:

1. $V_D = 50\text{ V}$, $I_{DQ} = 750\text{ mA}$, Pulse Width = 1 ms. Duty Cycle = 10%. Performance is at 3dB gain compression referenced to peak gain.
2. See page 11 for load-pull and source-pull reference planes. 50 Ω load-pull TRL fixtures are built with 20 mils RO4350B material.

1.3GHz, Load-pull




Load Pull Contours^{1, 2}

Notes:

1. $V_D = 50\text{ V}$, $I_{DQ} = 750\text{ mA}$, Pulse Width = 1 ms. Duty Cycle = 10%. Performance is at 3dB gain compression referenced to peak gain.
2. See page 11 for load-pull and source-pull reference planes. 50 Ω load-pull TRL fixtures are built with 20 mils RO4350B material.







1.4GHz, Load-pull



Typical Performance – Load-Pull Drive-up^{1, 2}

Notes:





1. Pulse Width = 1 ms, Duty Cycle = 10%, $V_D = 50\text{ V}$, $I_{DQ} = 750\text{ mA}$
2. See page 11 for load-pull and source-pull reference planes where the performance was measured.



Power Drive-Up Performance Over Temperatures of 1.2 – 1.4 GHz EVB¹

Notes:





1. Pulse Width = 1 ms, Duty Cycle = 10%, $V_D = 50$ V, $I_{DQ} = 750$ mA




Power Drive-Up Performance at 25 C of 1.2 – 1.4 GHz EVB¹

Notes:

1. Pulse Width = 1 ms, Duty Cycle = 10%, $V_D = 50\text{ V}$, $I_{DQ} = 750\text{ mA}$



Pin Configuration and Package Marking¹




Pin	Symbol	Description
1	V_G / RF_{IN}	Gate Voltage / RF Input
2	V_D / RF_{OUT}	Drain Voltage / RF Output
3	GND	Package base/ Ground

Notes:

- The QPD1003 will be marked with the “1003” designator and a lot code marked below the part designator. The “YY” represents the last two digits of the calendar year the part was manufactured, the “WW” is the work week of the assembly lot start, the “MXXX” is the production lot number.


Assembly Notes

1. Carefully clean the PC board and package leads with alcohol. Allow it to dry fully.
2. To improve the thermal and RF performance, Qorvo recommends attaching a heat sink to the bottom of the PCB and apply thermal compound (Arctic Silver 5 recommended or 4 mil indium shim between the heat sink and the package).
3. (The following is for *information only*. There are many variables in a second level assembly that Qorvo does not control, so Qorvo does not recommend an absolute torque value.) Use screws to attach the component to the heat sink. A suggested torque value is 16 in-oz. for a 0-80 screw. Start with screws finger tight, then torque to 8 in-oz., then torque to final value. Use the following tightening pattern.



4. Apply no-flux solder to each pin of the QPD1003. The component leads should be manually soldered, and the package cannot be subjected to conventional reflow processes. The use of no-clean solder to avoid washing after soldering is recommended.


Package Dimensions^{1, 2, 3, 4, 5}



Notes:

1. All dimensions are in mm. Unless otherwise noted, the tolerance is ± 0.15 mm.
2. Package is an all metal design with ceramic lid and feed thru's.
3. Package is Ni/Au plated.
4. Package is epoxy sealed.
5. For instruction to mount the part, please refer to application note "[RF565 Package Mounting, Mechanical Mounting and PCB Considerations.](#)"

Schematic – 1.2 – 1.4 GHz EVB




Bias-up Procedure

1. Set V_G to -4 V
2. Set I_D current limit to 800 mA.
3. Set V_D to 50 V.
4. Slowly adjust V_G until I_D is set to 750 mA.
5. Set I_D current limit to 2 A.
6. Apply RF.

Bias-down Procedure

1. Turn off RF signal.
2. Turn off V_D .
3. Wait 2 seconds to allow drain capacitor to discharge
4. Turn off V_G

1.2 – 1.4 GHz EVB¹



Notes:

1. PCB Material: RO4350B, 20 mil thickness, 1 oz copper cladding

Bill of Material – 1.2 – 1.4 GHz EVB

Ref Des	Value	Qty	Manufacturer	Part Number
C1	680 uF	1	Panasonic	EEU-FC2A681
C4, C5	82 pF	2	ATC	ATC600S820JT250XT
C9	1000 pF	1	Samsung	CL31B102KGFNFNE
C6, C19	27 pF	2	ATC	600S270JT250XT
C7, C12	10000 pF	2	Panasonic	ECJ-2VB2A103K
C8	0.1 uF	1	Panasonic	ECJ-3YB2A104K
C10	100 pF	1	ATC	ATC800A101JT250X
C13	0.1 uF	1	Kemet	C0805C104K5RACTU
C14, C16	10 uF	2	Panasonic	ECA-2AM100
C17, C18	10000 pF	2	Samsung	CL31B103KGFNFNE
R2	51 Ω	1	Panasonic	ERJ-6GEYJ510
R3	10 Ω	1	Panasonic	ERJ-8GEYJ100V
R4	510 Ω	1	Panasonic	ERJ-6GEYJ511
L1	100 nH	1	Coilcraft	0603LS-101XJLB
L3, L4	N/A	1	STEWART, INC.	35F0121-1SR-10
L5, L6	N/A	1	STEWART, INC.	28F0181-1SR-10

Handling Precautions

Parameter	Rating	Standard
ESD – Human Body Model (HBM)	Class 1B (950 V)	ESDA / JEDEC JS-001-2012
ESD – Charged Device Model (CDM)	Class C3 (1000 V)	JEDEC JESD22-C101F
MSL – Moisture Sensitivity Level	MSL3	IPC/JEDEC J-STD-020



Caution!
ESD-Sensitive Device

Solderability

The component leads should be manually soldered, and the package cannot be subjected to conventional reflow processes. Soldering of the component leads is compatible with the latest version of J-STD-020, lead-free solder, 260 °C. The use of no-clean solder to avoid washing after soldering is recommended.

RoHS Compliance

This part is compliant with 2011/65/EU RoHS directive (Restrictions on the Use of Certain Hazardous Substances in Electrical and Electronic Equipment) as amended by Directive 2015/863/EU.

This product also has the following attributes:

- Halogen Free (Chlorine, Bromine)
- Antimony Free
- TBBP-A (C₁₅H₁₂Br₄O₂) Free
- PFOS Free
- SVHC Free

Contact Information

For the latest specifications, additional product information, worldwide sales and distribution locations:

Web: www.qorvo.com

Tel: 1-844-890-8163

Email: customer.support@qorvo.com

Important Notice

The information contained in this Data Sheet and any associated documents (“Data Sheet Information”) is believed to be reliable; however, Qorvo makes no warranties regarding the Data Sheet Information and assumes no responsibility or liability whatsoever for the use of said information. All Data Sheet Information is subject to change without notice. Customers should obtain and verify the latest relevant Data Sheet Information before placing orders for Qorvo® products. Data Sheet Information or the use thereof does not grant, explicitly, implicitly or otherwise any rights or licenses to any third party with respect to patents or any other intellectual property whether with regard to such Data Sheet Information itself or anything described by such information.

DATA SHEET INFORMATION DOES NOT CONSTITUTE A WARRANTY WITH RESPECT TO THE PRODUCTS DESCRIBED HEREIN, AND QORVO HEREBY DISCLAIMS ANY AND ALL WARRANTIES WITH RESPECT TO SUCH PRODUCTS WHETHER EXPRESS OR IMPLIED BY LAW, COURSE OF DEALING, COURSE OF PERFORMANCE, USAGE OF TRADE OR OTHERWISE, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. Without limiting the generality of the foregoing, Qorvo® products are not warranted or authorized for use as critical components in medical, life-saving, or life-sustaining applications, or other applications where a failure would reasonably be expected to cause severe personal injury or death. Applications described in the Data Sheet Information are for illustrative purposes only. Customers are responsible for validating that a particular product described in the Data Sheet Information is suitable for use in a particular application.

© 2026 Qorvo US, Inc. All rights reserved. This document is subject to copyright laws in various jurisdictions worldwide and may not be reproduced or distributed, in whole or in part, without the express written consent of Qorvo US, Inc. | QORVO® is a registered trademark of Qorvo US, Inc.