


Product Overview

Qorvo’s QPA1011 is an X-band high power MMIC amplifier fabricated on Qorvo’s production 0.15um GaN on SiC process (QGaN15). The QPA1011 operates from 7.9 – 11 GHz and typically provides 25 W saturated output power with power-added efficiency of 40% and large-signal gain of 19.5 dB. This combination of wideband performance provides the flexibility designers are looking for to improve system performance while reducing size and cost.

QPA1011 can also support a variety of operating conditions to best support system requirements. With good thermal properties, it can support a range of bias voltages and will perform well under both CW and pulse operations. The

QPA1011 is matched to 50Ω with integrated DC blocking capacitors on both RF I/O ports simplifying system integration. The wideband performance and operational flexibility allow it support satellite communication and data links, as well as military and commercial radar systems.

Lead-free and RoHS compliant




24-Lead 4.5 x 5.0 x 1.64 mm Air Cavity Laminate Package

Key Features

- Frequency Range: 7.9 – 11 GHz
- P_{OUT} (P_{IN} = 25 dBm): 44.5 dBm
- PAE (P_{IN} = 25 dBm): 40 %
- IM3 (P_{OUT}/Tone = 38 dBm): -20 dBc
- Small Signal Gain: 25 dB
- Integrated Power Detector
- Bias: Pulsed V_D = 24 V, I_{DQ} = 1200 mA, V_G = -2.1 V typ. range, PW = 100 uS, DC = 10%
- Package Dimensions: 4.5 x 5.0 x 1.64 mm

Performance is typical across frequency. Please reference electrical specification table and data plots for more details.

Functional Block Diagram



Applications

- Satellite Communications
- Data Links
- Military and commercial Radar

Ordering Information

Part No.	Description
QPA1011TR7	250 Piece 7" Reel
QPA1011PCB4B01	Evaluation Board

Absolute Maximum Ratings

Parameter	Value / Range
Drain Voltage (V_D)	29.5 V
Gate Voltage Range (V_G)	-6 V to 0 V
Drain Current (I_{D1}), $T_{BASE} = 85\text{ }^\circ\text{C}$ max (bias 1 side vs. 2 sides)	1 side: 672 mA 2 sides: 1344 mA
Drain Current (I_{D2}), $T_{BASE} = 85\text{ }^\circ\text{C}$ max	2880 mA
Drain Current Total (I_D), $T_{BASE} = 85\text{ }^\circ\text{C}$ max (bias 1 side vs. 2 sides)	1 side: 3552 mA 2 sides: 4224 mA
Gate Current (I_G)	See p. 27
Power Dissipation (P_{DISS}), $T_{BASE} = 85\text{ }^\circ\text{C}$, CW	70 W
Input Power (P_{IN}), 50 Ω , Pulsed $V_D = 28$ V or CW $V_D = 24$ V, $I_{DQ} = 1200$ mA, $T_{BASE} = 85\text{ }^\circ\text{C}$	30 dBm
Input Power (P_{IN}), 3:1 VSWR, Pulsed $V_D = 28$ V or CW $V_D = 24$ V, $I_{DQ} = 1200$ mA, $T_{BASE} = 85\text{ }^\circ\text{C}$	29 dBm
Mounting Temperature (30 seconds)	260 $^\circ\text{C}$
Storage Temperature	-55 to +150 $^\circ\text{C}$

Operation of this device outside the parameter ranges given above may cause permanent damage. These are stress ratings only, and functional operation of the device at these conditions is not implied.

Recommended Operating Conditions

Parameter	Min	Typ.	Max	Unit
Drain Voltage (V_D)		24	28	
Drain Current Total, Quiescent ($I_{DQ} = I_{D1} + I_{D2}$)		1200		mA
Gate Voltage Typ. Range (V_G)	-1.5 to -2.9			V
Drain Current Total, RF (I_{D_Drive})	See plot page			mA
Gate Current, RF (I_{G_Drive})	5, 8-10, 12, 15-17			
Input Power @ Saturation (P_{IN}) ⁽²⁾	$T_{BASE} -40^\circ\text{C}$: 25			dBm
	$T_{BASE} +25^\circ\text{C}$: 25			
	$T_{BASE} +85^\circ\text{C}$: 27 ⁽¹⁾			
Operating Temp. Range (T_{BASE}) ⁽³⁾	-40		+85	$^\circ\text{C}$

1. CW, $V_D > 24$ V @ $T_{BASE} +85^\circ\text{C}$ requires thermal consideration, recommended 25 dBm P_{IN} max.

2. See P_{IN} vs. T_{BASE} plots page 6, 7, 13, 14

3. T_{BASE} is back side of QPA1011

Electrical specifications are measured at specified test conditions. Specifications are not guaranteed over all recommended operating conditions.

Electrical Specifications







Parameter	Conditions ⁽¹⁾ ⁽²⁾	Min	Typ.	Max	Units
Operational Frequency Range		7.9		11	GHz
Output Power at Saturation, P _{SAT}	P _{IN} = 25 dBm Pulsed V _D	7.9 GHz	44	45	dBm
		9.5 GHz	45	45.5	
		11.0 GHz	43.5	45	
Power Added Efficiency, PAE	P _{IN} = 25 dBm Pulsed V _D	7.9 GHz	36	40	%
		9.5 GHz	35		
		11.0 GHz	35		
3 RD Intermodulation Products, IM3	P _{OUT} /Tone = 38 dBm, CW ΔF = 1 MHz		-20		dBc
5 RD Intermodulation Products, IM5			-35		
Small Signal Gain, S ₂₁	P _{IN} = -25 dBm, CW		25		dB
Input Return Loss, IRL			15		
Output Return Loss, ORL			10		
P _{SAT} Temperature Coefficient	T _{DIFF} = 25 °C to 85 °C; P _{IN} = 25 dBm		-0.01		dBm/°C
S ₂₁ Temperature Coefficient	T _{DIFF} = 25 °C to 85 °C		-0.05		dB/°C
Gate leakage	V _D = 10 V, V _G = -4 V	-13.2		0.1	mA

Notes:

1. Test conditions unless otherwise noted: Pulsed V_D = 24 V, I_{DQ} = 1200 mA, V_G = -2.2 V +/- 0.7 V typical, PW = 100 us, DC = 10%, T_{BASE} = 25°C, Z₀ = 50 Ω
2. T_{BASE} is back side of QPA1011







Performance Plots – Large Signal (Pulsed)

Test conditions, unless otherwise noted: Pulsed $V_D = 24\text{ V}$, $I_{DQ} = 1.2\text{ A}$, $P_{IN} = 25\text{ dBm}$, $PW = 100\text{ }\mu\text{s}$, $DC = 10\%$, $T_{BASE} = +25\text{ }^\circ\text{C}$ (T_{BASE} is backside of QPA1011).









Performance Plots – Large Signal (Pulsed)

Test conditions, unless otherwise noted: Pulsed $V_D = 24\text{ V}$, $I_{DQ} = 1.2\text{ A}$, $P_{IN} = 25\text{ dBm}$, $PW = 100\text{ }\mu\text{s}$, $DC = 10\%$, $T_{BASE} = +25\text{ }^\circ\text{C}$ (T_{BASE} is backside of QPA1011).









Performance Plots – Large Signal (Pulsed)

Test conditions, unless otherwise noted: Pulsed $V_D = 24\text{ V}$, $I_{DQ} = 1.2\text{ A}$, $P_{IN} = 25\text{ dBm}$, $PW = 100\text{ us}$, $DC = 10\%$, $T_{BASE} = +25\text{ }^\circ\text{C}$ (T_{BASE} is backside of QPA1011).









Performance Plots – Large Signal (Pulsed)

Test conditions, unless otherwise noted: Pulsed $V_D = 24\text{ V}$, $I_{DQ} = 1.2\text{ A}$, $P_{IN} = 25\text{ dBm}$, $PW = 100\text{ }\mu\text{s}$, $DC = 10\%$, $T_{BASE} = +25\text{ }^\circ\text{C}$ (T_{BASE} is backside of QPA1011).








Performance Plots – Large Signal (Pulsed)

Test conditions, unless otherwise noted: Pulsed $V_D = 24\text{ V}$, $I_{DQ} = 1.2\text{ A}$, $P_{IN} = 25\text{ dBm}$, $PW = 100\text{ us}$, $DC = 10\%$, $T_{BASE} = +25\text{ }^\circ\text{C}$ (T_{BASE} is backside of QPA1011).








Performance Plots – Large Signal (Pulsed)

Test conditions, unless otherwise noted: Pulsed $V_D = 24\text{ V}$, $I_{DQ} = 1.2\text{ A}$, $P_{IN} = 25\text{ dBm}$, $PW = 100\text{ }\mu\text{s}$, $DC = 10\%$, $T_{BASE} = +25\text{ }^\circ\text{C}$ (T_{BASE} is backside of QPA1011).









Performance Plots – Large Signal (Pulsed)

Test conditions, unless otherwise noted: Pulsed $V_D = 24\text{ V}$, $I_{DQ} = 1.2\text{ A}$, $P_{IN} = 25\text{ dBm}$, $PW = 100\text{ }\mu\text{s}$, $DC = 10\%$, $T_{BASE} = +25\text{ }^\circ\text{C}$ (T_{BASE} is backside of QPA1011).









Performance Plots – Large Signal (CW)

Test conditions, unless otherwise noted: CW, $V_D = 24\text{ V}$, $I_{DQ} = 1.2\text{ A}$, $P_{IN} = 25\text{ dBm}$, $T_{BASE} = +25\text{ }^\circ\text{C}$ (T_{BASE} is backside of QPA1011).









Performance Plots – Large Signal CW

Test conditions, unless otherwise noted: CW, $V_D = 24\text{ V}$, $I_{DQ} = 1.2\text{ A}$, $P_{IN} = 25\text{ dBm}$, $T_{BASE} = +25\text{ }^\circ\text{C}$ (T_{BASE} is backside of QPA1011).









Performance Plots – Large Signal (CW)

Test conditions, unless otherwise noted: CW, $V_D = 24\text{ V}$, $I_{DQ} = 1.2\text{ A}$, $P_{IN} = 25\text{ dBm}$, $T_{BASE} = +25\text{ }^\circ\text{C}$ (T_{BASE} is backside of QPA1011).









Performance Plots – Large Signal (CW)

Test conditions, unless otherwise noted: CW, $V_D = 24\text{ V}$, $I_{DQ} = 1.2\text{ A}$, $P_{IN} = 25\text{ dBm}$, $T_{BASE} = +25\text{ }^\circ\text{C}$ (T_{BASE} is backside of QPA1011).








Performance Plots – Large Signal (CW)

Test conditions, unless otherwise noted: CW, $V_D = 24\text{ V}$, $I_{DQ} = 1.2\text{ A}$, $P_{IN} = 25\text{ dBm}$, $T_{BASE} = +25\text{ }^\circ\text{C}$ (T_{BASE} is backside of QPA1011).








Performance Plots – Large Signal (CW)

Test conditions, unless otherwise noted: CW, $V_D = 24\text{ V}$, $I_{DQ} = 1.2\text{ A}$, $P_{IN} = 25\text{ dBm}$, $T_{BASE} = +25\text{ }^\circ\text{C}$ (T_{BASE} is backside of QPA1011).









Performance Plots – Large Signal (CW)

Test conditions, unless otherwise noted: CW, $V_D = 24\text{ V}$, $I_{DQ} = 1.2\text{ A}$, $P_{IN} = 25\text{ dBm}$, $T_{BASE} = +25\text{ }^\circ\text{C}$ (T_{BASE} is backside of QPA1011).






Performance Plots – Large Signal (CW)

Test conditions, unless otherwise noted: CW, $V_D = 24\text{ V}$, $I_{DQ} = 1.2\text{ A}$, $P_{IN} = 25\text{ dBm}$, $T_{BASE} = +25\text{ }^\circ\text{C}$ (T_{BASE} is backside of QPA1011).









Performance Plots – Large Signal (CW)

Test conditions, unless otherwise noted: CW, $V_D = 24\text{ V}$, $I_{DQ} = 1.2\text{ A}$, $P_{IN} = 25\text{ dBm}$, $T_{BASE} = +25\text{ }^\circ\text{C}$ (T_{BASE} is backside of QPA1011).









Performance Plots – Linearity (CW)

Test conditions, unless otherwise noted: CW, $V_D = 24\text{ V}$, $I_{DQ} = 1200\text{ mA}$, $\Delta f = 1\text{ MHz}$, $T_{BASE} = +25\text{ }^\circ\text{C}$ (T_{BASE} is backside of QPA1011).









Performance Plots – Linearity (CW)

Test conditions, unless otherwise noted: CW, $V_D = 24\text{ V}$, $I_{DQ} = 1200\text{ mA}$, $\Delta f = 1\text{ MHz}$, $T_{BASE} = +25\text{ }^\circ\text{C}$ (T_{BASE} is backside of QPA1011).









Performance Plots – Linearity (CW)

Test conditions, unless otherwise noted: CW, $V_D = 24\text{ V}$, $I_{DQ} = 1200\text{ mA}$, $\Delta f = 1\text{ MHz}$, $T_{BASE} = +25\text{ }^\circ\text{C}$ (T_{BASE} is backside of QPA1011).









Performance Plots – Harmonics (CW)

Test conditions, unless otherwise noted: CW, $V_D = 24\text{ V}$, $I_{DQ} = 1200\text{ mA}$, $\Delta f = 1\text{ MHz}$, $T_{BASE} = +25\text{ }^\circ\text{C}$ (T_{BASE} is backside of QPA1011).






Performance Plots – Small Signal (CW)

Test conditions, unless otherwise noted: CW, $V_D = 24\text{ V}$, $I_{DQ} = 1200\text{ mA}$, $T_{BASE} = +25\text{ }^\circ\text{C}$ (T_{BASE} is backside of QPA1011).



Performance Plots – Small Signal (CW)

Test conditions, unless otherwise noted: CW, $V_D = 24\text{ V}$, $I_{DQ} = 1200\text{ mA}$, $T_{BASE} = +25\text{ °C}$ (T_{BASE} is backside of QPA1011).




Thermal and Reliability Information

Parameter	Test Conditions	Value	Units
Thermal Resistance, θ_{JC} ⁽¹⁾	CW , $T_{BASE} = 85^{\circ}\text{C}$, $V_D = +24\text{V}$, $I_{DQ} = 1200\text{ mA}$, no RF ,	1.46	$^{\circ}\text{C}/\text{W}$
Channel Temperature, T_{CH} (No RF) ⁽²⁾	$P_{DISS} = 28.8\text{ W}$	127	$^{\circ}\text{C}$
Thermal Resistance, θ_{JC} ⁽¹⁾	Pulsed , $T_{BASE} = 85^{\circ}\text{C}$, $V_D = +24\text{ V}$, $I_{DQ} = 1200\text{ mA}$, V_D (100 $\mu\text{s}/10\%$), Freq = 9.75 GHz, $P_{IN} = 25\text{ dBm}$,	1.0	$^{\circ}\text{C}/\text{W}$
Channel Temperature, T_{CH} (Under RF drive) ⁽²⁾	$I_{D_Drive} = 3.3\text{ A}$, $P_{OUT} = 44.7\text{ dBm}$, $P_{DISS} = 48.9\text{ W}$	134	$^{\circ}\text{C}$
Thermal Resistance, θ_{JC} ⁽¹⁾	CW , $T_{BASE} = 85^{\circ}\text{C}$, $V_D = +24\text{ V}$, $I_{DQ} = 1200\text{ mA}$, Freq = 9.75 GHz, $P_{IN} = 25\text{ dBm}$, $I_{D_Drive} = 2.9\text{ A}$,	1.38	$^{\circ}\text{C}/\text{W}$
Channel Temperature, T_{CH} (Under RF drive) ⁽²⁾	$P_{OUT} = 44.2\text{ dBm}$, $P_{DISS} = 44.7\text{ W}$	147	$^{\circ}\text{C}$
Thermal Resistance, θ_{JC} ⁽¹⁾	CW , $T_{BASE} = 85^{\circ}\text{C}$, $V_D = +20\text{V}$, $I_{DQ} = 1200\text{ mA}$, no RF ,	1.46	$^{\circ}\text{C}/\text{W}$
Channel Temperature, T_{CH} (No RF) ⁽²⁾	$P_{DISS} = 24\text{ W}$	120	$^{\circ}\text{C}$
Thermal Resistance, θ_{JC} ⁽¹⁾	Pulsed , $T_{BASE} = 85^{\circ}\text{C}$, $V_D = +20\text{ V}$, $I_{DQ} = 1200\text{ mA}$, V_D (100 $\mu\text{s}/10\%$), Freq = 9.25 GHz, $P_{IN} = 25\text{ dBm}$,	0.95	$^{\circ}\text{C}/\text{W}$
Channel Temperature, T_{CH} (Under RF drive) ⁽²⁾	$I_{D_Drive} = 3.0\text{ A}$, $P_{OUT} = 44.1\text{ dBm}$, $P_{DISS} = 34.6\text{ W}$	118	$^{\circ}\text{C}$
Thermal Resistance, θ_{JC} ⁽¹⁾	CW , $T_{BASE} = 85^{\circ}\text{C}$, $V_D = +20\text{ V}$, $I_{DQ} = 1200\text{ mA}$, Freq = 9.5 GHz, $P_{IN} = 25\text{ dBm}$, $I_{D_Drive} = 2.8\text{ A}$,	1.44	$^{\circ}\text{C}/\text{W}$
Channel Temperature, T_{CH} (Under RF drive) ⁽²⁾	$P_{OUT} = 43.7\text{ dBm}$, $P_{DISS} = 33\text{ W}$	132	$^{\circ}\text{C}$

Notes:



1. Thermal resistance determined to T_{BASE} (T_{BASE} is backside of package QPA1011)
2. Channel temperature indicated is an IR scan equivalent temperature. Thermal resistance is calculated using this value. Additional information can be found in the Qorvo Applications Note "GaN Device TCHMAX Theta-JC and Reliability Estimates," located here <https://www.qorvo.com/products/d/da006480>

Maximum Gate Current




Channel Temperature is an IR scan equivalent

Dissipated Power



T_{BASE} = $85 \text{ }^\circ\text{C}$ (T_{BASE} is back side of QPA1011)

Applications Information for Pulsed and Linear Operations



- Tie all V_D's (V_{D1}, V_{D2}, top, bottom) together at the harness level to form V_D; tie the same for V_G (top, bottom) to form V_G
- The extra bypassing components R6, R17, C5 and C14 are required for optimum linearity
- If not using power detector function: recommended terminate V_{REF} and V_{DET} (pin 11, 12, 16, 17) with 50 Ohm (R8, R9, R18, R19 not needed)


Bias-Up Procedure

1. Set limit: I_D = 4000 mA, I_G = 20 mA
2. Turn on V_G = -5 V
3. Turn on V_D to 24 V. Ensure I_{DQ} ~ 0 mA
4. Adjust V_G until I_{DQ} = 1200 mA (V_G ≈ -2.2 +/- 0.7 V typical)
5. Turn on RF signal

Bias-Down Procedure

1. Turn off RF signal
2. Reduce V_G to -5 V. Ensure I_{DQ} ~ 0 mA
3. Set V_D to 0 V
4. Turn off V_D
5. Turn off V_G




Evaluation Board (EVB) Layout for Pulsed and Linear Operations



T_{BASE} is backside QPA1011
 Slide Thermocouple into Carrier's hole
 T_{BASE} ≈ Thermocouple + Offset °C
 Offset Pulsed = 10 °C, CW = 40 °C

Thru full loss (PCB, 2.9mm connectors) = 1 dB

Use screw (x4 to mount on cold plate or fan (apply thermal compound between interfaces)



Layer	Name	Material	Thickness	Constant	Board Layer Stack
1	SILKSCREEN_TOP				
2	SOLDERMASK_TOP	Solder Resist	0.40mil	0	
3	METAL1_TOP	Copper	0.70mil		
4	DIELECTRIC 1	ROGERS 4003C	8.00mil	3.38	
5	METAL2_GND	Copper	0.70mil		
6	DIELECTRIC 2	370HR	6.00mil	3.82	
7	METAL3_GND	Copper	0.70mil		
8	DIELECTRIC 3	370HR	6.00mil	4.14	
9	METAL4_BOT	Copper	0.70mil		


PCB is a multilayer:

1. Total thickness: 25.3 mil
2. Via, 98 mil round, is Cu-coined required for optimum thermal management
3. Other vias, 8 mil round, is non-conductive epoxy filled

Bill of Materials

Reference Des.	Qty	Value	Description	Part Number
C1, C10	2	10 uF	CAP, 10uF, ±20%, 50V, X5R, 1206	
C2, C6, C9, C13	4	0.01 uF	CAP, 0.01uF, ±10%, 50V, X7R, 0402	
R1, R12	2	5.1 Ω	RES, 5.1 Ohm, ±5%, 50V, 0402	
R2, R3, R7, R11, R15, R16	6	0 Ω	RES, 0 Ohm, Jumper, 0402	
R8, R9, R18, R19	4	25.5K Ω	RES, 25.5K Ohm, ±1%, 1/16W, 0402	
Optional for CW and optimum linearity (These 4 components are not included in Qorvo EVB – pulsed):				
C5, C14	2	10 uF	CAP, 10uF, ±20%, 50V, X5R, 1206	
R6, R17	2	0 Ω	RES, 0 Ohm, Jumper, 0402	
L1, L2	2	0 Ω	RES, 0 Ohm, Jumper, 1/10W, 0603	
PCB	1		PCB	Qorvo, Custom
H1, H2	2		DC Header, 2x6, 0.100", SMD	
J1, J2	2		RF Connector, 2.92mm, F, Pin 0.005, Diel 0.029	Southwest Microwave
H-Block	1		H-Block, Copper C110, 0.990 x 2.000 x 0.275 in	Qorvo, Custom
S1 – S8	8		Screw, Cap, Socket Head, 2-56X1/8"	
Solder Preform			Solder, Preform, SAC305) 1 x 1 x 0.002 in	
Solder Paste			Paste, solder, Sn63/Pb37	

Mechanical Information



Dimensions (unless otherwise specified) are in millimeters




0.000 no tolerance; minimum precision

Pin 1 Indicator; 2D Matrix – 16P (1.5mm x 1.5mm); Trace Code to be assigned for each part


Package is air-cavity and non-hermetic

Base is laminate; Lid is FR4; all metalized features are gold plated; part is epoxy sealed

Recommended Land Pattern & Mask



LAND PATTERN




LAND PATTERN MASK

Pin Description


Pin Number	Symbol	Description
1, 3, 13, 15	GND	Ground. Recommend grounding on PCB
2	RF _{IN}	RF Input; matched to 50 Ω; DC blocked
4, 7, 21, 24	N/C	No internal connection; recommend grounding on PCB
5, 23	V _G	Gate voltage for stage 1 and 2; external bypassing required (page 28)
6, 22	V _{D1}	Drain voltage for stage 1; external bypassing required (page 28)
8 – 10, 18 – 20	V _{D2}	Drain voltage for stage 2; external bypassing required (page 28)
11, 17	V _{REF}	Reference output voltage
12, 16	V _{DET}	Detector output voltage
14	RF _{OUT}	RF Output; matched to 50 Ω; DC blocked
25	GND	Ground (backside paddle); grounded on PCB; Cu-coin via should be employed to minimize inductance and thermal resistance

Tape & Reel Information


Standard T/R size: 250 pieces on a 7" reel
 Dimensions unless otherwise noted: millimeters (mm)
 Tolerances unless otherwise noted: ± 0.1



SECTION Y-Y



SECTION X-X



Ao	4.75	+/- 0.05
Bo	5.25	+/- 0.05
Ko	2.20	+/- 0.05
F	5.50	+/- 0.05
P1	8.00	+/- 0.10
W	12.00	+0.30 / -0.10

- (I) Measured from centreline of sprocket hole to centreline of pocket.
- (II) Cumulative tolerance of 10 sprocket holes is ± 0.20 .
- (III) Measured from centreline of sprocket hole to centreline of pocket.
- (IV) Other material available.


Assembly Notes

Compatible with lead-free soldering processes with 260°C peak reflow temperature.

This package is air-cavity and non-hermetic and therefore cannot be subjected to aqueous washing. The use of no-clean solder to avoid washing after soldering is highly recommended.

Contact plating: Ni-Au

Solder rework not recommended



Recommended Soldering Temperature Profile

Handling Precautions

Parameter	Rating	Standard
ESD – Human Body Model (HBM)	1A	ANSI/ESD/JEDEC JS-001
ESD – Charged Device Model (CDM)	C3	ANSI/ESD/JEDEC JS-002
MSL – Moisture Sensitivity Level	3	IPC/JEDEC J-STD-020



Caution!

ESD-Sensitive Device

RoHS Compliance

This part is compliant with 2011/65/EU RoHS directive (Restrictions on the Use of Certain Hazardous Substances in Electrical and Electronic Equipment) as amended by Directive 2015/863/EU.

This product also has the following attributes:

- Lead Free
- Antimony Free
- TBBP-A (C₁₅H₁₂Br₄O₂) Free
- PFOS Free

Contact Information

For the latest specifications, additional product information, worldwide sales and distribution locations:

Web: www.qorvo.com

Tel: 1-844-890-8163

Email: customer.support@qorvo.com

Important Notice

The information contained in this Data Sheet and any associated documents (“Data Sheet Information”) is believed to be reliable; however, Qorvo makes no warranties regarding the Data Sheet Information and assumes no responsibility or liability whatsoever for the use of or reliance on said information. All Data Sheet Information is subject to change without notice. Customers should obtain and verify the latest relevant Data Sheet Information before placing orders for Qorvo® products. Information concerning Qorvo’s product life cycles is available at <https://www.qorvo.com/support/product-lifecycle-information>. Data Sheet Information or the use thereof does not grant, explicitly, implicitly or otherwise any rights or licenses with respect to patents or any other intellectual property whether with regard to such Data Sheet Information itself or anything described by such information.

Qorvo grants you permission to use this Data Sheet and any associated resources only to develop an application that uses the Qorvo products described in the Data Sheet and any associated resources. Other reproduction and display of this Data Sheet and any associated resources is prohibited.

Qorvo’s products are provided subject to Qorvo’s [Terms of Sale](#) or provided in conjunction with such Qorvo products. Qorvo objects to and rejects any additional or different terms customer may have proposed regarding the purchase of Qorvo products.

DATA SHEET INFORMATION DOES NOT CONSTITUTE A WARRANTY WITH RESPECT TO THE PRODUCTS DESCRIBED HEREIN, AND QORVO HEREBY DISCLAIMS ANY AND ALL WARRANTIES WITH RESPECT TO SUCH PRODUCTS WHETHER EXPRESS OR IMPLIED BY LAW, COURSE OF DEALING, COURSE OF PERFORMANCE, USAGE OF TRADE OR OTHERWISE, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. Without limiting the generality of the foregoing, Qorvo® products are not warranted or authorized for use as critical components in medical, life-saving, or life-sustaining applications, or other applications where a failure would reasonably be expected to cause severe personal injury or death. Applications described in the Data Sheet Information are for illustrative purposes only. Customers are responsible for validating that a particular product described in the Data Sheet Information is suitable for use in a particular application.

© 2026 Qorvo US, Inc. All rights reserved. This document is subject to copyright laws in various jurisdictions worldwide and may not be reproduced or distributed, in whole or in part, without the express written consent of Qorvo US, Inc.

QORVO® is a registered trademark of Qorvo US, Inc. All other trademarks and trade names are property of their respective owners.