



# QM28014


## MHB, GNSS, and 2.4G WiFi Antennaplexer

### Product Overview

The QM28014 is part of Qorvo's family of antennaplexers using patented technology to meet the high performance expectations of insertion loss and rejection for Cellular, GNSS, and WLAN systems under all operating conditions


The QM28014 is a compact filter module designed to meet the strict requirements of out of band attenuation while optimizing for insertion loss of MHB Cellular, GNSS, and 2.4G WLAN from 1427 MHz – 2690 MHz, 1559.05 MHz – 1605.89 MHz, and 2403 MHz – 2481 MHz respectively.

The QM28014 uses common module packaging techniques to achieve a compact 2.0 mm x 1.6 mm footprint.



9 Pin 2.0mm x 1.6mm x 0.6mm leadless SMT package

### Functional Block Diagram



### Key Features

- Compact Form-Factor: 2.0 mm x 1.6 mm
- Highly selective filters achieving low insertion loss and high attenuation over full bandwidth
- Single antenna port, antennaplexing
- RoHS Compliant, Pb-Free Module Package

### Applications

- For cellular handsets with MHB (including NR), GNSS, and 2.4GHz WLAN

### Ordering Information

Part Number	Description
QM28014EVB	Evaluation Board (EVB)
QM28014SB	Sample bag of 5 pieces
QM28014SR	Sample reel of 100 pieces
QM28014TR13	13 inch reel of 10k pieces

## Absolute Maximum Ratings<sup>(1)</sup>

Parameter		Conditions		Rating	UNITS
Storage Temperature				-40 to +90	°C
Operating Case Temperature				-30 to +85	°C
RF Input Power (Pin7, 2.4GHz WiFi)		2403 MHz – 2481 MHz	CW, +55C, 5k hours	+24	dBm
RF Input Power (Pin3, MHB Cellular)		1427 MHz – 1470 MHz	CW, +55C, 5k hours	+30	dBm
		1710 MHz – 2315 MHz			
		2500 MHz – 2570 MHz			
		2300 MHz – 2370 MHz	40% Dutycycle 55C, 5k hours	+31.5	dBm
		2370 MHz – 2390 MHz		+31.5	
		2390 MHz – 2400 MHz		RX Only	
		2496 MHz – 2690 MHz		+31.5	
RF Input Power <sup>(2)</sup>	Pin 7, 2.4G WiFi	2403 MHz – 2481 MHz		+22	dBm
	Pin 3, MHB Cellular	1427 MHz – 1470 MHz	CW, +55C, 5k hours	+28	
		1710 MHz – 2315 MHz			
		2500 MHz – 2570 MHz			
		2300 MHz – 2370 MHz	40% Dutycycle 55C, 5k hours	+30	
		2370 MHz – 2390 MHz		+30	
		2390 MHz – 2400 MHz		RX Only	
		2496 MHz – 2690 MHz		+30	
RF Input Power (Pin1, ANT)		1427 MHz – 1518 MHz	CW, +55C, 5k hours	+15	dBm
		1559 MHz – 1606 MHz			
		1710 MHz – 2400 MHz			
		2403 MHz – 2481 MHz			
		2496 MHz – 2690 MHz			

1. Operation of this device outside the parameter ranges given above may cause permanent damage.
2. Power applied simultaneously

## Electrical Specifications<sup>(1)</sup> MHB - Antenna

Parameter	Conditions	Min.	Typ.	Max.	Units
Insertion Loss	1427 MHz – 1518 MHz	-	1.2 <sup>(2)</sup>	1.7	dB
	1710 MHz – 2200 MHz	-	1.1 <sup>(2)</sup>	1.4	
	2300 MHz – 2370 MHz	-	1.2 <sup>(2)</sup>	1.8	
	2370 MHz – 2390 MHz	-	1.7 <sup>(2)</sup>	4 <sup>(3)</sup>	
	2390 MHz – 2400 MHz	-	6.4 <sup>(2)</sup>	12 <sup>(3)(4)</sup>	
	2496 MHz – 2500 MHz	-	2.2 <sup>(2)</sup>	4 <sup>(5)</sup>	
	2500 MHz – 2505 MHz	-	1.7 <sup>(2)</sup>	2.8 <sup>(5)</sup>	
	2505 MHz – 2690 MHz	-	1.0 <sup>(2)</sup>	2.4	
VSWR (MHB)	1427 MHz – 1518 MHz	-	1.4:1	2.0:1	-
	1710 MHz – 2200 MHz	-	1.4:1	2.0:1	
	2300 MHz – 2370 MHz	-	1.3:1	2.0:1	
	2370 MHz – 2390 MHz	-	1.8:1	2.0:1	
	2390 MHz – 2400 MHz	-	4.5:1	5.3:1	
	2496 MHz – 2690 MHz	-	2.1:1	4.8:1	
VSWR (ANT)	1427 MHz – 1518 MHz	-	1.5:1	2.0:1	-
	1710 MHz – 2200 MHz	-	1.3:1	2.0:1	
	2300 MHz – 2370 MHz	-	1.3:1	2.0:1	
	2370 MHz – 2390 MHz	-	1.3:1	2.0:1	
	2390 MHz – 2400 MHz	-	1.5:1	2.0:1	
	2496 MHz – 2690 MHz	-	1.5:1	3.0:1	
Attenuation	1559 MHz – 1606 MHz	10	15	-	dB
	2403 MHz – 2481 MHz <sup>(6)</sup>	13	17	-	

**Notes:**

1. All specifications are based on the applications circuit and Min/Max is specified over -30°C to +85°C unless otherwise noted.
2. Typical specified as average at room temperature
3. Specified from -30°C to +25°C
4. Integrated over any 5MHz bandwidth
5. Specified from +25°C to +85°C
6. Integrated over each 18MHz WiFi Channel

## Electrical Specifications<sup>(1)</sup> L1 GNSS - Antenna

Parameter	Conditions	Min.	Typ.	Max.	Units
Insertion Loss	1559.05 MHz – 1563.15 MHz	-	1.4 <sup>(2)</sup>	2.2	dB
	1574.39 MHz – 1576.45 MHz	-	0.8 <sup>(2)</sup>	1.1	
	1597.55 MHz – 1605.89 MHz	-	1.1 <sup>(2)</sup>	1.6	
VSWR (GNSS)	1559.05 MHz – 1563.15 MHz	-	1.2:1	2.0:1	-
	1574.39 MHz – 1576.45 MHz	-	1.1:1	2.0:1	
	1597.55 MHz – 1605.89 MHz	-	1.4:1	2.0:1	
VSWR (ANT)	1559.05 MHz – 1563.15 MHz	-	1.1:1	2.0:1	-
	1574.39 MHz – 1576.45 MHz	-	1.1:1	2.0:1	
	1597.55 MHz – 1605.89 MHz	-	1.3:1	2.0:1	
Attenuation	10 MHz – 960 MHz	48	49	-	dB
	777 MHz – 787 MHz	48	49	-	
	1427.9 MHz – 1462.9 MHz	47	57	-	
	1640 MHz – 1695 MHz	49	55	-	
	1695 MHz – 1710 MHz	48	54	-	
	1710 MHz – 1785 MHz	46	52	-	
	1786 MHz – 1797 MHz	46	52	-	
	1850 MHz – 1910 MHz	46	52	-	
	1910 MHz – 1980 MHz	46	52	-	
	2010 MHz – 2025 MHz	46	54	-	
	2305 MHz – 2315 MHz	49	52	-	
	2403 MHz – 2481 MHz <sup>(3)</sup>	45	55	-	
	2500 MHz – 2570 MHz	46	49	-	
	2570 MHz – 2690 MHz	43	45	-	
	3400 MHz – 3600 MHz	32	33	-	
	4400 MHz – 4900 MHz	30	32	-	
	5150 MHz – 5925 MHz	10	24	-	

**Notes:**

1. All specifications are based on the applications circuit and Min/Max is specified over -30°C to +85°C unless otherwise noted.
2. Typical specified as average at room temperature
3. Integrated over each 18MHz WiFi channel

## Electrical Specifications<sup>(1)</sup> 2.4GHz WiFi - Antenna

Parameter	Conditions	Min.	Typ.	Max.	Units
Insertion Loss	2403 MHz – 2421 MHz <sup>(2)</sup> (WiFi CH1)	-	1.8	2.4	dB
	2408 MHz – 2426 MHz <sup>(2)</sup> (WiFi CH2)	-	1.6	2	
	2413 MHz – 2446 MHz <sup>(2)</sup> (WiFi CH3-6)	-	1.5	2	
	2433 MHz – 2466 MHz <sup>(2)</sup> (WiFi CH7-10)	-	1.5	2	
	2453 MHz – 2471 MHz <sup>(2)</sup> (WiFi CH11)	-	1.6	2.1	
	2458 MHz – 2476 MHz <sup>(2)</sup> (WiFi CH12)	-	1.7	2.4	
	2463 MHz – 2481 MHz <sup>(2)</sup> (WiFi CH13)	-	1.9	3	
VSWR (WiFi)	2403 MHz – 2481 MHz	-	1.5:1	2.0:1	-
VSWR (ANT)	2403 MHz – 2481 MHz	-	1.5:1	2.0:1	
Attenuation	925 MHz – 960 MHz	40	41	-	dB
	1559 MHz – 1606 MHz	41	44	-	
	2110 MHz – 2170 MHz	34	50	-	
	2300 MHz – 2370 MHz	39	43	-	
	2500 MHz – 2505 MHz	26	48	-	
	2505 MHz – 2690 MHz	45	57	-	
	4800 MHz – 5000 MHz	31	48	-	
	7200 MHz – 7500 MHz	25	30	-	

Notes:

1. All specifications are based on the applications circuit and Min/Max is specified over -30°C to +85°C unless otherwise noted.
2. Integrated over each 18MHz WiFi Channel

## Electrical Specifications<sup>(1)</sup> Isolation

Parameter		Conditions	Min.	Typ.	Max.	Units
Isolation	2.4G WiFi – GNSS	1559.05 MHz – 1605.89 MHz	43	46	-	dB
		2403 MHz – 2481 MHz	48	53	-	
	2.4G WiFi – MHB	1427 MHz – 1518 MHz	43	46	-	
		1710 MHz – 2200 MHz	30	40	-	
		2300 MHz – 2370 MHz	38	41	-	
		2370 MHz – 2390 MHz	8	13	-	
		2390 MHz – 2400 MHz	7	10	-	
		2496 MHz – 2690 MHz	16	37	-	
		2403 MHz – 2481 MHz	6	14	-	
	MHB – GNSS	1559.05 MHz – 1605.89 MHz	12	16	-	
		1427 MHz – 1518 MHz	48	50	-	
		1710 MHz – 2200 MHz	46	51	-	
		2300 MHz – 2370 MHz	46	49	-	
		2370 MHz – 2390 MHz	46	49	-	
		2390 MHz – 2400 MHz	46	50	-	
		2496 MHz – 2690 MHz	43	44	-	

Notes:

1. All specifications are based on the applications circuit and Min/Max is specified over -30°C to +85°C unless otherwise noted.


## QM28014EVB PCB Information

Layer	Name	Material	Thickness	Constant	Board Layer Stack
1	Top Overlay				
2	Top Solder	Solder Resist	0.79mil	3.5	
3	L1	Copper	0.70mil		
4	Dielectric1	FR-408HR	4.10mil	3.3	
5	L2	Copper	0.70mil		
6	Dielectric 2	FR-408HR	26.00mil	3.6	
7	L3	Copper	0.70mil		
8	Dielectric 3	FR-408HR	4.10mil	3.3	
9	L4	Copper	0.70mil		
10	Bottom Solder	Solder Resist	0.79mil	3.5	
11	Bottom Overlay				


Total thickness: 40 MILS +/-10%

Where:

- J1 = 2.4G WiFi
- J2 = ANT
- J3 = MHB
- J4 = GNSS



## Application Circuit Schematic



Note:






1. All RF ports internally matched to 50 ohm impedance
2. Recommend connecting all ground pins together on PCB
3. Recommend adding Pi network close to each RF port for phone level tuning/optimization

## Bill of Materials

Ref. Des.	Value	Description	Manuf.	Part number
U1	N/A	MHB, GNSS, and 2.4G WiFi Antennaplexer	Qorvo	QM28014
PCB	N/A	Printed Circuit Board		QM28014-4000

## MHB Insertion Loss and Attenuation Plots







Test conditions unless otherwise noted: Temp. = +25 °C






## MHB Return Loss Plots

Test conditions unless otherwise noted: Temp. = +25 °C






## MHB Impedance Plots

Test conditions unless otherwise noted: Temp. = +25 °C







## GNSS Insertion Loss and Attenuation Plots

Test conditions unless otherwise noted: Temp. = +25 °C



## GNSS Return Loss and Impedance Plots


Test conditions unless otherwise noted: Temp. = +25 °C




## 2.4GHz WiFi Insertion Loss and Attenuation Plots

Test conditions unless otherwise noted: Temp. = +25 °C


2.4G Wi-Fi Pass Band




2.4G Wi-Fi Narrow Band




2.4G Wi-Fi B40 Attenuation



2.4G Wi-Fi B41 Attenuation







2.4G Wi-Fi Wide Band



## 2.4GHz WiFi Return Loss and Impedance Plots


Test conditions unless otherwise noted: Temp. = +25 °C




## Isolation Plots

Test conditions unless otherwise noted: Temp. = +25 °C


2.4G WiFi to GNSS Isolation




2.4G WiFi to MHB Isolation



MHB to GNSS Isolation



Pin Configuration and Description




Top View

Pin Number	Label	Description
1	ANT	Antenna Port
3	MHB Cellular	MHB Cellular Port
5	GNSS	GNSS Port
7	2.4G WiFi	2.4G WiFi Port
2, 4, 6, and 8	GND	Ground
9	GND	Package Ground




## Part Marking and Package Outline Dimensions

Part Marking Diagram – Top View



Pin 1 Indicator  
Trace Code to be assigned by SubCon  
(where YYY indicates the Trace Code)  
"5V" is the product code.

Package Outline Dimension Drawing





Notes:

1. All dimensions are in millimeters.
2. Dimension and tolerance formats conform to ASME Y14.4M-1994.
3. The terminal #1 identifier and terminal numbering conform to JESD 95-1 SPP-012

Land Pattern and Mask Dimensions

Recommended Land Pattern Drawing – Top View	Recommended Land Pattern Mask Drawing – Top View
<div><div><div><div><div>DETAIL PAD A- 7x</div><div>(0.290)</div><div>(0.330)</div></div><div><div>DETAIL PAD S- 1x</div><div>(0.610)</div><div>(0.290)</div></div><div><div>DETAIL PAD B- 1x</div><div>(0.140)</div><div>(0.330)</div><div>(0.180)</div><div>(0.290)</div></div></div></div><div><div><div><div>PIN 1</div><div>0.5800</div><div>0.7600</div><div>0</div><div>0</div><div>0</div><div>0</div><div>0</div><div>0</div><div>0</div></div><div><div>A</div><div>A</div><div>A</div><div>B</div><div>S</div><div>A</div><div>A</div><div>A</div><div>A</div></div></div></div><div>RECOMMENDED LAND PATTERN</div></div>	<div><div><div><div>DETAIL PAD MASK OPENING A- 7x</div><div>(0.390)</div><div>(0.430)</div></div><div><div>DETAIL PAD MASK OPENING S- 1x</div><div>(0.710)</div><div>(0.390)</div></div><div><div>DETAIL PAD MASK OPENING B- 1x</div><div>(0.211)</div><div>(0.430)</div><div>(0.251)</div><div>(0.390)</div></div></div></div> <div><div><div><div>PIN 1</div><div>0.5800</div><div>0.7600</div><div>0</div><div>0</div><div>0</div><div>0</div><div>0</div><div>0</div><div>0</div></div><div><div>A</div><div>A</div><div>A</div><div>B</div><div>S</div><div>A</div><div>A</div><div>A</div><div>A</div></div></div></div> <div>RECOMMENDED LAND PATTERN MASK</div>
<div><div>Notes:</div><div><div>1. All dimensions are in millimeters.</div><div>2. Dimension and tolerance formats conform to ASME Y14.4M-1994.</div></div></div>	

Tape and Reel Information

							
Feature	Measure	Symbol	Size (mm)	Feature	Measure	Symbol	Size (mm)
Flange	Diameter	D1	330.0	Cavity	Length	Ao	1.8
	Thickness	W2	14.4		Width	Bo	2.2
	Space Between Flange	W1	8.4		Depth	Ko	0.8
Hub	Outer Diameter	D2	102.0		Pitch	P1	4.0
	Arbor Hole Diameter	D3	13.0	Centerline Distance	Cavity to Perforation (Length)	P2	2.0
	Key Slit Width	B	2.0		Cavity to Perforation (Width)	P3	3.5
	Key Slit Diameter	D4	20.0	Carrier Tape	Width	W	8

(Unless otherwise specified, all dimension tolerances per EIA-481)

## Handling Precautions

PARAMETER	RATING	STANDARD
ESD – Human Body Model (HBM)	Class 1B	ESDA/JEDEC JS-001
ESD – Charged Device Model (CDM)	Class C3	ESDA/JEDEC JS-002
MSL – Moisture Sensitivity Level	Level 3	IPC/JEDEC J-STD-020



Caution!

ESD sensitive device

## Solderability

Compatible with both lead-free (260 °C max. reflow temperature) and tin/lead (245 °C max. reflow temperature) soldering processes.

Package lead plating: Electrolytic plated Au over Ni

## RoHS Compliance

This part is compliant with the 2011/65/EU RoHS directive (Restrictions on the Use of Certain Hazardous Substances in Electrical and Electronic Equipment), as amended by Directive 2015/863/EU.

This product also has the following attributes:

- Lead free
- Halogen Free (Chlorine, Bromine)
  - Antimony Free
- TBBP-A (C<sub>15</sub>H<sub>12</sub>Br<sub>4</sub>O<sub>2</sub>) Free
- PFOS Free
- SVHC Free
- Qorvo Green



## Contact Information

For the latest specifications, additional product information, worldwide sales and distribution locations:

**Web:** [www.qorvo.com](http://www.qorvo.com)

**Tel:** 1-844-890-8163

**Email:** [customer.support@qorvo.com](mailto:customer.support@qorvo.com)

## Important Notice

The information contained herein is believed to be reliable; however, Qorvo makes no warranties regarding the information contained herein and assumes no responsibility or liability whatsoever for the use of the information contained herein. All information contained herein is subject to change without notice. Customers should obtain and verify the latest relevant information before placing orders for Qorvo products. The information contained herein or any use of such information does not grant, explicitly or implicitly, to any party any patent rights, licenses, or any other intellectual property rights, whether with regard to such information itself or anything described by such information. **THIS INFORMATION DOES NOT CONSTITUTE A WARRANTY WITH RESPECT TO THE PRODUCTS DESCRIBED HEREIN, AND QORVO HEREBY DISCLAIMS ANY AND ALL WARRANTIES WITH RESPECT TO SUCH PRODUCTS WHETHER EXPRESS OR IMPLIED BY LAW, COURSE OF DEALING, COURSE OF PERFORMANCE, USAGE OF TRADE OR OTHERWISE, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.** Without limiting the generality of the foregoing, Qorvo products are not warranted or authorized for use as critical components in medical, life-saving, or life-sustaining applications, or other applications where a failure would reasonably be expected to cause severe personal injury or death.

Copyright 2016 © Qorvo, Inc. | Qorvo is a registered trademark of Qorvo, Inc.

## REVISION HISTORY

Revision	Date (YYYYMMDD)	Description
A	20200114	Initial Document
B	20200205	Updated Pinout
C	20200507	Updated with measured data
D	20200624	Updated power handling
E	20200707	Updated electrical specifications
F	20200713	Updated specifications to include 2390-2400MHz
G	20200716	Updated GNSS attenuation spec