



# QPA2212D

## 27.5–31 GHz 25 Watt GaN Power Amplifier

### Product Overview


Qorvo's QPA2212D is a Ka-band power amplifier fabricated on Qorvo's 0.15um GaN on SiC process (QGaN15). Operating between 27.5 and 31 GHz, it achieves 10 W linear power with -25 dBc intermodulation distortion products and 22 dB small signal gain. Saturated output power is 25 W with power-added efficiency of 25%.

QPA2212D is ideally suited to support satellite communications and 5G infrastructure.

To simplify system integration, the QPA2212D is fully matched to 50 ohms with integrated DC blocking caps on both I/O ports.

The QPA2212D is 100% DC and RF tested on-wafer to ensure compliance to electrical specifications.

Lead-free and RoHS compliant.




### Key Features

- Frequency Range: 27.5–31 GHz
- $P_{SAT}$  ( $P_{IN}=25$  dBm): 43.4 dBm
- PAE ( $P_{IN}=25$  dBm): 25 %
- Power Gain ( $P_{IN}=25$  dBm): 18.4 dB
- IMD3 (at 37 dBm/tone): -25 dBc
- Small Signal Gain: 22 dB
- Bias:  $V_D = 22$  V,  $I_{DQ} = 460$  mA
- Die Dimensions: 3.630 x 4.792 x 0.050 mm

*Performance is typical across frequency. Please reference electrical specification table and data plots for more details.*

### Functional Block Diagram



### Applications

- 5G Infrastructure
- Satellite Communications

### Ordering Information

Part No.	Description
QPA2212D	27.5–31 GHz 25 Watt GaN Amplifier (10 Pcs.)
QPA2212DEVB	Evaluation Board for QPA2212D

## Absolute Maximum Ratings

Parameter	Value / Range
Drain Voltage ( $V_D$ )	29.5 V
Gate Voltage Range ( $V_G$ )	–5 V to 0 V
Drain Current ( $I_D$ )	5860 mA
Gate Current ( $I_G$ )	See plot pg. 17
Power Dissipation ( $P_{DISS}$ ), 85 °C	80.3 W
Input Power ( $P_{IN}$ ), 50 $\Omega$ , $V_D=22$ V, $I_{DQ}=460$ mA, 85 °C	34 dBm
Input Power ( $P_{IN}$ ), 3:1 VSWR, $V_D=22$ V, $I_{DQ}=460$ mA, 85 °C	34 dBm
Soldering Temperature (30 s max.)	320 °C
Storage Temperature	–55 to +150 °C

Operation of this device outside the parameter ranges given above may cause permanent damage. These are stress ratings only, and functional operation of the device at these conditions is not implied.

## Recommended Operating Conditions

Parameter	Value / Range
Drain Voltage ( $V_D$ )	22 V
Drain Current ( $I_{DQ}$ )	460 mA
Operating Temperature	–40 to +85 °C

Electrical specifications are measured at specified test conditions. Specifications are not guaranteed over all recommended operating conditions.

## Electrical Specifications







Parameter		Min	Typ	Max	Units
Operational Frequency		27.5		31	GHz
Output Power ( $P_{IN}=25$ dBm) <sup>1</sup>	27.5GHz 29 GHz 31 GHz		44.0 44.2 43.9		dBm dBm dBm
Power Added Efficiency ( $P_{IN}=25$ dBm)	27.5GHz 29 GHz 31 GHz		27.2 26.9 25.3		% % %
Small Signal Gain	27.5GHz 29 GHz 31 GHz		23.0 22.4 21.7		dB dB dB
Input Return Loss	27.5GHz 29 GHz 31 GHz		9 17 29		dB dB dB
Output Return Loss	27.5GHz 29 GHz 31 GHz		9 14 9		dB dB dB
IMD3 ( $P_{OUT}/\text{Tone} = 37$ dBm, 10 MHz tone spacing)	27.5 GHz 29 GHz 31 GHz		–38 –38 –29		dBc dBc dBc
$P_{OUT}$ Temp. Coeff. (85 °C to 25 °C, $P_{IN} = 25$ dBm))			–0.033		dB/°C
Sm. Sig. Gain Temp. Coefficient (85 °C to –40 °C)			–0.119		dB/°C

Test conditions, unless otherwise noted:  $T = +25$  °C,  $V_D = 22$  V,  $I_{DQ} = 460$  mA

<sup>1</sup> Typical  $P_{SAT}$  measured on evaluation board. Manufacturing test RF probe minimum  $P_{SAT}$  specification is 42.5 dBm at 27.5 and 31 GHz, 43 dBm at 28, 29, and 30 GHz.







## Performance Plots – Large Signal

Test conditions, unless otherwise noted:  $V_D = 22\text{ V}$ ,  $I_{DQ} = 460\text{ mA}$ ,  $T = +25^\circ\text{C}$ ,  $P_{IN} = 25\text{ dBm}$







## Performance Plots – Large Signal

Test conditions, unless otherwise noted:  $V_D = 22\text{ V}$ ,  $I_{DQ} = 460\text{ mA}$ ,  $T = +25^\circ\text{C}$ ,  $P_{IN} = 25\text{ dBm}$









## Performance Plots – Large Signal

Test conditions, unless otherwise noted:  $V_D = 22\text{ V}$ ,  $I_{DQ} = 460\text{ mA}$ ,  $T = +25\text{ }^\circ\text{C}$






## Performance Plots – Large Signal

Test conditions, unless otherwise noted:  $V_D = 22\text{ V}$ ,  $I_{DQ} = 460\text{ mA}$ ,  $T = +25\text{ }^{\circ}\text{C}$









## Performance Plots – Large Signal

Test conditions, unless otherwise noted:  $V_D = 22\text{ V}$ ,  $I_{DQ} = 460\text{ mA}$ ,  $T = +25\text{ }^\circ\text{C}$



## Performance Plots – Large Signal




Test conditions, unless otherwise noted:  $V_D = 22\text{ V}$ ,  $I_{DQ} = 460\text{ mA}$ ,  $T = +25\text{ }^\circ\text{C}$











## Performance Plots – Large Signal

Test conditions, unless otherwise noted:  $V_D = 22\text{ V}$ ,  $I_{DQ} = 460\text{ mA}$ ,  $T = +25\text{ }^\circ\text{C}$






## Performance Plots – Large Signal

Test conditions, unless otherwise noted:  $V_D = 22\text{ V}$ ,  $I_{DQ} = 460\text{ mA}$ ,  $T = +25\text{ }^\circ\text{C}$









## Performance Plots – Large Signal

Test conditions, unless otherwise noted:  $V_D = 22\text{ V}$ ,  $I_{DQ} = 460\text{ mA}$ ,  $T = +25\text{ }^{\circ}\text{C}$









## Performance Plots – Linearity

Test conditions, unless otherwise noted:  $V_D = 22\text{ V}$ ,  $I_{DQ} = 460\text{ mA}$ ,  $T = +25^\circ\text{C}$ , 10 MHz tone spacing




## Performance Plots – Linearity

Test conditions, unless otherwise noted:  $V_D = 22\text{ V}$ ,  $I_{DQ} = 460\text{ mA}$ ,  $T = +25^\circ\text{C}$ , 10 MHz tone spacing









## Performance Plots – Linearity

Test conditions, unless otherwise noted:  $V_D = 22\text{ V}$ ,  $I_{DQ} = 460\text{ mA}$ ,  $T = +25^\circ\text{C}$ , 10 MHz tone spacing






## Performance Plots – Small Signal

Test conditions, unless otherwise noted:  $V_D = 22\text{ V}$ ,  $I_{DQ} = 460\text{ mA}$ ,  $T = +25^\circ\text{C}$



## Performance Plots – Small Signal

Test conditions, unless otherwise noted:  $V_D = 22\text{ V}$ ,  $I_{DQ} = 460\text{ mA}$ ,  $T = +25\text{ }^\circ\text{C}$






## Thermal and Reliability Information

Parameter	Test Conditions	Value	Units
Thermal Resistance ( $\theta_{JC}$ ) <sup>(1)</sup>	$T_{base} = 85^\circ\text{C}$ , $V_D = 22\text{ V}$ , $I_{DQ} = 460\text{ mA}$ , $P_{DISS} = 10.12\text{ W}$ , No RF (quiescent DC operation)	1.077	$^\circ\text{C/W}$
Channel Temperature, $T_{CH}$ (No RF) <sup>(2)</sup>		95.9	$^\circ\text{C}$
Thermal Resistance ( $\theta_{JC}$ ) <sup>(1)</sup>	$T_{base} = 85^\circ\text{C}$ , $V_D = 22\text{ V}$ , $I_{DQ} = 460\text{ mA}$ , $\text{Freq} = 28.5\text{ GHz}$ , $I_{D\_Drive} = 3.41\text{ A}$ , $P_{IN} = 25\text{ dBm}$ , $P_{OUT} = 42.3\text{ dBm}$ , $P_{DISS} = 58.6\text{ W}$	1.392	$^\circ\text{C/W}$
Channel Temperature, $T_{CH}$ (Under RF) <sup>(2)</sup>		166.6	$^\circ\text{C}$
Thermal Resistance ( $\theta_{JC}$ ) <sup>(1)</sup>	$T_{base} = 85^\circ\text{C}$ , $V_D = 24\text{ V}$ , $I_{DQ} = 460\text{ mA}$ , $\text{Freq} = 28.5\text{ GHz}$ , $I_{D\_Drive} = 3.71\text{ A}$ , $P_{IN} = 25\text{ dBm}$ , $P_{OUT} = 42.9\text{ dBm}$ , $P_{DISS} = 70.1\text{ W}$	1.432	$^\circ\text{C/W}$
Channel Temperature, $T_{CH}$ (Under RF) <sup>(2)</sup>		185.4	$^\circ\text{C}$


Notes:

- Thermal resistance determined to the back of 20 mil CuMo carrier plate ( $85^\circ\text{C}$ )
- IR scan equivalent. Refer to the following document: [GaN Device Channel Temperature, Thermal Resistance, and Reliability Estimates](#)


## Dissipated Power and Maximum Gate Current



Test conditions, unless otherwise noted:  
 $I_{DQ} = 460\text{ mA}$ ,  $T = +85^\circ\text{C}$ ,  $P_{IN} = 25\text{ dBm}$



## Applications Information (EVB Schematic)



$V_{G\_TOP}$  and  $V_{G\_BOTTOM}$  should be tied together


$V_{D\_TOP}$  and  $V_{D\_BOTTOM}$  should be tied together

$V_{G12}$  and  $V_{G3}$  can be separated, if desired, in an attempt to improve IMD performance, but are connected on the EVB.

## Bill of Materials

Reference Des.	Value	Description	Manuf.	Part Number
C1,C3,C5,C7,C10,C12,C14,C16	10 uF	CAP, 10uF, 20%, 50V, 20%, X5R, 1206	Various	
C17,C18,C19,C20,C21,C22,C23,C24	10 nF	CAP, 10nF, 15%, 30V, 0303, SLC Si WP	Various	
J1, J2	2.4 mm	RF Connector, 2.4 mm	Southwest Microwave	1492-04A-5

## Evaluation Board (EVB) Layout Assembly



PCB is made from Rogers 6202 dielectric, .005 inch thick, 0.5 oz. copper both sides.


### Bias-Up Procedure

1. Set  $I_D$  limit to 5500 mA,  $I_G$  limit to 40 mA
2. Set  $V_G$  to  $-5.0$  V
3. Set  $V_D$  to  $+22$  V
4. Adjust  $V_G$  more positive until  $I_{DQ} \approx 460$  mA
5. Apply RF signal

### Bias-Down Procedure

1. Turn off RF signal
2. Reduce  $V_G$  to  $-5.0$  V. Ensure  $I_{DQ} \sim 0$  mA
4. Set  $V_D$  to  $0$  V
5. Turn off  $V_D$  supply
6. Turn off  $V_G$  supply

## Mechanical Information



Dimensions are in mm  
Thickness: 0.050  
Die x, y size tolerance:  $\pm 0.050$   
Ground is backside of die

## Bond Pad Description

Pad No.	Symbol	Size (um x um)	Description
1	RF IN	90 x 140	RF input. 50 Ohms. DC grounded.
2, 12	V <sub>G12</sub>	100 x 100	Gate voltage stages 1 & 2. Bypass network required; refer to page 18.
3, 11	V <sub>G3</sub>	100 x 100	Gate voltage stage3. Bypass network required; refer to page 18.
4, 10	V <sub>D1</sub>	100 x 100	Drain voltage stages 1. Bypass network required; refer to page 18.
5, 9	V <sub>D2</sub>	200 x 100	Drain voltage stage 2. Bypass network required; refer to page 18.
6, 8	V <sub>D3</sub>	500 x 90	Drain voltage stage 3. Bypass network required; refer to page 18.
7	RF OUT	90 x 140	RF output. 50 Ohms. DC grounded.

## Assembly Notes

---

Component placement and adhesive attachment assembly notes:

- Vacuum pencils and/or vacuum collets are the preferred method of pick up.
- Air bridges must be avoided during placement.
- The force impact is critical during auto placement.

Reflow process assembly notes:

- Use AuSn (80/20) solder and limit exposure to temperatures above 300 °C to 3–4 minutes, maximum.
- An alloy station or conveyor furnace with reducing atmosphere should be used.
- Do not use any kind of flux.
- Coefficient of thermal expansion matching is critical for long-term reliability.
- Devices must be stored in a dry nitrogen atmosphere.

Interconnect process assembly notes:

- Thermosonic ball bonding is the preferred interconnect technique.
- Force, time, and ultrasonic are critical parameters.
- Aluminum wire should not be used.
- Devices with small pad sizes should be bonded with 0.0007-inch wire.

## Handling Precautions

Parameter	Rating	Standard
ESD – Human Body Model (HBM)	1C	ANSI/ESD/JEDEC JS-001



Caution!  
ESD-Sensitive Device

## Solderability

Use only AuSn (80/20) solder, and limit exposure to temperatures above 300 °C to 3–4 minutes, maximum.

## RoHS Compliance

This part is compliant with 2011/65/EU RoHS directive (Restrictions on the Use of Certain Hazardous Substances in Electrical and Electronic Equipment) as amended by Directive 2015/863/EU.

This product also has the following attributes:

- Lead Free
- Halogen Free (Chlorine, Bromine)
- Antimony Free
- TBBP-A (C<sub>15</sub>H<sub>12</sub>Br<sub>4</sub>O<sub>2</sub>) Free
- PFOS Free
- SVHC Free

## Contact Information

For the latest specifications, additional product information, worldwide sales and distribution locations:

**Web:** [www.qorvo.com](http://www.qorvo.com)

**Tel:** 1-844-890-8163

**Email:** [customer.support@qorvo.com](mailto:customer.support@qorvo.com)

## Important Notice

The information contained herein is believed to be reliable; however, Qorvo makes no warranties regarding the information contained herein and assumes no responsibility or liability whatsoever for the use of the information contained herein. All information contained herein is subject to change without notice. Customers should obtain and verify the latest relevant information before placing orders for Qorvo products. The information contained herein or any use of such information does not grant, explicitly or implicitly, to any party any patent rights, licenses, or any other intellectual property rights, whether with regard to such information itself or anything described by such information. **THIS INFORMATION DOES NOT CONSTITUTE A WARRANTY WITH RESPECT TO THE PRODUCTS DESCRIBED HEREIN, AND QORVO HEREBY DISCLAIMS ANY AND ALL WARRANTIES WITH RESPECT TO SUCH PRODUCTS WHETHER EXPRESS OR IMPLIED BY LAW, COURSE OF DEALING, COURSE OF PERFORMANCE, USAGE OF TRADE OR OTHERWISE, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.**

Without limiting the generality of the foregoing, Qorvo products are not warranted or authorized for use as critical components in medical, life-saving, or life-sustaining applications, or other applications where a failure would reasonably be expected to cause severe personal injury or death.

© 2022 Qorvo US, Inc. All rights reserved. This document is subject to copyright laws in various jurisdictions worldwide and may not be reproduced or distributed, in whole or in part, without the express written consent of Qorvo US, Inc.