



QPA4246D

37.5 – 42.5 GHz 10 Watt GaN Power Amplifier

Product Overview

Qorvo's QPA4246D is a high power MMIC amplifier fabricated on Qorvo's production 0.15 μm GaN on SiC process (QGaN15). It is targeted to the 37.5 - 42.5 GHz Satcom Q-V band. QPA4246D achieves 5 W linear power with 25 dBc third order intermodulation distortion products, and 16 dB small signal gain. It provides 10 W of saturated output power while achieving 17% power-added efficiency.

To simplify system integration, the QPA4246D is fully matched to 50 ohms with integrated DC blocking caps on both I/O ports. Its RF ports are DC coupled to ground for optimum ESD performance.

The QPA4246D is ideal for supporting communications and radar applications in both commercial and military markets.

The QPA4246D is 100% DC and RF tested on-wafer to ensure compliance to electrical specifications.

Lead-free and RoHS compliant




Key Features

- Frequency Range: 37.5 – 42.5 GHz
- P_{SAT} ($P_{\text{IN}} = 29 \text{ dBm}$): 40 dBm
- PAE ($P_{\text{IN}} = 29 \text{ dBm}$): 17%
- IM3 ($P_{\text{OUT}}/\text{Tone} = 34 \text{ dBm}$): -25 dBc
- Small Signal Gain: 16 dB
- Bias: $V_{\text{D}} = 24 \text{ V}$, $I_{\text{DQ}} = 280 \text{ mA}$, $V_{\text{G}} = -2.3 \text{ V typ. range}$
- Die Dimensions: 4.2 x 5.0 x 0.05 mm

Performance is typical across frequency. Please reference electrical specification table and data plots for more details.

Functional Block Diagram



Applications

- Satellite Communications

Ordering Information

Part No.	Description
QPA4246D	10 Watt GaN PA
QPA4246DEVB	Evaluation Board for QPA4246D



Absolute Maximum Ratings

Parameter	Value / Rang
Drain Voltage (V_D)	29.5 V
Gate Voltage Range (V_G)	-4 V to 0 V
Drain Current (I_{D1}), $T_{BASE} = 85\text{ }^{\circ}\text{C}$ max	510 mA
Drain Current (I_{D2}), $T_{BASE} = 85\text{ }^{\circ}\text{C}$ max	900 mA
Drain Current (I_{D3}), $T_{BASE} = 85\text{ }^{\circ}\text{C}$ max	3450 mA
Drain Current Total (I_D), $T_{BASE} = 85\text{ }^{\circ}\text{C}$ max	4860 mA
Gate Current (I_G)	See p. 25
Power Dissipation (P_{DISS}), $T_{BASE} = 85\text{ }^{\circ}\text{C}$	70 W
Input Power (P_{IN}), 50 Ω , CW, $V_D = 24\text{ V}$, $I_D = 280\text{ mA}$, $T_{BASE} = 85\text{ }^{\circ}\text{C}$	35 dBm
Input Power (P_{IN}), 3:1 VSWR, CW, $V_D = 24\text{ V}$, $I_D = 280\text{ mA}$, $T_{BASE} = 85\text{ }^{\circ}\text{C}$	35 dBm
Mounting Temperature (30 seconds)	320 $^{\circ}\text{C}$
Storage Temperature	-55 to +150 $^{\circ}\text{C}$

Operation of this device outside the parameter ranges given above may cause permanent damage. These are stress ratings only, and functional operation of the device at these conditions is not implied.

Recommended Operating Conditions

Parameter	Min	Typ.	Max	Units
Drain Voltage (V_D)	20	24	24	V
Drain Current, Quiescent (I_D)	280	280		mA
Drain Current, RF (I_{D_Drive})	See plot page 4,5,8,11,14			mA
Gate Voltage Typical Range (V_G)	-1.7 to -2.9			V
Gate Current, RF (I_{G_Drive})	See plot page 4,5			mA
Input Power @ Saturation, (P_{IN}) ⁽¹⁾	T _{BASE} -40 °C : 29			dBm
	T _{BASE} +25 °C: 29			
	T _{BASE} +85 °C: 31			
Operating Temp. Range (T _{BASE}) ⁽²⁾	-40		+85	°C

1. See plots page 6

2. T_{BASE} is back side of 0.02" CuMo carrier plate with AuSn solder

Electrical specifications are measured at specified test conditions. Specifications are not guaranteed over all recommended operating conditions.

Electrical Specifications







Parameter	Conditions ^{(1) (2)}	Min	Typ.	Max	Units
Operational Frequency Range		37.5		42.5	GHz
Output Power at Saturation, P_{SAT}	$P_{IN} = 29\text{ dBm}$		40		dBm
Power Added Efficiency, PAE	$P_{IN} = 29\text{ dBm}$		17		%
3 RD Intermodulation Products, IM3	$P_{OUT}/\text{Tone} = 34\text{ dBm}$		-25		dBc
5 RD Intermodulation Products, IM5	$\Delta F = 100\text{ MHz}$		-30		
Small Signal Gain, S21	$P_{IN} = -30\text{ dBm}$		16		dB
Input Return Loss, IRL			10		
Output Return Loss, ORL			10		
P_{SAT} Temperature Coefficient	$T_{DIFF} = 25\text{ }^{\circ}\text{C}$ to $85\text{ }^{\circ}\text{C}$; $P_{IN} = 29\text{ dBm}$		-0.05		dBm/ $^{\circ}\text{C}$
S21 Temperature Coefficient	$T_{DIFF} = 25\text{ }^{\circ}\text{C}$ to $85\text{ }^{\circ}\text{C}$		-0.10		dB/ $^{\circ}\text{C}$

Notes:

- Test conditions unless otherwise noted: CW, $V_D = 24\text{ V}$, $I_D = 280\text{ mA}$, $V_G = -2.3\text{ V} \pm 0.6\text{ V}$ typical, $T_{BASE} = 25^{\circ}\text{C}$, $Z_0 = 50\text{ }\Omega$
- T_{BASE} is back side of 0.02 in CuMo carrier plate with AuSn die attached







Performance Plots – Large Signal

Test conditions, unless otherwise noted: CW, $V_D = 24$ V, $I_{DQ} = 280$ mA, $P_{IN} = 29$ dBm, $T_{BASE} = +25$ °C (T_{BASE} is backside of 0.02 in CuMo carrier plate)








Performance Plots – Large Signal

Test conditions, unless otherwise noted: CW, $V_D = 24$ V, $I_{DQ} = 280$ mA, $P_{IN} = 29$ dBm, $T_{BASE} = +25$ °C (T_{BASE} is backside of 0.02 in CuMo carrier plate)









Performance Plots – Large Signal

Test conditions, unless otherwise noted: CW, $V_D = 24$ V, $I_{DQ} = 280$ mA, $P_{IN} = 29$ dBm, $T_{BASE} = +25$ °C (T_{BASE} is backside of 0.02 in CuMo carrier plate)









Performance Plots – Large Signal

Test conditions, unless otherwise noted: CW, $V_D = 24$ V, $I_{DQ} = 280$ mA, $P_{IN} = 29$ dBm, $T_{BASE} = +25$ °C (T_{BASE} is backside of 0.02 in CuMo carrier plate)









Performance Plots – Large Signal

Test conditions, unless otherwise noted: CW, $V_D = 24$ V, $I_{DQ} = 280$ mA, $P_{IN} = 29$ dBm, $T_{BASE} = +25$ °C (T_{BASE} is backside of 0.02 in CuMo carrier plate)









Performance Plots – Large Signal

Test conditions, unless otherwise noted: CW, $V_D = 24$ V, $I_{DQ} = 280$ mA, $P_{IN} = 29$ dBm, $T_{BASE} = +25$ °C (T_{BASE} is backside of 0.02 in CuMo carrier plate)









Performance Plots – Large Signal

Test conditions, unless otherwise noted: CW, $V_D = 24$ V, $I_{DQ} = 280$ mA, $P_{IN} = 29$ dBm, $T_{BASE} = +25$ °C (T_{BASE} is backside of 0.02 in CuMo carrier plate)









Performance Plots – Large Signal

Test conditions, unless otherwise noted: CW, $V_D = 24$ V, $I_{DQ} = 280$ mA, $P_{IN} = 29$ dBm, $T_{BASE} = +25$ °C (T_{BASE} is backside of 0.02 in CuMo carrier plate)









Performance Plots – Large Signal

Test conditions, unless otherwise noted: CW, $V_D = 24$ V, $I_{DQ} = 280$ mA, $P_{IN} = 29$ dBm, $T_{BASE} = +25$ °C (T_{BASE} is backside of 0.02 in CuMo carrier plate)









Performance Plots – Large Signal

Test conditions, unless otherwise noted: CW, $V_D = 24$ V, $I_{DQ} = 280$ mA, $P_{IN} = 29$ dBm, $T_{BASE} = +25$ °C (T_{BASE} is backside of 0.02 in CuMo carrier plate)









Performance Plots – Large Signal

Test conditions, unless otherwise noted: CW, $V_D = 24$ V, $I_{DQ} = 280$ mA, $P_{IN} = 29$ dBm, $T_{BASE} = +25$ °C (T_{BASE} is backside of 0.02 in CuMo carrier plate)









Performance Plots – Large Signal

Test conditions, unless otherwise noted: CW, $V_D = 24$ V, $I_{DQ} = 280$ mA, $P_{IN} = 29$ dBm, $T_{BASE} = +25$ °C (T_{BASE} is backside of 0.02 in CuMo carrier plate)









Performance Plots – Linearity

Test conditions, unless otherwise noted: CW, $V_D = 24$ V, $I_{DQ} = 280$ mA, $\Delta f = 100$ MHz, $T_{BASE} = +25$ °C (T_{BASE} is backside of 0.02 in CuMo carrier plate)









Performance Plots – Linearity

Test conditions, unless otherwise noted: CW, $V_D = 24$ V, $I_{DQ} = 280$ mA, $\Delta f = 100$ MHz, $T_{BASE} = +25$ °C (T_{BASE} is backside of 0.02 in CuMo carrier plate)









Performance Plots – Linearity

Test conditions, unless otherwise noted: CW, $V_D = 24$ V, $I_{DQ} = 280$ mA, $\Delta f = 100$ MHz, $T_{BASE} = +25$ °C (T_{BASE} is backside of 0.02 in CuMo carrier plate)





Performance Plots – Linearity

Test conditions, unless otherwise noted: CW, $V_D = 24$ V, $I_{DQ} = 280$ mA, $F_C = 40$ GHz, $T_{BASE} = +25$ °C (T_{BASE} is backside of 0.02 in CuMo carrier plate)









Performance Plots – Linearity

Test conditions, unless otherwise noted: CW, $V_D = 24$ V, $I_{DQ} = 280$ mA, $F_C = 40$ GHz, $T_{BASE} = +25$ °C (T_{BASE} is backside of 0.02 in CuMo carrier plate)





Performance Plots – Linearity

Test conditions, unless otherwise noted: CW, $V_D = 24\text{ V}$, $I_{DQ} = 280\text{ mA}$, $F_C = 40\text{ GHz}$, $T_{BASE} = +25\text{ }^\circ\text{C}$ (T_{BASE} is backside of 0.02 in CuMo carrier plate)




Performance Plots – Linearity

Test conditions, unless otherwise noted: CW, $V_D = 24$ V, $I_{DQ} = 280$ mA, $F_C = 40$ GHz, $T_{BASE} = +25$ °C (T_{BASE} is backside of 0.02 in CuMo carrier plate)




Performance Plots – Small Signal

Test conditions, unless otherwise noted: CW, $V_D = 24$ V, $I_{DQ} = 280$ mA, $P_{IN} = -30$ dBm, $T_{BASE} = +25$ °C (T_{BASE} is backside of 0.02 in CuMo carrier plate)



Performance Plots – Small Signal

Test conditions, unless otherwise noted: CW, $V_D = 24$ V, $I_{DQ} = 280$ mA, $P_{IN} = -30$ dBm, $T_{BASE} = +25$ °C (T_{BASE} is backside of 0.02 in CuMo carrier plate)





Thermal and Reliability Information

Parameter	Test Conditions	Value	Units
Thermal Resistance, θ_{JC} ⁽¹⁾	Quiescent, no RF	1.3	$^{\circ}\text{C}/\text{W}$
Channel Temperature, T_{CH} ⁽²⁾	$T_{BASE} = 85^{\circ}\text{C}$, $V_D = 24\text{ V}$, $I_{DQ} = 280\text{ mA}$, $P_{DISS} = 6.72\text{ W}$	94	$^{\circ}\text{C}$
Thermal Resistance, θ_{JC} ⁽¹⁾	$P_{IN} = 29\text{ dBm}$, $T_{BASE} = 85^{\circ}\text{C}$, CW, $V_D = 24\text{ V}$, $I_{DQ} = 280\text{ mA}$, Freq = 41 GHz, $I_{D_DRIVE} = 2.2\text{ A}$, $P_{OUT} = 38.6\text{ dBm}$, $P_{DISS} = 46.3\text{ W}$	1.41	$^{\circ}\text{C}/\text{W}$
Channel Temperature, T_{CH} ⁽²⁾		150	$^{\circ}\text{C}$
Thermal Resistance, θ_{JC} ⁽¹⁾	$P_{IN} = 31\text{ dBm}$, $T_{BASE} = 85^{\circ}\text{C}$, CW, $V_D = 24\text{ V}$, $I_{DQ} = 280\text{ mA}$, Freq = 41 GHz, $I_{D_DRIVE} = 2.44\text{ A}$, $P_{OUT} = 39.2\text{ dBm}$, $P_{DISS} = 51.4\text{ W}$	1.42	$^{\circ}\text{C}/\text{W}$
Channel Temperature, T_{CH} ⁽²⁾		158	$^{\circ}\text{C}$

Notes:


1. Thermal resistance determined to T_{BASE} (T_{BASE} is backside of 0.02 in carrier plate CuMo with AuSn die attached)
2. Channel temperature indicated is an IR scan equivalent temperature. Thermal resistance is calculated using this value. Additional information can be found in the Qorvo Applications Note "GaN Device TCHMAX Theta-JC and Reliability Estimates," located here <https://www.qorvo.com/products/d/da006480>

Dissipated Power




Test conditions, unless otherwise noted: CW, $V_D = 24\text{ V}$, $I_{DQ} = 280\text{ mA}$, $T_{BASE} = 85^{\circ}\text{C}$
 T_{BASE} is back side of 0.02 in CuMo carrier plate with AuSn die attached

Maximum Gate Current




Channel Temperature is an IR scan equivalent

Applications Information




DC must be applied to both sides, top and bottom, of the die
External bypassing required on both sides


Evaluation Board (EVB) Layout



DETAIL B



DETAIL C



Bill of Materials

Reference Des.	Qty	Value	Description	Part Number
C1, C3, C5, C6, C8, C9, C10, C12, C14, C15	10	0.01 uF	CAP, 0.01uF, ±10%, 50V, X7R, 0402	
C2, C4, C7, C11, C13, C16, C27 – C30	10	10 uF	CAP, 10uF, 20%, 50V, 20%, X5R, 1206	
C17 – C26	10	10 nF	CAP, 10nF, ±15%, 30V, SLC, 0303	
R1, R5 – R9, R12, R14 – R16	10	0 Ω	RES, 0 Ohm, JMPR, 0402	
R2 – R4, R10, R11, R13	6	0 Ω	RES, 0 Ohm, JMPR, 0603	
R17 – R20	4	5.1 Ω	RES, 5.1 Ohm, ±1%, 1/10W, 0402	
PCB_MMIC	1		PCB for MMIC, Taconics TSM-S3B 0.005", 0.5oz Ni/Pd/Au plating both sides, total thickness 0.009"	Qorvo, Custom
PCB,_Bias	2		PCB for DC Bias	Qorvo, Custom
H1, H2	2		CONN, HDR, Male-vert, 7 PIN, 1 RAW, MTA	TE Connectivity 640456-7 *7 PINS*
J1, J2	2		Connector, RF 2.4mm, F, Pin 0.005, Diel 0.0295	Southwest Microwave 1092-04A-12
CP	1		Carrier Plate, CuMo, 0.9 x 1.15 x 0.02T in	Qorvo, Custom
H-Block	1		H-Block, Copper C110, 1.14 x 2.49 x 0.59T in	Qorvo, Custom
S1 – S4	12		Screw, Cap, Socket Head, 2-56X1/8"	
AuSn			AuSn Solder preform	
Epoxy			Epoxy preform	
Ablebond			Epoxy, Ablebond 84-1LMI	
Solder			Paste, solder, Syntech, Sn63/Pb37	
TC			Thermal Compound, Silver 5GR	Artic Silver 5 AS5-5G

Bias-Up Procedure


1. Set I_D limit to 4.5 A, I_G limit to 20 mA
2. Set V_G to -3.5 V
3. Set V_D +24 V. Ensure $I_{DQ} \sim 0$ mA
4. Adjust V_G more positive until $I_D = 280$ mA;
 $V_G \approx -2.3$ V +/- 0.6V typical range
5. Apply RF signal

Bias-Down Procedure

1. Turn off RF signal
2. Reduce V_G to -3.5 V. Ensure $I_{DQ} \sim 0$ mA
3. Set V_D to 0 V
4. Turn off V_D supply
5. Turn off V_G supply

Combined $V_D = V_{D1} + V_{D2} + V_{D3}$, $V_G = V_{G12} + V_{G3}$
DC must be applied to both sides, top and bottom, of the die

Mechanical Information



Dimensions: mm; Thickness: 0.05 mm; Die x, y size tolerance: ± 0.050 ; Ground is backside of die

Bond Pad Description

Pad No.	Symbol	Pad Size (mm)	Description
1	RF _{IN}	0.13 x 0.16	RF Input. Matched to 50 Ω , DC blocked, DC shorted to ground
2, 12	V _{G12}	0.09 x 0.09	Gate voltage for stage 1 and 2 ⁽¹⁾
3, 11	V _{D1}	0.20 x 0.09	Drain voltage for stage 1 ⁽¹⁾
4, 10	V _{D2}	0.20 x 0.09	Drain voltage for stage 2 ⁽¹⁾
5, 9	V _{G3}	0.09 x 0.09	Gate voltage for stage 3 ⁽¹⁾
6, 8	V _{D3}	0.30 x 0.20	Drain voltage for stage 3 ⁽¹⁾
7	RF _{OUT}	0.13 x 0.16	RF Output. Matched to 50 Ω , DC blocked, DC shorted to ground

1. External bypassing required; refer to page 26 for recommendation

Assembly Notes

Component placement and adhesive attachment assembly notes:

- Vacuum pencils and/or vacuum collets are the preferred method of pick up.
- Air bridges must be avoided during placement.
- The force impact is critical during auto placement.

Reflow process assembly notes:

- Use AuSn (80/20) solder and limit exposure to temperatures above 300 °C to 3 – 4 minutes, maximum.
- An alloy station or conveyor furnace with reducing atmosphere should be used.
- Do not use any kind of flux.
- Coefficient of thermal expansion matching is critical for long-term reliability.
- Devices must be stored in a dry nitrogen atmosphere.

Interconnect process assembly notes:

- Thermosonic ball bonding is the preferred interconnect technique.
- Force, time, and ultrasonic are critical parameters.
- Aluminum wire should not be used.
- Devices with small pad sizes should be bonded with 0.0007-inch wire.

Handling Precautions

Parameter	Rating	Standard
ESD – Human Body Model (HBM)	2	ANSI/ESD/JEDEC JS-001


Caution!
ESD-Sensitive Device

Solderability

Use only AuSn (80/20) solder, and limit exposure to temperatures above 300 °C to 3–4 minutes, maximum.

RoHS Compliance

This part is compliant with 2011/65/EU RoHS directive (Restrictions on the Use of Certain Hazardous Substances in Electrical and Electronic Equipment) as amended by Directive 2015/863/EU.

This product also has the following attributes:

- Lead Free
- Halogen Free (Chlorine, Bromine)
- Antimony Free
- TBBP-A (C₁₅H₁₂Br₄O₂) Free
- SVHC Free
- PFOS Free

Contact Information

For the latest specifications, additional product information, worldwide sales and distribution locations:

Web: www.qorvo.com

Tel: 1-844-890-8163

Email: customer.support@qorvo.com

Important Notice

The information contained herein is believed to be reliable; however, Qorvo makes no warranties regarding the information contained herein and assumes no responsibility or liability whatsoever for the use of the information contained herein. All information contained herein is subject to change without notice. Customers should obtain and verify the latest relevant information before placing orders for Qorvo products. The information contained herein or any use of such information does not grant, explicitly or implicitly, to any party any patent rights, licenses, or any other intellectual property rights, whether with regard to such information itself or anything described by such information. **THIS INFORMATION DOES NOT CONSTITUTE A WARRANTY WITH RESPECT TO THE PRODUCTS DESCRIBED HEREIN, AND QORVO HEREBY DISCLAIMS ANY AND ALL WARRANTIES WITH RESPECT TO SUCH PRODUCTS WHETHER EXPRESS OR IMPLIED BY LAW, COURSE OF DEALING, COURSE OF PERFORMANCE, USAGE OF TRADE OR OTHERWISE, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.**

Without limiting the generality of the foregoing, Qorvo products are not warranted or authorized for use as critical components in medical, life-saving, or life-sustaining applications, or other applications where a failure would reasonably be expected to cause severe personal injury or death.

© 2022 Qorvo US, Inc. All rights reserved. This document is subject to copyright laws in various jurisdictions worldwide and may not be reproduced or distributed, in whole or in part, without the express written consent of Qorvo US, Inc.